

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902221

Luminaire Tested: DFN2DIP-4P3F0-040D030US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902221
REPORT IS A COMBINATION OF REPORTS P900564 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D030US830-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6004.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1776	1776	1776
5°	1777	1746	1758
10°	1759	1711	1700
15°	1733	1653	1611
20°	1700	1574	1502
25°	1666	1486	1397
30°	1621	1395	1264
35°	1577	1298	1147
40°	1532	1198	1013
45°	1479	1086	891
50°	1425	974	773
55°	1368	854	659
60°	1302	729	542
65°	1226	602	487
70°	1134	484	440
75°	1018	424	399
80°	851	352	344
85°	578	230	255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1479 cd/sqm

TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	2.4
10°-20°	400.9	6.7
20°-30°	562.8	9.4
30°-40°	613.5	10.2
40°-50°	563.9	9.4
50°-60°	442.9	7.4
60°-70°	288.3	4.8
70°-80°	148.4	2.5
80°-90°	39.6	0.7
90°-100°	31.5	0.5
100°-110°	117.3	2.0
110°-120°	311.1	5.2
120°-130°	516.0	8.6
130°-140°	548.1	9.1
140°-150°	509.4	8.5
150°-160°	409.6	6.8
160°-170°	263.9	4.4
170°-180°	90.8	1.5
0°-30°	1109.8	18.5
0°-40°	1723.3	28.7
0°-60°	2730.1	45.5
0°-90°	3206.3	53.4
90°-120°	459.9	7.7
90°-150°	2033.4	33.9
90°-180°	2798.0	46.6
0°-180°	6004.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	1	8	14	17	19	6
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6



TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P902221

CATALOG NUMBER: DFN2DIP-4P3F0-040D030US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.42	10.28	10.36	11.23	12.45	5.38	6.24	6.32	7.19	8.41
	3H	11.10	11.86	12.04	12.82	14.07	6.57	7.33	7.51	8.29	9.54
	4H	11.70	12.43	12.66	13.39	14.65	7.01	7.74	7.97	8.70	9.96
	6H	12.12	12.79	13.09	13.76	15.03	7.33	8.00	8.30	8.96	10.23
	8H	12.25	12.88	13.23	13.87	15.13	7.42	8.05	8.40	9.04	10.30
	12H	12.31	12.91	13.29	13.89	15.18	7.46	8.06	8.44	9.04	10.33
4H	2H	9.44	10.17	10.41	11.13	12.38	5.98	6.70	6.94	7.66	8.92
	3H	11.27	11.87	12.24	12.86	14.13	7.32	7.93	8.30	8.92	10.19
	4H	11.96	12.51	12.94	13.49	14.79	7.87	8.42	8.85	9.40	10.70
	6H	12.47	12.94	13.47	13.95	15.24	8.28	8.75	9.28	9.76	11.06
	8H	12.64	13.08	13.64	14.09	15.39	8.41	8.85	9.40	9.85	11.16
	12H	12.74	13.13	13.75	14.15	15.46	8.47	8.87	9.48	9.88	11.20
8H	4H	11.93	12.37	12.92	13.37	14.68	8.15	8.59	9.14	9.59	10.90
	6H	12.49	12.85	13.51	13.89	15.20	8.66	9.02	9.68	10.07	11.37
	8H	12.70	13.02	13.73	14.05	15.38	8.84	9.16	9.87	10.19	11.52
	12H	12.84	13.12	13.87	14.14	15.51	8.96	9.24	9.99	10.26	11.63
12H	4H	11.88	12.28	12.89	13.29	14.61	8.15	8.55	9.17	9.57	10.88
	6H	12.46	12.78	13.49	13.81	15.14	8.71	9.03	9.74	10.06	11.38
	8H	12.68	12.96	13.71	13.99	15.36	8.91	9.19	9.94	10.22	11.59