

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902222

Luminaire Tested: DFN2DIP-4P3F0-040D040US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902222
REPORT IS A COMBINATION OF REPORTS P899053 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D040US830-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7069.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1672	1672	1672
5°	1673	1647	1659
10°	1659	1624	1636
15°	1633	1596	1600
20°	1599	1558	1564
25°	1565	1513	1522
30°	1523	1470	1469
35°	1483	1420	1412
40°	1434	1370	1358
45°	1385	1319	1303
50°	1331	1266	1240
55°	1275	1205	1181
60°	1211	1132	1114
65°	1142	1056	1035
70°	1053	964	949
75°	931	853	870
80°	782	712	719
85°	551	471	471

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1385 cd/sqm

TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	2.0
10°-20°	388.5	5.5
20°-30°	570.9	8.1
30°-40°	663.1	9.4
40°-50°	662.3	9.4
50°-60°	577.5	8.2
60°-70°	426.9	6.0
70°-80°	241.5	3.4
80°-90°	67.1	0.9
90°-100°	73.8	1.0
100°-110°	234.4	3.3
110°-120°	401.2	5.7
120°-130°	527.6	7.5
130°-140°	592.2	8.4
140°-150°	580.8	8.2
150°-160°	487.2	6.9
160°-170°	323.1	4.6
170°-180°	112.9	1.6
0°-30°	1097.5	15.5
0°-40°	1760.6	24.9
0°-60°	3000.3	42.4
0°-90°	3735.9	52.8
90°-120°	709.4	10.0
90°-150°	2410.0	34.1
90°-180°	3333.0	47.1
0°-180°	7069.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	1	13	35	33	34	7
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	403	408	406	406	403	398
125°	586	595	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	1.0	12.9	35.3	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.2	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9

TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.6	408.4	406.5	405.5	402.6
117.5°	449.7	457.6	452.6	449.7	446.9
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.3	550.4	545.4	542.4	540.3
125°	585.6	594.6	591.7	588.4	587.4
127.5°	629.8	640.9	637.0	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.2
132.5°	717.5	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.8
137.5°	802.0	811.0	812.8	812.0	807.8
140°	841.1	850.2	855.2	855.2	851.2
142.5°	881.5	890.4	893.2	894.4	890.4
145°	919.5	926.7	932.5	933.6	929.6
147.5°	953.7	962.6	967.0	968.7	964.8
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.3	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.5	1080.5	1082.3	1089.6	1084.5
160°	1102.5	1104.7	1105.7	1111.8	1107.5
162.5°	1124.7	1124.7	1125.9	1132.7	1127.7
165°	1143.9	1142.7	1142.7	1149.9	1144.9
167.5°	1161.1	1157.8	1157.8	1165.1	1160.0
170°	1174.0	1171.1	1170.1	1177.2	1171.1
172.5°	1183.0	1180.2	1179.0	1186.3	1180.2
175°	1190.2	1187.3	1185.2	1192.3	1186.3
177.5°	1194.2	1191.3	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P902222

CATALOG NUMBER: DFN2DIP-4P3F0-040D040US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.28	10.17	10.21	11.12	12.35	8.84	9.73	9.77	10.68	11.91
	3H	10.94	11.74	11.88	12.70	13.95	10.45	11.25	11.39	12.20	13.46
	4H	11.53	12.28	12.48	13.24	14.50	11.03	11.79	11.99	12.75	14.01
	6H	11.92	12.62	12.89	13.59	14.86	11.42	12.12	12.39	13.09	14.36
	8H	12.03	12.69	13.00	13.67	14.95	11.53	12.19	12.50	13.17	14.45
	12H	12.08	12.70	13.06	13.68	14.98	11.57	12.20	12.55	13.17	14.47
4H	2H	9.74	10.50	10.71	11.46	12.72	9.39	10.14	10.35	11.10	12.37
	3H	11.61	12.23	12.58	13.23	14.50	11.20	11.83	12.17	12.82	14.10
	4H	12.32	12.89	13.30	13.88	15.18	11.89	12.47	12.88	13.45	14.76
	6H	12.83	13.32	13.82	14.34	15.63	12.40	12.89	13.39	13.90	15.20
	8H	12.98	13.44	13.97	14.44	15.76	12.54	13.00	13.54	14.01	15.32
	12H	13.05	13.47	14.07	14.49	15.81	12.60	13.02	13.62	14.04	15.36
8H	4H	12.51	12.97	13.51	13.98	15.29	12.13	12.60	13.13	13.60	14.91
	6H	13.14	13.52	14.16	14.57	15.88	12.75	13.14	13.78	14.18	15.49
	8H	13.36	13.69	14.39	14.73	16.06	12.96	13.30	13.99	14.33	15.66
	12H	13.49	13.78	14.52	14.81	16.18	13.07	13.37	14.11	14.40	15.77
12H	4H	12.50	12.92	13.51	13.94	15.25	12.13	12.55	13.14	13.57	14.89
	6H	13.17	13.50	14.20	14.54	15.87	12.79	13.13	13.82	14.16	15.49
	8H	13.41	13.70	14.44	14.73	16.10	13.03	13.32	14.06	14.35	15.72

END OF REPORT