

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333005-935

Luminaire Tested: **SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333005-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7497.2 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333005-935  
CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	63	57	55	54	50
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	55	49	45	47	43	40	41	38	35	32
5	71	59	51	45	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	48	41	35	56	46	39	33	40	35	30	35	31	27	31	27	24	22
8	56	44	36	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13774	13774	13774	13774
5°	15977	13816	12211	13816
10°	18901	13755	10899	13755
15°	21833	13628	9365	13628
20°	24308	13454	8469	13454
25°	25093	13281	7863	13281
30°	21967	13073	7498	13073
35°	17100	12764	7276	12764
40°	12823	12410	7158	12410
45°	10123	11843	7096	11843
50°	8547	11189	6889	11189
55°	7450	10469	6521	10469
60°	6704	9723	5772	9723
65°	5910	8915	4963	8915
70°	5323	8080	4480	8080
75°	4460	7162	3815	7162
80°	3770	6104	3580	6104
85°	3186	4780	3186	4780



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	165.3	2.2
10°-20°	498.7	6.7
20°-30°	780.0	10.4
30°-40°	867.1	11.6
40°-50°	769.3	10.3
50°-60°	599.5	8.0
60°-70°	392.5	5.2
70°-80°	193.0	2.6
80°-90°	50.0	0.7
90°-100°	316.0	4.2
100°-110°	657.7	8.8
110°-120°	589.1	7.9
120°-130°	495.5	6.6
130°-140°	413.2	5.5
140°-150°	315.7	4.2
150°-160°	221.9	3.0
160°-170°	130.5	1.7
170°-180°	42.5	0.6
0°-30°	1444.0	19.3
0°-40°	2311.0	30.8
0°-60°	3679.8	49.1
0°-90°	4315.3	57.6
90°-120°	1562.8	20.8
90°-150°	2787.1	37.2
90°-180°	3182.0	42.4
0°-180°	7497.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1706	1706	1706	1706	1706	
5°	1972	1705	1507	1705	1972	199
15°	2612	1631	1120	1631	2612	743
25°	2817	1491	883	1491	2817	1250
35°	1735	1295	738	1295	1735	1088
45°	887	1037	622	1037	887	702
55°	529	744	463	744	529	481
65°	309	467	260	467	309	311
75°	143	230	122	230	143	157
85°	34	52	34	52	34	39
90°	18	1	18	1	18	16
95°	210	28	210	28	210	325
105°	1209	101	1209	101	1209	1196
115°	1161	177	1161	177	1161	1153
125°	927	247	927	247	927	842
135°	829	293	829	293	829	640
145°	676	338	676	338	676	429
155°	566	384	566	384	566	264
165°	494	419	494	419	494	142
175°	445	437	445	437	445	43
180°	438	438	438	438	438	



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1799.7	1804.7	1799.7	1799.1	1793.6	1792.0	1789.8	1782.6	1769.4	1761.8	1763.4
5°	1971.5	1988.7	1979.1	1977.7	1962.6	1947.5	1937.9	1915.9	1892.5	1876.7	1863.6
7.5°	2170.3	2180.2	2174.2	2164.6	2140.1	2126.2	2103.9	2074.9	2033.0	2001.0	1971.7
10°	2305.7	2313.9	2311.2	2293.3	2275.4	2238.9	2218.4	2177.8	2124.9	2082.9	2043.8
12.5°	2438.7	2447.6	2423.4	2424.1	2390.3	2361.6	2328.9	2277.9	2216.7	2162.7	2113.6
15°	2612.3	2601.3	2601.3	2587.5	2549.7	2509.8	2476.1	2422.5	2345.5	2280.9	2212.9
17.5°	2748.1	2751.9	2746.2	2713.9	2684.2	2642.9	2581.2	2518.6	2447.1	2360.3	2290.8
20°	2829.5	2829.5	2823.3	2801.3	2762.8	2718.8	2652.1	2584.0	2493.3	2406.0	2327.6
22.5°	2862.5	2864.6	2857.4	2839.2	2804.6	2761.7	2704.9	2635.8	2542.3	2443.9	2346.9
25°	2817.1	2830.2	2831.5	2826.7	2816.4	2790.2	2741.5	2670.6	2586.8	2480.3	2375.8
27.5°	2586.4	2602.9	2617.4	2641.1	2672.7	2689.2	2691.4	2655.4	2582.2	2479.7	2374.6
30°	2356.5	2370.2	2414.9	2473.4	2518.8	2560.0	2595.7	2605.4	2564.1	2472.0	2361.3
32.5°	2101.4	2120.0	2164.7	2227.6	2303.2	2373.0	2453.3	2494.2	2493.2	2437.9	2335.5
35°	1735.1	1748.9	1790.1	1856.1	1946.8	2050.6	2177.8	2276.7	2344.2	2339.3	2276.7
37.5°	1399.3	1414.9	1456.6	1511.2	1599.2	1727.8	1850.8	1987.2	2111.8	2181.8	2160.9
40°	1216.8	1217.5	1258.0	1314.4	1396.9	1508.9	1643.0	1794.2	1933.0	2046.5	2068.5
42.5°	1072.6	1072.8	1099.6	1160.4	1219.8	1325.3	1453.2	1603.4	1765.9	1896.9	1955.2
45°	886.7	892.9	915.0	951.4	998.2	1087.5	1189.9	1329.5	1511.7	1667.0	1763.9
47.5°	751.0	760.0	774.0	803.7	841.0	900.5	985.2	1110.6	1258.8	1429.7	1567.6
50°	680.5	681.9	699.8	716.3	748.6	796.1	870.3	974.7	1110.9	1275.1	1428.5
52.5°	620.1	619.7	630.5	651.4	677.7	714.6	774.6	869.7	990.4	1137.7	1296.0
55°	529.3	532.8	541.0	557.5	577.5	603.6	651.0	722.5	817.3	943.1	1086.8
57.5°	460.3	462.1	468.6	475.5	493.9	512.8	548.5	598.1	678.1	781.1	915.0
60°	415.2	415.9	417.9	428.3	442.7	460.5	484.7	526.6	593.9	688.1	794.0
62.5°	371.2	372.5	375.7	383.1	394.3	406.7	431.9	465.5	521.3	601.8	697.2
65°	309.4	310.0	314.9	317.6	326.5	337.5	356.1	378.8	417.2	484.7	556.8
67.5°	258.5	258.5	258.7	262.4	268.6	276.0	287.1	305.2	334.2	375.7	439.3
70°	225.5	225.5	226.9	228.9	232.4	238.5	244.7	258.5	279.8	313.5	362.3
72.5°	194.7	195.2	196.6	197.0	198.8	203.9	208.4	217.2	233.1	258.5	297.9
75°	143.0	145.1	148.5	151.3	154.6	153.9	158.8	164.3	169.1	184.3	206.9
77.5°	106.4	105.3	105.7	108.1	108.5	109.2	112.6	116.8	120.5	127.6	135.7
80°	81.1	81.1	83.2	83.9	83.2	83.9	87.3	89.4	90.7	93.5	101.1
82.5°	61.3	62.4	61.7	62.4	62.9	63.5	66.4	66.8	68.2	69.3	72.5
85°	34.4	35.0	35.7	34.4	34.4	34.4	35.7	36.4	37.8	37.1	38.5
87.5°	15.7	15.2	15.8	15.7	16.1	15.5	15.9	16.9	15.6	16.3	15.9
90°	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5	14.6	15.5	13.8
92.5°	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8	227.1	272.7	238.6
95°	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9	720.3	700.5	528.7
97.5°	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1	904.9	737.8	494.7
100°	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6	911.1	691.0	448.7
102.5°	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8	859.5	632.7	417.8
105°	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7	765.9	563.9	391.1
107.5°	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5	690.2	525.4	386.2
110°	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4	652.4	512.3	387.6



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1	631.1	506.1	391.8
115°	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6	611.1	502.8	399.7
117.5°	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2	602.2	502.0	408.1
120°	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6	597.4	502.0	414.3
122.5°	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4	591.9	501.3	420.5
125°	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3	582.8	500.2	429.8
127.5°	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1	570.6	498.3	437.1
130°	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4	563.0	497.7	442.6
132.5°	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9	556.1	497.0	447.5
135°	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9	545.8	495.9	454.7
137.5°	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9	536.8	495.8	459.0
140°	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6	532.1	495.1	462.4
142.5°	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0	528.0	495.1	465.2
145°	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4	520.9	493.4	466.7
147.5°	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2	514.5	490.3	467.6
150°	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4	509.7	488.2	467.6
152.5°	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8	504.2	484.7	466.2
155°	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4	495.9	479.7	464.2
157.5°	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2	487.5	474.3	461.9
160°	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6	481.4	470.2	459.9
162.5°	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1	475.9	466.1	457.8
165°	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6	466.7	459.9	453.8
167.5°	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5	458.5	453.7	449.7
170°	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3	453.0	449.5	446.9
172.5°	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8	448.2	445.4	444.2
175°	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4	442.6	440.9	440.9
177.5°	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5	438.9	438.2	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1757.9	1750.2	1746.4	1737.6	1727.1	1721.6	1716.7	1709.5	1700.1	1690.2	1683.1
5°	1847.1	1830.7	1810.0	1785.3	1763.2	1742.0	1723.4	1704.9	1683.5	1661.6	1639.5
7.5°	1938.7	1906.3	1871.2	1830.7	1791.1	1755.3	1722.3	1690.7	1654.9	1622.9	1593.7
10°	2002.5	1958.5	1909.7	1858.1	1806.6	1761.9	1717.9	1678.0	1634.0	1594.8	1561.9
12.5°	2054.2	2002.5	1943.8	1879.6	1817.6	1763.5	1713.0	1661.0	1610.9	1568.5	1524.5
15°	2139.9	2069.2	1990.1	1913.1	1832.7	1759.1	1691.1	1630.6	1573.6	1513.7	1471.8
17.5°	2199.0	2115.0	2018.9	1926.3	1831.3	1744.6	1666.0	1594.1	1528.2	1467.1	1417.2
20°	2234.1	2141.3	2034.8	1929.6	1823.1	1730.3	1645.7	1566.0	1497.9	1431.9	1380.4
22.5°	2253.9	2151.2	2034.8	1924.7	1814.3	1713.7	1620.9	1537.9	1463.8	1397.8	1340.7
25°	2260.3	2150.3	2031.4	1904.9	1783.9	1677.3	1581.1	1491.0	1408.5	1342.6	1282.0
27.5°	2251.5	2121.9	2000.2	1870.4	1745.5	1633.2	1532.1	1437.5	1355.0	1284.1	1222.1
30°	2238.3	2099.4	1968.8	1834.1	1707.5	1599.7	1493.1	1402.4	1316.5	1242.9	1180.3
32.5°	2209.7	2071.9	1931.4	1793.4	1665.3	1554.0	1452.9	1361.7	1277.4	1202.2	1135.7
35°	2153.0	2013.4	1860.9	1719.2	1593.5	1478.0	1383.1	1295.1	1214.7	1134.3	1064.1
37.5°	2078.4	1935.8	1784.0	1628.9	1503.0	1394.0	1306.9	1224.3	1145.8	1072.4	994.7
40°	2008.0	1878.1	1721.3	1567.4	1438.1	1332.9	1252.5	1177.6	1098.5	1025.6	948.0
42.5°	1922.8	1812.1	1653.7	1499.2	1371.6	1270.2	1195.3	1122.1	1050.2	979.5	898.5
45°	1780.5	1696.6	1548.1	1399.6	1271.1	1170.7	1102.0	1037.3	974.0	906.7	830.4
47.5°	1617.4	1560.6	1432.4	1280.4	1161.5	1071.2	1004.8	951.9	898.5	831.1	764.1
50°	1504.1	1467.7	1343.9	1205.1	1091.7	1008.5	940.4	890.9	846.2	781.6	721.8
52.5°	1383.1	1363.7	1259.2	1126.4	1016.8	935.3	877.2	832.6	787.4	733.7	677.8
55°	1198.9	1209.2	1120.5	1005.7	902.6	833.9	780.9	743.8	705.3	660.0	616.6
57.5°	1010.6	1048.2	988.7	887.9	791.3	727.7	687.9	656.6	624.3	586.7	549.7
60°	897.8	929.4	895.7	807.0	722.5	663.4	626.3	602.2	569.9	535.5	507.3
62.5°	787.8	821.7	801.7	730.0	651.5	600.7	567.9	545.5	521.5	491.5	462.3
65°	649.6	671.6	662.0	612.5	556.8	513.5	483.3	466.7	444.8	422.8	396.7
67.5°	497.6	540.0	534.4	508.2	460.0	426.2	406.4	391.8	371.8	355.4	337.7
70°	409.1	448.2	447.5	426.2	400.1	368.4	354.7	342.3	324.4	308.7	294.2
72.5°	334.8	370.7	376.0	359.6	341.8	317.9	304.7	296.2	278.8	267.9	256.2
75°	234.5	260.5	267.4	267.4	259.2	246.8	235.1	229.6	217.2	207.6	200.7
77.5°	153.7	170.2	180.9	183.4	184.7	180.6	170.9	167.0	157.6	154.1	147.5
80°	108.6	119.6	132.0	136.1	139.6	138.2	134.1	131.3	122.3	118.9	116.1
82.5°	75.1	81.1	91.3	100.4	99.4	103.0	99.4	97.2	90.5	89.2	86.4
85°	39.2	39.9	41.2	47.4	50.9	52.3	53.0	51.6	49.5	49.5	44.7
87.5°	15.6	15.1	15.2	15.2	15.5	17.6	18.7	18.9	17.6	16.4	15.0
90°	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9	2.6	5.2	6.0
92.5°	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8	14.3	22.4	32.8
95°	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3	30.9	39.5	50.7
97.5°	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9	50.9	58.3	68.6
100°	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3	65.3	71.4	81.6
102.5°	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0	80.4	85.8	95.4
105°	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6	103.1	107.5	117.8
107.5°	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3	126.1	130.3	141.3
110°	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1	141.8	146.1	156.4





TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2	157.0	162.0	171.6
115°	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1	179.6	185.6	194.2
117.5°	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8	202.2	207.5	217.0
120°	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9	216.6	222.7	232.0
122.5°	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7	230.3	236.3	245.1
125°	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7	250.1	255.3	264.8
127.5°	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7	265.4	271.6	282.4
130°	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6	275.1	281.9	294.8
132.5°	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5	283.3	292.2	304.4
135°	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1	296.5	305.1	319.8
137.5°	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7	308.9	318.4	332.3
140°	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6	317.2	326.7	341.2
142.5°	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3	326.8	335.5	349.5
145°	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8	340.4	349.0	361.0
147.5°	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1	354.0	361.5	373.9
150°	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7	363.6	370.5	380.8
152.5°	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7	371.9	378.8	388.3
155°	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2	385.0	390.2	398.8
157.5°	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4	396.4	401.2	407.9
160°	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0	404.0	407.4	413.5
162.5°	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9	410.2	412.9	418.3
165°	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6	418.6	420.3	424.6
167.5°	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4	425.5	426.4	429.6
170°	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8	429.0	429.8	432.4
172.5°	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2	432.4	432.5	434.4
175°	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6	435.8	435.8	436.6
177.5°	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2	437.5	436.8	437.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1675.4	1669.9	1662.8	1654.5	1644.6	1635.8	1631.9	1635.3	1636.9	1632.5	1631.9
5°	1624.4	1607.2	1593.5	1572.9	1556.3	1542.6	1533.0	1528.9	1530.3	1519.2	1516.5
7.5°	1567.1	1546.7	1524.1	1499.7	1476.9	1456.6	1446.0	1440.3	1428.7	1423.7	1415.3
10°	1530.3	1502.7	1480.7	1451.8	1425.7	1401.7	1390.0	1380.4	1368.6	1363.1	1351.5
12.5°	1492.3	1460.3	1436.1	1406.2	1379.5	1350.6	1339.4	1321.5	1303.2	1291.7	1276.7
15°	1438.8	1400.3	1370.7	1335.0	1303.4	1270.4	1240.8	1207.8	1195.4	1169.3	1154.2
17.5°	1376.2	1337.2	1300.6	1252.7	1203.9	1162.9	1131.4	1099.8	1080.8	1064.1	1056.4
20°	1335.0	1299.2	1248.4	1192.7	1138.4	1093.0	1067.6	1047.0	1026.3	1014.7	1006.4
22.5°	1296.0	1250.3	1191.2	1131.1	1076.8	1041.3	1019.8	998.6	981.8	970.7	959.7
25°	1230.5	1170.7	1108.1	1039.4	1002.3	971.4	948.0	930.7	920.5	906.0	900.5
27.5°	1163.3	1090.8	1021.8	975.6	936.9	908.6	888.3	875.4	862.3	853.1	845.9
30°	1111.6	1038.0	976.1	932.1	892.9	869.6	853.1	838.0	827.7	820.1	814.6
32.5°	1060.4	986.9	934.9	887.6	856.7	833.9	816.2	804.9	796.9	787.1	783.8
35°	986.4	921.2	875.8	833.2	801.5	780.9	767.2	755.5	748.6	745.9	743.8
37.5°	915.4	861.9	813.1	778.2	750.0	733.7	717.6	711.8	707.1	702.1	704.4
40°	870.3	820.1	776.8	739.7	717.0	699.1	689.5	682.6	678.5	678.5	678.5
42.5°	831.2	782.1	739.9	706.7	684.0	668.9	658.1	652.4	651.0	650.5	653.8
45°	770.6	725.2	682.6	655.1	635.8	620.8	614.6	609.8	609.8	612.5	613.2
47.5°	710.5	668.0	633.8	603.0	585.4	575.9	570.6	568.1	568.3	571.1	574.3
50°	673.6	631.7	598.1	570.6	554.1	545.1	540.3	539.0	540.3	540.3	545.1
52.5°	633.5	596.0	562.8	539.8	521.1	512.7	510.1	508.2	508.9	511.2	513.2
55°	574.7	541.0	509.4	487.4	473.6	468.1	461.9	462.6	461.2	462.6	462.6
57.5°	515.7	485.4	456.1	438.6	426.5	418.5	411.7	413.7	411.6	411.4	410.3
60°	477.8	444.8	421.4	405.6	391.8	385.0	378.8	380.1	378.1	376.7	373.9
62.5°	436.5	409.1	386.8	371.5	360.5	352.5	346.3	344.9	340.2	335.4	329.4
65°	376.7	354.0	334.1	319.7	309.4	303.2	298.3	294.2	283.9	272.9	267.4
67.5°	318.6	302.2	283.6	271.4	263.0	254.9	245.7	238.7	229.0	223.0	219.6
70°	281.1	265.4	249.5	237.8	228.9	221.4	211.0	206.2	199.3	196.6	193.2
72.5°	245.4	230.7	216.0	205.4	195.9	190.0	181.9	177.1	174.1	173.0	169.5
75°	191.1	179.4	168.4	158.8	151.3	147.1	143.7	140.3	138.9	132.7	129.2
77.5°	139.4	131.7	124.8	118.0	112.6	109.9	103.2	99.3	96.9	94.0	93.3
80°	108.6	103.1	96.3	92.1	84.6	81.8	79.0	78.4	77.7	77.0	76.3
82.5°	81.7	76.2	69.3	66.8	64.7	63.1	61.5	60.8	60.1	60.5	60.4
85°	41.2	38.5	38.5	37.8	37.1	36.4	35.7	35.7	35.0	35.7	35.0
87.5°	15.2	14.6	15.6	14.5	15.4	15.8	15.0	15.2	15.9	15.0	15.0
90°	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5	16.4	17.2	17.2
92.5°	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8	127.1	101.1	83.9
95°	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9	503.7	388.5	305.1
97.5°	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1	891.5	807.4	717.7
100°	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6	1053.8	1011.7	948.0
102.5°	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8	1117.1	1129.3	1102.8
105°	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7	1111.4	1196.4	1231.7
107.5°	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5	1022.9	1142.7	1219.3
110°	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4	954.1	1078.7	1173.3



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1	893.5	1011.3	1105.9
115°	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6	824.3	924.9	1007.4
117.5°	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2	784.8	863.8	933.8
120°	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6	767.6	836.4	897.3
122.5°	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4	756.6	819.2	872.6
125°	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3	739.2	798.5	845.8
127.5°	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1	718.8	777.9	822.8
130°	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4	702.2	760.7	806.2
132.5°	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9	683.7	740.7	786.4
135°	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9	655.8	708.3	751.2
137.5°	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9	629.2	673.4	712.2
140°	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6	612.0	650.7	686.7
142.5°	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0	597.5	630.8	662.0
145°	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4	577.6	603.4	627.5
147.5°	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2	560.4	581.1	599.9
150°	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4	550.1	567.3	582.8
152.5°	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8	539.8	555.6	568.3
155°	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4	525.2	538.0	548.4
157.5°	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2	510.7	521.6	529.9
160°	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6	501.1	510.6	517.5
162.5°	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1	492.1	499.6	505.8
165°	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6	478.8	484.7	489.0
167.5°	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5	467.4	472.3	474.8
170°	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3	459.9	463.3	465.9
172.5°	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8	453.7	455.7	457.6
175°	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4	445.2	446.9	446.9
177.5°	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5	440.2	440.2	440.9
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1628.7	1629.8	1625.9	1624.8	1625.9	1629.8	1628.7	1631.9	1632.5	1636.9	1635.3
5°	1511.0	1509.6	1506.1	1506.8	1506.1	1509.6	1511.0	1516.5	1519.2	1530.3	1528.9
7.5°	1410.3	1405.0	1406.4	1401.0	1406.4	1405.0	1410.3	1415.3	1423.7	1428.7	1440.3
10°	1348.8	1341.2	1335.0	1329.5	1335.0	1341.2	1348.8	1351.5	1363.1	1368.6	1380.4
12.5°	1264.6	1258.1	1249.7	1251.4	1249.7	1258.1	1264.6	1276.7	1291.7	1303.2	1321.5
15°	1145.2	1135.0	1118.4	1120.5	1118.4	1135.0	1145.2	1154.2	1169.3	1195.4	1207.8
17.5°	1044.2	1044.3	1036.8	1038.5	1036.8	1044.3	1044.2	1056.4	1064.1	1080.8	1099.8
20°	992.0	987.1	987.8	985.8	987.8	987.1	992.0	1006.4	1014.7	1026.3	1047.0
22.5°	955.6	949.8	944.9	940.6	944.9	949.8	955.6	959.7	970.7	981.8	998.6
25°	894.3	890.2	884.1	882.7	884.1	890.2	894.3	900.5	906.0	920.5	930.7
27.5°	840.4	839.6	837.2	834.0	837.2	839.6	840.4	845.9	853.1	862.3	875.4
30°	809.1	807.7	806.3	804.3	806.3	807.7	809.1	814.6	820.1	827.7	838.0
32.5°	781.1	780.2	778.9	779.0	778.9	780.2	781.1	783.8	787.1	796.9	804.9
35°	741.1	740.4	739.0	738.3	739.0	740.4	741.1	743.8	745.9	748.6	755.5
37.5°	703.7	705.4	704.6	704.5	704.6	705.4	703.7	704.4	702.1	707.1	711.8
40°	677.8	678.5	679.8	679.2	679.8	678.5	677.8	678.5	678.5	678.5	682.6
42.5°	656.3	656.5	658.4	656.1	658.4	656.5	656.3	653.8	650.5	651.0	652.4
45°	618.0	622.2	621.5	621.5	621.5	622.2	618.0	613.2	612.5	609.8	609.8
47.5°	576.1	579.6	580.6	580.5	580.6	579.6	576.1	574.3	571.1	568.3	568.1
50°	548.5	547.2	549.2	548.5	549.2	547.2	548.5	545.1	540.3	540.3	539.0
52.5°	515.1	515.3	515.1	514.4	515.1	515.3	515.1	513.2	511.2	508.9	508.2
55°	463.3	464.0	462.6	463.3	462.6	464.0	463.3	462.6	462.6	461.2	462.6
57.5°	407.3	403.9	405.3	403.6	405.3	403.9	407.3	410.3	411.4	411.6	413.7
60°	367.1	361.6	360.2	357.5	360.2	361.6	367.1	373.9	376.7	378.1	380.1
62.5°	322.0	318.1	313.5	315.6	313.5	318.1	322.0	329.4	335.4	340.2	344.9
65°	261.9	259.2	257.1	259.8	257.1	259.2	261.9	267.4	272.9	283.9	294.2
67.5°	216.8	215.3	215.3	214.0	215.3	215.3	216.8	219.6	223.0	229.0	238.7
70°	193.2	191.1	191.1	189.8	191.1	191.1	193.2	193.2	196.6	199.3	206.2
72.5°	168.9	166.9	167.5	166.6	167.5	166.9	168.9	169.5	173.0	174.1	177.1
75°	125.1	121.7	121.7	122.3	121.7	121.7	125.1	129.2	132.7	138.9	140.3
77.5°	93.3	92.6	93.6	92.4	93.6	92.6	93.3	93.3	94.0	96.9	99.3
80°	76.3	75.6	74.9	77.0	74.9	75.6	76.3	76.3	77.0	77.7	78.4
82.5°	59.2	59.2	59.0	61.6	59.0	59.2	59.2	60.4	60.5	60.1	60.8
85°	35.7	34.4	35.7	34.4	35.7	34.4	35.7	35.0	35.7	35.0	35.7
87.5°	16.3	15.8	15.2	15.7	15.2	15.8	16.3	15.0	15.0	15.9	15.2
90°	18.1	18.9	18.1	18.1	18.1	18.9	18.1	17.2	17.2	16.4	15.5
92.5°	73.8	69.1	66.2	66.2	66.2	69.1	73.8	83.9	101.1	127.1	168.8
95°	263.0	236.3	220.9	209.7	220.9	236.3	263.0	305.1	388.5	503.7	636.9
97.5°	656.0	604.2	578.5	560.6	578.5	604.2	656.0	717.7	807.4	891.5	941.1
100°	873.3	820.9	795.0	788.2	795.0	820.9	873.3	948.0	1011.7	1053.8	1036.6
102.5°	1056.9	1018.9	991.8	986.3	991.8	1018.9	1056.9	1102.8	1129.3	1117.1	1031.8
105°	1233.5	1226.6	1214.5	1209.4	1214.5	1226.6	1233.5	1231.7	1196.4	1111.4	962.7
107.5°	1261.8	1281.4	1290.0	1292.3	1290.0	1281.4	1261.8	1219.3	1142.7	1022.9	864.5
110°	1234.3	1270.4	1285.9	1293.7	1285.9	1270.4	1234.3	1173.3	1078.7	954.1	805.4



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1175.2	1218.8	1240.5	1253.0	1240.5	1218.8	1175.2	1105.9	1011.3	893.5	762.1
115°	1075.3	1126.9	1154.3	1161.2	1154.3	1126.9	1075.3	1007.4	924.9	824.3	718.6
117.5°	991.8	1035.1	1062.9	1068.2	1062.9	1035.1	991.8	933.8	863.8	784.8	697.2
120°	946.3	984.2	1006.5	1016.0	1006.5	984.2	946.3	897.3	836.4	767.6	687.6
122.5°	914.0	946.3	965.3	974.7	965.3	946.3	914.0	872.6	819.2	756.6	679.4
125°	880.2	905.1	921.4	926.6	921.4	905.1	880.2	845.8	798.5	739.2	665.3
127.5°	857.3	879.5	893.2	898.4	893.2	879.5	857.3	822.8	777.9	718.8	648.1
130°	841.5	863.0	876.8	881.9	876.8	863.0	841.5	806.2	760.7	702.2	634.4
132.5°	820.9	845.1	858.2	863.3	858.2	845.1	820.9	786.4	740.7	683.7	619.9
135°	785.7	809.7	823.5	828.6	823.5	809.7	785.7	751.2	708.3	655.8	599.9
137.5°	744.3	768.1	779.5	785.7	779.5	768.1	744.3	712.2	673.4	629.2	581.9
140°	716.9	735.8	747.8	754.7	747.8	735.8	716.9	686.7	650.7	612.0	571.6
142.5°	688.6	706.2	716.9	721.7	716.9	706.2	688.6	662.0	630.8	597.5	562.0
145°	648.9	663.6	672.2	676.5	672.2	663.6	648.9	627.5	603.4	577.6	548.4
147.5°	615.8	628.4	634.9	636.4	634.9	628.4	615.8	599.9	581.1	560.4	537.2
150°	596.5	607.7	612.9	613.7	612.9	607.7	596.5	582.8	567.3	550.1	530.4
152.5°	580.1	589.1	592.2	593.1	592.2	589.1	580.1	568.3	555.6	539.8	522.8
155°	557.0	563.9	566.5	566.5	566.5	563.9	557.0	548.4	538.0	525.2	511.4
157.5°	536.3	541.5	543.0	543.0	543.0	541.5	536.3	529.9	521.6	510.7	499.2
160°	522.6	527.8	528.7	528.7	528.7	527.8	522.6	517.5	510.6	501.1	491.6
162.5°	509.5	514.7	515.6	514.9	515.6	514.7	509.5	505.8	499.6	492.1	484.1
165°	492.5	495.9	495.1	494.2	495.1	495.9	492.5	489.0	484.7	478.8	473.6
167.5°	476.6	478.8	478.6	477.9	478.6	478.8	476.6	474.8	472.3	467.4	463.5
170°	467.6	468.5	467.6	467.6	467.6	468.5	467.6	465.9	463.3	459.9	457.3
172.5°	458.7	459.5	458.7	457.3	458.7	459.5	458.7	457.6	455.7	453.7	451.8
175°	446.9	448.7	446.9	445.2	446.9	448.7	446.9	446.9	446.9	445.2	444.4
177.5°	440.2	440.9	439.5	438.2	439.5	440.9	440.2	440.9	440.2	440.2	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935  
 CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1631.9	1635.8	1644.6	1654.5	1662.8	1669.9	1675.4	1683.1	1690.2	1700.1	1709.5
5°	1533.0	1542.6	1556.3	1572.9	1593.5	1607.2	1624.4	1639.5	1661.6	1683.5	1704.9
7.5°	1446.0	1456.6	1476.9	1499.7	1524.1	1546.7	1567.1	1593.7	1622.9	1654.9	1690.7
10°	1390.0	1401.7	1425.7	1451.8	1480.7	1502.7	1530.3	1561.9	1594.8	1634.0	1678.0
12.5°	1339.4	1350.6	1379.5	1406.2	1436.1	1460.3	1492.3	1524.5	1568.5	1610.9	1661.0
15°	1240.8	1270.4	1303.4	1335.0	1370.7	1400.3	1438.8	1471.8	1513.7	1573.6	1630.6
17.5°	1131.4	1162.9	1203.9	1252.7	1300.6	1337.2	1376.2	1417.2	1467.1	1528.2	1594.1
20°	1067.6	1093.0	1138.4	1192.7	1248.4	1299.2	1335.0	1380.4	1431.9	1497.9	1566.0
22.5°	1019.8	1041.3	1076.8	1131.1	1191.2	1250.3	1296.0	1340.7	1397.8	1463.8	1537.9
25°	948.0	971.4	1002.3	1039.4	1108.1	1170.7	1230.5	1282.0	1342.6	1408.5	1491.0
27.5°	888.3	908.6	936.9	975.6	1021.8	1090.8	1163.3	1222.1	1284.1	1355.0	1437.5
30°	853.1	869.6	892.9	932.1	976.1	1038.0	1111.6	1180.3	1242.9	1316.5	1402.4
32.5°	816.2	833.9	856.7	887.6	934.9	986.9	1060.4	1135.7	1202.2	1277.4	1361.7
35°	767.2	780.9	801.5	833.2	875.8	921.2	986.4	1064.1	1134.3	1214.7	1295.1
37.5°	717.6	733.7	750.0	778.2	813.1	861.9	915.4	994.7	1072.4	1145.8	1224.3
40°	689.5	699.1	717.0	739.7	776.8	820.1	870.3	948.0	1025.6	1098.5	1177.6
42.5°	658.1	668.9	684.0	706.7	739.9	782.1	831.2	898.5	979.5	1050.2	1122.1
45°	614.6	620.8	635.8	655.1	682.6	725.2	770.6	830.4	906.7	974.0	1037.3
47.5°	570.6	575.9	585.4	603.0	633.8	668.0	710.5	764.1	831.1	898.5	951.9
50°	540.3	545.1	554.1	570.6	598.1	631.7	673.6	721.8	781.6	846.2	890.9
52.5°	510.1	512.7	521.1	539.8	562.8	596.0	633.5	677.8	733.7	787.4	832.6
55°	461.9	468.1	473.6	487.4	509.4	541.0	574.7	616.6	660.0	705.3	743.8
57.5°	411.7	418.5	426.5	438.6	456.1	485.4	515.7	549.7	586.7	624.3	656.6
60°	378.8	385.0	391.8	405.6	421.4	444.8	477.8	507.3	535.5	569.9	602.2
62.5°	346.3	352.5	360.5	371.5	386.8	409.1	436.5	462.3	491.5	521.5	545.5
65°	298.3	303.2	309.4	319.7	334.1	354.0	376.7	396.7	422.8	444.8	466.7
67.5°	245.7	254.9	263.0	271.4	283.6	302.2	318.6	337.7	355.4	371.8	391.8
70°	211.0	221.4	228.9	237.8	249.5	265.4	281.1	294.2	308.7	324.4	342.3
72.5°	181.9	190.0	195.9	205.4	216.0	230.7	245.4	256.2	267.9	278.8	296.2
75°	143.7	147.1	151.3	158.8	168.4	179.4	191.1	200.7	207.6	217.2	229.6
77.5°	103.2	109.9	112.6	118.0	124.8	131.7	139.4	147.5	154.1	157.6	167.0
80°	79.0	81.8	84.6	92.1	96.3	103.1	108.6	116.1	118.9	122.3	131.3
82.5°	61.5	63.1	64.7	66.8	69.3	76.2	81.7	86.4	89.2	90.5	97.2
85°	35.7	36.4	37.1	37.8	38.5	38.5	41.2	44.7	49.5	49.5	51.6
87.5°	15.0	15.8	15.4	14.5	15.6	14.6	15.2	15.0	16.4	17.6	18.9
90°	14.6	15.5	13.8	12.1	12.1	6.9	6.9	6.0	5.2	2.6	0.9
92.5°	227.1	272.7	238.6	173.7	106.9	63.3	45.4	32.8	22.4	14.3	9.8
95°	720.3	700.5	528.7	323.2	182.2	107.5	71.4	50.7	39.5	30.9	28.3
97.5°	904.9	737.8	494.7	290.5	174.2	116.6	86.3	68.6	58.3	50.9	50.9
100°	911.1	691.0	448.7	273.4	176.2	125.5	98.0	81.6	71.4	65.3	65.3
102.5°	859.5	632.7	417.8	268.5	183.0	137.2	111.1	95.4	85.8	80.4	79.0
105°	765.9	563.9	391.1	270.8	199.4	158.2	133.2	117.8	107.5	103.1	100.6
107.5°	690.2	525.4	386.2	283.4	218.5	180.6	156.1	141.3	130.3	126.1	124.3
110°	652.4	512.3	387.6	293.1	232.9	195.1	171.9	156.4	146.1	141.8	140.1



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	631.1	506.1	391.8	303.4	246.7	210.3	187.0	171.6	162.0	157.0	155.2
115°	611.1	502.8	399.7	319.8	268.2	233.8	210.6	194.2	185.6	179.6	177.1
117.5°	602.2	502.0	408.1	336.4	289.0	256.3	232.2	217.0	207.5	202.2	199.8
120°	597.4	502.0	414.3	348.1	303.4	270.8	246.7	232.0	222.7	216.6	214.9
122.5°	591.9	501.3	420.5	359.1	317.2	284.5	261.1	245.1	236.3	230.3	228.7
125°	582.8	500.2	429.8	375.7	336.0	305.1	281.0	264.8	255.3	250.1	246.7
127.5°	570.6	498.3	437.1	389.9	353.6	323.7	299.5	282.4	271.6	265.4	262.7
130°	563.0	497.7	442.6	398.8	365.3	336.0	311.2	294.8	281.9	275.1	271.6
132.5°	556.1	497.0	447.5	407.8	375.0	345.7	322.2	304.4	292.2	283.3	280.5
135°	545.8	495.9	454.7	419.5	388.5	360.2	337.8	319.8	305.1	296.5	293.1
137.5°	536.8	495.8	459.0	427.7	398.8	372.4	351.0	332.3	318.4	308.9	305.7
140°	532.1	495.1	462.4	433.2	405.7	380.0	359.3	341.2	326.7	317.2	314.6
142.5°	528.0	495.1	465.2	437.3	411.9	386.8	366.9	349.5	335.5	326.8	324.3
145°	520.9	493.4	466.7	441.8	418.6	396.2	377.4	361.0	349.0	340.4	337.8
147.5°	514.5	490.3	467.6	445.7	425.5	404.5	387.4	373.9	361.5	354.0	353.1
150°	509.7	488.2	467.6	447.8	429.0	410.0	393.6	380.8	370.5	363.6	362.7
152.5°	504.2	484.7	466.2	449.2	431.7	414.8	399.8	388.3	378.8	371.9	371.7
155°	495.9	479.7	464.2	450.4	435.8	421.2	408.3	398.8	390.2	385.0	384.2
157.5°	487.5	474.3	461.9	450.4	438.7	426.4	416.2	407.9	401.2	396.4	396.4
160°	481.4	470.2	459.9	450.4	440.1	429.8	420.3	413.5	407.4	404.0	404.0
162.5°	475.9	466.1	457.8	450.4	441.4	431.9	424.5	418.3	412.9	410.2	410.9
165°	466.7	459.9	453.8	448.7	441.8	434.0	429.0	424.6	420.3	418.6	418.6
167.5°	458.5	453.7	449.7	446.6	441.6	435.9	432.0	429.6	426.4	425.5	426.4
170°	453.0	449.5	446.9	445.2	440.9	436.6	434.0	432.4	429.8	429.0	429.8
172.5°	448.2	445.4	444.2	443.8	440.2	437.3	435.4	434.4	432.5	432.4	433.2
175°	442.6	440.9	440.9	441.8	439.2	437.5	437.5	436.6	435.8	435.8	436.6
177.5°	438.9	438.2	438.2	439.5	438.2	437.5	437.5	437.5	436.8	437.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1716.7	1721.6	1727.1	1737.6	1746.4	1750.2	1757.9	1763.4	1761.8	1769.4	1782.6
5°	1723.4	1742.0	1763.2	1785.3	1810.0	1830.7	1847.1	1863.6	1876.7	1892.5	1915.9
7.5°	1722.3	1755.3	1791.1	1830.7	1871.2	1906.3	1938.7	1971.7	2001.0	2033.0	2074.9
10°	1717.9	1761.9	1806.6	1858.1	1909.7	1958.5	2002.5	2043.8	2082.9	2124.9	2177.8
12.5°	1713.0	1763.5	1817.6	1879.6	1943.8	2002.5	2054.2	2113.6	2162.7	2216.7	2277.9
15°	1691.1	1759.1	1832.7	1913.1	1990.1	2069.2	2139.9	2212.9	2280.9	2345.5	2422.5
17.5°	1666.0	1744.6	1831.3	1926.3	2018.9	2115.0	2199.0	2290.8	2360.3	2447.1	2518.6
20°	1645.7	1730.3	1823.1	1929.6	2034.8	2141.3	2234.1	2327.6	2406.0	2493.3	2584.0
22.5°	1620.9	1713.7	1814.3	1924.7	2034.8	2151.2	2253.9	2346.9	2443.9	2542.3	2635.8
25°	1581.1	1677.3	1783.9	1904.9	2031.4	2150.3	2260.3	2375.8	2480.3	2586.8	2670.6
27.5°	1532.1	1633.2	1745.5	1870.4	2000.2	2121.9	2251.5	2374.6	2479.7	2582.2	2655.4
30°	1493.1	1599.7	1707.5	1834.1	1968.8	2099.4	2238.3	2361.3	2472.0	2564.1	2605.4
32.5°	1452.9	1554.0	1665.3	1793.4	1931.4	2071.9	2209.7	2335.5	2437.9	2493.2	2494.2
35°	1383.1	1478.0	1593.5	1719.2	1860.9	2013.4	2153.0	2276.7	2339.3	2344.2	2276.7
37.5°	1306.9	1394.0	1503.0	1628.9	1784.0	1935.8	2078.4	2160.9	2181.8	2111.8	1987.2
40°	1252.5	1332.9	1438.1	1567.4	1721.3	1878.1	2008.0	2068.5	2046.5	1933.0	1794.2
42.5°	1195.3	1270.2	1371.6	1499.2	1653.7	1812.1	1922.8	1955.2	1896.9	1765.9	1603.4
45°	1102.0	1170.7	1271.1	1399.6	1548.1	1696.6	1780.5	1763.9	1667.0	1511.7	1329.5
47.5°	1004.8	1071.2	1161.5	1280.4	1432.4	1560.6	1617.4	1567.6	1429.7	1258.8	1110.6
50°	940.4	1008.5	1091.7	1205.1	1343.9	1467.7	1504.1	1428.5	1275.1	1110.9	974.7
52.5°	877.2	935.3	1016.8	1126.4	1259.2	1363.7	1383.1	1296.0	1137.7	990.4	869.7
55°	780.9	833.9	902.6	1005.7	1120.5	1209.2	1198.9	1086.8	943.1	817.3	722.5
57.5°	687.9	727.7	791.3	887.9	988.7	1048.2	1010.6	915.0	781.1	678.1	598.1
60°	626.3	663.4	722.5	807.0	895.7	929.4	897.8	794.0	688.1	593.9	526.6
62.5°	567.9	600.7	651.5	730.0	801.7	821.7	787.8	697.2	601.8	521.3	465.5
65°	483.3	513.5	556.8	612.5	662.0	671.6	649.6	556.8	484.7	417.2	378.8
67.5°	406.4	426.2	460.0	508.2	534.4	540.0	497.6	439.3	375.7	334.2	305.2
70°	354.7	368.4	400.1	426.2	447.5	448.2	409.1	362.3	313.5	279.8	258.5
72.5°	304.7	317.9	341.8	359.6	376.0	370.7	334.8	297.9	258.5	233.1	217.2
75°	235.1	246.8	259.2	267.4	267.4	260.5	234.5	206.9	184.3	169.1	164.3
77.5°	170.9	180.6	184.7	183.4	180.9	170.2	153.7	135.7	127.6	120.5	116.8
80°	134.1	138.2	139.6	136.1	132.0	119.6	108.6	101.1	93.5	90.7	89.4
82.5°	99.4	103.0	99.4	100.4	91.3	81.1	75.1	72.5	69.3	68.2	66.8
85°	53.0	52.3	50.9	47.4	41.2	39.9	39.2	38.5	37.1	37.8	36.4
87.5°	18.7	17.6	15.5	15.2	15.2	15.1	15.6	15.9	16.3	15.6	16.9
90°	2.6	5.2	6.0	6.9	6.9	12.1	12.1	13.8	15.5	14.6	15.5
92.5°	14.3	22.4	32.8	45.4	63.3	106.9	173.7	238.6	272.7	227.1	168.8
95°	30.9	39.5	50.7	71.4	107.5	182.2	323.2	528.7	700.5	720.3	636.9
97.5°	50.9	58.3	68.6	86.3	116.6	174.2	290.5	494.7	737.8	904.9	941.1
100°	65.3	71.4	81.6	98.0	125.5	176.2	273.4	448.7	691.0	911.1	1036.6
102.5°	80.4	85.8	95.4	111.1	137.2	183.0	268.5	417.8	632.7	859.5	1031.8
105°	103.1	107.5	117.8	133.2	158.2	199.4	270.8	391.1	563.9	765.9	962.7
107.5°	126.1	130.3	141.3	156.1	180.6	218.5	283.4	386.2	525.4	690.2	864.5
110°	141.8	146.1	156.4	171.9	195.1	232.9	293.1	387.6	512.3	652.4	805.4





TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	162.0	171.6	187.0	210.3	246.7	303.4	391.8	506.1	631.1	762.1
115°	179.6	185.6	194.2	210.6	233.8	268.2	319.8	399.7	502.8	611.1	718.6
117.5°	202.2	207.5	217.0	232.2	256.3	289.0	336.4	408.1	502.0	602.2	697.2
120°	216.6	222.7	232.0	246.7	270.8	303.4	348.1	414.3	502.0	597.4	687.6
122.5°	230.3	236.3	245.1	261.1	284.5	317.2	359.1	420.5	501.3	591.9	679.4
125°	250.1	255.3	264.8	281.0	305.1	336.0	375.7	429.8	500.2	582.8	665.3
127.5°	265.4	271.6	282.4	299.5	323.7	353.6	389.9	437.1	498.3	570.6	648.1
130°	275.1	281.9	294.8	311.2	336.0	365.3	398.8	442.6	497.7	563.0	634.4
132.5°	283.3	292.2	304.4	322.2	345.7	375.0	407.8	447.5	497.0	556.1	619.9
135°	296.5	305.1	319.8	337.8	360.2	388.5	419.5	454.7	495.9	545.8	599.9
137.5°	308.9	318.4	332.3	351.0	372.4	398.8	427.7	459.0	495.8	536.8	581.9
140°	317.2	326.7	341.2	359.3	380.0	405.7	433.2	462.4	495.1	532.1	571.6
142.5°	326.8	335.5	349.5	366.9	386.8	411.9	437.3	465.2	495.1	528.0	562.0
145°	340.4	349.0	361.0	377.4	396.2	418.6	441.8	466.7	493.4	520.9	548.4
147.5°	354.0	361.5	373.9	387.4	404.5	425.5	445.7	467.6	490.3	514.5	537.2
150°	363.6	370.5	380.8	393.6	410.0	429.0	447.8	467.6	488.2	509.7	530.4
152.5°	371.9	378.8	388.3	399.8	414.8	431.7	449.2	466.2	484.7	504.2	522.8
155°	385.0	390.2	398.8	408.3	421.2	435.8	450.4	464.2	479.7	495.9	511.4
157.5°	396.4	401.2	407.9	416.2	426.4	438.7	450.4	461.9	474.3	487.5	499.2
160°	404.0	407.4	413.5	420.3	429.8	440.1	450.4	459.9	470.2	481.4	491.6
162.5°	410.2	412.9	418.3	424.5	431.9	441.4	450.4	457.8	466.1	475.9	484.1
165°	418.6	420.3	424.6	429.0	434.0	441.8	448.7	453.8	459.9	466.7	473.6
167.5°	425.5	426.4	429.6	432.0	435.9	441.6	446.6	449.7	453.7	458.5	463.5
170°	429.0	429.8	432.4	434.0	436.6	440.9	445.2	446.9	449.5	453.0	457.3
172.5°	432.4	432.5	434.4	435.4	437.3	440.2	443.8	444.2	445.4	448.2	451.8
175°	435.8	435.8	436.6	437.5	437.5	439.2	441.8	440.9	440.9	442.6	444.4
177.5°	437.5	436.8	437.5	437.5	437.5	438.2	439.5	438.2	438.2	438.9	439.5
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5	437.5



TEST NUMBER: P333005-935  
 CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2	1706.2
2.5°	1789.8	1792.0	1793.6	1799.1	1799.7	1804.7	1799.7
5°	1937.9	1947.5	1962.6	1977.7	1979.1	1988.7	1971.5
7.5°	2103.9	2126.2	2140.1	2164.6	2174.2	2180.2	2170.3
10°	2218.4	2238.9	2275.4	2293.3	2311.2	2313.9	2305.7
12.5°	2328.9	2361.6	2390.3	2424.1	2423.4	2447.6	2438.7
15°	2476.1	2509.8	2549.7	2587.5	2601.3	2601.3	2612.3
17.5°	2581.2	2642.9	2684.2	2713.9	2746.2	2751.9	2748.1
20°	2652.1	2718.8	2762.8	2801.3	2823.3	2829.5	2829.5
22.5°	2704.9	2761.7	2804.6	2839.2	2857.4	2864.6	2862.5
25°	2741.5	2790.2	2816.4	2826.7	2831.5	2830.2	2817.1
27.5°	2691.4	2689.2	2672.7	2641.1	2617.4	2602.9	2586.4
30°	2595.7	2560.0	2518.8	2473.4	2414.9	2370.2	2356.5
32.5°	2453.3	2373.0	2303.2	2227.6	2164.7	2120.0	2101.4
35°	2177.8	2050.6	1946.8	1856.1	1790.1	1748.9	1735.1
37.5°	1850.8	1727.8	1599.2	1511.2	1456.6	1414.9	1399.3
40°	1643.0	1508.9	1396.9	1314.4	1258.0	1217.5	1216.8
42.5°	1453.2	1325.3	1219.8	1160.4	1099.6	1072.8	1072.6
45°	1189.9	1087.5	998.2	951.4	915.0	892.9	886.7
47.5°	985.2	900.5	841.0	803.7	774.0	760.0	751.0
50°	870.3	796.1	748.6	716.3	699.8	681.9	680.5
52.5°	774.6	714.6	677.7	651.4	630.5	619.7	620.1
55°	651.0	603.6	577.5	557.5	541.0	532.8	529.3
57.5°	548.5	512.8	493.9	475.5	468.6	462.1	460.3
60°	484.7	460.5	442.7	428.3	417.9	415.9	415.2
62.5°	431.9	406.7	394.3	383.1	375.7	372.5	371.2
65°	356.1	337.5	326.5	317.6	314.9	310.0	309.4
67.5°	287.1	276.0	268.6	262.4	258.7	258.5	258.5
70°	244.7	238.5	232.4	228.9	226.9	225.5	225.5
72.5°	208.4	203.9	198.8	197.0	196.6	195.2	194.7
75°	158.8	153.9	154.6	151.3	148.5	145.1	143.0
77.5°	112.6	109.2	108.5	108.1	105.7	105.3	106.4
80°	87.3	83.9	83.2	83.9	83.2	81.1	81.1
82.5°	66.4	63.5	62.9	62.4	61.7	62.4	61.3
85°	35.7	34.4	34.4	34.4	35.7	35.0	34.4
87.5°	15.9	15.5	16.1	15.7	15.8	15.2	15.7
90°	16.4	17.2	17.2	18.1	18.9	18.1	18.1
92.5°	127.1	101.1	83.9	73.8	69.1	66.2	66.2
95°	503.7	388.5	305.1	263.0	236.3	220.9	209.7
97.5°	891.5	807.4	717.7	656.0	604.2	578.5	560.6
100°	1053.8	1011.7	948.0	873.3	820.9	795.0	788.2
102.5°	1117.1	1129.3	1102.8	1056.9	1018.9	991.8	986.3
105°	1111.4	1196.4	1231.7	1233.5	1226.6	1214.5	1209.4
107.5°	1022.9	1142.7	1219.3	1261.8	1281.4	1290.0	1292.3
110°	954.1	1078.7	1173.3	1234.3	1270.4	1285.9	1293.7



TEST NUMBER: P333005-935

CATALOG NUMBER: SA4XXRDIP-C1195D1035U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	893.5	1011.3	1105.9	1175.2	1218.8	1240.5	1253.0
115°	824.3	924.9	1007.4	1075.3	1126.9	1154.3	1161.2
117.5°	784.8	863.8	933.8	991.8	1035.1	1062.9	1068.2
120°	767.6	836.4	897.3	946.3	984.2	1006.5	1016.0
122.5°	756.6	819.2	872.6	914.0	946.3	965.3	974.7
125°	739.2	798.5	845.8	880.2	905.1	921.4	926.6
127.5°	718.8	777.9	822.8	857.3	879.5	893.2	898.4
130°	702.2	760.7	806.2	841.5	863.0	876.8	881.9
132.5°	683.7	740.7	786.4	820.9	845.1	858.2	863.3
135°	655.8	708.3	751.2	785.7	809.7	823.5	828.6
137.5°	629.2	673.4	712.2	744.3	768.1	779.5	785.7
140°	612.0	650.7	686.7	716.9	735.8	747.8	754.7
142.5°	597.5	630.8	662.0	688.6	706.2	716.9	721.7
145°	577.6	603.4	627.5	648.9	663.6	672.2	676.5
147.5°	560.4	581.1	599.9	615.8	628.4	634.9	636.4
150°	550.1	567.3	582.8	596.5	607.7	612.9	613.7
152.5°	539.8	555.6	568.3	580.1	589.1	592.2	593.1
155°	525.2	538.0	548.4	557.0	563.9	566.5	566.5
157.5°	510.7	521.6	529.9	536.3	541.5	543.0	543.0
160°	501.1	510.6	517.5	522.6	527.8	528.7	528.7
162.5°	492.1	499.6	505.8	509.5	514.7	515.6	514.9
165°	478.8	484.7	489.0	492.5	495.9	495.1	494.2
167.5°	467.4	472.3	474.8	476.6	478.8	478.6	477.9
170°	459.9	463.3	465.9	467.6	468.5	467.6	467.6
172.5°	453.7	455.7	457.6	458.7	459.5	458.7	457.3
175°	445.2	446.9	446.9	446.9	448.7	446.9	445.2
177.5°	440.2	440.2	440.9	440.2	440.9	439.5	438.2
180°	437.5	437.5	437.5	437.5	437.5	437.5	437.5

(END OF REPORT)