

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904906

Luminaire Tested: DFN2DIP-4P3F0-020D030US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904906
REPORT IS A COMBINATION OF REPORTS P899039 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US835-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4635.0 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	887	887	887
5°	888	874	880
10°	880	862	868
15°	866	847	849
20°	848	826	830
25°	830	802	807
30°	808	780	779
35°	787	753	749
40°	761	727	721
45°	735	700	691
50°	706	672	658
55°	676	639	627
60°	643	600	591
65°	605	560	549
70°	558	511	504
75°	494	452	461
80°	415	378	381
85°	292	250	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 953 cd/sqm

TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	1.6
10°-20°	206.1	4.4
20°-30°	302.9	6.5
30°-40°	351.8	7.6
40°-50°	351.3	7.6
50°-60°	306.3	6.6
60°-70°	226.5	4.9
70°-80°	128.1	2.8
80°-90°	36.5	0.8
90°-100°	58.7	1.3
100°-110°	186.5	4.0
110°-120°	319.2	6.9
120°-130°	419.8	9.1
130°-140°	471.2	10.2
140°-150°	462.1	10.0
150°-160°	387.7	8.4
160°-170°	257.1	5.5
170°-180°	89.9	1.9
0°-30°	582.2	12.6
0°-40°	934.0	20.2
0°-60°	1591.6	34.3
0°-90°	1982.7	42.8
90°-120°	564.5	12.2
90°-150°	1917.7	41.4
90°-180°	2652.0	57.2
0°-180°	4635.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	778	778	778	778	778	
5°	778	775	767	773	772	74
15°	741	736	727	730	726	209
25°	670	664	652	653	652	309
35°	578	571	559	554	551	361
45°	471	466	454	446	443	363
55°	356	352	343	334	330	318
65°	240	236	228	222	218	238
75°	126	124	120	116	118	134
85°	31	30	29	27	26	34
90°	1	10	28	26	27	5
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	778.2	778.2	778.2	778.2	778.2
2.5°	782.7	779.0	770.7	778.2	776.8
5°	778.2	775.3	767.0	773.0	771.5
7.5°	773.0	768.5	760.3	766.3	764.8
10°	764.8	759.6	750.6	756.5	754.3
12.5°	753.5	749.1	740.1	743.8	742.3
15°	740.8	736.4	726.6	729.6	725.9
17.5°	725.1	720.7	710.9	714.6	710.9
20°	707.9	703.4	692.9	695.2	692.2
22.5°	690.7	684.0	674.2	674.2	672.7
25°	670.5	664.5	651.8	653.2	651.8
27.5°	648.0	642.8	633.1	630.9	627.1
30°	625.6	619.6	608.4	606.2	603.1
32.5°	601.6	597.2	585.2	580.7	577.7
35°	578.5	571.0	559.0	554.5	550.7
37.5°	552.3	545.5	533.5	528.3	524.5
40°	525.3	519.3	507.3	500.7	497.6
42.5°	499.1	493.1	481.2	473.7	469.2
45°	470.7	465.5	454.2	446.0	443.0
47.5°	443.0	437.8	425.8	417.5	413.1
50°	413.8	410.1	399.6	389.1	385.4
52.5°	385.4	380.1	370.4	362.2	357.0
55°	356.2	351.7	342.7	333.8	330.0
57.5°	327.0	323.3	313.5	304.6	301.5
60°	297.8	294.9	284.4	276.1	273.9
62.5°	269.4	264.1	256.7	249.2	246.2
65°	240.2	235.7	228.3	221.5	217.8
67.5°	210.3	206.5	199.8	194.6	191.6
70°	182.6	179.6	172.8	167.6	164.7
72.5°	154.2	151.2	147.4	142.2	140.0
75°	125.7	124.3	120.4	116.0	117.5
77.5°	100.3	97.3	95.7	93.5	91.3
80°	74.9	74.1	72.6	70.3	68.8
82.5°	50.9	50.9	50.2	47.2	47.2
85°	30.6	29.9	29.2	26.9	26.2
87.5°	13.5	12.0	10.5	8.3	7.5
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6

TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P904906

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.11	6.91	7.13	7.94	9.31	5.67	6.47	6.69	7.49	8.87
	3H	7.76	8.48	8.79	9.52	10.91	7.27	7.99	8.30	9.03	10.42
	4H	8.35	9.03	9.39	10.06	11.46	7.85	8.53	8.89	9.57	10.97
	6H	8.74	9.37	9.79	10.41	11.82	8.24	8.87	9.29	9.91	11.32
	8H	8.84	9.44	9.90	10.49	11.90	8.34	8.93	9.39	9.99	11.40
	12H	8.89	9.45	9.94	10.50	11.93	8.38	8.94	9.44	9.99	11.42
4H	2H	6.56	7.24	7.61	8.28	9.68	6.21	6.89	7.25	7.93	9.32
	3H	8.42	8.98	9.47	10.05	11.46	8.01	8.58	9.06	9.64	11.05
	4H	9.13	9.65	10.19	10.70	12.14	8.70	9.22	9.76	10.28	11.71
	6H	9.63	10.08	10.70	11.16	12.59	9.20	9.65	10.27	10.73	12.15
	8H	9.78	10.20	10.85	11.27	12.71	9.34	9.76	10.41	10.83	12.27
	12H	9.85	10.22	10.94	11.31	12.76	9.40	9.78	10.49	10.86	12.31
8H	4H	9.31	9.73	10.38	10.80	12.25	8.94	9.35	10.01	10.43	11.87
	6H	9.94	10.28	11.03	11.40	12.84	9.55	9.90	10.64	11.01	12.45
	8H	10.15	10.46	11.25	11.55	13.01	9.76	10.06	10.86	11.16	12.62
	12H	10.28	10.54	11.38	11.64	13.14	9.87	10.13	10.97	11.23	12.73
12H	4H	9.29	9.67	10.38	10.76	12.21	8.93	9.30	10.01	10.39	11.84
	6H	9.96	10.27	11.06	11.36	12.82	9.59	9.89	10.69	10.99	12.45
	8H	10.20	10.47	11.30	11.56	13.06	9.82	10.08	10.92	11.18	12.68

END OF REPORT