

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904909

Luminaire Tested: DFN2DIP-4P3F0-020D030US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904909
REPORT IS A COMBINATION OF REPORTS P900560 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US835-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4670.0 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38
2	87	80	74	69	78	73	68	63	59	56	53	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	45	41	38	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	15	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	942	942	942
5°	943	926	933
10°	933	908	902
15°	920	877	855
20°	902	835	797
25°	884	788	741
30°	860	740	670
35°	836	689	608
40°	812	635	537
45°	785	576	473
50°	756	517	410
55°	726	453	349
60°	691	387	287
65°	651	320	258
70°	602	256	233
75°	540	225	212
80°	452	187	182
85°	306	122	135

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 785 cd/sqm

TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	1.7
10°-20°	212.7	4.6
20°-30°	298.6	6.4
30°-40°	325.5	7.0
40°-50°	299.1	6.4
50°-60°	234.9	5.0
60°-70°	152.9	3.3
70°-80°	78.7	1.7
80°-90°	21.9	0.5
90°-100°	33.4	0.7
100°-110°	124.4	2.7
110°-120°	330.1	7.1
120°-130°	547.5	11.7
130°-140°	581.5	12.5
140°-150°	540.5	11.6
150°-160°	434.5	9.3
160°-170°	280.0	6.0
170°-180°	96.4	2.1
0°-30°	588.7	12.6
0°-40°	914.2	19.6
0°-60°	1448.3	31.0
0°-90°	1701.8	36.4
90°-120°	487.9	10.4
90°-150°	2157.3	46.2
90°-180°	2968.0	63.6
0°-180°	4670.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	827	823	813	820	818	78
15°	786	778	752	738	731	222
25°	714	690	640	610	598	328
35°	615	577	511	464	447	385
45°	503	452	374	321	303	388
55°	382	324	243	198	184	342
65°	258	198	130	105	102	256
75°	138	85	60	55	54	146
85°	32	16	14	14	14	37
90°	1	9	15	18	20	4
95°	48	23	28	32	32	56
105°	223	245	45	53	56	238
115°	421	434	452	113	60	415
125°	596	605	619	624	626	531
135°	737	749	755	763	761	569
145°	855	854	867	872	868	535
155°	941	935	944	948	942	434
165°	992	988	990	995	990	280
175°	1015	1010	1011	1016	1009	97
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.6	826.6	826.6	826.6	826.6
2.5°	830.3	826.6	818.3	825.9	824.4
5°	826.6	822.9	813.1	819.9	817.6
7.5°	819.9	815.4	804.9	807.9	804.1
10°	810.9	805.6	790.7	788.4	784.0
12.5°	799.7	792.9	772.7	768.3	760.0
15°	786.2	777.9	752.5	738.3	730.9
17.5°	770.5	758.5	727.1	710.6	698.7
20°	752.5	737.5	700.2	681.5	665.0
22.5°	733.1	715.9	672.5	647.1	635.9
25°	713.7	689.7	640.3	609.7	598.4
27.5°	690.5	665.0	610.4	575.2	558.0
30°	665.8	637.3	577.5	539.4	519.1
32.5°	641.8	607.4	546.1	501.2	482.5
35°	614.9	576.8	511.0	463.8	447.3
37.5°	588.7	547.5	478.0	426.4	407.7
40°	561.0	516.2	443.6	390.5	371.0
42.5°	532.6	484.8	409.2	353.8	335.2
45°	502.7	452.5	374.1	320.9	302.9
47.5°	474.3	421.2	340.4	287.2	270.8
50°	442.9	389.8	307.5	255.8	240.2
52.5°	412.1	356.0	276.0	226.7	212.5
55°	382.2	323.9	243.1	198.3	184.0
57.5°	351.6	291.7	214.0	172.1	160.1
60°	320.2	260.3	183.3	145.2	133.2
62.5°	289.5	229.7	157.1	121.2	115.2
65°	258.1	197.5	130.2	104.8	102.5
67.5°	228.2	167.5	104.8	92.0	89.8
70°	196.7	138.4	86.7	79.3	76.3
72.5°	166.8	111.4	72.5	66.6	65.1
75°	137.6	85.2	59.8	54.6	53.9
77.5°	108.5	60.6	47.1	44.1	42.6
80°	81.5	43.4	35.9	32.9	32.9
82.5°	56.8	29.2	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.7	8.8	14.6	18.4	19.7
92.5°	18.4	15.4	17.6	19.1	19.7
95°	47.6	23.4	28.5	32.3	31.5
97.5°	85.7	25.7	37.3	39.6	40.3
100°	129.7	29.3	41.8	47.6	49.1
102.5°	178.0	176.6	43.2	51.2	53.5
105°	222.7	244.7	44.7	52.7	55.7
107.5°	274.7	293.0	46.2	54.2	57.2
110°	324.6	339.9	128.2	55.0	57.9

TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.5	384.6	372.2	56.4	58.6
115°	421.2	433.7	452.0	112.8	60.1
117.5°	464.5	479.1	491.6	386.8	194.9
120°	512.8	523.8	537.0	545.8	446.9
122.5°	553.8	565.6	580.3	584.6	585.4
125°	595.6	605.1	619.1	624.2	626.4
127.5°	633.7	643.9	655.0	662.3	663.0
130°	669.6	681.4	689.4	697.4	696.8
132.5°	706.2	715.8	723.8	730.4	729.7
135°	737.0	748.8	755.3	762.7	761.2
137.5°	769.2	778.0	785.4	792.7	790.5
140°	800.7	806.6	814.6	821.2	817.6
142.5°	827.2	832.3	841.8	847.6	844.0
145°	855.0	854.2	866.7	871.8	868.1
147.5°	879.1	876.9	889.4	893.0	890.1
150°	902.6	897.5	909.2	913.5	909.9
152.5°	922.3	916.5	927.5	931.9	926.8
155°	941.4	934.9	943.6	948.0	942.2
157.5°	956.8	951.0	957.6	962.7	956.8
160°	970.0	965.6	970.0	974.4	969.2
162.5°	981.7	977.3	981.0	986.1	979.5
165°	991.9	987.6	989.8	994.9	989.8
167.5°	1000.0	995.6	997.8	1003.0	996.4
170°	1006.6	1002.2	1003.7	1008.8	1002.2
172.5°	1011.0	1006.6	1008.1	1013.2	1006.6
175°	1014.6	1009.5	1011.0	1016.1	1008.8
177.5°	1016.1	1011.0	1011.8	1016.9	1010.3
180°	1012.5	1012.5	1012.5	1012.5	1012.5

TEST NUMBER: P904909

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.49	6.22	6.56	7.29	8.74	1.45	2.18	2.52	3.25	4.71
	3H	7.16	7.81	8.24	8.89	10.36	2.63	3.28	3.71	4.36	5.83
	4H	7.76	8.38	8.85	9.45	10.93	3.07	3.69	4.16	4.77	6.25
	6H	8.17	8.74	9.27	9.82	11.31	3.38	3.95	4.48	5.03	6.52
	8H	8.29	8.83	9.40	9.93	11.42	3.46	4.00	4.57	5.10	6.59
	12H	8.35	8.86	9.46	9.95	11.46	3.50	4.01	4.61	5.11	6.61
4H	2H	5.49	6.11	6.59	7.19	8.67	2.03	2.65	3.13	3.73	5.21
	3H	7.31	7.82	8.41	8.93	10.42	3.37	3.88	4.47	4.99	6.48
	4H	7.99	8.47	9.10	9.56	11.07	3.91	4.38	5.02	5.47	6.99
	6H	8.50	8.90	9.62	10.02	11.53	4.31	4.72	5.43	5.84	7.34
	8H	8.67	9.05	9.79	10.16	11.68	4.44	4.81	5.55	5.92	7.45
	12H	8.76	9.10	9.89	10.22	11.75	4.49	4.83	5.63	5.96	7.48
8H	4H	7.95	8.33	9.07	9.44	10.96	4.18	4.55	5.29	5.66	7.19
	6H	8.51	8.82	9.65	9.97	11.49	4.68	4.99	5.82	6.15	7.66
	8H	8.72	9.00	9.87	10.13	11.67	4.87	5.14	6.01	6.27	7.81
	12H	8.85	9.09	10.00	10.22	11.80	4.98	5.22	6.12	6.35	7.92
12H	4H	7.90	8.24	9.03	9.36	10.89	4.18	4.52	5.31	5.64	7.17
	6H	8.48	8.76	9.63	9.89	11.43	4.73	5.00	5.87	6.14	7.67
	8H	8.70	8.94	9.84	10.07	11.64	4.93	5.17	6.08	6.30	7.87

END OF REPORT