

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332890-935

Luminaire Tested: **SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332890-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4870.7 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16	13
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	43	36	31	49	39	33	28	31	26	23	24	20	18	16	14	13	10
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	10	8
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4083	4083	4083	4083
5°	4736	4095	3620	4095
10°	5603	4077	3231	4077
15°	6471	4040	2776	4040
20°	7205	3988	2510	3988
25°	7439	3937	2331	3937
30°	6511	3875	2222	3875
35°	5069	3783	2157	3783
40°	3801	3678	2121	3678
45°	3001	3511	2103	3511
50°	2533	3317	2042	3317
55°	2208	3103	1932	3103
60°	1986	2882	1711	2882
65°	1752	2644	1473	2644
70°	1577	2396	1327	2396
75°	1323	2121	1129	2121
80°	1116	1808	1060	1808
85°	945	1417	945	1417



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	1.0
10°-20°	147.8	3.0
20°-30°	231.2	4.7
30°-40°	257.0	5.3
40°-50°	228.0	4.7
50°-60°	177.7	3.6
60°-70°	116.3	2.4
70°-80°	57.2	1.2
80°-90°	18.0	0.4
90°-100°	85.3	1.8
100°-110°	252.7	5.2
110°-120°	428.9	8.8
120°-130°	565.6	11.6
130°-140°	635.2	13.0
140°-150°	624.2	12.8
150°-160°	525.0	10.8
160°-170°	349.3	7.2
170°-180°	122.3	2.5
0°-30°	428.0	8.8
0°-40°	685.0	14.1
0°-60°	1090.8	22.4
0°-90°	1282.3	26.3
90°-120°	767.0	15.7
90°-150°	2591.9	53.2
90°-180°	3588.0	73.7
0°-180°	4870.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	506	506	506	506	506	
5°	584	505	447	505	584	59
15°	774	483	332	483	774	220
25°	835	442	262	442	835	370
35°	514	384	219	384	514	322
45°	263	308	184	308	263	208
55°	157	220	137	220	157	143
65°	92	138	77	138	92	92
75°	42	68	36	68	42	47
85°	10	15	10	15	10	12
90°	30	3	30	3	30	16
95°	79	60	79	60	79	82
105°	244	233	244	233	244	257
115°	432	436	432	436	432	427
125°	630	635	630	635	630	562
135°	820	819	820	819	820	633
145°	996	995	996	995	996	623
155°	1139	1140	1139	1140	1139	524
165°	1238	1241	1238	1241	1238	349
175°	1285	1291	1285	1291	1285	122
180°	1293	1293	1293	1293	1293	



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	533.5	534.9	533.5	533.3	531.7	531.2	530.5	528.4	524.5	522.2	522.7
5°	584.4	589.5	586.7	586.3	581.8	577.3	574.5	567.9	560.9	556.3	552.4
7.5°	643.3	646.3	644.5	641.6	634.4	630.3	623.6	615.1	602.6	593.1	584.4
10°	683.5	685.9	685.1	679.8	674.5	663.7	657.5	645.6	629.8	617.4	605.8
12.5°	722.9	725.5	718.3	718.6	708.5	700.0	690.3	675.2	657.1	641.1	626.5
15°	774.3	771.0	771.0	767.0	755.8	744.0	734.0	718.1	695.3	676.1	655.9
17.5°	814.6	815.7	814.1	804.4	795.7	783.4	765.1	746.6	725.4	699.6	679.1
20°	838.7	838.7	836.9	830.3	819.0	805.9	786.2	765.9	739.1	713.2	690.0
22.5°	848.5	849.1	847.0	841.6	831.4	818.6	801.8	781.3	753.5	724.4	695.7
25°	835.1	839.0	839.3	837.9	834.8	827.1	812.6	791.7	766.8	735.2	704.2
27.5°	766.6	771.5	775.8	782.9	792.3	797.1	797.8	787.1	765.4	735.0	703.9
30°	698.5	702.6	715.8	733.1	746.6	758.8	769.5	772.3	760.1	732.8	700.0
32.5°	622.8	628.4	641.7	660.3	682.7	703.4	727.2	739.3	739.0	722.6	692.3
35°	514.3	518.4	530.6	550.2	577.0	607.9	645.6	674.9	694.8	693.4	674.9
37.5°	414.8	419.4	431.7	448.0	474.1	512.1	548.6	589.1	625.9	646.7	640.5
40°	360.7	360.8	372.9	389.6	414.1	447.3	487.0	531.8	573.0	606.7	613.1
42.5°	318.0	318.0	326.0	344.0	361.5	392.8	430.8	475.3	523.5	562.3	579.5
45°	262.9	264.7	271.2	282.0	295.8	322.4	352.8	394.1	448.1	494.1	522.9
47.5°	222.6	225.3	229.5	238.2	249.3	266.9	292.1	329.2	373.2	423.8	464.7
50°	201.7	202.2	207.4	212.3	221.9	236.0	258.0	289.0	329.3	378.0	423.4
52.5°	183.8	183.7	186.9	193.1	200.9	211.8	229.6	257.8	293.6	337.3	384.2
55°	156.9	157.9	160.4	165.2	171.2	178.9	193.0	214.1	242.3	279.6	322.2
57.5°	136.5	137.0	138.9	140.9	146.4	152.1	162.6	177.3	201.0	231.5	271.2
60°	123.0	123.3	123.9	126.9	131.2	136.6	143.7	156.1	176.1	204.0	235.4
62.5°	110.0	110.4	111.3	113.6	116.9	120.5	128.0	138.0	154.5	178.4	206.6
65°	91.7	91.9	93.3	94.1	96.8	100.0	105.6	112.3	123.7	143.7	165.1
67.5°	76.6	76.6	76.7	77.8	79.6	81.8	85.1	90.5	99.1	111.3	130.2
70°	66.8	66.8	67.2	67.8	68.9	70.7	72.6	76.6	82.9	92.9	107.4
72.5°	57.7	57.9	58.3	58.4	58.9	60.4	61.8	64.4	69.1	76.6	88.3
75°	42.4	43.0	44.0	44.9	45.9	45.6	47.1	48.7	50.1	54.6	61.3
77.5°	31.5	31.3	31.3	32.0	32.1	32.4	33.4	34.6	35.7	37.8	40.2
80°	24.0	24.0	24.6	24.9	24.6	24.9	25.9	26.5	26.9	27.7	30.0
82.5°	18.2	18.5	18.3	18.5	18.6	18.9	19.7	19.8	20.2	20.6	21.4
85°	10.2	10.4	10.6	10.2	10.2	10.2	10.6	10.8	11.2	11.0	11.5
87.5°	9.6	9.3	9.4	9.3	9.4	9.0	9.0	9.0	8.4	8.4	7.9
90°	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7	23.3	22.0	20.2
92.5°	44.4	44.2	43.9	43.7	43.3	42.8	42.0	41.2	40.4	39.6	38.4
95°	79.0	79.0	79.0	79.0	79.0	78.7	78.0	77.3	76.7	76.0	74.5
97.5°	123.8	123.8	123.8	123.8	123.8	123.5	122.6	121.8	121.1	120.2	118.4
100°	155.1	155.1	155.1	155.1	155.1	154.8	154.4	153.9	153.5	153.1	151.0
102.5°	190.3	190.1	189.9	189.8	189.5	189.2	188.6	187.9	187.3	186.7	184.9
105°	244.1	243.4	242.7	242.1	241.4	240.7	240.0	239.4	238.8	238.1	237.2
107.5°	296.5	296.5	296.6	296.6	296.7	296.4	295.8	295.2	294.5	293.9	293.8
110°	334.1	333.5	332.8	332.1	331.4	331.3	331.7	332.2	332.7	333.1	333.3



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.6	372.4	372.2	372.1	372.0	372.0	372.0	372.1	372.2	372.3	372.7
115°	432.1	432.4	432.6	432.8	433.0	433.3	433.4	433.7	433.9	434.1	434.5
117.5°	489.0	489.4	489.8	490.3	490.8	491.3	492.1	492.8	493.6	494.4	494.6
120°	532.2	531.8	531.2	530.8	530.4	530.7	531.8	533.0	534.1	535.2	535.8
122.5°	568.2	568.9	569.8	570.6	571.4	572.1	572.9	573.7	574.5	575.1	575.5
125°	630.2	630.6	631.1	631.5	632.0	632.4	632.8	633.3	633.8	634.2	634.4
127.5°	687.6	687.9	688.3	688.7	689.1	689.4	689.9	690.3	690.8	691.2	691.6
130°	725.2	726.1	727.0	727.9	728.8	729.4	729.9	730.3	730.8	731.2	731.2
132.5°	765.3	765.6	765.9	766.3	766.6	767.1	767.5	767.9	768.4	768.9	769.0
135°	820.3	820.9	821.6	822.3	822.9	823.5	823.9	824.4	824.8	825.3	825.3
137.5°	878.0	878.0	877.8	877.7	877.5	877.8	878.3	878.9	879.5	880.0	879.7
140°	913.3	913.5	913.7	914.0	914.2	914.4	914.6	914.8	915.1	915.2	915.2
142.5°	948.5	948.6	948.6	948.6	948.6	948.7	948.7	948.8	948.8	948.9	949.1
145°	996.3	997.0	997.6	998.3	998.9	999.4	999.6	999.9	1000.1	1000.3	1000.1
147.5°	1044.7	1044.9	1045.2	1045.4	1045.6	1045.8	1046.0	1046.2	1046.4	1046.5	1046.7
150°	1074.4	1074.5	1074.8	1075.0	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3
152.5°	1101.6	1102.1	1102.7	1103.3	1103.9	1103.9	1103.4	1102.8	1102.3	1101.7	1101.6
155°	1139.4	1140.2	1141.2	1142.0	1142.9	1142.9	1142.0	1141.2	1140.2	1139.4	1139.5
157.5°	1173.2	1173.9	1174.7	1175.4	1176.2	1176.2	1175.5	1174.9	1174.2	1173.5	1173.6
160°	1192.4	1193.5	1194.6	1195.7	1196.8	1197.0	1196.4	1195.7	1195.1	1194.4	1194.6
162.5°	1212.4	1213.5	1214.6	1215.7	1216.9	1216.8	1215.6	1214.4	1213.1	1211.9	1212.2
165°	1238.4	1239.2	1240.2	1241.0	1241.9	1241.7	1240.4	1239.1	1237.7	1236.4	1236.8
167.5°	1257.0	1258.4	1259.7	1261.1	1262.5	1262.5	1261.2	1259.8	1258.5	1257.1	1257.1
170°	1267.4	1268.9	1270.5	1272.0	1273.6	1273.8	1272.4	1271.1	1269.7	1268.4	1268.2
172.5°	1276.2	1277.7	1279.3	1280.8	1282.5	1282.5	1280.9	1279.4	1277.9	1276.4	1276.3
175°	1285.4	1286.9	1288.5	1290.0	1291.6	1291.6	1290.0	1288.5	1286.9	1285.4	1285.6
177.5°	1290.2	1291.6	1293.0	1294.4	1295.9	1296.0	1294.8	1293.5	1292.3	1291.0	1291.0
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	521.1	518.8	517.6	515.1	512.0	510.3	508.9	506.7	503.9	501.0	498.9
5°	547.5	542.6	536.5	529.2	522.7	516.3	510.8	505.3	499.0	492.5	486.0
7.5°	574.6	565.1	554.7	542.6	531.0	520.3	510.5	501.2	490.6	481.0	472.4
10°	593.6	580.6	566.1	550.8	535.5	522.3	509.2	497.4	484.4	472.8	463.0
12.5°	608.9	593.6	576.2	557.2	538.7	522.7	507.7	492.3	477.5	464.9	451.9
15°	634.3	613.4	590.0	567.1	543.3	521.4	501.3	483.4	466.4	448.7	436.3
17.5°	651.9	626.9	598.4	571.0	542.9	517.1	493.9	472.5	453.0	434.9	420.1
20°	662.3	634.7	603.1	572.0	540.4	512.9	487.8	464.2	444.0	424.5	409.1
22.5°	668.1	637.7	603.1	570.5	537.8	508.0	480.5	455.9	433.9	414.3	397.4
25°	670.0	637.4	602.2	564.6	528.8	497.2	468.6	442.0	417.5	398.0	380.0
27.5°	667.4	629.0	592.9	554.4	517.4	484.1	454.2	426.1	401.7	380.6	362.2
30°	663.5	622.3	583.6	543.6	506.2	474.2	442.6	415.7	390.2	368.4	349.9
32.5°	655.0	614.2	572.5	531.6	493.6	460.6	430.7	403.6	378.7	356.4	336.7
35°	638.2	596.8	551.6	509.6	472.3	438.1	410.0	383.9	360.1	336.2	315.5
37.5°	616.0	573.9	528.8	482.8	445.5	413.2	387.4	362.9	339.7	317.9	294.9
40°	595.2	556.7	510.2	464.6	426.3	395.1	371.3	349.0	325.6	304.0	281.0
42.5°	570.0	537.2	490.2	444.4	406.6	376.5	354.3	332.6	311.3	290.3	266.3
45°	527.8	502.9	458.9	414.9	376.8	347.0	326.7	307.5	288.8	268.8	246.2
47.5°	479.4	462.6	424.6	379.5	344.3	317.5	297.8	282.1	266.3	246.3	226.5
50°	445.8	435.1	398.4	357.2	323.6	298.9	278.8	264.1	250.8	231.7	214.0
52.5°	410.0	404.2	373.2	333.9	301.4	277.2	260.0	246.8	233.4	217.5	201.0
55°	355.3	358.4	332.2	298.1	267.5	247.2	231.5	220.5	209.1	195.6	182.8
57.5°	299.5	310.7	293.1	263.2	234.5	215.7	203.9	194.7	185.0	173.9	162.9
60°	266.1	275.5	265.5	239.2	214.1	196.7	185.6	178.5	168.9	158.8	150.4
62.5°	233.5	243.6	237.6	216.4	193.1	178.1	168.3	161.7	154.5	145.7	137.0
65°	192.6	199.1	196.2	181.6	165.1	152.2	143.3	138.4	131.8	125.4	117.6
67.5°	147.5	160.1	158.4	150.6	136.4	126.3	120.5	116.1	110.2	105.4	100.1
70°	121.2	132.9	132.7	126.3	118.6	109.3	105.1	101.5	96.2	91.5	87.2
72.5°	99.3	109.9	111.5	106.6	101.3	94.2	90.3	87.8	82.7	79.5	75.9
75°	69.5	77.2	79.3	79.3	76.8	73.2	69.7	68.0	64.4	61.6	59.5
77.5°	45.5	50.5	53.6	54.3	54.8	53.5	50.6	49.5	46.7	45.7	43.7
80°	32.2	35.5	39.1	40.4	41.3	41.0	39.8	38.9	36.2	35.2	34.4
82.5°	22.2	24.0	27.0	29.8	29.4	30.6	29.4	28.8	26.8	26.4	25.7
85°	11.6	11.8	12.2	14.0	15.1	15.5	15.7	15.3	14.6	14.6	13.3
87.5°	7.6	7.1	7.1	6.6	6.3	6.5	6.5	6.1	6.1	6.1	6.1
90°	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0	5.4	7.9	10.3
92.5°	37.1	35.9	34.6	32.6	29.8	27.0	24.2	21.4	24.2	27.0	29.8
95°	72.9	71.4	69.8	68.0	66.0	64.1	62.0	60.0	62.0	64.1	66.0
97.5°	116.6	114.8	113.0	111.2	109.6	108.1	106.4	104.9	106.4	108.1	109.6
100°	149.0	147.1	145.1	143.6	142.7	141.8	140.9	140.1	140.9	141.8	142.7
102.5°	183.0	181.2	179.3	178.3	177.9	177.5	177.2	176.8	177.2	177.5	177.9
105°	236.3	235.4	234.5	233.9	233.8	233.5	233.3	233.1	233.3	233.5	233.8
107.5°	293.6	293.5	293.3	293.2	292.9	292.7	292.4	292.1	292.4	292.7	292.9
110°	333.6	333.8	334.0	333.9	333.5	332.9	332.5	332.1	332.5	332.9	333.5





TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	373.2	373.5	373.9	374.1	374.0	373.9	373.8	373.7	373.8	373.9	374.0
115°	435.1	435.5	435.9	436.1	436.1	436.1	436.1	436.1	436.1	436.1	436.1
117.5°	495.0	495.2	495.6	495.7	495.5	495.3	495.2	495.0	495.2	495.3	495.5
120°	536.5	537.2	537.9	537.7	536.8	536.0	535.0	534.2	535.0	536.0	536.8
122.5°	575.8	576.1	576.4	576.4	576.0	575.7	575.3	575.0	575.3	575.7	576.0
125°	634.6	634.9	635.1	635.2	635.2	635.2	635.2	635.2	635.2	635.2	635.2
127.5°	691.9	692.2	692.7	692.5	691.8	691.1	690.5	689.8	690.5	691.1	691.8
130°	731.2	731.2	731.2	730.9	730.2	729.5	728.9	728.2	728.9	729.5	730.2
132.5°	769.2	769.4	769.6	769.4	768.9	768.4	767.9	767.4	767.9	768.4	768.9
135°	825.3	825.3	825.3	824.6	823.3	821.9	820.6	819.2	820.6	821.9	823.3
137.5°	879.3	879.0	878.7	878.1	877.5	876.9	876.3	875.6	876.3	876.9	877.5
140°	915.2	915.2	915.2	915.1	914.6	914.2	913.7	913.3	913.7	914.2	914.6
142.5°	949.3	949.4	949.6	949.5	949.0	948.6	948.1	947.7	948.1	948.6	949.0
145°	999.9	999.6	999.4	998.8	998.0	997.1	996.2	995.3	996.2	997.1	998.0
147.5°	1046.9	1047.1	1047.2	1046.8	1045.7	1044.7	1043.6	1042.5	1043.6	1044.7	1045.7
150°	1075.3	1075.3	1075.3	1074.9	1074.0	1073.2	1072.2	1071.3	1072.2	1073.2	1074.0
152.5°	1101.4	1101.2	1101.0	1100.7	1100.1	1099.6	1099.1	1098.5	1099.1	1099.6	1100.1
155°	1139.8	1140.1	1140.2	1140.3	1140.3	1140.3	1140.3	1140.3	1140.3	1140.3	1140.3
157.5°	1173.6	1173.7	1173.7	1174.0	1174.4	1174.7	1175.2	1175.5	1175.2	1174.7	1174.4
160°	1194.8	1195.1	1195.2	1195.5	1195.7	1195.9	1196.2	1196.4	1196.2	1195.9	1195.7
162.5°	1212.5	1212.6	1212.9	1213.2	1213.8	1214.4	1215.0	1215.6	1215.0	1214.4	1213.8
165°	1237.3	1237.7	1238.1	1238.7	1239.4	1240.0	1240.7	1241.4	1240.7	1240.0	1239.4
167.5°	1257.1	1257.1	1257.0	1257.5	1258.4	1259.3	1260.2	1261.2	1260.2	1259.3	1258.4
170°	1267.9	1267.7	1267.5	1267.9	1269.0	1270.1	1271.3	1272.4	1271.3	1270.1	1269.0
172.5°	1276.3	1276.3	1276.2	1276.7	1277.6	1278.5	1279.4	1280.4	1279.4	1278.5	1277.6
175°	1285.8	1286.1	1286.2	1286.9	1288.1	1289.2	1290.3	1291.4	1290.3	1289.2	1288.1
177.5°	1291.0	1291.0	1291.0	1291.4	1292.4	1293.2	1294.1	1295.0	1294.1	1293.2	1292.4
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	496.6	495.0	492.9	490.4	487.5	484.9	483.7	484.7	485.3	483.9	483.7
5°	481.5	476.4	472.3	466.2	461.3	457.3	454.4	453.1	453.6	450.3	449.5
7.5°	464.5	458.5	451.8	444.5	437.8	431.8	428.7	427.0	423.4	422.0	419.5
10°	453.6	445.5	438.9	430.3	422.6	415.5	412.0	409.1	405.7	404.1	400.6
12.5°	442.4	432.9	425.7	416.8	408.9	400.4	397.0	391.8	386.3	382.9	378.4
15°	426.5	415.1	406.3	395.7	386.3	376.6	367.8	358.0	354.4	346.6	342.2
17.5°	407.9	396.4	385.6	371.3	356.9	344.7	335.4	326.0	320.4	315.5	313.1
20°	395.7	385.1	370.1	353.5	337.4	324.0	316.4	310.3	304.2	300.7	298.3
22.5°	384.2	370.6	353.1	335.3	319.2	308.7	302.3	296.0	291.0	287.7	284.5
25°	364.7	347.0	328.5	308.1	297.1	287.9	281.0	275.9	272.9	268.5	266.9
27.5°	344.8	323.3	302.9	289.2	277.8	269.3	263.3	259.5	255.6	252.9	250.7
30°	329.5	307.7	289.4	276.3	264.7	257.8	252.9	248.4	245.3	243.1	241.5
32.5°	314.4	292.6	277.2	263.1	253.9	247.2	241.9	238.6	236.2	233.3	232.3
35°	292.4	273.0	259.6	246.9	237.6	231.5	227.4	223.9	221.9	221.1	220.5
37.5°	271.3	255.5	241.0	230.7	222.3	217.5	212.7	210.9	209.6	208.1	208.8
40°	258.0	243.1	230.2	219.3	212.5	207.2	204.4	202.3	201.1	201.1	201.1
42.5°	246.4	231.9	219.3	209.5	202.8	198.3	195.1	193.4	193.0	192.8	193.8
45°	228.4	215.0	202.3	194.2	188.5	184.0	182.2	180.7	180.7	181.6	181.8
47.5°	210.6	198.0	187.9	178.7	173.5	170.7	169.1	168.4	168.5	169.3	170.2
50°	199.7	187.3	177.3	169.1	164.3	161.6	160.1	159.7	160.1	160.1	161.6
52.5°	187.8	176.7	166.9	160.0	154.5	152.0	151.2	150.6	150.8	151.5	152.1
55°	170.4	160.4	151.0	144.5	140.4	138.8	136.9	137.2	136.7	137.2	137.2
57.5°	152.8	143.9	135.2	130.0	126.4	124.1	122.1	122.6	122.0	121.9	121.6
60°	141.6	131.8	124.9	120.2	116.1	114.1	112.3	112.7	112.1	111.7	110.8
62.5°	129.4	121.2	114.6	110.1	106.9	104.5	102.6	102.3	100.8	99.4	97.6
65°	111.7	105.0	99.0	94.8	91.7	89.9	88.4	87.2	84.1	80.9	79.3
67.5°	94.5	89.5	84.0	80.4	77.9	75.6	72.8	70.8	67.9	66.1	65.1
70°	83.3	78.7	74.0	70.5	67.8	65.6	62.6	61.1	59.1	58.3	57.3
72.5°	72.8	68.4	64.1	60.9	58.1	56.3	53.9	52.5	51.6	51.2	50.3
75°	56.7	53.2	49.9	47.1	44.9	43.6	42.6	41.6	41.2	39.3	38.3
77.5°	41.3	39.0	37.0	35.0	33.4	32.5	30.6	29.4	28.8	27.9	27.6
80°	32.2	30.6	28.5	27.3	25.1	24.3	23.4	23.2	23.0	22.8	22.6
82.5°	24.2	22.6	20.6	19.8	19.2	18.7	18.3	18.0	17.8	17.9	17.9
85°	12.2	11.5	11.5	11.2	11.0	10.8	10.6	10.6	10.4	10.6	10.4
87.5°	6.6	6.9	7.2	7.3	7.8	8.2	8.3	8.5	9.0	8.9	9.0
90°	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7	26.0	27.4	28.2
92.5°	32.6	34.6	35.9	37.1	38.4	39.6	40.4	41.2	42.0	42.8	43.3
95°	68.0	69.8	71.4	72.9	74.5	76.0	76.7	77.3	78.0	78.7	79.0
97.5°	111.2	113.0	114.8	116.6	118.4	120.2	121.1	121.8	122.6	123.5	123.8
100°	143.6	145.1	147.1	149.0	151.0	153.1	153.5	153.9	154.4	154.8	155.1
102.5°	178.3	179.3	181.2	183.0	184.9	186.7	187.3	187.9	188.6	189.2	189.5
105°	233.9	234.5	235.4	236.3	237.2	238.1	238.8	239.4	240.0	240.7	241.4
107.5°	293.2	293.3	293.5	293.6	293.8	293.9	294.5	295.2	295.8	296.4	296.7
110°	333.9	334.0	333.8	333.6	333.3	333.1	332.7	332.2	331.7	331.3	331.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	374.1	373.9	373.5	373.2	372.7	372.3	372.2	372.1	372.0	372.0	372.0
115°	436.1	435.9	435.5	435.1	434.5	434.1	433.9	433.7	433.4	433.3	433.0
117.5°	495.7	495.6	495.2	495.0	494.6	494.4	493.6	492.8	492.1	491.3	490.8
120°	537.7	537.9	537.2	536.5	535.8	535.2	534.1	533.0	531.8	530.7	530.4
122.5°	576.4	576.4	576.1	575.8	575.5	575.1	574.5	573.7	572.9	572.1	571.4
125°	635.2	635.1	634.9	634.6	634.4	634.2	633.8	633.3	632.8	632.4	632.0
127.5°	692.5	692.7	692.2	691.9	691.6	691.2	690.8	690.3	689.9	689.4	689.1
130°	730.9	731.2	731.2	731.2	731.2	731.2	730.8	730.3	729.9	729.4	728.8
132.5°	769.4	769.6	769.4	769.2	769.0	768.9	768.4	767.9	767.5	767.1	766.6
135°	824.6	825.3	825.3	825.3	825.3	825.3	824.8	824.4	823.9	823.5	822.9
137.5°	878.1	878.7	879.0	879.3	879.7	880.0	879.5	878.9	878.3	877.8	877.5
140°	915.1	915.2	915.2	915.2	915.2	915.2	915.1	914.8	914.6	914.4	914.2
142.5°	949.5	949.6	949.4	949.3	949.1	948.9	948.8	948.8	948.7	948.7	948.6
145°	998.8	999.4	999.6	999.9	1000.1	1000.3	1000.1	999.9	999.6	999.4	998.9
147.5°	1046.8	1047.2	1047.1	1046.9	1046.7	1046.5	1046.4	1046.2	1046.0	1045.8	1045.6
150°	1074.9	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.2
152.5°	1100.7	1101.0	1101.2	1101.4	1101.6	1101.7	1102.3	1102.8	1103.4	1103.9	1103.9
155°	1140.3	1140.2	1140.1	1139.8	1139.5	1139.4	1140.2	1141.2	1142.0	1142.9	1142.9
157.5°	1174.0	1173.7	1173.7	1173.6	1173.6	1173.5	1174.2	1174.9	1175.5	1176.2	1176.2
160°	1195.5	1195.2	1195.1	1194.8	1194.6	1194.4	1195.1	1195.7	1196.4	1197.0	1196.8
162.5°	1213.2	1212.9	1212.6	1212.5	1212.2	1211.9	1213.1	1214.4	1215.6	1216.8	1216.9
165°	1238.7	1238.1	1237.7	1237.3	1236.8	1236.4	1237.7	1239.1	1240.4	1241.7	1241.9
167.5°	1257.5	1257.0	1257.1	1257.1	1257.1	1257.1	1258.5	1259.8	1261.2	1262.5	1262.5
170°	1267.9	1267.5	1267.7	1267.9	1268.2	1268.4	1269.7	1271.1	1272.4	1273.8	1273.6
172.5°	1276.7	1276.2	1276.3	1276.3	1276.3	1276.4	1277.9	1279.4	1280.9	1282.5	1282.5
175°	1286.9	1286.2	1286.1	1285.8	1285.6	1285.4	1286.9	1288.5	1290.0	1291.6	1291.6
177.5°	1291.4	1291.0	1291.0	1291.0	1291.0	1291.0	1292.3	1293.5	1294.8	1296.0	1295.9
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	482.8	483.1	482.0	481.6	482.0	483.1	482.8	483.7	483.9	485.3	484.7
5°	447.9	447.5	446.4	446.7	446.4	447.5	447.9	449.5	450.3	453.6	453.1
7.5°	418.0	416.5	416.9	415.3	416.9	416.5	418.0	419.5	422.0	423.4	427.0
10°	399.8	397.5	395.7	394.1	395.7	397.5	399.8	400.6	404.1	405.7	409.1
12.5°	374.9	372.9	370.5	370.9	370.5	372.9	374.9	378.4	382.9	386.3	391.8
15°	339.5	336.4	331.6	332.2	331.6	336.4	339.5	342.2	346.6	354.4	358.0
17.5°	309.5	309.5	307.3	307.9	307.3	309.5	309.5	313.1	315.5	320.4	326.0
20°	294.0	292.7	292.8	292.2	292.8	292.7	294.0	298.3	300.7	304.2	310.3
22.5°	283.3	281.5	280.1	278.9	280.1	281.5	283.3	284.5	287.7	291.0	296.0
25°	265.1	263.9	262.1	261.7	262.1	263.9	265.1	266.9	268.5	272.9	275.9
27.5°	249.1	248.9	248.1	247.2	248.1	248.9	249.1	250.7	252.9	255.6	259.5
30°	239.9	239.4	239.0	238.4	239.0	239.4	239.9	241.5	243.1	245.3	248.4
32.5°	231.5	231.3	230.8	230.9	230.8	231.3	231.5	232.3	233.3	236.2	238.6
35°	219.6	219.5	219.0	218.9	219.0	219.5	219.6	220.5	221.1	221.9	223.9
37.5°	208.6	209.1	208.9	208.8	208.9	209.1	208.6	208.8	208.1	209.6	210.9
40°	201.0	201.1	201.6	201.3	201.6	201.1	201.0	201.1	201.1	201.1	202.3
42.5°	194.6	194.6	195.2	194.5	195.2	194.6	194.6	193.8	192.8	193.0	193.4
45°	183.2	184.4	184.2	184.2	184.2	184.4	183.2	181.8	181.6	180.7	180.7
47.5°	170.7	171.9	172.1	172.0	172.1	171.9	170.7	170.2	169.3	168.5	168.4
50°	162.6	162.2	162.8	162.6	162.8	162.2	162.6	161.6	160.1	160.1	159.7
52.5°	152.7	152.7	152.7	152.5	152.7	152.7	152.7	152.1	151.5	150.8	150.6
55°	137.3	137.6	137.2	137.3	137.2	137.6	137.3	137.2	137.2	136.7	137.2
57.5°	120.7	119.8	120.1	119.7	120.1	119.8	120.7	121.6	121.9	122.0	122.6
60°	108.8	107.2	106.8	106.0	106.8	107.2	108.8	110.8	111.7	112.1	112.7
62.5°	95.5	94.3	92.9	93.6	92.9	94.3	95.5	97.6	99.4	100.8	102.3
65°	77.7	76.8	76.2	77.1	76.2	76.8	77.7	79.3	80.9	84.1	87.2
67.5°	64.2	63.8	63.8	63.5	63.8	63.8	64.2	65.1	66.1	67.9	70.8
70°	57.3	56.7	56.7	56.2	56.7	56.7	57.3	57.3	58.3	59.1	61.1
72.5°	50.1	49.5	49.7	49.4	49.7	49.5	50.1	50.3	51.2	51.6	52.5
75°	37.1	36.1	36.1	36.2	36.1	36.1	37.1	38.3	39.3	41.2	41.6
77.5°	27.6	27.5	27.7	27.4	27.7	27.5	27.6	27.6	27.9	28.8	29.4
80°	22.6	22.4	22.2	22.8	22.2	22.4	22.6	22.6	22.8	23.0	23.2
82.5°	17.6	17.6	17.5	18.3	17.5	17.6	17.6	17.9	17.9	17.8	18.0
85°	10.6	10.2	10.6	10.2	10.6	10.2	10.6	10.4	10.6	10.4	10.6
87.5°	9.5	9.4	9.3	9.6	9.3	9.4	9.5	9.0	8.9	9.0	8.5
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.4	26.0	24.7
92.5°	43.7	43.9	44.2	44.4	44.2	43.9	43.7	43.3	42.8	42.0	41.2
95°	79.0	79.0	79.0	79.0	79.0	79.0	79.0	79.0	78.7	78.0	77.3
97.5°	123.8	123.8	123.8	123.8	123.8	123.8	123.8	123.8	123.5	122.6	121.8
100°	155.1	155.1	155.1	155.1	155.1	155.1	155.1	155.1	154.8	154.4	153.9
102.5°	189.8	189.9	190.1	190.3	190.1	189.9	189.8	189.5	189.2	188.6	187.9
105°	242.1	242.7	243.4	244.1	243.4	242.7	242.1	241.4	240.7	240.0	239.4
107.5°	296.6	296.6	296.5	296.5	296.5	296.6	296.6	296.7	296.4	295.8	295.2
110°	332.1	332.8	333.5	334.1	333.5	332.8	332.1	331.4	331.3	331.7	332.2



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	372.1	372.2	372.4	372.6	372.4	372.2	372.1	372.0	372.0	372.0	372.1
115°	432.8	432.6	432.4	432.1	432.4	432.6	432.8	433.0	433.3	433.4	433.7
117.5°	490.3	489.8	489.4	489.0	489.4	489.8	490.3	490.8	491.3	492.1	492.8
120°	530.8	531.2	531.8	532.2	531.8	531.2	530.8	530.4	530.7	531.8	533.0
122.5°	570.6	569.8	568.9	568.2	568.9	569.8	570.6	571.4	572.1	572.9	573.7
125°	631.5	631.1	630.6	630.2	630.6	631.1	631.5	632.0	632.4	632.8	633.3
127.5°	688.7	688.3	687.9	687.6	687.9	688.3	688.7	689.1	689.4	689.9	690.3
130°	727.9	727.0	726.1	725.2	726.1	727.0	727.9	728.8	729.4	729.9	730.3
132.5°	766.3	765.9	765.6	765.3	765.6	765.9	766.3	766.6	767.1	767.5	767.9
135°	822.3	821.6	820.9	820.3	820.9	821.6	822.3	822.9	823.5	823.9	824.4
137.5°	877.7	877.8	878.0	878.0	878.0	877.8	877.7	877.5	877.8	878.3	878.9
140°	914.0	913.7	913.5	913.3	913.5	913.7	914.0	914.2	914.4	914.6	914.8
142.5°	948.6	948.6	948.6	948.5	948.6	948.6	948.6	948.6	948.7	948.7	948.8
145°	998.3	997.6	997.0	996.3	997.0	997.6	998.3	998.9	999.4	999.6	999.9
147.5°	1045.4	1045.2	1044.9	1044.7	1044.9	1045.2	1045.4	1045.6	1045.8	1046.0	1046.2
150°	1075.0	1074.8	1074.5	1074.4	1074.5	1074.8	1075.0	1075.2	1075.3	1075.3	1075.3
152.5°	1103.3	1102.7	1102.1	1101.6	1102.1	1102.7	1103.3	1103.9	1103.9	1103.4	1102.8
155°	1142.0	1141.2	1140.2	1139.4	1140.2	1141.2	1142.0	1142.9	1142.9	1142.0	1141.2
157.5°	1175.4	1174.7	1173.9	1173.2	1173.9	1174.7	1175.4	1176.2	1176.2	1175.5	1174.9
160°	1195.7	1194.6	1193.5	1192.4	1193.5	1194.6	1195.7	1196.8	1197.0	1196.4	1195.7
162.5°	1215.7	1214.6	1213.5	1212.4	1213.5	1214.6	1215.7	1216.9	1216.8	1215.6	1214.4
165°	1241.0	1240.2	1239.2	1238.4	1239.2	1240.2	1241.0	1241.9	1241.7	1240.4	1239.1
167.5°	1261.1	1259.7	1258.4	1257.0	1258.4	1259.7	1261.1	1262.5	1262.5	1261.2	1259.8
170°	1272.0	1270.5	1268.9	1267.4	1268.9	1270.5	1272.0	1273.6	1273.8	1272.4	1271.1
172.5°	1280.8	1279.3	1277.7	1276.2	1277.7	1279.3	1280.8	1282.5	1282.5	1280.9	1279.4
175°	1290.0	1288.5	1286.9	1285.4	1286.9	1288.5	1290.0	1291.6	1291.6	1290.0	1288.5
177.5°	1294.4	1293.0	1291.6	1290.2	1291.6	1293.0	1294.4	1295.9	1296.0	1294.8	1293.5
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	483.7	484.9	487.5	490.4	492.9	495.0	496.6	498.9	501.0	503.9	506.7
5°	454.4	457.3	461.3	466.2	472.3	476.4	481.5	486.0	492.5	499.0	505.3
7.5°	428.7	431.8	437.8	444.5	451.8	458.5	464.5	472.4	481.0	490.6	501.2
10°	412.0	415.5	422.6	430.3	438.9	445.5	453.6	463.0	472.8	484.4	497.4
12.5°	397.0	400.4	408.9	416.8	425.7	432.9	442.4	451.9	464.9	477.5	492.3
15°	367.8	376.6	386.3	395.7	406.3	415.1	426.5	436.3	448.7	466.4	483.4
17.5°	335.4	344.7	356.9	371.3	385.6	396.4	407.9	420.1	434.9	453.0	472.5
20°	316.4	324.0	337.4	353.5	370.1	385.1	395.7	409.1	424.5	444.0	464.2
22.5°	302.3	308.7	319.2	335.3	353.1	370.6	384.2	397.4	414.3	433.9	455.9
25°	281.0	287.9	297.1	308.1	328.5	347.0	364.7	380.0	398.0	417.5	442.0
27.5°	263.3	269.3	277.8	289.2	302.9	323.3	344.8	362.2	380.6	401.7	426.1
30°	252.9	257.8	264.7	276.3	289.4	307.7	329.5	349.9	368.4	390.2	415.7
32.5°	241.9	247.2	253.9	263.1	277.2	292.6	314.4	336.7	356.4	378.7	403.6
35°	227.4	231.5	237.6	246.9	259.6	273.0	292.4	315.5	336.2	360.1	383.9
37.5°	212.7	217.5	222.3	230.7	241.0	255.5	271.3	294.9	317.9	339.7	362.9
40°	204.4	207.2	212.5	219.3	230.2	243.1	258.0	281.0	304.0	325.6	349.0
42.5°	195.1	198.3	202.8	209.5	219.3	231.9	246.4	266.3	290.3	311.3	332.6
45°	182.2	184.0	188.5	194.2	202.3	215.0	228.4	246.2	268.8	288.8	307.5
47.5°	169.1	170.7	173.5	178.7	187.9	198.0	210.6	226.5	246.3	266.3	282.1
50°	160.1	161.6	164.3	169.1	177.3	187.3	199.7	214.0	231.7	250.8	264.1
52.5°	151.2	152.0	154.5	160.0	166.9	176.7	187.8	201.0	217.5	233.4	246.8
55°	136.9	138.8	140.4	144.5	151.0	160.4	170.4	182.8	195.6	209.1	220.5
57.5°	122.1	124.1	126.4	130.0	135.2	143.9	152.8	162.9	173.9	185.0	194.7
60°	112.3	114.1	116.1	120.2	124.9	131.8	141.6	150.4	158.8	168.9	178.5
62.5°	102.6	104.5	106.9	110.1	114.6	121.2	129.4	137.0	145.7	154.5	161.7
65°	88.4	89.9	91.7	94.8	99.0	105.0	111.7	117.6	125.4	131.8	138.4
67.5°	72.8	75.6	77.9	80.4	84.0	89.5	94.5	100.1	105.4	110.2	116.1
70°	62.6	65.6	67.8	70.5	74.0	78.7	83.3	87.2	91.5	96.2	101.5
72.5°	53.9	56.3	58.1	60.9	64.1	68.4	72.8	75.9	79.5	82.7	87.8
75°	42.6	43.6	44.9	47.1	49.9	53.2	56.7	59.5	61.6	64.4	68.0
77.5°	30.6	32.5	33.4	35.0	37.0	39.0	41.3	43.7	45.7	46.7	49.5
80°	23.4	24.3	25.1	27.3	28.5	30.6	32.2	34.4	35.2	36.2	38.9
82.5°	18.3	18.7	19.2	19.8	20.6	22.6	24.2	25.7	26.4	26.8	28.8
85°	10.6	10.8	11.0	11.2	11.5	11.5	12.2	13.3	14.6	14.6	15.3
87.5°	8.3	8.2	7.8	7.3	7.2	6.9	6.6	6.1	6.1	6.1	6.1
90°	23.3	22.0	20.2	18.4	16.7	14.9	12.7	10.3	7.9	5.4	3.0
92.5°	40.4	39.6	38.4	37.1	35.9	34.6	32.6	29.8	27.0	24.2	21.4
95°	76.7	76.0	74.5	72.9	71.4	69.8	68.0	66.0	64.1	62.0	60.0
97.5°	121.1	120.2	118.4	116.6	114.8	113.0	111.2	109.6	108.1	106.4	104.9
100°	153.5	153.1	151.0	149.0	147.1	145.1	143.6	142.7	141.8	140.9	140.1
102.5°	187.3	186.7	184.9	183.0	181.2	179.3	178.3	177.9	177.5	177.2	176.8
105°	238.8	238.1	237.2	236.3	235.4	234.5	233.9	233.8	233.5	233.3	233.1
107.5°	294.5	293.9	293.8	293.6	293.5	293.3	293.2	292.9	292.7	292.4	292.1
110°	332.7	333.1	333.3	333.6	333.8	334.0	333.9	333.5	332.9	332.5	332.1



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	372.2	372.3	372.7	373.2	373.5	373.9	374.1	374.0	373.9	373.8	373.7
115°	433.9	434.1	434.5	435.1	435.5	435.9	436.1	436.1	436.1	436.1	436.1
117.5°	493.6	494.4	494.6	495.0	495.2	495.6	495.7	495.5	495.3	495.2	495.0
120°	534.1	535.2	535.8	536.5	537.2	537.9	537.7	536.8	536.0	535.0	534.2
122.5°	574.5	575.1	575.5	575.8	576.1	576.4	576.4	576.0	575.7	575.3	575.0
125°	633.8	634.2	634.4	634.6	634.9	635.1	635.2	635.2	635.2	635.2	635.2
127.5°	690.8	691.2	691.6	691.9	692.2	692.7	692.5	691.8	691.1	690.5	689.8
130°	730.8	731.2	731.2	731.2	731.2	731.2	730.9	730.2	729.5	728.9	728.2
132.5°	768.4	768.9	769.0	769.2	769.4	769.6	769.4	768.9	768.4	767.9	767.4
135°	824.8	825.3	825.3	825.3	825.3	825.3	824.6	823.3	821.9	820.6	819.2
137.5°	879.5	880.0	879.7	879.3	879.0	878.7	878.1	877.5	876.9	876.3	875.6
140°	915.1	915.2	915.2	915.2	915.2	915.2	915.1	914.6	914.2	913.7	913.3
142.5°	948.8	948.9	949.1	949.3	949.4	949.6	949.5	949.0	948.6	948.1	947.7
145°	1000.1	1000.3	1000.1	999.9	999.6	999.4	998.8	998.0	997.1	996.2	995.3
147.5°	1046.4	1046.5	1046.7	1046.9	1047.1	1047.2	1046.8	1045.7	1044.7	1043.6	1042.5
150°	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1074.9	1074.0	1073.2	1072.2	1071.3
152.5°	1102.3	1101.7	1101.6	1101.4	1101.2	1101.0	1100.7	1100.1	1099.6	1099.1	1098.5
155°	1140.2	1139.4	1139.5	1139.8	1140.1	1140.2	1140.3	1140.3	1140.3	1140.3	1140.3
157.5°	1174.2	1173.5	1173.6	1173.6	1173.7	1173.7	1174.0	1174.4	1174.7	1175.2	1175.5
160°	1195.1	1194.4	1194.6	1194.8	1195.1	1195.2	1195.5	1195.7	1195.9	1196.2	1196.4
162.5°	1213.1	1211.9	1212.2	1212.5	1212.6	1212.9	1213.2	1213.8	1214.4	1215.0	1215.6
165°	1237.7	1236.4	1236.8	1237.3	1237.7	1238.1	1238.7	1239.4	1240.0	1240.7	1241.4
167.5°	1258.5	1257.1	1257.1	1257.1	1257.1	1257.0	1257.5	1258.4	1259.3	1260.2	1261.2
170°	1269.7	1268.4	1268.2	1267.9	1267.7	1267.5	1267.9	1269.0	1270.1	1271.3	1272.4
172.5°	1277.9	1276.4	1276.3	1276.3	1276.3	1276.2	1276.7	1277.6	1278.5	1279.4	1280.4
175°	1286.9	1285.4	1285.6	1285.8	1286.1	1286.2	1286.9	1288.1	1289.2	1290.3	1291.4
177.5°	1292.3	1291.0	1291.0	1291.0	1291.0	1291.0	1291.4	1292.4	1293.2	1294.1	1295.0
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	508.9	510.3	512.0	515.1	517.6	518.8	521.1	522.7	522.2	524.5	528.4
5°	510.8	516.3	522.7	529.2	536.5	542.6	547.5	552.4	556.3	560.9	567.9
7.5°	510.5	520.3	531.0	542.6	554.7	565.1	574.6	584.4	593.1	602.6	615.1
10°	509.2	522.3	535.5	550.8	566.1	580.6	593.6	605.8	617.4	629.8	645.6
12.5°	507.7	522.7	538.7	557.2	576.2	593.6	608.9	626.5	641.1	657.1	675.2
15°	501.3	521.4	543.3	567.1	590.0	613.4	634.3	655.9	676.1	695.3	718.1
17.5°	493.9	517.1	542.9	571.0	598.4	626.9	651.9	679.1	699.6	725.4	746.6
20°	487.8	512.9	540.4	572.0	603.1	634.7	662.3	690.0	713.2	739.1	765.9
22.5°	480.5	508.0	537.8	570.5	603.1	637.7	668.1	695.7	724.4	753.5	781.3
25°	468.6	497.2	528.8	564.6	602.2	637.4	670.0	704.2	735.2	766.8	791.7
27.5°	454.2	484.1	517.4	554.4	592.9	629.0	667.4	703.9	735.0	765.4	787.1
30°	442.6	474.2	506.2	543.6	583.6	622.3	663.5	700.0	732.8	760.1	772.3
32.5°	430.7	460.6	493.6	531.6	572.5	614.2	655.0	692.3	722.6	739.0	739.3
35°	410.0	438.1	472.3	509.6	551.6	596.8	638.2	674.9	693.4	694.8	674.9
37.5°	387.4	413.2	445.5	482.8	528.8	573.9	616.0	640.5	646.7	625.9	589.1
40°	371.3	395.1	426.3	464.6	510.2	556.7	595.2	613.1	606.7	573.0	531.8
42.5°	354.3	376.5	406.6	444.4	490.2	537.2	570.0	579.5	562.3	523.5	475.3
45°	326.7	347.0	376.8	414.9	458.9	502.9	527.8	522.9	494.1	448.1	394.1
47.5°	297.8	317.5	344.3	379.5	424.6	462.6	479.4	464.7	423.8	373.2	329.2
50°	278.8	298.9	323.6	357.2	398.4	435.1	445.8	423.4	378.0	329.3	289.0
52.5°	260.0	277.2	301.4	333.9	373.2	404.2	410.0	384.2	337.3	293.6	257.8
55°	231.5	247.2	267.5	298.1	332.2	358.4	355.3	322.2	279.6	242.3	214.1
57.5°	203.9	215.7	234.5	263.2	293.1	310.7	299.5	271.2	231.5	201.0	177.3
60°	185.6	196.7	214.1	239.2	265.5	275.5	266.1	235.4	204.0	176.1	156.1
62.5°	168.3	178.1	193.1	216.4	237.6	243.6	233.5	206.6	178.4	154.5	138.0
65°	143.3	152.2	165.1	181.6	196.2	199.1	192.6	165.1	143.7	123.7	112.3
67.5°	120.5	126.3	136.4	150.6	158.4	160.1	147.5	130.2	111.3	99.1	90.5
70°	105.1	109.3	118.6	126.3	132.7	132.9	121.2	107.4	92.9	82.9	76.6
72.5°	90.3	94.2	101.3	106.6	111.5	109.9	99.3	88.3	76.6	69.1	64.4
75°	69.7	73.2	76.8	79.3	79.3	77.2	69.5	61.3	54.6	50.1	48.7
77.5°	50.6	53.5	54.8	54.3	53.6	50.5	45.5	40.2	37.8	35.7	34.6
80°	39.8	41.0	41.3	40.4	39.1	35.5	32.2	30.0	27.7	26.9	26.5
82.5°	29.4	30.6	29.4	29.8	27.0	24.0	22.2	21.4	20.6	20.2	19.8
85°	15.7	15.5	15.1	14.0	12.2	11.8	11.6	11.5	11.0	11.2	10.8
87.5°	6.5	6.5	6.3	6.6	7.1	7.1	7.6	7.9	8.4	8.4	9.0
90°	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3	24.7
92.5°	24.2	27.0	29.8	32.6	34.6	35.9	37.1	38.4	39.6	40.4	41.2
95°	62.0	64.1	66.0	68.0	69.8	71.4	72.9	74.5	76.0	76.7	77.3
97.5°	106.4	108.1	109.6	111.2	113.0	114.8	116.6	118.4	120.2	121.1	121.8
100°	140.9	141.8	142.7	143.6	145.1	147.1	149.0	151.0	153.1	153.5	153.9
102.5°	177.2	177.5	177.9	178.3	179.3	181.2	183.0	184.9	186.7	187.3	187.9
105°	233.3	233.5	233.8	233.9	234.5	235.4	236.3	237.2	238.1	238.8	239.4
107.5°	292.4	292.7	292.9	293.2	293.3	293.5	293.6	293.8	293.9	294.5	295.2
110°	332.5	332.9	333.5	333.9	334.0	333.8	333.6	333.3	333.1	332.7	332.2





TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	373.8	373.9	374.0	374.1	373.9	373.5	373.2	372.7	372.3	372.2	372.1
115°	436.1	436.1	436.1	436.1	435.9	435.5	435.1	434.5	434.1	433.9	433.7
117.5°	495.2	495.3	495.5	495.7	495.6	495.2	495.0	494.6	494.4	493.6	492.8
120°	535.0	536.0	536.8	537.7	537.9	537.2	536.5	535.8	535.2	534.1	533.0
122.5°	575.3	575.7	576.0	576.4	576.4	576.1	575.8	575.5	575.1	574.5	573.7
125°	635.2	635.2	635.2	635.2	635.1	634.9	634.6	634.4	634.2	633.8	633.3
127.5°	690.5	691.1	691.8	692.5	692.7	692.2	691.9	691.6	691.2	690.8	690.3
130°	728.9	729.5	730.2	730.9	731.2	731.2	731.2	731.2	731.2	730.8	730.3
132.5°	767.9	768.4	768.9	769.4	769.6	769.4	769.2	769.0	768.9	768.4	767.9
135°	820.6	821.9	823.3	824.6	825.3	825.3	825.3	825.3	825.3	824.8	824.4
137.5°	876.3	876.9	877.5	878.1	878.7	879.0	879.3	879.7	880.0	879.5	878.9
140°	913.7	914.2	914.6	915.1	915.2	915.2	915.2	915.2	915.2	915.1	914.8
142.5°	948.1	948.6	949.0	949.5	949.6	949.4	949.3	949.1	948.9	948.8	948.8
145°	996.2	997.1	998.0	998.8	999.4	999.6	999.9	1000.1	1000.3	1000.1	999.9
147.5°	1043.6	1044.7	1045.7	1046.8	1047.2	1047.1	1046.9	1046.7	1046.5	1046.4	1046.2
150°	1072.2	1073.2	1074.0	1074.9	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3	1075.3
152.5°	1099.1	1099.6	1100.1	1100.7	1101.0	1101.2	1101.4	1101.6	1101.7	1102.3	1102.8
155°	1140.3	1140.3	1140.3	1140.3	1140.2	1140.1	1139.8	1139.5	1139.4	1140.2	1141.2
157.5°	1175.2	1174.7	1174.4	1174.0	1173.7	1173.7	1173.6	1173.6	1173.5	1174.2	1174.9
160°	1196.2	1195.9	1195.7	1195.5	1195.2	1195.1	1194.8	1194.6	1194.4	1195.1	1195.7
162.5°	1215.0	1214.4	1213.8	1213.2	1212.9	1212.6	1212.5	1212.2	1211.9	1213.1	1214.4
165°	1240.7	1240.0	1239.4	1238.7	1238.1	1237.7	1237.3	1236.8	1236.4	1237.7	1239.1
167.5°	1260.2	1259.3	1258.4	1257.5	1257.0	1257.1	1257.1	1257.1	1257.1	1258.5	1259.8
170°	1271.3	1270.1	1269.0	1267.9	1267.5	1267.7	1267.9	1268.2	1268.4	1269.7	1271.1
172.5°	1279.4	1278.5	1277.6	1276.7	1276.2	1276.3	1276.3	1276.3	1276.4	1277.9	1279.4
175°	1290.3	1289.2	1288.1	1286.9	1286.2	1286.1	1285.8	1285.6	1285.4	1286.9	1288.5
177.5°	1294.1	1293.2	1292.4	1291.4	1291.0	1291.0	1291.0	1291.0	1291.0	1292.3	1293.5
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	505.8	505.8	505.8	505.8	505.8	505.8	505.8
2.5°	530.5	531.2	531.7	533.3	533.5	534.9	533.5
5°	574.5	577.3	581.8	586.3	586.7	589.5	584.4
7.5°	623.6	630.3	634.4	641.6	644.5	646.3	643.3
10°	657.5	663.7	674.5	679.8	685.1	685.9	683.5
12.5°	690.3	700.0	708.5	718.6	718.3	725.5	722.9
15°	734.0	744.0	755.8	767.0	771.0	771.0	774.3
17.5°	765.1	783.4	795.7	804.4	814.1	815.7	814.6
20°	786.2	805.9	819.0	830.3	836.9	838.7	838.7
22.5°	801.8	818.6	831.4	841.6	847.0	849.1	848.5
25°	812.6	827.1	834.8	837.9	839.3	839.0	835.1
27.5°	797.8	797.1	792.3	782.9	775.8	771.5	766.6
30°	769.5	758.8	746.6	733.1	715.8	702.6	698.5
32.5°	727.2	703.4	682.7	660.3	641.7	628.4	622.8
35°	645.6	607.9	577.0	550.2	530.6	518.4	514.3
37.5°	548.6	512.1	474.1	448.0	431.7	419.4	414.8
40°	487.0	447.3	414.1	389.6	372.9	360.8	360.7
42.5°	430.8	392.8	361.5	344.0	326.0	318.0	318.0
45°	352.8	322.4	295.8	282.0	271.2	264.7	262.9
47.5°	292.1	266.9	249.3	238.2	229.5	225.3	222.6
50°	258.0	236.0	221.9	212.3	207.4	202.2	201.7
52.5°	229.6	211.8	200.9	193.1	186.9	183.7	183.8
55°	193.0	178.9	171.2	165.2	160.4	157.9	156.9
57.5°	162.6	152.1	146.4	140.9	138.9	137.0	136.5
60°	143.7	136.6	131.2	126.9	123.9	123.3	123.0
62.5°	128.0	120.5	116.9	113.6	111.3	110.4	110.0
65°	105.6	100.0	96.8	94.1	93.3	91.9	91.7
67.5°	85.1	81.8	79.6	77.8	76.7	76.6	76.6
70°	72.6	70.7	68.9	67.8	67.2	66.8	66.8
72.5°	61.8	60.4	58.9	58.4	58.3	57.9	57.7
75°	47.1	45.6	45.9	44.9	44.0	43.0	42.4
77.5°	33.4	32.4	32.1	32.0	31.3	31.3	31.5
80°	25.9	24.9	24.6	24.9	24.6	24.0	24.0
82.5°	19.7	18.9	18.6	18.5	18.3	18.5	18.2
85°	10.6	10.2	10.2	10.2	10.6	10.4	10.2
87.5°	9.0	9.0	9.4	9.3	9.4	9.3	9.6
90°	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	42.0	42.8	43.3	43.7	43.9	44.2	44.4
95°	78.0	78.7	79.0	79.0	79.0	79.0	79.0
97.5°	122.6	123.5	123.8	123.8	123.8	123.8	123.8
100°	154.4	154.8	155.1	155.1	155.1	155.1	155.1
102.5°	188.6	189.2	189.5	189.8	189.9	190.1	190.3
105°	240.0	240.7	241.4	242.1	242.7	243.4	244.1
107.5°	295.8	296.4	296.7	296.6	296.6	296.5	296.5
110°	331.7	331.3	331.4	332.1	332.8	333.5	334.1



TEST NUMBER: P332890-935

CATALOG NUMBER: SA4XXRDIP-C350D1205U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.0	372.0	372.0	372.1	372.2	372.4	372.6
115°	433.4	433.3	433.0	432.8	432.6	432.4	432.1
117.5°	492.1	491.3	490.8	490.3	489.8	489.4	489.0
120°	531.8	530.7	530.4	530.8	531.2	531.8	532.2
122.5°	572.9	572.1	571.4	570.6	569.8	568.9	568.2
125°	632.8	632.4	632.0	631.5	631.1	630.6	630.2
127.5°	689.9	689.4	689.1	688.7	688.3	687.9	687.6
130°	729.9	729.4	728.8	727.9	727.0	726.1	725.2
132.5°	767.5	767.1	766.6	766.3	765.9	765.6	765.3
135°	823.9	823.5	822.9	822.3	821.6	820.9	820.3
137.5°	878.3	877.8	877.5	877.7	877.8	878.0	878.0
140°	914.6	914.4	914.2	914.0	913.7	913.5	913.3
142.5°	948.7	948.7	948.6	948.6	948.6	948.6	948.5
145°	999.6	999.4	998.9	998.3	997.6	997.0	996.3
147.5°	1046.0	1045.8	1045.6	1045.4	1045.2	1044.9	1044.7
150°	1075.3	1075.3	1075.2	1075.0	1074.8	1074.5	1074.4
152.5°	1103.4	1103.9	1103.9	1103.3	1102.7	1102.1	1101.6
155°	1142.0	1142.9	1142.9	1142.0	1141.2	1140.2	1139.4
157.5°	1175.5	1176.2	1176.2	1175.4	1174.7	1173.9	1173.2
160°	1196.4	1197.0	1196.8	1195.7	1194.6	1193.5	1192.4
162.5°	1215.6	1216.8	1216.9	1215.7	1214.6	1213.5	1212.4
165°	1240.4	1241.7	1241.9	1241.0	1240.2	1239.2	1238.4
167.5°	1261.2	1262.5	1262.5	1261.1	1259.7	1258.4	1257.0
170°	1272.4	1273.8	1273.6	1272.0	1270.5	1268.9	1267.4
172.5°	1280.9	1282.5	1282.5	1280.8	1279.3	1277.7	1276.2
175°	1290.0	1291.6	1291.6	1290.0	1288.5	1286.9	1285.4
177.5°	1294.8	1296.0	1295.9	1294.4	1293.0	1291.6	1290.2
180°	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4	1293.4

(END OF REPORT)