

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332869-935

Luminaire Tested: **SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332869-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2322.3 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	2.2
10°-20°	139.4	6.0
20°-30°	201.3	8.7
30°-40°	228.2	9.8
40°-50°	220.4	9.5
50°-60°	183.2	7.9
60°-70°	126.5	5.4
70°-80°	64.1	2.8
80°-90°	17.6	0.8
90°-100°	25.9	1.1
100°-110°	76.9	3.3
110°-120°	130.5	5.6
120°-130°	172.0	7.4
130°-140°	193.2	8.3
140°-150°	189.8	8.2
150°-160°	159.7	6.9
160°-170°	106.2	4.6
170°-180°	37.2	1.6
0°-30°	390.7	16.8
0°-40°	619.0	26.7
0°-60°	1022.6	44.0
0°-90°	1230.9	53.0
90°-120°	233.3	10.0
90°-150°	788.3	33.9
90°-180°	1091.0	47.0
0°-180°	2322.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	1	4	7	8	9	2
95°	18	21	23	24	24	20
105°	71	71	72	73	74	75
115°	133	133	132	132	132	131
125°	193	193	193	192	192	172
135°	249	251	251	250	250	193
145°	303	304	304	304	303	189
155°	347	347	347	348	347	160
165°	378	377	376	378	377	106
175°	393	391	391	393	391	37
180°	393	393	393	393	393	



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.7	7.2	6.8	6.4	5.9	5.8	5.8	5.9	5.9	5.9	5.9
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	6.5	7.4	8.2	9.0	9.9	10.5	10.9	11.3	11.7	12.1	12.3
95°	18.3	18.9	19.5	20.1	20.7	21.3	21.7	22.2	22.6	23.2	23.3
97.5°	31.9	32.4	32.9	33.3	33.8	34.4	34.9	35.5	36.0	36.6	36.9
100°	42.6	42.9	43.1	43.4	43.7	44.1	44.7	45.4	46.0	46.6	46.7
102.5°	53.8	53.9	54.0	54.2	54.2	54.6	55.1	55.7	56.2	56.7	57.0
105°	70.9	70.9	71.0	71.1	71.1	71.3	71.6	71.9	72.2	72.4	72.6
107.5°	88.9	88.9	89.0	89.1	89.2	89.2	89.3	89.3	89.4	89.4	89.5
110°	101.0	101.2	101.3	101.4	101.5	101.6	101.5	101.4	101.3	101.3	101.2



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.5	113.4	113.2	113.2
115°	132.7	132.7	132.7	132.7	132.7	132.6	132.4	132.3	132.2	132.1	132.0
117.5°	150.5	150.6	150.7	150.7	150.8	150.8	150.7	150.6	150.4	150.3	150.2
120°	162.5	162.7	163.0	163.2	163.6	163.6	163.4	163.2	163.0	162.8	162.5
122.5°	174.9	175.0	175.1	175.2	175.3	175.3	175.2	175.1	175.0	175.0	174.7
125°	193.2	193.2	193.2	193.2	193.2	193.1	193.1	193.0	193.0	192.9	192.8
127.5°	209.8	210.0	210.3	210.4	210.6	210.7	210.6	210.4	210.3	210.3	210.1
130°	221.5	221.7	221.9	222.1	222.3	222.4	222.4	222.4	222.4	222.4	222.3
132.5°	233.4	233.6	233.7	233.8	234.0	234.0	234.0	233.9	233.9	233.8	233.7
135°	249.2	249.6	249.9	250.4	250.8	251.0	251.0	251.0	251.0	251.0	250.9
137.5°	266.3	266.6	266.7	266.9	267.1	267.3	267.3	267.4	267.6	267.7	267.5
140°	277.8	277.9	278.0	278.2	278.4	278.4	278.4	278.4	278.4	278.4	278.4
142.5°	288.3	288.3	288.5	288.6	288.8	288.9	288.8	288.7	288.7	288.6	288.6
145°	302.7	303.0	303.2	303.5	303.8	304.0	304.0	304.1	304.2	304.3	304.2
147.5°	317.1	317.5	317.7	318.1	318.4	318.5	318.5	318.4	318.4	318.3	318.2
150°	325.9	326.1	326.4	326.7	326.9	327.1	327.1	327.1	327.1	327.1	327.1
152.5°	334.2	334.3	334.4	334.6	334.8	334.8	334.9	335.0	335.0	335.1	335.3
155°	346.8	346.8	346.8	346.8	346.8	346.8	346.7	346.6	346.6	346.6	346.8
157.5°	357.6	357.4	357.3	357.2	357.1	357.0	357.0	357.0	357.0	357.0	357.1
160°	363.9	363.8	363.8	363.7	363.6	363.5	363.5	363.4	363.3	363.3	363.5
162.5°	369.7	369.5	369.4	369.2	369.0	368.9	368.9	368.8	368.7	368.6	369.0
165°	377.5	377.4	377.2	376.9	376.8	376.6	376.4	376.3	376.2	376.1	376.4
167.5°	383.6	383.3	383.1	382.7	382.5	382.3	382.4	382.4	382.4	382.4	382.8
170°	387.0	386.7	386.3	386.0	385.6	385.6	385.6	385.6	385.7	385.8	386.2
172.5°	389.4	389.2	388.8	388.6	388.3	388.1	388.1	388.2	388.2	388.2	388.7
175°	392.8	392.4	392.1	391.8	391.4	391.2	391.2	391.1	391.1	391.0	391.4
177.5°	393.9	393.6	393.3	393.0	392.8	392.7	392.7	392.7	392.7	392.7	393.0
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	5.9	5.9	5.9	6.0	6.1	6.2	6.3	6.4
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.6	12.7	13.0	13.2	13.3	13.3	13.4	13.5
95°	23.5	23.8	23.9	24.0	24.0	24.0	24.0	24.0
97.5°	37.0	37.3	37.5	37.6	37.6	37.6	37.6	37.6
100°	46.8	46.9	47.1	47.2	47.2	47.2	47.2	47.2
102.5°	57.2	57.3	57.5	57.7	57.7	57.8	57.8	57.9
105°	72.8	73.0	73.2	73.4	73.6	73.9	74.0	74.2
107.5°	89.8	90.0	90.1	90.2	90.2	90.2	90.2	90.1
110°	101.1	100.9	100.7	100.8	101.0	101.3	101.4	101.6



TEST NUMBER: P332869-935

CATALOG NUMBER: SA4XXRDIP-C350D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	113.2	113.1	113.1	113.1	113.2	113.2	113.2	113.3
115°	131.9	131.8	131.7	131.7	131.6	131.6	131.5	131.5
117.5°	149.9	149.6	149.5	149.3	149.1	149.0	148.9	148.7
120°	162.1	161.8	161.4	161.4	161.4	161.6	161.7	161.9
122.5°	174.5	174.3	174.0	173.7	173.6	173.3	173.1	172.8
125°	192.6	192.5	192.3	192.2	192.1	191.9	191.8	191.7
127.5°	210.0	209.8	209.7	209.6	209.5	209.4	209.2	209.1
130°	222.1	222.0	221.9	221.6	221.4	221.1	220.8	220.6
132.5°	233.6	233.4	233.3	233.2	233.1	233.0	232.9	232.7
135°	250.7	250.6	250.5	250.3	250.1	249.9	249.7	249.5
137.5°	267.3	267.2	267.0	266.9	266.9	267.0	267.0	267.1
140°	278.3	278.2	278.1	278.0	278.0	277.9	277.8	277.8
142.5°	288.6	288.6	288.5	288.5	288.5	288.5	288.5	288.5
145°	304.1	304.0	304.0	303.8	303.7	303.4	303.2	303.1
147.5°	318.2	318.1	318.1	318.1	318.0	317.9	317.8	317.8
150°	327.1	327.1	327.1	327.0	327.0	326.9	326.8	326.7
152.5°	335.4	335.6	335.8	335.7	335.5	335.4	335.2	335.0
155°	347.1	347.3	347.6	347.6	347.3	347.1	346.8	346.6
157.5°	357.3	357.6	357.7	357.7	357.5	357.3	357.1	356.8
160°	363.7	363.9	364.1	364.0	363.7	363.3	363.0	362.7
162.5°	369.4	369.7	370.1	370.1	369.8	369.5	369.1	368.8
165°	376.9	377.3	377.6	377.7	377.5	377.2	376.9	376.7
167.5°	383.2	383.6	384.0	384.0	383.6	383.1	382.7	382.3
170°	386.6	387.0	387.4	387.4	386.9	386.4	386.0	385.5
172.5°	389.2	389.6	390.0	390.0	389.6	389.1	388.7	388.1
175°	391.9	392.4	392.9	392.9	392.4	391.9	391.4	391.0
177.5°	393.4	393.8	394.2	394.2	393.7	393.3	392.9	392.4
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4

(END OF REPORT)