

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904937

Luminaire Tested: DFN2DIP-4P3F0-030D050US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904937
REPORT IS A COMBINATION OF REPORTS P900582 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D050US835-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7500.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 64.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1413	1413	1413
5°	1414	1390	1399
10°	1399	1361	1353
15°	1379	1316	1282
20°	1353	1253	1196
25°	1326	1182	1112
30°	1290	1110	1006
35°	1255	1033	913
40°	1219	953	806
45°	1177	865	709
50°	1134	775	615
55°	1088	680	524
60°	1036	580	431
65°	976	479	387
70°	903	385	350
75°	810	337	317
80°	678	280	274
85°	459	183	203

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1177 cd/sqm

TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.5
10°-20°	319.0	4.3
20°-30°	447.9	6.0
30°-40°	488.2	6.5
40°-50°	448.7	6.0
50°-60°	352.4	4.7
60°-70°	229.4	3.1
70°-80°	118.1	1.6
80°-90°	33.1	0.4
90°-100°	55.7	0.7
100°-110°	207.4	2.8
110°-120°	550.1	7.3
120°-130°	912.4	12.2
130°-140°	969.2	12.9
140°-150°	900.8	12.0
150°-160°	724.2	9.7
160°-170°	466.6	6.2
170°-180°	160.6	2.1
0°-30°	883.1	11.8
0°-40°	1371.3	18.3
0°-60°	2172.4	29.0
0°-90°	2552.9	34.0
90°-120°	813.2	10.8
90°-150°	3595.6	47.9
90°-180°	4947.0	66.0
0°-180°	7500.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	15	24	31	33	7
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	

TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4

TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4

TEST NUMBER: P904937

CATALOG NUMBER: DFN2DIP-4P3F0-030D050US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.61	7.32	7.70	8.41	9.89	2.57	3.29	3.66	4.37	5.85
	3H	8.27	8.91	9.37	10.01	11.51	3.74	4.38	4.84	5.47	6.98
	4H	8.87	9.48	9.98	10.57	12.08	4.18	4.79	5.29	5.88	7.39
	6H	9.29	9.84	10.40	10.94	12.46	4.49	5.05	5.61	6.15	7.67
	8H	9.41	9.94	10.53	11.05	12.56	4.58	5.11	5.70	6.22	7.73
	12H	9.46	9.97	10.59	11.07	12.61	4.61	5.12	5.74	6.22	7.76
4H	2H	6.61	7.22	7.73	8.31	9.82	3.15	3.75	4.26	4.85	6.36
	3H	8.42	8.93	9.55	10.05	11.57	4.48	4.99	5.60	6.11	7.63
	4H	9.11	9.57	10.23	10.68	12.22	5.02	5.48	6.14	6.59	8.13
	6H	9.61	10.01	10.74	11.14	12.68	5.43	5.82	6.56	6.95	8.49
	8H	9.78	10.15	10.91	11.28	12.83	5.55	5.92	6.68	7.04	8.59
	12H	9.87	10.21	11.02	11.34	12.90	5.60	5.94	6.75	7.08	8.63
8H	4H	9.07	9.44	10.20	10.56	12.11	5.29	5.66	6.42	6.78	8.33
	6H	9.62	9.93	10.78	11.09	12.64	5.79	6.10	6.95	7.27	8.81
	8H	9.84	10.10	10.99	11.25	12.81	5.98	6.25	7.14	7.39	8.96
	12H	9.97	10.20	11.13	11.34	12.94	6.09	6.32	7.25	7.47	9.07
12H	4H	9.01	9.35	10.16	10.48	12.04	5.29	5.62	6.43	6.76	8.31
	6H	9.60	9.86	10.76	11.01	12.58	5.84	6.11	7.00	7.25	8.82
	8H	9.81	10.04	10.97	11.19	12.79	6.04	6.28	7.20	7.42	9.02

END OF REPORT