

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332875-935

Luminaire Tested: **SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332875-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2993.2 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332875-935
CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	25
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	14	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.7
10°-20°	139.4	4.7
20°-30°	201.3	6.7
30°-40°	228.2	7.6
40°-50°	220.4	7.4
50°-60°	183.2	6.1
60°-70°	126.5	4.2
70°-80°	64.1	2.1
80°-90°	18.4	0.6
90°-100°	41.9	1.4
100°-110°	124.1	4.1
110°-120°	210.6	7.0
120°-130°	277.7	9.3
130°-140°	311.8	10.4
140°-150°	306.4	10.2
150°-160°	257.7	8.6
160°-170°	171.5	5.7
170°-180°	60.0	2.0
0°-30°	390.7	13.1
0°-40°	619.0	20.7
0°-60°	1022.6	34.2
0°-90°	1231.6	41.1
90°-120°	376.5	12.6
90°-150°	1272.4	42.5
90°-180°	1762.0	58.9
0°-180°	2993.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	2	7	11	14	15	3
95°	29	34	37	39	39	33
105°	114	115	117	118	120	121
115°	214	214	213	213	212	211
125°	312	312	311	310	309	278
135°	402	405	405	404	403	311
145°	489	490	491	490	489	306
155°	560	560	559	561	559	257
165°	609	608	607	610	608	172
175°	634	632	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.8	7.5	7.1	6.8	6.5	6.3	6.5	6.5	6.6	6.7	6.8
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	10.5	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8
95°	29.4	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6
97.5°	51.5	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4
100°	68.7	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3
102.5°	86.8	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0
105°	114.4	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2
107.5°	143.4	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6
110°	163.1	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3



TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	183.5	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7
115°	214.1	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0
117.5°	243.0	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3
120°	262.3	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2
122.5°	282.2	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0
125°	311.9	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1
127.5°	338.6	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1
130°	357.5	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8
132.5°	376.8	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2
135°	402.2	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9
137.5°	429.9	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8
140°	448.3	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2
142.5°	465.2	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8
145°	488.6	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	511.8	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7
150°	525.9	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.3	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1
155°	559.8	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7
157.5°	577.1	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4
160°	587.3	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7
162.5°	596.8	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6
165°	609.4	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6
167.5°	619.1	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9
170°	624.7	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4
172.5°	628.5	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3
175°	634.0	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8
177.5°	635.8	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	6.8	6.9	7.0	7.1	7.1	7.3	7.4	7.5
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.2	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.0	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	59.8	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.6	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.2	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.5	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	144.9	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	163.1	162.9	162.6	162.7	163.1	163.3	163.7	164.0



TEST NUMBER: P332875-935

CATALOG NUMBER: SA4XXRDIP-C350D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	182.7	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.9	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.9	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.7	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.6	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.9	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.9	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.5	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	377.0	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.7	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.4	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.1	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.9	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.6	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.4	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	576.8	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.0	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.2	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.3	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	618.5	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.0	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.1	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.0	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)