

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332882-935

Luminaire Tested: **SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332882-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3723.8 lumens  
Efficiency: N/A  
Efficacy: 119.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332882-935  
CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	23	27	22	19	22	18	16	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4297	4297	4297
5°	4306	4254	4280
10°	4279	4203	4203
15°	4231	4115	4084
20°	4163	3998	3924
25°	4077	3862	3764
30°	3993	3719	3564
35°	3900	3571	3362
40°	3789	3402	3144
45°	3685	3234	2923
50°	3567	3041	2688
55°	3441	2839	2432
60°	3303	2619	2172
65°	3177	2344	1914
70°	2991	2039	1626
75°	2757	1691	1323
80°	2404	1288	1213
85°	2038	1176	1093



TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.0	1.3
10°-20°	139.4	3.7
20°-30°	201.3	5.4
30°-40°	228.2	6.1
40°-50°	220.4	5.9
50°-60°	183.2	4.9
60°-70°	126.5	3.4
70°-80°	64.1	1.7
80°-90°	18.3	0.5
90°-100°	247.5	6.6
100°-110°	515.1	13.8
110°-120°	461.4	12.4
120°-130°	388.1	10.4
130°-140°	323.6	8.7
140°-150°	247.2	6.6
150°-160°	173.8	4.7
160°-170°	102.2	2.7
170°-180°	33.3	0.9
0°-30°	390.7	10.5
0°-40°	619.0	16.6
0°-60°	1022.6	27.5
0°-90°	1231.6	33.1
90°-120°	1224.0	32.9
90°-150°	2183.0	58.6
90°-180°	2492.0	66.9
0°-180°	3723.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	532	532	532	532	532	
5°	531	530	525	529	528	50
15°	506	502	492	491	489	143
25°	458	450	434	427	423	211
35°	396	382	362	349	341	247
45°	323	307	283	264	256	249
55°	244	228	202	181	173	219
65°	166	148	123	106	100	164
75°	88	73	54	45	42	93
85°	22	14	13	12	12	25
90°	1	5	12	13	14	2
95°	22	70	549	272	164	25
105°	79	114	442	951	947	84
115°	139	174	394	757	910	138
125°	193	230	392	644	726	172
135°	230	273	388	572	649	177
145°	265	303	386	482	530	166
155°	301	325	376	426	444	139
165°	328	338	360	381	387	93
175°	342	343	345	350	349	32
180°	343	343	343	343	343	



TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	533.6	533.2	533.0	532.7	532.4	531.8	531.1	530.3	529.4	528.7	529.4
5°	531.4	531.1	530.7	530.4	529.9	529.3	528.1	527.1	526.0	525.0	525.8
7.5°	526.6	526.2	525.9	525.5	525.1	524.2	522.8	521.3	520.0	518.6	519.1
10°	522.0	521.6	521.2	520.7	520.2	519.2	517.5	515.9	514.3	512.7	513.1
12.5°	516.2	515.7	515.1	514.6	514.1	512.9	510.9	509.0	507.1	505.1	505.4
15°	506.2	505.3	504.5	503.7	502.9	501.4	499.1	496.8	494.6	492.3	492.1
17.5°	494.0	492.8	491.6	490.5	489.3	487.3	484.7	481.9	479.2	476.5	476.0
20°	484.6	483.4	482.2	481.0	479.8	477.8	474.7	471.6	468.5	465.4	464.7
22.5°	474.2	472.8	471.5	470.2	468.8	466.5	463.2	459.9	456.7	453.3	452.3
25°	457.7	456.1	454.4	452.8	451.2	448.5	444.8	441.1	437.3	433.6	432.0
27.5°	440.4	438.3	436.3	434.3	432.2	429.2	425.2	421.3	417.3	413.4	411.4
30°	428.3	426.0	423.8	421.5	419.3	416.0	411.7	407.5	403.2	399.0	396.7
32.5°	415.6	413.0	410.5	407.9	405.4	401.9	397.5	393.1	388.7	384.4	381.7
35°	395.7	392.8	389.9	387.0	384.1	380.4	375.9	371.3	366.9	362.3	359.2
37.5°	374.4	371.4	368.5	365.5	362.5	358.5	353.4	348.4	343.5	338.5	335.0
40°	359.5	356.5	353.4	350.5	347.5	343.5	338.3	333.1	328.0	322.8	319.0
42.5°	345.1	342.0	338.8	335.7	332.6	328.3	323.0	317.5	312.2	306.8	302.9
45°	322.8	319.4	316.1	312.7	309.4	305.0	299.5	294.1	288.7	283.3	278.8
47.5°	299.7	296.3	292.8	289.3	285.9	281.3	275.7	270.0	264.3	258.7	254.1
50°	284.0	280.5	277.0	273.5	269.9	265.3	259.5	253.7	247.9	242.1	237.5
52.5°	268.1	264.6	261.1	257.7	254.3	249.5	243.6	237.6	231.7	225.8	221.2
55°	244.5	240.9	237.3	233.7	230.1	225.2	219.4	213.5	207.6	201.7	197.0
57.5°	221.2	217.4	213.7	209.9	206.1	201.4	195.5	189.8	184.0	178.1	173.4
60°	204.6	201.0	197.3	193.7	190.1	185.4	179.6	173.7	168.0	162.2	157.5
62.5°	189.6	185.8	182.0	178.3	174.5	169.7	163.8	157.8	151.9	145.9	141.5
65°	166.3	162.4	158.5	154.6	150.7	145.9	140.1	134.2	128.5	122.7	118.8
67.5°	142.1	138.4	134.6	130.9	127.2	122.6	117.2	111.8	106.4	101.1	97.7
70°	126.7	123.0	119.2	115.4	111.5	107.0	101.9	96.7	91.5	86.4	83.4
72.5°	110.5	107.0	103.6	100.1	96.7	92.6	87.6	82.7	77.9	73.0	70.5
75°	88.4	85.1	81.7	78.4	75.0	71.2	67.0	62.7	58.5	54.2	52.1
77.5°	66.1	63.3	60.4	57.6	54.8	51.6	48.1	44.7	41.2	37.8	36.6
80°	51.7	49.2	46.5	43.9	41.2	38.6	35.9	33.1	30.4	27.7	27.5
82.5°	39.3	36.9	34.5	32.1	29.7	27.7	26.2	24.6	23.1	21.5	21.4
85°	22.0	20.2	18.4	16.5	14.7	13.7	13.4	13.2	12.9	12.7	12.5
87.5°	7.7	7.3	7.1	6.7	6.3	5.9	6.6	6.6	6.8	7.0	6.8
90°	0.7	2.0	4.0	4.7	5.4	5.4	9.4	9.4	10.8	12.1	11.5
92.5°	7.7	11.2	17.5	25.7	35.6	49.5	83.8	136.0	186.9	213.5	177.9
95°	22.2	24.2	31.0	39.7	55.9	84.1	142.8	253.1	414.1	548.7	564.2
97.5°	39.9	39.9	45.6	53.7	67.6	91.3	136.4	227.6	387.5	577.9	708.8
100°	51.1	51.1	55.9	64.0	76.7	98.3	138.0	214.1	351.5	541.3	713.6
102.5°	61.9	63.0	67.2	74.7	87.0	107.5	143.4	210.3	327.2	495.5	673.2
105°	78.8	80.8	84.1	92.2	104.4	123.9	156.2	212.1	306.3	441.6	599.9
107.5°	97.4	98.7	102.0	110.6	122.3	141.5	171.2	222.1	302.6	411.5	540.6
110°	109.8	111.1	114.4	122.5	134.7	152.8	182.4	229.5	303.6	401.2	511.0



TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	123.0	126.8	134.4	146.5	164.7	193.2	237.6	306.9	396.4	494.3
115°	138.7	140.7	145.4	152.1	165.0	183.1	210.1	250.5	313.1	393.8	478.6
117.5°	156.4	158.3	162.6	170.0	181.9	200.8	226.4	263.5	319.7	393.1	471.7
120°	168.3	169.6	174.4	181.8	193.2	212.1	237.6	272.7	324.5	393.1	467.9
122.5°	179.1	180.5	185.1	192.0	204.5	222.8	248.4	281.3	329.3	392.6	463.6
125°	193.2	195.9	199.9	207.3	220.2	239.0	263.2	294.2	336.7	391.8	456.4
127.5°	205.8	207.9	212.8	221.2	234.5	253.6	277.0	305.4	342.4	390.4	446.9
130°	212.8	215.4	220.8	230.9	243.7	263.2	286.1	312.4	346.7	389.8	441.0
132.5°	219.7	221.9	228.9	238.5	252.4	270.8	293.7	319.3	350.5	389.3	435.6
135°	229.5	232.3	239.0	250.5	264.6	282.1	304.3	328.6	356.1	388.5	427.5
137.5°	239.4	241.9	249.3	260.3	274.9	291.6	312.4	335.0	359.5	388.3	420.5
140°	246.4	248.4	255.8	267.3	281.4	297.6	317.8	339.3	362.2	387.8	416.7
142.5°	253.9	256.0	262.9	273.7	287.3	303.0	322.6	342.5	364.4	387.8	413.5
145°	264.6	266.6	273.4	282.8	295.6	310.4	327.9	346.0	365.6	386.4	407.9
147.5°	276.6	277.2	283.2	292.8	303.5	316.8	333.3	349.1	366.3	384.0	403.0
150°	284.1	284.8	290.2	298.3	308.3	321.2	336.0	350.8	366.3	382.4	399.2
152.5°	291.1	291.3	296.6	304.2	313.2	324.9	338.1	351.8	365.2	379.7	394.9
155°	300.9	301.6	305.7	312.4	319.8	329.8	341.3	352.8	363.5	375.7	388.5
157.5°	310.5	310.5	314.3	319.5	326.0	333.9	343.6	352.8	361.8	371.5	381.9
160°	316.4	316.4	319.1	323.8	329.2	336.7	344.7	352.8	360.2	368.2	377.0
162.5°	321.8	321.2	323.4	327.6	332.4	338.2	345.8	352.8	358.6	365.1	372.7
165°	327.9	327.9	329.2	332.6	336.0	340.0	346.0	351.5	355.5	360.2	365.6
167.5°	333.9	333.3	333.9	336.5	338.4	341.5	345.9	349.8	352.2	355.3	359.1
170°	336.7	336.0	336.7	338.6	340.0	342.0	345.3	348.7	350.1	352.1	354.8
172.5°	339.3	338.6	338.8	340.3	341.0	342.5	344.8	347.7	347.9	348.9	351.0
175°	342.0	341.3	341.3	342.0	342.7	342.7	344.1	346.0	345.3	345.3	346.7
177.5°	343.2	342.7	342.2	342.7	342.7	342.7	343.2	344.3	343.2	343.2	343.7
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7



TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
2.5°	530.3	531.1	531.8	532.2	532.1	532.1	532.0	531.9
5°	526.8	527.6	528.6	528.9	528.7	528.6	528.3	528.1
7.5°	519.7	520.3	520.9	521.0	520.7	520.5	520.1	519.9
10°	513.4	513.8	514.1	514.1	513.8	513.4	513.1	512.7
12.5°	505.6	505.8	506.1	505.9	505.4	504.9	504.4	503.9
15°	492.0	491.8	491.5	491.2	490.5	489.9	489.3	488.6
17.5°	475.4	475.0	474.5	473.7	472.8	471.8	470.9	469.9
20°	464.0	463.2	462.5	461.6	460.4	459.2	458.1	456.8
22.5°	451.2	450.0	449.0	448.0	447.0	446.1	445.1	444.1
25°	430.5	429.0	427.5	426.3	425.3	424.4	423.5	422.6
27.5°	409.5	407.6	405.7	404.2	402.8	401.5	400.2	398.9
30°	394.4	392.2	389.9	388.1	386.6	385.2	383.7	382.3
32.5°	379.1	376.4	373.8	371.8	370.4	369.0	367.6	366.3
35°	356.1	353.1	350.0	347.7	346.0	344.4	342.8	341.1
37.5°	331.6	328.1	324.7	322.1	320.5	318.8	317.2	315.6
40°	315.1	311.3	307.5	304.9	303.2	301.6	300.0	298.3
42.5°	299.0	295.2	291.3	288.5	286.8	285.1	283.4	281.7
45°	274.4	269.9	265.4	262.4	260.8	259.2	257.5	256.0
47.5°	249.5	244.9	240.3	237.1	235.3	233.5	231.7	230.0
50°	233.0	228.5	223.9	220.8	219.1	217.4	215.7	214.0
52.5°	216.5	212.0	207.4	204.1	202.4	200.6	198.8	197.0
55°	192.3	187.6	182.9	179.7	178.0	176.2	174.5	172.8
57.5°	168.6	163.8	159.0	156.0	154.7	153.4	152.1	150.8
60°	152.7	148.1	143.4	140.3	138.8	137.4	136.0	134.5
62.5°	137.2	132.9	128.5	125.8	124.6	123.5	122.3	121.1
65°	114.9	111.0	107.1	104.6	103.5	102.5	101.3	100.2
67.5°	94.4	91.0	87.6	85.4	84.2	83.0	81.8	80.6
70°	80.4	77.4	74.5	72.5	71.5	70.7	69.7	68.9
72.5°	67.9	65.3	62.9	61.1	60.3	59.5	58.6	57.8
75°	50.0	48.0	45.9	44.6	44.0	43.5	43.0	42.4
77.5°	35.4	34.2	33.0	32.3	32.1	31.9	31.8	31.6
80°	27.2	26.9	26.6	26.4	26.3	26.3	26.2	26.1
82.5°	21.1	20.9	20.8	20.6	20.5	20.4	20.3	20.2
85°	12.3	12.1	11.9	11.8	11.8	11.8	11.8	11.8
87.5°	6.8	6.9	7.0	7.0	7.1	7.4	7.3	7.4
90°	12.1	12.8	13.4	13.4	14.1	14.8	14.1	14.1
92.5°	132.2	99.5	79.2	65.7	57.8	54.2	51.8	51.8
95°	498.9	394.5	304.3	239.0	206.0	185.1	173.1	164.3
97.5°	737.0	698.3	632.4	562.1	513.8	473.3	453.1	439.1
100°	811.9	825.4	792.4	742.6	684.0	642.9	622.8	617.3
102.5°	808.1	874.9	884.5	863.8	827.9	798.1	776.8	772.5
105°	754.1	870.5	937.1	964.8	966.1	960.7	951.3	947.3
107.5°	677.2	801.2	895.0	955.0	988.3	1003.7	1010.4	1012.1
110°	630.9	747.3	844.9	918.9	966.7	995.1	1007.2	1013.2





TEST NUMBER: P332882-935

CATALOG NUMBER: SA4XXRDIP-C350D810U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	596.9	699.9	792.1	866.2	920.4	954.7	971.6	981.5
115°	562.8	645.7	724.4	789.0	842.2	882.6	904.1	909.6
117.5°	546.1	614.7	676.6	731.4	776.8	810.7	832.5	836.7
120°	538.6	601.2	655.0	702.8	741.2	770.9	788.3	795.7
122.5°	532.1	592.5	641.6	683.5	715.9	741.2	756.0	763.4
125°	521.1	579.0	625.4	662.5	689.4	708.9	721.7	725.7
127.5°	507.6	562.9	609.2	644.5	671.5	688.9	699.6	703.7
130°	496.9	550.0	595.8	631.5	659.1	676.0	686.7	690.8
132.5°	485.5	535.5	580.2	615.9	642.9	661.9	672.2	676.2
135°	469.9	513.7	554.7	588.4	615.4	634.2	645.0	649.0
137.5°	455.8	492.8	527.4	557.8	583.0	601.6	610.4	615.4
140°	447.7	479.3	509.6	538.0	561.5	576.3	585.7	591.1
142.5°	440.1	468.0	494.0	518.5	539.4	553.1	561.5	565.2
145°	429.6	452.5	472.6	491.5	508.3	519.7	526.5	529.9
147.5°	420.8	438.9	455.1	469.9	482.3	492.1	497.2	498.4
150°	415.3	430.8	444.4	456.4	467.3	476.0	480.0	480.7
152.5°	409.5	422.8	435.1	445.1	454.3	461.4	463.8	464.5
155°	400.5	411.4	421.5	429.6	436.3	441.6	443.7	443.7
157.5°	391.0	400.0	408.5	415.0	420.1	424.1	425.3	425.3
160°	385.1	392.5	399.9	405.3	409.3	413.4	414.1	414.1
162.5°	379.2	385.5	391.3	396.1	399.1	403.1	403.8	403.3
165°	370.9	375.0	379.7	383.1	385.7	388.5	387.8	387.1
167.5°	363.0	366.1	369.9	371.9	373.2	375.0	374.9	374.3
170°	358.2	360.2	362.9	364.9	366.3	366.9	366.3	366.3
172.5°	353.9	355.3	357.0	358.4	359.2	359.9	359.2	358.2
175°	348.1	348.7	350.1	350.1	350.1	351.5	350.1	348.7
177.5°	344.3	344.8	344.8	345.3	344.8	345.3	344.3	343.2
180°	342.7	342.7	342.7	342.7	342.7	342.7	342.7	342.7

(END OF REPORT)