

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332898-935

Luminaire Tested: **SA4XXRDIP-C575D365U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332898-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3281.3 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332898-935
CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	96	93	89	94	90	87	84	79	77	75	69	67	66	60	58	57	53				
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45				
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38				
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33				
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29				
6	66	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25				
7	61	48	40	35	57	46	38	33	41	35	31	36	31	28	32	28	25	23				
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	23	20				
9	53	40	33	28	49	38	31	27	34	29	25	31	26	22	27	23	20	18				
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7064	7064	7064
5°	7080	6994	7037
10°	7035	6909	6909
15°	6955	6764	6714
20°	6844	6574	6453
25°	6702	6350	6188
30°	6564	6114	5858
35°	6412	5870	5527
40°	6227	5592	5168
45°	6058	5316	4804
50°	5865	4999	4417
55°	5658	4669	3997
60°	5430	4306	3570
65°	5223	3851	3148
70°	4919	3354	2672
75°	4535	2779	2174
80°	3956	2115	1994
85°	3353	1927	1806



TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.2	2.5
10°-20°	229.2	7.0
20°-30°	331.0	10.1
30°-40°	375.2	11.4
40°-50°	362.3	11.0
50°-60°	301.3	9.2
60°-70°	208.0	6.3
70°-80°	105.4	3.2
80°-90°	28.2	0.9
90°-100°	13.9	0.4
100°-110°	88.7	2.7
110°-120°	169.7	5.2
120°-130°	215.4	6.6
130°-140°	230.5	7.0
140°-150°	215.6	6.6
150°-160°	173.8	5.3
160°-170°	112.1	3.4
170°-180°	38.6	1.2
0°-30°	642.4	19.6
0°-40°	1017.6	31.0
0°-60°	1681.1	51.2
0°-90°	2022.8	61.6
90°-120°	272.4	8.3
90°-150°	933.9	28.5
90°-180°	1258.0	38.3
0°-180°	3281.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	875	875	875	875	875	
5°	874	871	863	869	868	83
15°	832	825	809	808	803	234
25°	752	740	713	702	695	347
35°	651	628	596	573	561	406
45°	531	505	466	434	421	409
55°	402	374	332	298	284	359
65°	273	244	202	174	165	270
75°	145	120	89	74	70	154
85°	36	23	21	20	20	41
90°	1	4	7	8	9	2
95°	17	7	7	8	9	22
105°	92	93	95	97	87	96
115°	171	172	172	172	172	168
125°	240	242	241	242	242	215
135°	298	298	299	300	300	230
145°	344	345	345	345	346	215
155°	377	377	376	378	377	174
165°	398	396	396	398	396	112
175°	407	405	405	408	404	39
180°	407	407	407	407	407	



TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	877.2	876.7	876.2	875.7	875.3	874.3	873.1	871.8	870.4	869.1	870.4
5°	873.7	873.1	872.5	871.8	871.3	870.1	868.3	866.5	864.7	863.0	864.4
7.5°	865.7	865.1	864.5	863.9	863.2	861.8	859.5	857.1	854.8	852.5	853.4
10°	858.2	857.6	856.8	856.0	855.3	853.6	850.9	848.2	845.5	842.8	843.4
12.5°	848.6	847.7	846.9	846.0	845.2	843.2	840.0	836.8	833.7	830.5	830.9
15°	832.2	830.8	829.5	828.1	826.7	824.2	820.5	816.8	813.0	809.3	809.1
17.5°	812.2	810.2	808.3	806.3	804.4	801.2	796.8	792.3	787.8	783.3	782.6
20°	796.6	794.7	792.7	790.8	788.8	785.4	780.3	775.2	770.2	765.2	764.0
22.5°	779.5	777.3	775.2	772.9	770.8	767.0	761.6	756.1	750.7	745.3	743.5
25°	752.4	749.8	747.0	744.3	741.7	737.3	731.2	725.0	718.9	712.9	710.3
27.5°	724.0	720.7	717.3	713.9	710.5	705.6	699.0	692.6	686.0	679.5	676.4
30°	704.1	700.4	696.7	693.0	689.3	683.9	676.9	669.9	662.9	655.9	652.2
32.5°	683.3	679.1	674.9	670.6	666.5	660.7	653.5	646.3	639.0	631.8	627.5
35°	650.6	645.8	641.0	636.3	631.5	625.4	617.9	610.5	603.0	595.6	590.6
37.5°	615.6	610.7	605.8	600.9	595.9	589.4	581.1	572.8	564.6	556.4	550.7
40°	590.9	586.0	581.1	576.2	571.3	564.6	556.1	547.6	539.2	530.6	524.3
42.5°	567.3	562.2	557.1	551.9	546.7	539.8	530.9	522.0	513.2	504.4	498.0
45°	530.6	525.1	519.6	514.1	508.6	501.4	492.4	483.5	474.6	465.6	458.3
47.5°	492.8	487.1	481.3	475.6	469.9	462.4	453.1	443.9	434.6	425.3	417.8
50°	467.0	461.2	455.4	449.5	443.8	436.1	426.5	417.1	407.5	398.0	390.5
52.5°	440.7	435.1	429.4	423.7	417.9	410.3	400.5	390.7	380.9	371.2	363.6
55°	402.0	396.1	390.1	384.1	378.2	370.3	360.7	351.0	341.3	331.7	323.9
57.5°	363.7	357.5	351.3	345.1	338.9	331.1	321.5	311.9	302.5	292.9	285.1
60°	336.3	330.4	324.4	318.5	312.5	304.8	295.2	285.7	276.2	266.7	258.9
62.5°	311.7	305.5	299.3	293.1	286.9	279.0	269.1	259.4	249.6	239.9	232.7
65°	273.4	267.0	260.5	254.2	247.7	239.8	230.2	220.8	211.2	201.6	195.3
67.5°	233.6	227.4	221.3	215.2	209.1	201.6	192.7	183.8	175.0	166.2	160.7
70°	208.4	202.1	195.9	189.6	183.4	176.0	167.5	159.0	150.5	142.1	137.2
72.5°	181.6	175.9	170.2	164.6	158.9	152.1	144.1	136.1	128.0	120.0	115.9
75°	145.4	139.9	134.4	128.9	123.4	117.1	110.1	103.1	96.1	89.1	85.7
77.5°	108.7	104.0	99.4	94.6	90.0	84.8	79.1	73.5	67.8	62.2	60.2
80°	85.1	80.8	76.5	72.2	67.8	63.5	59.0	54.5	50.0	45.5	45.1
82.5°	64.7	60.8	56.8	52.9	48.9	45.6	43.0	40.5	38.0	35.4	35.0
85°	36.2	33.2	30.2	27.2	24.3	22.6	22.1	21.7	21.2	20.8	20.5
87.5°	12.5	11.7	10.9	10.1	9.3	8.9	8.9	8.9	8.9	8.9	8.8
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	3.9	3.9	3.9	4.0	4.0	4.3	4.8	5.3	5.9	6.5	6.9
95°	16.7	14.5	12.1	9.8	7.6	6.5	6.5	6.5	6.6	6.7	7.1
97.5°	35.6	36.9	38.4	39.9	41.2	38.2	30.7	23.2	15.6	8.0	8.1
100°	49.9	51.1	52.3	53.6	54.8	50.7	41.4	32.0	22.7	13.4	12.2
102.5°	66.0	66.9	67.8	68.6	69.6	69.4	68.2	67.0	65.7	64.5	52.1
105°	91.6	92.0	92.4	92.8	93.2	93.6	93.9	94.3	94.6	95.0	95.6
107.5°	115.4	115.5	115.8	116.0	116.2	116.5	117.0	117.4	117.9	118.4	118.6
110°	131.5	131.6	131.8	132.1	132.2	132.6	132.9	133.4	133.8	134.2	134.3



TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.1	147.4	147.7	148.1	148.5	148.8	149.0	149.1	149.3	149.6	149.5
115°	171.0	171.3	171.4	171.6	171.9	171.9	171.9	171.8	171.7	171.6	171.8
117.5°	192.6	192.9	193.1	193.5	193.7	193.9	194.1	194.2	194.3	194.5	194.5
120°	207.2	207.5	207.8	208.0	208.3	208.4	208.4	208.3	208.2	208.1	208.3
122.5°	220.8	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.9	222.1	222.1
125°	240.4	240.6	240.9	241.2	241.5	241.5	241.4	241.3	241.2	241.0	241.2
127.5°	258.9	259.0	259.0	259.1	259.2	259.3	259.7	259.9	260.3	260.6	260.5
130°	270.8	270.9	271.0	271.0	271.1	271.2	271.4	271.6	271.8	272.1	272.1
132.5°	281.8	281.9	282.0	282.1	282.2	282.4	282.7	282.9	283.2	283.4	283.5
135°	298.2	298.2	298.1	298.0	297.9	298.0	298.3	298.6	298.9	299.1	299.3
137.5°	312.7	312.8	312.8	312.8	312.9	313.1	313.3	313.6	313.9	314.2	314.4
140°	322.3	322.4	322.5	322.6	322.8	322.9	323.0	323.2	323.3	323.5	323.6
142.5°	330.8	331.0	331.2	331.5	331.7	331.9	332.0	332.1	332.2	332.3	332.3
145°	343.9	344.1	344.2	344.5	344.7	344.7	344.7	344.7	344.7	344.7	344.8
147.5°	354.2	354.6	355.0	355.4	355.8	355.9	355.9	355.8	355.7	355.7	355.7
150°	361.8	362.1	362.3	362.7	362.9	363.0	362.9	362.8	362.7	362.7	362.7
152.5°	368.2	368.3	368.6	368.8	369.0	369.0	368.9	368.8	368.7	368.6	368.7
155°	377.0	377.1	377.1	377.2	377.3	377.2	377.0	376.8	376.6	376.4	376.7
157.5°	384.5	384.4	384.4	384.4	384.4	384.2	384.0	383.7	383.5	383.3	383.7
160°	388.9	388.7	388.5	388.3	388.1	388.0	387.9	387.8	387.7	387.6	388.1
162.5°	392.8	392.5	392.3	392.0	391.8	391.6	391.5	391.4	391.4	391.3	391.8
165°	397.7	397.4	397.0	396.7	396.3	396.1	396.1	396.1	396.1	396.1	396.7
167.5°	401.6	401.2	400.9	400.5	400.2	400.0	399.9	399.9	399.8	399.8	400.5
170°	403.8	403.4	402.9	402.6	402.2	402.0	402.1	402.2	402.2	402.3	402.8
172.5°	405.3	404.8	404.4	404.1	403.6	403.5	403.6	403.6	403.6	403.7	404.2
175°	406.8	406.4	406.0	405.6	405.2	405.0	405.1	405.2	405.3	405.3	406.0
177.5°	407.6	407.2	406.8	406.4	406.0	405.9	406.0	406.1	406.2	406.3	406.8
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8



TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	875.0	875.0	875.0	875.0	875.0	875.0	875.0	875.0
2.5°	871.8	873.1	874.3	874.9	874.9	874.7	874.6	874.5
5°	865.9	867.5	868.9	869.5	869.2	868.9	868.6	868.3
7.5°	854.4	855.3	856.4	856.5	856.1	855.6	855.1	854.6
10°	844.0	844.6	845.2	845.2	844.6	844.0	843.4	842.8
12.5°	831.2	831.6	832.0	831.7	830.9	830.1	829.2	828.4
15°	808.7	808.5	808.1	807.5	806.4	805.4	804.3	803.3
17.5°	781.7	780.8	780.0	778.8	777.2	775.7	774.0	772.5
20°	762.8	761.6	760.3	758.8	756.9	754.9	753.0	751.1
22.5°	741.8	739.9	738.1	736.5	734.9	733.3	731.8	730.1
25°	707.8	705.2	702.7	700.8	699.2	697.8	696.3	694.7
27.5°	673.2	670.1	667.0	664.3	662.2	660.0	658.0	655.8
30°	648.5	644.7	641.0	638.0	635.6	633.2	630.9	628.4
32.5°	623.2	618.9	614.5	611.2	609.0	606.7	604.4	602.2
35°	585.5	580.4	575.4	571.5	568.9	566.1	563.4	560.8
37.5°	545.0	539.4	533.7	529.6	526.8	524.2	521.5	518.8
40°	518.1	511.9	505.6	501.2	498.4	495.8	493.1	490.4
42.5°	491.6	485.3	478.9	474.3	471.5	468.7	465.9	463.1
45°	451.1	443.8	436.4	431.4	428.8	426.1	423.4	420.8
47.5°	410.2	402.6	395.0	389.8	386.8	383.9	381.0	378.0
50°	383.1	375.7	368.2	363.1	360.2	357.4	354.6	351.7
52.5°	356.0	348.4	341.0	335.7	332.7	329.8	326.8	323.9
55°	316.2	308.4	300.7	295.4	292.6	289.7	286.9	284.0
57.5°	277.2	269.3	261.5	256.5	254.3	252.2	250.0	247.9
60°	251.2	243.4	235.7	230.7	228.3	225.8	223.5	221.1
62.5°	225.6	218.4	211.3	206.7	204.8	202.9	201.0	199.1
65°	188.9	182.4	176.1	171.9	170.2	168.4	166.6	164.8
67.5°	155.2	149.6	144.1	140.4	138.4	136.5	134.5	132.5
70°	132.2	127.3	122.3	119.2	117.7	116.2	114.7	113.2
72.5°	111.7	107.5	103.2	100.5	99.1	97.7	96.3	95.0
75°	82.2	78.9	75.4	73.3	72.3	71.5	70.6	69.7
77.5°	58.2	56.2	54.2	53.0	52.8	52.5	52.3	52.0
80°	44.7	44.3	43.7	43.5	43.3	43.1	43.0	42.9
82.5°	34.7	34.4	34.1	33.8	33.7	33.5	33.4	33.2
85°	20.1	19.9	19.5	19.5	19.5	19.5	19.5	19.5
87.5°	8.8	8.7	8.7	8.8	8.9	9.0	9.2	9.3
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	7.2	7.7	8.1	8.3	8.4	8.4	8.4	8.4
95°	7.5	7.9	8.4	8.5	8.6	8.7	8.8	8.8
97.5°	8.1	8.2	8.2	8.3	8.4	8.4	8.4	8.5
100°	11.1	9.9	8.8	8.3	8.4	8.4	8.4	8.5
102.5°	39.7	27.3	14.9	8.7	8.7	8.7	8.8	8.8
105°	96.2	96.8	97.4	96.4	94.0	91.6	89.1	86.7
107.5°	119.0	119.2	119.6	119.9	120.1	120.4	120.6	120.9
110°	134.5	134.6	134.7	134.9	135.1	135.3	135.5	135.7



TEST NUMBER: P332898-935

CATALOG NUMBER: SA4XXRDIP-C575D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	149.5	149.5	149.4	149.6	149.8	150.1	150.3	150.6
115°	171.9	172.0	172.2	172.2	172.2	172.2	172.2	172.2
117.5°	194.4	194.4	194.4	194.3	194.3	194.3	194.3	194.2
120°	208.4	208.5	208.7	208.7	208.5	208.4	208.3	208.1
122.5°	222.1	222.2	222.3	222.3	222.1	222.1	221.9	221.8
125°	241.4	241.6	241.8	241.9	242.0	242.1	242.1	242.2
127.5°	260.5	260.5	260.5	260.4	260.4	260.3	260.2	260.2
130°	272.2	272.2	272.3	272.3	272.3	272.3	272.3	272.3
132.5°	283.6	283.7	283.8	283.8	283.7	283.6	283.6	283.5
135°	299.4	299.5	299.6	299.8	299.9	300.1	300.2	300.3
137.5°	314.5	314.7	314.8	314.9	314.8	314.8	314.7	314.7
140°	323.8	324.1	324.3	324.4	324.5	324.5	324.6	324.7
142.5°	332.5	332.7	332.8	332.9	332.9	332.9	332.9	332.9
145°	344.9	345.0	345.0	345.1	345.3	345.4	345.5	345.7
147.5°	355.8	355.9	355.9	355.9	356.0	356.0	356.1	356.2
150°	362.7	362.7	362.7	362.7	362.8	362.9	362.9	363.0
152.5°	368.8	368.9	369.0	369.0	368.9	368.9	368.9	368.9
155°	376.9	377.2	377.5	377.5	377.3	377.1	376.9	376.7
157.5°	384.0	384.4	384.7	384.7	384.4	384.0	383.7	383.3
160°	388.5	388.9	389.3	389.3	388.9	388.5	388.1	387.6
162.5°	392.1	392.5	393.0	392.9	392.4	392.0	391.5	391.1
165°	397.3	397.8	398.4	398.3	397.7	397.1	396.5	395.9
167.5°	401.1	401.7	402.2	402.2	401.5	400.8	400.1	399.5
170°	403.4	403.9	404.4	404.3	403.7	403.0	402.3	401.7
172.5°	404.8	405.4	405.9	405.8	405.1	404.3	403.6	402.9
175°	406.6	407.2	407.8	407.7	406.8	406.0	405.2	404.4
177.5°	407.3	407.7	408.1	407.9	407.3	406.7	406.0	405.4
180°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8

(END OF REPORT)