

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332946-935

Luminaire Tested: **SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332946-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6321.4 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332946-935
CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44				
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37				
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32				
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27				
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	1.8
10°-20°	313.3	5.0
20°-30°	452.4	7.2
30°-40°	512.8	8.1
40°-50°	495.2	7.8
50°-60°	411.8	6.5
60°-70°	284.4	4.5
70°-80°	144.1	2.3
80°-90°	40.3	0.6
90°-100°	39.3	0.6
100°-110°	250.6	4.0
110°-120°	479.4	7.6
120°-130°	608.6	9.6
130°-140°	651.1	10.3
140°-150°	608.9	9.6
150°-160°	491.0	7.8
160°-170°	316.7	5.0
170°-180°	109.2	1.7
0°-30°	878.1	13.9
0°-40°	1390.9	22.0
0°-60°	2297.9	36.4
0°-90°	2766.7	43.8
90°-120°	769.3	12.2
90°-150°	2637.9	41.7
90°-180°	3555.0	56.2
0°-180°	6321.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	3	12	19	24	26	5
95°	47	20	19	24	25	61
105°	259	264	268	274	245	271
115°	483	485	485	486	486	475
125°	679	682	681	683	684	606
135°	842	842	845	847	848	649
145°	971	974	974	975	976	607
155°	1065	1066	1063	1066	1064	491
165°	1123	1119	1119	1125	1118	317
175°	1149	1144	1145	1152	1142	109
180°	1149	1149	1149	1149	1149	



TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.4	16.4	15.6	14.7	13.9	13.4	13.6	13.8	13.9	14.0	14.1
90°	2.6	4.6	6.8	8.9	11.0	12.8	14.3	15.8	17.4	18.9	20.1
92.5°	10.8	10.9	11.0	11.2	11.3	12.1	13.6	15.2	16.7	18.3	19.4
95°	47.3	40.8	34.3	27.8	21.3	18.2	18.3	18.5	18.7	18.9	20.1
97.5°	100.4	104.4	108.5	112.5	116.6	108.0	86.6	65.3	44.0	22.7	22.8
100°	140.9	144.4	147.8	151.3	154.7	143.3	116.9	90.6	64.1	37.8	34.6
102.5°	186.3	188.9	191.4	193.9	196.4	196.0	192.5	189.1	185.6	182.2	147.1
105°	258.7	259.8	261.0	262.2	263.3	264.3	265.3	266.2	267.3	268.2	269.9
107.5°	325.9	326.5	327.1	327.6	328.2	329.2	330.5	331.7	333.0	334.3	335.2
110°	371.3	371.9	372.5	373.0	373.6	374.4	375.6	376.8	377.9	379.0	379.4



TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	415.3	416.4	417.4	418.4	419.5	420.3	420.8	421.3	421.8	422.3	422.3
115°	483.0	483.6	484.2	484.7	485.3	485.5	485.3	485.2	484.9	484.7	485.2
117.5°	544.1	544.8	545.6	546.4	547.2	547.7	548.1	548.5	549.0	549.4	549.3
120°	585.3	586.1	586.9	587.6	588.4	588.7	588.5	588.3	588.1	587.9	588.3
122.5°	623.8	624.3	624.7	625.2	625.7	626.0	626.3	626.5	626.8	627.1	627.3
125°	679.0	679.8	680.5	681.3	682.1	682.3	681.9	681.5	681.1	680.7	681.3
127.5°	731.2	731.4	731.7	731.8	732.0	732.5	733.5	734.3	735.2	736.1	736.0
130°	765.0	765.2	765.3	765.5	765.7	766.1	766.7	767.2	767.8	768.4	768.6
132.5°	795.9	796.3	796.6	796.9	797.3	797.8	798.6	799.3	800.0	800.7	800.9
135°	842.3	842.1	842.0	841.7	841.5	841.8	842.6	843.3	844.1	844.9	845.2
137.5°	883.4	883.5	883.6	883.6	883.7	884.2	885.0	885.9	886.7	887.5	887.9
140°	910.2	910.6	911.0	911.4	911.7	912.1	912.5	912.9	913.3	913.7	914.2
142.5°	934.3	935.0	935.6	936.3	937.0	937.5	937.7	938.0	938.1	938.4	938.8
145°	971.2	971.8	972.4	972.9	973.5	973.8	973.8	973.8	973.8	973.8	974.0
147.5°	1000.7	1001.7	1002.8	1003.8	1005.0	1005.4	1005.1	1005.0	1004.8	1004.6	1004.8
150°	1021.9	1022.7	1023.5	1024.2	1025.0	1025.3	1025.1	1024.9	1024.8	1024.5	1024.5
152.5°	1039.8	1040.4	1041.0	1041.6	1042.2	1042.4	1042.1	1041.7	1041.4	1041.0	1041.4
155°	1065.0	1065.1	1065.3	1065.5	1065.7	1065.5	1065.0	1064.4	1063.8	1063.2	1063.9
157.5°	1086.1	1086.0	1085.8	1085.7	1085.6	1085.2	1084.6	1083.9	1083.3	1082.6	1083.7
160°	1098.5	1097.9	1097.3	1096.7	1096.1	1095.8	1095.6	1095.4	1095.2	1095.0	1096.1
162.5°	1109.5	1108.7	1108.0	1107.2	1106.6	1106.1	1105.9	1105.7	1105.5	1105.4	1106.5
165°	1123.3	1122.4	1121.5	1120.5	1119.6	1119.0	1119.0	1119.0	1119.0	1119.0	1120.6
167.5°	1134.4	1133.4	1132.4	1131.4	1130.4	1129.9	1129.7	1129.6	1129.5	1129.4	1131.1
170°	1140.6	1139.4	1138.2	1137.1	1136.0	1135.5	1135.7	1135.9	1136.1	1136.3	1137.8
172.5°	1144.7	1143.6	1142.4	1141.3	1140.1	1139.6	1139.8	1140.1	1140.2	1140.4	1141.9
175°	1149.2	1148.1	1146.9	1145.7	1144.6	1144.1	1144.3	1144.5	1144.7	1144.9	1146.6
177.5°	1151.2	1150.1	1149.1	1148.1	1146.9	1146.6	1146.9	1147.2	1147.5	1147.8	1149.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2



TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	14.2	14.2	14.3	14.5	14.7	14.9	15.2	15.4
90°	21.2	22.4	23.5	24.3	24.6	25.1	25.4	25.7
92.5°	20.5	21.7	22.8	23.4	23.5	23.6	23.7	23.8
95°	21.2	22.4	23.5	24.2	24.4	24.5	24.7	24.9
97.5°	22.9	23.1	23.2	23.3	23.5	23.7	23.8	24.1
100°	31.3	28.1	24.8	23.3	23.5	23.7	23.8	24.1
102.5°	112.2	77.1	42.1	24.6	24.6	24.7	24.7	24.8
105°	271.6	273.3	275.0	272.5	265.6	258.7	251.8	245.0
107.5°	336.0	336.9	337.7	338.5	339.2	339.9	340.7	341.4
110°	379.8	380.2	380.6	381.1	381.6	382.2	382.8	383.3



TEST NUMBER: P332946-935

CATALOG NUMBER: SA4XXRDIP-C795D1035U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	422.2	422.1	422.1	422.4	423.1	423.9	424.6	425.2
115°	485.5	485.9	486.3	486.5	486.5	486.5	486.5	486.5
117.5°	549.2	549.1	549.1	549.1	549.0	548.9	548.8	548.7
120°	588.7	589.0	589.4	589.4	589.0	588.7	588.3	587.9
122.5°	627.6	627.8	628.0	627.9	627.6	627.2	626.8	626.4
125°	681.9	682.4	683.0	683.4	683.6	683.8	684.0	684.2
127.5°	735.9	735.7	735.6	735.5	735.4	735.2	735.0	734.9
130°	768.8	769.0	769.1	769.3	769.3	769.3	769.3	769.3
132.5°	801.1	801.3	801.5	801.5	801.3	801.2	801.1	800.9
135°	845.7	846.0	846.4	846.8	847.2	847.6	847.9	848.3
137.5°	888.4	888.8	889.2	889.3	889.2	889.2	889.0	888.9
140°	914.8	915.4	915.9	916.4	916.5	916.7	916.9	917.1
142.5°	939.3	939.7	940.1	940.3	940.4	940.4	940.5	940.5
145°	974.2	974.4	974.6	974.9	975.3	975.6	976.0	976.4
147.5°	1004.9	1005.0	1005.2	1005.4	1005.6	1005.7	1006.0	1006.2
150°	1024.5	1024.5	1024.5	1024.6	1024.8	1025.0	1025.2	1025.4
152.5°	1041.6	1042.0	1042.2	1042.3	1042.2	1042.2	1042.0	1041.9
155°	1064.7	1065.5	1066.3	1066.3	1065.8	1065.2	1064.6	1064.1
157.5°	1084.6	1085.6	1086.6	1086.6	1085.6	1084.6	1083.7	1082.6
160°	1097.3	1098.5	1099.6	1099.6	1098.5	1097.3	1096.1	1095.0
162.5°	1107.6	1108.8	1109.9	1109.8	1108.5	1107.2	1106.0	1104.7
165°	1122.1	1123.7	1125.2	1125.1	1123.3	1121.6	1119.9	1118.2
167.5°	1132.7	1134.5	1136.1	1136.0	1134.1	1132.2	1130.2	1128.3
170°	1139.4	1140.8	1142.4	1142.2	1140.3	1138.4	1136.4	1134.5
172.5°	1143.5	1145.0	1146.5	1146.2	1144.2	1142.1	1140.1	1138.0
175°	1148.3	1150.0	1151.8	1151.4	1149.2	1146.9	1144.6	1142.3
177.5°	1150.2	1151.4	1152.7	1152.4	1150.6	1148.7	1146.9	1145.0
180°	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2	1149.2

(END OF REPORT)