

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332952-935

Luminaire Tested: **SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332952-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6904.8 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332952-935
CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40				
1	96	92	88	84	87	84	80	78	68	66	64	55	53	52	42	41	40	34				
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	35	34	29				
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	49	66	57	51	46	47	42	39	38	35	32	30	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	17				
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	1.6
10°-20°	313.3	4.5
20°-30°	452.4	6.6
30°-40°	512.8	7.4
40°-50°	495.2	7.2
50°-60°	411.8	6.0
60°-70°	284.4	4.1
70°-80°	144.1	2.1
80°-90°	40.8	0.6
90°-100°	45.8	0.7
100°-110°	291.7	4.2
110°-120°	558.0	8.1
120°-130°	708.4	10.3
130°-140°	757.9	11.0
140°-150°	708.7	10.3
150°-160°	571.5	8.3
160°-170°	368.6	5.3
170°-180°	127.0	1.8
0°-30°	878.1	12.7
0°-40°	1390.9	20.1
0°-60°	2297.9	33.3
0°-90°	2767.2	40.1
90°-120°	895.4	13.0
90°-150°	3070.4	44.5
90°-180°	4138.0	59.9
0°-180°	6904.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	3	14	22	28	30	5
95°	55	23	22	28	29	71
105°	301	307	312	319	285	315
115°	562	565	564	566	566	553
125°	790	794	792	795	796	705
135°	980	980	983	985	987	755
145°	1130	1133	1134	1135	1136	706
155°	1240	1240	1238	1241	1238	571
165°	1308	1303	1303	1310	1302	369
175°	1338	1332	1333	1340	1330	127
180°	1338	1338	1338	1338	1338	



TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.5	16.6	15.8	15.0	14.2	13.9	14.1	14.3	14.5	14.6	14.7
90°	3.0	5.4	7.9	10.3	12.7	14.9	16.7	18.4	20.2	22.0	23.3
92.5°	12.6	12.7	12.9	13.0	13.2	14.1	15.8	17.7	19.5	21.2	22.6
95°	55.0	47.4	39.9	32.4	24.8	21.1	21.4	21.5	21.8	22.0	23.3
97.5°	116.8	121.6	126.3	131.0	135.7	125.6	100.8	76.0	51.2	26.4	26.5
100°	164.1	168.1	172.1	176.1	180.1	166.8	136.0	105.4	74.7	44.0	40.2
102.5°	216.9	219.8	222.7	225.7	228.6	228.1	224.1	220.1	216.1	212.1	171.3
105°	301.1	302.5	303.8	305.1	306.4	307.7	308.8	309.9	311.0	312.1	314.2
107.5°	379.4	380.0	380.7	381.3	382.0	383.1	384.6	386.2	387.6	389.2	390.1
110°	432.2	432.8	433.5	434.2	434.9	435.8	437.2	438.5	439.9	441.2	441.6



TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.5	484.7	485.8	487.0	488.2	489.1	489.7	490.3	491.0	491.6	491.5
115°	562.2	562.9	563.6	564.2	564.9	565.2	564.9	564.7	564.5	564.2	564.7
117.5°	633.3	634.1	635.1	635.9	636.8	637.5	638.0	638.5	639.0	639.5	639.4
120°	681.3	682.2	683.1	684.0	684.8	685.2	685.0	684.8	684.5	684.3	684.8
122.5°	726.1	726.7	727.2	727.7	728.2	728.7	729.0	729.3	729.6	730.0	730.2
125°	790.3	791.3	792.1	793.0	793.9	794.1	793.7	793.2	792.8	792.4	793.0
127.5°	851.2	851.4	851.6	851.9	852.0	852.6	853.7	854.7	855.7	856.8	856.6
130°	890.4	890.6	890.9	891.0	891.3	891.7	892.4	893.0	893.7	894.4	894.6
132.5°	926.4	926.8	927.2	927.6	928.0	928.7	929.4	930.3	931.2	932.0	932.2
135°	980.4	980.2	980.0	979.7	979.6	979.9	980.8	981.6	982.6	983.4	983.9
137.5°	1028.3	1028.4	1028.5	1028.6	1028.6	1029.2	1030.1	1031.1	1032.1	1033.0	1033.5
140°	1059.5	1059.9	1060.3	1060.8	1061.3	1061.7	1062.1	1062.6	1063.0	1063.5	1064.1
142.5°	1087.4	1088.3	1089.1	1089.9	1090.7	1091.2	1091.5	1091.7	1092.0	1092.3	1092.8
145°	1130.5	1131.2	1131.9	1132.5	1133.2	1133.5	1133.5	1133.5	1133.5	1133.5	1133.8
147.5°	1164.7	1166.0	1167.2	1168.5	1169.7	1170.2	1170.0	1169.8	1169.5	1169.3	1169.5
150°	1189.6	1190.4	1191.3	1192.2	1193.1	1193.4	1193.2	1193.0	1192.7	1192.5	1192.5
152.5°	1210.3	1211.1	1211.8	1212.5	1213.1	1213.3	1213.0	1212.5	1212.1	1211.8	1212.1
155°	1239.6	1239.8	1240.0	1240.2	1240.4	1240.2	1239.6	1238.9	1238.2	1237.5	1238.5
157.5°	1264.1	1264.0	1263.9	1263.8	1263.6	1263.2	1262.4	1261.7	1260.9	1260.2	1261.3
160°	1278.6	1277.9	1277.2	1276.6	1275.9	1275.5	1275.2	1275.0	1274.8	1274.5	1275.9
162.5°	1291.3	1290.6	1289.7	1288.8	1288.0	1287.5	1287.2	1287.0	1286.8	1286.6	1287.9
165°	1307.6	1306.5	1305.4	1304.2	1303.1	1302.6	1302.6	1302.6	1302.6	1302.6	1304.3
167.5°	1320.3	1319.2	1318.1	1316.9	1315.8	1315.1	1315.0	1314.8	1314.7	1314.6	1316.6
170°	1327.6	1326.3	1324.9	1323.6	1322.2	1321.7	1321.9	1322.2	1322.3	1322.6	1324.4
172.5°	1332.4	1331.0	1329.7	1328.4	1327.1	1326.5	1326.7	1327.0	1327.1	1327.4	1329.1
175°	1337.6	1336.3	1334.9	1333.6	1332.2	1331.7	1331.9	1332.1	1332.4	1332.6	1334.6
177.5°	1340.0	1338.8	1337.5	1336.3	1335.0	1334.6	1334.9	1335.2	1335.7	1336.0	1337.4
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6



TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	14.9	15.0	15.1	15.2	15.5	15.8	16.0	16.3
90°	24.7	26.0	27.4	28.2	28.7	29.1	29.5	30.0
92.5°	23.8	25.2	26.5	27.3	27.4	27.5	27.6	27.6
95°	24.7	26.0	27.4	28.2	28.3	28.6	28.8	29.0
97.5°	26.7	26.8	26.9	27.1	27.4	27.6	27.8	28.0
100°	36.4	32.7	28.9	27.1	27.4	27.6	27.8	28.0
102.5°	130.5	89.8	49.0	28.7	28.7	28.8	28.8	28.8
105°	316.2	318.1	320.1	317.1	309.1	301.1	293.2	285.2
107.5°	391.2	392.1	393.0	394.0	394.9	395.7	396.5	397.4
110°	442.1	442.6	443.0	443.5	444.2	444.9	445.6	446.2



TEST NUMBER: P332952-935

CATALOG NUMBER: SA4XXRDIP-C795D1205U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	491.5	491.4	491.3	491.6	492.5	493.4	494.2	495.0
115°	565.2	565.6	566.0	566.3	566.3	566.3	566.3	566.3
117.5°	639.3	639.2	639.1	639.0	638.9	638.9	638.8	638.7
120°	685.2	685.6	686.0	686.0	685.6	685.2	684.8	684.3
122.5°	730.5	730.7	731.0	730.9	730.5	730.0	729.5	729.1
125°	793.7	794.4	795.0	795.5	795.7	795.9	796.2	796.3
127.5°	856.5	856.4	856.3	856.1	855.9	855.7	855.6	855.4
130°	894.8	895.1	895.3	895.4	895.4	895.4	895.4	895.4
132.5°	932.5	932.7	932.9	932.9	932.7	932.5	932.4	932.2
135°	984.3	984.7	985.2	985.7	986.1	986.5	987.0	987.4
137.5°	1034.1	1034.5	1035.0	1035.2	1035.1	1034.9	1034.7	1034.7
140°	1064.8	1065.5	1066.2	1066.6	1066.8	1067.0	1067.2	1067.5
142.5°	1093.3	1093.7	1094.2	1094.5	1094.6	1094.6	1094.7	1094.7
145°	1133.9	1134.2	1134.4	1134.7	1135.1	1135.6	1136.1	1136.5
147.5°	1169.7	1169.8	1170.0	1170.2	1170.4	1170.7	1170.9	1171.1
150°	1192.5	1192.5	1192.5	1192.7	1192.8	1193.1	1193.3	1193.5
152.5°	1212.5	1212.8	1213.1	1213.2	1213.1	1213.0	1212.9	1212.7
155°	1239.3	1240.2	1241.1	1241.2	1240.5	1239.8	1239.2	1238.5
157.5°	1262.5	1263.6	1264.8	1264.8	1263.6	1262.5	1261.3	1260.2
160°	1277.2	1278.6	1279.9	1279.9	1278.6	1277.2	1275.9	1274.5
162.5°	1289.3	1290.6	1291.9	1291.8	1290.3	1288.8	1287.3	1285.7
165°	1306.1	1307.9	1309.7	1309.6	1307.6	1305.5	1303.6	1301.6
167.5°	1318.5	1320.4	1322.4	1322.2	1320.1	1317.8	1315.6	1313.4
170°	1326.1	1327.9	1329.7	1329.5	1327.2	1325.0	1322.8	1320.6
172.5°	1330.9	1332.7	1334.5	1334.2	1331.8	1329.4	1327.0	1324.6
175°	1336.6	1338.6	1340.6	1340.2	1337.6	1334.9	1332.2	1329.6
177.5°	1338.9	1340.2	1341.7	1341.4	1339.2	1337.0	1334.9	1332.8
180°	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6	1337.6

(END OF REPORT)