

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904980

Luminaire Tested: DFN2DIP-4P3F0-050D060US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904980
REPORT IS A COMBINATION OF REPORTS P899076 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D060US835-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9560.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44			38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38			33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33			28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28			25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25			22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22			19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16			14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2355	2355	2355
5°	2357	2316	2332
10°	2332	2269	2255
15°	2299	2193	2137
20°	2255	2088	1993
25°	2210	1971	1853
30°	2150	1851	1676
35°	2091	1722	1521
40°	2031	1588	1343
45°	1962	1441	1182
50°	1890	1292	1025
55°	1814	1133	874
60°	1727	967	718
65°	1626	799	646
70°	1504	642	583
75°	1351	562	529
80°	1129	467	456
85°	766	304	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1962 cd/sqm

TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	2.0
10°-20°	531.7	5.6
20°-30°	746.5	7.8
30°-40°	813.7	8.5
40°-50°	747.9	7.8
50°-60°	587.3	6.1
60°-70°	382.3	4.0
70°-80°	196.8	2.1
80°-90°	55.6	0.6
90°-100°	117.4	1.2
100°-110°	373.1	3.9
110°-120°	638.5	6.7
120°-130°	839.7	8.8
130°-140°	942.5	9.9
140°-150°	924.2	9.7
150°-160°	775.3	8.1
160°-170°	514.2	5.4
170°-180°	179.7	1.9
0°-30°	1471.8	15.4
0°-40°	2285.5	23.9
0°-60°	3620.7	37.9
0°-90°	4255.4	44.5
90°-120°	1129.0	11.8
90°-150°	3835.4	40.1
90°-180°	5305.0	55.5
0°-180°	9560.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	92
90°	2	21	56	53	54	9
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	

TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1



TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6

TEST NUMBER: P904980

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.55	10.34	10.56	11.35	12.70	5.51	6.30	6.52	7.32	8.67
	3H	11.22	11.93	12.24	12.95	14.32	6.69	7.40	7.71	8.42	9.79
	4H	11.83	12.49	12.86	13.52	14.90	7.14	7.80	8.17	8.83	10.21
	6H	12.24	12.85	13.28	13.89	15.28	7.45	8.06	8.49	9.09	10.48
	8H	12.37	12.95	13.41	14.00	15.38	7.54	8.12	8.58	9.17	10.55
	12H	12.42	12.98	13.48	14.02	15.43	7.57	8.13	8.63	9.17	10.58
4H	2H	9.56	10.23	10.60	11.26	12.63	6.10	6.77	7.14	7.79	9.17
	3H	11.38	11.94	12.43	12.99	14.38	7.44	7.99	8.49	9.05	10.44
	4H	12.07	12.58	13.12	13.62	15.04	7.98	8.49	9.03	9.53	10.95
	6H	12.58	13.01	13.64	14.08	15.49	8.39	8.83	9.45	9.90	11.30
	8H	12.75	13.16	13.81	14.22	15.64	8.52	8.92	9.58	9.98	11.41
	12H	12.84	13.21	13.92	14.28	15.71	8.57	8.94	9.65	10.02	11.45
8H	4H	12.03	12.44	13.10	13.50	14.93	8.26	8.66	9.32	9.72	11.15
	6H	12.59	12.93	13.68	14.03	15.45	8.76	9.10	9.85	10.20	11.62
	8H	12.81	13.10	13.90	14.19	15.63	8.95	9.24	10.04	10.33	11.77
	12H	12.94	13.20	14.04	14.28	15.76	9.06	9.32	10.16	10.40	11.88
12H	4H	11.98	12.35	13.06	13.43	14.86	8.26	8.62	9.34	9.70	11.13
	6H	12.57	12.86	13.66	13.95	15.39	8.81	9.11	9.90	10.19	11.63
	8H	12.78	13.04	13.88	14.12	15.61	9.01	9.27	10.11	10.36	11.84

END OF REPORT