

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332929-935

Luminaire Tested: **SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332929-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3856.0 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	72	
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65	65	65	65	61	
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55	55	55	55	52	
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	48	48	48	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	39	36	36	36	36	33	
6	67	55	47	41	64	53	45	39	48	42	37	44	38	34	40	35	32	32	32	32	30	
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	29	29	29	26	
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26	26	26	26	24	
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	21	21	21	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	2.9
10°-20°	313.3	8.1
20°-30°	452.4	11.7
30°-40°	512.8	13.3
40°-50°	495.2	12.8
50°-60°	411.8	10.7
60°-70°	284.4	7.4
70°-80°	144.1	3.7
80°-90°	38.2	1.0
90°-100°	25.9	0.7
100°-110°	76.9	2.0
110°-120°	130.5	3.4
120°-130°	172.0	4.5
130°-140°	193.2	5.0
140°-150°	189.8	4.9
150°-160°	159.7	4.1
160°-170°	106.2	2.8
170°-180°	37.2	1.0
0°-30°	878.1	22.8
0°-40°	1390.9	36.1
0°-60°	2297.9	59.6
0°-90°	2764.6	71.7
90°-120°	233.3	6.0
90°-150°	788.3	20.4
90°-180°	1091.0	28.3
0°-180°	3856.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	1	4	7	8	9	3
95°	18	21	23	24	24	20
105°	71	71	72	73	74	75
115°	133	133	132	132	132	131
125°	193	193	193	192	192	172
135°	249	251	251	250	250	193
145°	303	304	304	304	303	189
155°	347	347	347	348	347	160
165°	378	377	376	378	377	106
175°	393	391	391	393	391	37
180°	393	393	393	393	393	



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.0	15.8	14.7	13.6	12.4	11.8	11.8	11.7	11.6	11.6	11.5
90°	0.9	1.6	2.4	3.2	3.9	4.6	5.1	5.6	6.1	6.7	7.1
92.5°	6.5	7.4	8.2	9.0	9.9	10.5	10.9	11.3	11.7	12.1	12.3
95°	18.3	18.9	19.5	20.1	20.7	21.3	21.7	22.2	22.6	23.2	23.3
97.5°	31.9	32.4	32.9	33.3	33.8	34.4	34.9	35.5	36.0	36.6	36.9
100°	42.6	42.9	43.1	43.4	43.7	44.1	44.7	45.4	46.0	46.6	46.7
102.5°	53.8	53.9	54.0	54.2	54.2	54.6	55.1	55.7	56.2	56.7	57.0
105°	70.9	70.9	71.0	71.1	71.1	71.3	71.6	71.9	72.2	72.4	72.6
107.5°	88.9	88.9	89.0	89.1	89.2	89.2	89.3	89.3	89.4	89.4	89.5
110°	101.0	101.2	101.3	101.4	101.5	101.6	101.5	101.4	101.3	101.3	101.2



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.5	113.4	113.2	113.2
115°	132.7	132.7	132.7	132.7	132.7	132.6	132.4	132.3	132.2	132.1	132.0
117.5°	150.5	150.6	150.7	150.7	150.8	150.8	150.7	150.6	150.4	150.3	150.2
120°	162.5	162.7	163.0	163.2	163.6	163.6	163.4	163.2	163.0	162.8	162.5
122.5°	174.9	175.0	175.1	175.2	175.3	175.3	175.2	175.1	175.0	175.0	174.7
125°	193.2	193.2	193.2	193.2	193.2	193.1	193.1	193.0	193.0	192.9	192.8
127.5°	209.8	210.0	210.3	210.4	210.6	210.7	210.6	210.4	210.3	210.3	210.1
130°	221.5	221.7	221.9	222.1	222.3	222.4	222.4	222.4	222.4	222.4	222.3
132.5°	233.4	233.6	233.7	233.8	234.0	234.0	234.0	233.9	233.9	233.8	233.7
135°	249.2	249.6	249.9	250.4	250.8	251.0	251.0	251.0	251.0	251.0	250.9
137.5°	266.3	266.6	266.7	266.9	267.1	267.3	267.3	267.4	267.6	267.7	267.5
140°	277.8	277.9	278.0	278.2	278.4	278.4	278.4	278.4	278.4	278.4	278.4
142.5°	288.3	288.3	288.5	288.6	288.8	288.9	288.8	288.7	288.7	288.6	288.6
145°	302.7	303.0	303.2	303.5	303.8	304.0	304.0	304.1	304.2	304.3	304.2
147.5°	317.1	317.5	317.7	318.1	318.4	318.5	318.5	318.4	318.4	318.3	318.2
150°	325.9	326.1	326.4	326.7	326.9	327.1	327.1	327.1	327.1	327.1	327.1
152.5°	334.2	334.3	334.4	334.6	334.8	334.8	334.9	335.0	335.0	335.1	335.3
155°	346.8	346.8	346.8	346.8	346.8	346.8	346.7	346.6	346.6	346.6	346.8
157.5°	357.6	357.4	357.3	357.2	357.1	357.0	357.0	357.0	357.0	357.0	357.1
160°	363.9	363.8	363.8	363.7	363.6	363.5	363.5	363.4	363.3	363.3	363.5
162.5°	369.7	369.5	369.4	369.2	369.0	368.9	368.9	368.8	368.7	368.6	369.0
165°	377.5	377.4	377.2	376.9	376.8	376.6	376.4	376.3	376.2	376.1	376.4
167.5°	383.6	383.3	383.1	382.7	382.5	382.3	382.4	382.4	382.4	382.4	382.8
170°	387.0	386.7	386.3	386.0	385.6	385.6	385.6	385.6	385.7	385.8	386.2
172.5°	389.4	389.2	388.8	388.6	388.3	388.1	388.1	388.2	388.2	388.2	388.7
175°	392.8	392.4	392.1	391.8	391.4	391.2	391.2	391.1	391.1	391.0	391.4
177.5°	393.9	393.6	393.3	393.0	392.8	392.7	392.7	392.7	392.7	392.7	393.0
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	11.5	11.4	11.3	11.4	11.5	11.7	11.9	12.1
90°	7.5	7.9	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	12.6	12.7	13.0	13.2	13.3	13.3	13.4	13.5
95°	23.5	23.8	23.9	24.0	24.0	24.0	24.0	24.0
97.5°	37.0	37.3	37.5	37.6	37.6	37.6	37.6	37.6
100°	46.8	46.9	47.1	47.2	47.2	47.2	47.2	47.2
102.5°	57.2	57.3	57.5	57.7	57.7	57.8	57.8	57.9
105°	72.8	73.0	73.2	73.4	73.6	73.9	74.0	74.2
107.5°	89.8	90.0	90.1	90.2	90.2	90.2	90.2	90.1
110°	101.1	100.9	100.7	100.8	101.0	101.3	101.4	101.6



TEST NUMBER: P332929-935

CATALOG NUMBER: SA4XXRDIP-C795D365U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	113.2	113.1	113.1	113.1	113.2	113.2	113.2	113.3
115°	131.9	131.8	131.7	131.7	131.6	131.6	131.5	131.5
117.5°	149.9	149.6	149.5	149.3	149.1	149.0	148.9	148.7
120°	162.1	161.8	161.4	161.4	161.4	161.6	161.7	161.9
122.5°	174.5	174.3	174.0	173.7	173.6	173.3	173.1	172.8
125°	192.6	192.5	192.3	192.2	192.1	191.9	191.8	191.7
127.5°	210.0	209.8	209.7	209.6	209.5	209.4	209.2	209.1
130°	222.1	222.0	221.9	221.6	221.4	221.1	220.8	220.6
132.5°	233.6	233.4	233.3	233.2	233.1	233.0	232.9	232.7
135°	250.7	250.6	250.5	250.3	250.1	249.9	249.7	249.5
137.5°	267.3	267.2	267.0	266.9	266.9	267.0	267.0	267.1
140°	278.3	278.2	278.1	278.0	278.0	277.9	277.8	277.8
142.5°	288.6	288.6	288.5	288.5	288.5	288.5	288.5	288.5
145°	304.1	304.0	304.0	303.8	303.7	303.4	303.2	303.1
147.5°	318.2	318.1	318.1	318.1	318.0	317.9	317.8	317.8
150°	327.1	327.1	327.1	327.0	327.0	326.9	326.8	326.7
152.5°	335.4	335.6	335.8	335.7	335.5	335.4	335.2	335.0
155°	347.1	347.3	347.6	347.6	347.3	347.1	346.8	346.6
157.5°	357.3	357.6	357.7	357.7	357.5	357.3	357.1	356.8
160°	363.7	363.9	364.1	364.0	363.7	363.3	363.0	362.7
162.5°	369.4	369.7	370.1	370.1	369.8	369.5	369.1	368.8
165°	376.9	377.3	377.6	377.7	377.5	377.2	376.9	376.7
167.5°	383.2	383.6	384.0	384.0	383.6	383.1	382.7	382.3
170°	386.6	387.0	387.4	387.4	386.9	386.4	386.0	385.5
172.5°	389.2	389.6	390.0	390.0	389.6	389.1	388.7	388.1
175°	391.9	392.4	392.9	392.9	392.4	391.9	391.4	391.0
177.5°	393.4	393.8	394.2	394.2	393.7	393.3	392.9	392.4
180°	393.4	393.4	393.4	393.4	393.4	393.4	393.4	393.4

(END OF REPORT)