

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904988

Luminaire Tested: DFN2DIP-4P3F0-060D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904988
REPORT IS A COMBINATION OF REPORTS P899048 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D030US835-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7755.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66		
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	57		
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52	49		
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45	42		
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40	36		
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35	32		
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31	29		
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28	26		
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25	23		
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23	21		
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2826	2826	2826
5°	2829	2779	2798
10°	2799	2723	2706
15°	2759	2631	2564
20°	2706	2505	2391
25°	2652	2365	2224
30°	2580	2221	2012
35°	2509	2066	1825
40°	2437	1906	1612
45°	2354	1729	1418
50°	2268	1550	1230
55°	2177	1360	1048
60°	2072	1161	862
65°	1952	958	775
70°	1805	770	700
75°	1621	675	635
80°	1355	560	547
85°	919	365	406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2354 cd/sqm

TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.4	3.0
10°-20°	638.0	8.2
20°-30°	895.7	11.6
30°-40°	976.4	12.6
40°-50°	897.4	11.6
50°-60°	704.8	9.1
60°-70°	458.8	5.9
70°-80°	236.1	3.0
80°-90°	63.0	0.8
90°-100°	58.7	0.8
100°-110°	186.5	2.4
110°-120°	319.2	4.1
120°-130°	419.8	5.4
130°-140°	471.2	6.1
140°-150°	462.1	6.0
150°-160°	387.7	5.0
160°-170°	257.1	3.3
170°-180°	89.9	1.2
0°-30°	1766.2	22.8
0°-40°	2742.6	35.4
0°-60°	4344.8	56.0
0°-90°	5102.7	65.8
90°-120°	564.5	7.3
90°-150°	1917.7	24.7
90°-180°	2652.0	34.2
0°-180°	7755.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2480	2480	2480	2480	2480	
5°	2480	2469	2439	2460	2453	235
15°	2359	2334	2258	2215	2193	665
25°	2141	2069	1921	1829	1795	985
35°	1845	1730	1533	1391	1342	1155
45°	1508	1358	1122	963	909	1165
55°	1147	972	729	595	552	1025
65°	774	592	390	314	307	768
75°	413	256	180	164	162	437
85°	96	49	43	43	43	111
90°	1	10	28	26	27	8
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.8	2479.8	2479.8	2479.8	2479.8
2.5°	2491.0	2479.8	2455.0	2477.6	2473.1
5°	2479.8	2468.6	2439.3	2459.6	2452.9
7.5°	2459.6	2446.2	2414.8	2423.6	2412.4
10°	2432.6	2416.9	2372.2	2365.3	2351.9
12.5°	2399.1	2378.8	2318.1	2304.8	2280.0
15°	2358.6	2333.8	2257.6	2215.0	2192.6
17.5°	2311.5	2275.5	2181.2	2131.9	2096.0
20°	2257.6	2212.6	2100.5	2044.5	1995.0
22.5°	2199.3	2147.6	2017.4	1941.2	1907.6
25°	2141.0	2069.1	1921.0	1829.1	1795.3
27.5°	2071.5	1995.0	1831.2	1725.7	1674.1
30°	1997.4	1911.9	1732.4	1618.1	1557.4
32.5°	1925.5	1822.2	1638.4	1503.6	1447.4
35°	1844.8	1730.3	1532.9	1391.4	1341.9
37.5°	1766.2	1642.6	1434.1	1279.1	1223.1
40°	1683.1	1548.6	1330.7	1171.4	1113.1
42.5°	1597.9	1454.3	1227.6	1061.4	1005.5
45°	1508.1	1357.6	1122.2	962.6	908.8
47.5°	1422.9	1263.6	1021.2	861.7	812.4
50°	1328.6	1169.3	922.4	767.4	720.5
52.5°	1236.4	1068.1	828.1	680.0	637.4
55°	1146.7	971.7	729.3	594.8	552.1
57.5°	1054.8	875.2	641.9	516.2	480.2
60°	960.5	781.0	549.8	435.5	399.5
62.5°	868.6	689.1	471.2	363.6	345.7
65°	774.3	592.4	390.5	314.3	307.4
67.5°	684.5	502.6	314.3	276.0	269.3
70°	590.2	415.2	260.2	237.9	228.8
72.5°	500.5	334.3	217.6	199.8	195.2
75°	412.9	255.7	179.5	163.8	161.7
77.5°	325.5	181.7	141.4	132.4	127.9
80°	244.5	130.2	107.6	98.8	98.8
82.5°	170.5	87.6	74.0	69.5	69.5
85°	96.4	49.3	42.6	42.6	42.6
87.5°	36.0	17.9	17.9	15.7	15.7
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6

TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P904988

CATALOG NUMBER: DFN2DIP-4P3F0-060D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.08	13.06	12.90	13.89	14.92	8.04	9.02	8.86	9.86	10.88
	3H	13.77	14.64	14.60	15.49	16.54	9.24	10.11	10.07	10.96	12.01
	4H	14.38	15.20	15.23	16.05	17.12	9.69	10.52	10.54	11.37	12.43
	6H	14.81	15.57	15.66	16.42	17.50	10.01	10.77	10.87	11.63	12.71
	8H	14.93	15.66	15.80	16.53	17.61	10.10	10.83	10.97	11.70	12.78
	12H	15.00	15.69	15.87	16.56	17.66	10.15	10.84	11.02	11.71	12.81
4H	2H	12.12	12.94	12.97	13.79	14.86	8.65	9.48	9.51	10.33	11.40
	3H	13.95	14.64	14.82	15.52	16.61	10.01	10.70	10.87	11.58	12.66
	4H	14.65	15.27	15.52	16.15	17.26	10.56	11.18	11.43	12.06	13.17
	6H	15.17	15.70	16.06	16.61	17.72	10.98	11.52	11.87	12.42	13.54
	8H	15.34	15.84	16.24	16.74	17.87	11.11	11.61	12.00	12.51	13.64
	12H	15.44	15.89	16.35	16.81	17.94	11.18	11.63	12.09	12.55	13.68
8H	4H	14.63	15.13	15.52	16.03	17.15	10.85	11.35	11.74	12.25	13.37
	6H	15.19	15.61	16.11	16.55	17.67	11.36	11.78	12.28	12.72	13.84
	8H	15.41	15.77	16.34	16.71	17.85	11.55	11.92	12.48	12.85	13.99
	12H	15.55	15.87	16.48	16.80	17.99	11.67	11.99	12.60	12.92	14.11
12H	4H	14.58	15.04	15.50	15.95	17.09	10.86	11.31	11.77	12.23	13.36
	6H	15.17	15.53	16.10	16.47	17.61	11.41	11.78	12.34	12.71	13.86
	8H	15.39	15.71	16.32	16.64	17.83	11.62	11.95	12.55	12.87	14.07