

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332932-935

Luminaire Tested: **SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332932-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4636.4 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332932-935
CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	54	52	50	46
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33	30
6	66	54	46	40	62	51	44	39	46	40	35	41	36	32	36	32	29	26
7	61	49	41	36	57	47	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23	21
9	53	41	34	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	38	30	26	47	36	29	25	32	27	23	29	24	21	26	22	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9175	9175	9175	9175
5°	10643	9203	8135	9203
10°	12591	9163	7260	9163
15°	14543	9078	6238	9078
20°	16192	8961	5642	8961
25°	16715	8847	5238	8847
30°	14632	8708	4994	8708
35°	11391	8502	4847	8502
40°	8541	8266	4769	8266
45°	6744	7889	4727	7889
50°	5693	7454	4589	7454
55°	4963	6973	4345	6973
60°	4466	6476	3846	6476
65°	3935	5939	3307	5939
70°	3545	5384	2984	5384
75°	2969	4769	2542	4769
80°	2515	4068	2385	4068
85°	2121	3186	2121	3186



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.1	2.4
10°-20°	332.2	7.2
20°-30°	519.5	11.2
30°-40°	577.6	12.5
40°-50°	512.4	11.1
50°-60°	399.3	8.6
60°-70°	261.4	5.6
70°-80°	128.6	2.8
80°-90°	33.6	0.7
90°-100°	41.9	0.9
100°-110°	124.1	2.7
110°-120°	210.6	4.5
120°-130°	277.7	6.0
130°-140°	311.8	6.7
140°-150°	306.4	6.6
150°-160°	257.7	5.6
160°-170°	171.5	3.7
170°-180°	60.0	1.3
0°-30°	961.8	20.7
0°-40°	1539.4	33.2
0°-60°	2451.2	52.9
0°-90°	2874.8	62.0
90°-120°	376.5	8.1
90°-150°	1272.4	27.4
90°-180°	1762.0	38.0
0°-180°	4636.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1136	1136	1136	1136	1136	
5°	1313	1136	1004	1136	1313	133
15°	1740	1086	746	1086	1740	495
25°	1876	993	588	993	1876	832
35°	1156	863	492	863	1156	724
45°	591	691	414	691	591	468
55°	353	495	309	495	353	321
65°	206	311	173	311	206	207
75°	95	153	82	153	95	105
85°	23	34	23	34	23	26
90°	15	2	15	2	15	9
95°	39	29	39	29	39	40
105°	120	114	120	114	120	126
115°	212	214	212	214	212	210
125°	309	312	309	312	309	276
135°	403	402	403	402	403	311
145°	489	489	489	489	489	306
155°	559	560	559	560	559	257
165°	608	609	608	609	608	171
175°	631	634	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1198.8	1202.1	1198.8	1198.4	1194.8	1193.7	1192.2	1187.5	1178.6	1173.5	1174.7
5°	1313.3	1324.7	1318.4	1317.4	1307.3	1297.3	1290.8	1276.2	1260.6	1250.1	1241.4
7.5°	1445.7	1452.3	1448.3	1441.8	1425.6	1416.3	1401.4	1382.2	1354.3	1332.9	1313.4
10°	1535.9	1541.4	1539.5	1527.6	1515.7	1491.4	1477.6	1450.7	1415.4	1387.5	1361.4
12.5°	1624.4	1630.4	1614.2	1614.8	1592.2	1573.1	1551.3	1517.3	1476.6	1440.6	1407.9
15°	1740.1	1732.8	1732.8	1723.5	1698.4	1671.8	1649.4	1613.7	1562.4	1519.3	1474.0
17.5°	1830.6	1833.1	1829.4	1807.8	1788.0	1760.5	1719.3	1677.7	1630.0	1572.3	1526.0
20°	1884.7	1884.7	1880.7	1866.0	1840.4	1811.0	1766.6	1721.3	1660.9	1602.7	1550.5
22.5°	1906.8	1908.2	1903.3	1891.3	1868.2	1839.6	1801.8	1755.8	1693.4	1628.0	1563.3
25°	1876.5	1885.2	1886.1	1882.9	1876.0	1858.6	1826.2	1779.0	1723.1	1652.2	1582.5
27.5°	1722.9	1733.8	1743.4	1759.3	1780.4	1791.3	1792.8	1768.8	1720.1	1651.7	1581.7
30°	1569.7	1578.9	1608.6	1647.5	1677.8	1705.3	1729.1	1735.5	1708.1	1646.7	1573.0
32.5°	1399.7	1412.2	1442.0	1483.8	1534.2	1580.7	1634.2	1661.5	1660.8	1623.9	1555.7
35°	1155.8	1164.9	1192.4	1236.4	1296.8	1366.0	1450.7	1516.6	1561.5	1558.2	1516.6
37.5°	932.1	942.5	970.3	1006.7	1065.3	1150.9	1232.9	1323.7	1406.7	1453.3	1439.4
40°	810.5	811.0	838.0	875.6	930.5	1005.1	1094.4	1195.2	1287.6	1363.2	1377.9
42.5°	714.5	714.6	732.5	772.9	812.5	882.8	968.0	1068.1	1176.3	1263.6	1302.4
45°	590.7	594.9	609.5	633.8	664.9	724.4	792.6	885.6	1006.9	1110.4	1175.0
47.5°	500.2	506.3	515.6	535.4	560.2	599.9	656.3	739.8	838.5	952.4	1044.2
50°	453.3	454.3	466.1	477.2	498.7	530.3	579.7	649.3	739.9	849.5	951.6
52.5°	413.0	412.8	420.0	433.9	451.4	476.0	516.0	579.4	659.8	757.9	863.2
55°	352.6	354.9	360.4	371.3	384.6	402.1	433.6	481.3	544.5	628.3	723.9
57.5°	306.6	307.8	312.1	316.8	329.0	341.6	365.3	398.4	451.7	520.3	609.5
60°	276.6	277.1	278.4	285.2	294.9	306.8	322.8	350.8	395.6	458.4	528.9
62.5°	247.3	248.1	250.2	255.2	262.7	270.9	287.7	310.1	347.2	400.9	464.4
65°	206.0	206.6	209.7	211.5	217.5	224.8	237.2	252.3	277.9	322.8	370.9
67.5°	172.2	172.2	172.4	174.9	178.9	183.8	191.2	203.3	222.7	250.2	292.6
70°	150.2	150.2	151.1	152.5	154.8	158.9	163.0	172.2	186.4	208.8	241.3
72.5°	129.7	130.0	131.0	131.2	132.4	135.8	138.9	144.7	155.2	172.2	198.5
75°	95.2	96.6	98.9	100.7	103.1	102.5	105.8	109.4	112.6	122.7	137.8
77.5°	70.9	70.2	70.4	72.0	72.2	72.8	75.0	77.8	80.2	85.0	90.4
80°	54.1	54.1	55.4	55.9	55.4	55.9	58.1	59.5	60.4	62.3	67.3
82.5°	40.8	41.6	41.2	41.6	41.8	42.3	44.3	44.5	45.5	46.1	48.3
85°	22.9	23.3	23.8	22.9	22.9	22.9	23.8	24.3	25.2	24.7	25.7
87.5°	11.0	10.6	10.9	10.8	11.2	10.8	11.0	11.6	10.7	10.9	10.8
90°	14.7	14.6	14.3	14.1	13.9	13.4	12.7	12.1	11.5	10.8	9.9
92.5°	21.8	21.7	21.5	21.4	21.3	21.0	20.7	20.2	19.8	19.5	18.9
95°	38.8	38.8	38.8	38.8	38.8	38.7	38.3	38.0	37.6	37.3	36.6
97.5°	60.8	60.8	60.8	60.8	60.8	60.6	60.2	59.8	59.4	59.1	58.1
100°	76.1	76.1	76.1	76.1	76.1	76.0	75.8	75.6	75.3	75.2	74.1
102.5°	93.4	93.3	93.2	93.2	93.1	92.8	92.6	92.2	92.0	91.6	90.7
105°	119.9	119.5	119.2	118.8	118.5	118.2	117.9	117.5	117.2	116.8	116.4
107.5°	145.6	145.6	145.6	145.6	145.7	145.5	145.2	144.9	144.6	144.3	144.2
110°	164.0	163.7	163.3	163.1	162.7	162.6	162.9	163.1	163.3	163.5	163.7



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.9	182.8	182.7	182.7	182.6	182.6	182.6	182.7	182.7	182.8	183.0
115°	212.2	212.2	212.3	212.5	212.6	212.7	212.8	212.9	213.0	213.1	213.4
117.5°	240.0	240.2	240.5	240.6	240.9	241.2	241.6	241.9	242.3	242.7	242.8
120°	261.2	261.1	260.8	260.6	260.4	260.5	261.1	261.7	262.2	262.7	263.0
122.5°	279.0	279.3	279.7	280.1	280.5	280.9	281.3	281.6	282.0	282.4	282.5
125°	309.4	309.6	309.8	310.0	310.2	310.5	310.6	310.9	311.1	311.3	311.4
127.5°	337.6	337.8	337.9	338.1	338.3	338.5	338.7	338.9	339.1	339.3	339.5
130°	356.0	356.5	356.9	357.3	357.7	358.1	358.3	358.5	358.8	359.0	359.0
132.5°	375.7	375.8	376.0	376.2	376.3	376.6	376.8	377.0	377.2	377.5	377.5
135°	402.7	403.0	403.3	403.6	404.0	404.2	404.5	404.7	404.9	405.1	405.1
137.5°	431.1	431.0	430.9	430.8	430.8	430.9	431.2	431.4	431.8	432.0	431.9
140°	448.3	448.5	448.6	448.7	448.8	448.9	449.0	449.1	449.2	449.4	449.4
142.5°	465.6	465.6	465.7	465.7	465.7	465.7	465.8	465.8	465.8	465.8	465.9
145°	489.1	489.4	489.7	490.1	490.4	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	512.9	513.0	513.1	513.2	513.3	513.4	513.5	513.6	513.7	513.8	513.8
150°	527.4	527.5	527.6	527.7	527.9	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	540.8	541.1	541.3	541.7	541.9	541.9	541.7	541.4	541.1	540.9	540.8
155°	559.3	559.7	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3	559.5
157.5°	575.9	576.3	576.7	577.0	577.4	577.5	577.1	576.8	576.4	576.1	576.2
160°	585.4	585.9	586.4	587.0	587.5	587.6	587.3	587.0	586.7	586.3	586.4
162.5°	595.2	595.7	596.2	596.8	597.4	597.4	596.8	596.2	595.6	595.0	595.1
165°	608.0	608.4	608.8	609.2	609.7	609.6	608.9	608.3	607.6	607.0	607.2
167.5°	617.1	617.8	618.5	619.1	619.7	619.8	619.1	618.5	617.9	617.2	617.2
170°	622.2	622.9	623.7	624.5	625.3	625.3	624.7	624.0	623.4	622.7	622.6
172.5°	626.5	627.2	628.0	628.8	629.6	629.6	628.9	628.1	627.3	626.6	626.5
175°	631.0	631.8	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0	631.1
177.5°	633.4	634.0	634.8	635.5	636.2	636.2	635.6	635.0	634.4	633.8	633.8
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1171.0	1165.9	1163.3	1157.4	1150.5	1146.8	1143.5	1138.8	1132.5	1125.9	1121.1
5°	1230.4	1219.4	1205.7	1189.2	1174.6	1160.4	1148.0	1135.7	1121.5	1106.7	1092.1
7.5°	1291.4	1269.8	1246.5	1219.4	1193.2	1169.2	1147.3	1126.2	1102.3	1081.1	1061.6
10°	1333.9	1304.6	1272.0	1237.8	1203.4	1173.6	1144.4	1117.8	1088.5	1062.4	1040.3
12.5°	1368.3	1333.9	1294.8	1252.0	1210.7	1174.7	1141.0	1106.4	1073.1	1044.7	1015.5
15°	1425.5	1378.3	1325.7	1274.4	1220.8	1171.8	1126.4	1086.2	1048.2	1008.3	980.4
17.5°	1464.7	1408.8	1344.8	1283.1	1219.9	1162.1	1109.8	1061.8	1018.0	977.2	944.0
20°	1488.2	1426.4	1355.4	1285.4	1214.4	1152.5	1096.2	1043.1	997.8	953.8	919.5
22.5°	1501.4	1433.0	1355.4	1282.0	1208.5	1141.6	1079.8	1024.4	975.1	931.1	893.1
25°	1505.6	1432.4	1353.1	1268.9	1188.3	1117.3	1053.2	993.2	938.2	894.3	854.0
27.5°	1499.8	1413.5	1332.3	1245.9	1162.7	1087.9	1020.6	957.6	902.6	855.4	814.1
30°	1491.0	1398.4	1311.5	1221.7	1137.5	1065.6	994.5	934.1	876.9	827.9	786.3
32.5°	1471.9	1380.2	1286.5	1194.6	1109.2	1035.2	967.9	907.1	850.9	800.8	756.6
35°	1434.2	1341.3	1239.6	1145.2	1061.4	984.5	921.4	862.7	809.2	755.5	708.9
37.5°	1384.5	1289.5	1188.4	1085.0	1001.2	928.6	870.6	815.5	763.3	714.4	662.6
40°	1337.6	1251.0	1146.6	1044.0	957.9	887.9	834.3	784.4	731.8	683.2	631.5
42.5°	1280.7	1207.0	1101.6	998.6	913.6	846.1	796.3	747.4	699.5	652.5	598.5
45°	1186.0	1130.1	1031.2	932.3	846.7	779.8	734.0	691.0	648.8	604.0	553.2
47.5°	1077.4	1039.6	954.2	852.9	773.7	713.5	669.3	634.1	598.5	553.6	509.0
50°	1001.9	977.7	895.2	802.7	727.2	671.8	626.5	593.5	563.7	520.6	480.8
52.5°	921.4	908.4	838.8	750.4	677.3	623.0	584.3	554.7	524.5	488.8	451.5
55°	798.6	805.5	746.4	669.9	601.2	555.4	520.2	495.4	469.8	439.6	410.8
57.5°	673.1	698.2	658.6	591.4	527.0	484.7	458.2	437.4	415.9	390.8	366.2
60°	598.1	619.1	596.7	537.6	481.3	441.9	417.2	401.1	379.6	356.7	337.9
62.5°	524.8	547.3	534.0	486.3	434.0	400.1	378.3	363.4	347.4	327.4	307.9
65°	432.7	447.4	441.0	408.0	370.9	342.1	321.9	310.9	296.3	281.6	264.2
67.5°	331.4	359.7	356.0	338.5	306.4	283.9	270.7	261.0	247.6	236.8	224.9
70°	272.4	298.6	298.1	283.9	266.5	245.5	236.3	228.1	216.1	205.6	196.0
72.5°	223.0	246.9	250.5	239.6	227.6	211.7	202.9	197.3	185.7	178.5	170.7
75°	156.2	173.6	178.1	178.1	172.6	164.4	156.6	152.9	144.7	138.3	133.7
77.5°	102.4	113.4	120.5	122.2	123.0	120.3	113.8	111.2	105.0	102.6	98.2
80°	72.3	79.6	87.9	90.7	93.0	92.0	89.3	87.5	81.5	79.2	77.4
82.5°	50.0	54.1	60.8	66.8	66.2	68.6	66.2	64.7	60.3	59.4	57.6
85°	26.1	26.5	27.5	31.6	33.9	34.8	35.3	34.4	33.0	33.0	29.8
87.5°	10.6	10.1	10.6	10.4	10.5	11.8	12.7	12.7	11.9	11.0	10.2
90°	9.0	8.2	7.3	6.3	5.1	3.9	2.7	1.5	2.7	3.9	5.1
92.5°	18.3	17.7	17.0	16.0	14.6	13.3	11.9	10.5	11.9	13.3	14.6
95°	35.8	35.0	34.3	33.4	32.4	31.4	30.5	29.4	30.5	31.4	32.4
97.5°	57.3	56.3	55.4	54.6	53.8	53.0	52.3	51.5	52.3	53.0	53.8
100°	73.2	72.2	71.2	70.5	70.1	69.7	69.2	68.7	69.2	69.7	70.1
102.5°	89.8	88.9	88.1	87.5	87.3	87.1	87.0	86.8	87.0	87.1	87.3
105°	116.0	115.5	115.1	114.9	114.8	114.6	114.5	114.4	114.5	114.6	114.8
107.5°	144.1	144.0	144.0	144.0	143.8	143.6	143.5	143.4	143.5	143.6	143.8
110°	163.8	163.8	163.9	163.9	163.7	163.5	163.2	163.1	163.2	163.5	163.7



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	183.1	183.4	183.6	183.7	183.6	183.6	183.5	183.5	183.5	183.6	183.6
115°	213.5	213.8	214.0	214.1	214.1	214.1	214.1	214.1	214.1	214.1	214.1
117.5°	243.0	243.1	243.3	243.3	243.2	243.1	243.1	243.0	243.1	243.1	243.2
120°	263.4	263.7	264.1	264.0	263.6	263.1	262.7	262.3	262.7	263.1	263.6
122.5°	282.7	282.8	283.0	282.9	282.8	282.6	282.4	282.2	282.4	282.6	282.8
125°	311.6	311.7	311.8	311.9	311.9	311.9	311.9	311.9	311.9	311.9	311.9
127.5°	339.7	339.8	340.0	339.9	339.7	339.3	339.0	338.6	339.0	339.3	339.7
130°	359.0	359.0	359.0	358.8	358.5	358.2	357.8	357.5	357.8	358.2	358.5
132.5°	377.6	377.7	377.8	377.7	377.5	377.2	377.0	376.8	377.0	377.2	377.5
135°	405.1	405.1	405.1	404.8	404.2	403.5	402.9	402.2	402.9	403.5	404.2
137.5°	431.7	431.5	431.4	431.1	430.8	430.5	430.2	429.9	430.2	430.5	430.8
140°	449.4	449.4	449.4	449.2	449.0	448.8	448.6	448.3	448.6	448.8	449.0
142.5°	466.0	466.1	466.1	466.1	465.9	465.7	465.5	465.2	465.5	465.7	465.9
145°	490.9	490.8	490.6	490.3	489.9	489.5	489.0	488.6	489.0	489.5	489.9
147.5°	513.9	514.0	514.1	513.9	513.3	512.8	512.3	511.8	512.3	512.8	513.3
150°	527.9	527.9	527.9	527.7	527.3	526.8	526.4	525.9	526.4	526.8	527.3
152.5°	540.7	540.6	540.5	540.4	540.1	539.8	539.6	539.3	539.6	539.8	540.1
155°	559.6	559.6	559.7	559.8	559.8	559.8	559.8	559.8	559.8	559.8	559.8
157.5°	576.2	576.2	576.2	576.4	576.5	576.7	576.9	577.1	576.9	576.7	576.5
160°	586.6	586.7	586.8	586.9	587.0	587.1	587.2	587.3	587.2	587.1	587.0
162.5°	595.2	595.3	595.4	595.6	595.9	596.2	596.5	596.8	596.5	596.2	595.9
165°	607.4	607.6	607.9	608.1	608.5	608.7	609.1	609.4	609.1	608.7	608.5
167.5°	617.2	617.1	617.1	617.3	617.8	618.2	618.7	619.1	618.7	618.2	617.8
170°	622.4	622.3	622.2	622.4	623.0	623.5	624.1	624.7	624.1	623.5	623.0
172.5°	626.5	626.5	626.5	626.7	627.2	627.7	628.1	628.5	628.1	627.7	627.2
175°	631.3	631.4	631.5	631.8	632.3	632.9	633.4	634.0	633.4	632.9	632.3
177.5°	633.8	633.8	633.8	634.0	634.5	634.9	635.3	635.8	635.3	634.9	634.5
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1116.0	1112.3	1107.6	1102.1	1095.5	1089.7	1087.1	1089.3	1090.4	1087.4	1087.1
5°	1082.0	1070.6	1061.4	1047.7	1036.7	1027.5	1021.1	1018.4	1019.3	1012.0	1010.1
7.5°	1043.9	1030.3	1015.3	999.0	983.8	970.3	963.3	959.4	951.7	948.3	942.7
10°	1019.3	1001.0	986.4	967.1	949.7	933.7	925.9	919.5	911.7	908.0	900.3
12.5°	994.0	972.8	956.7	936.7	918.9	899.6	892.2	880.3	868.1	860.4	850.4
15°	958.4	932.8	913.1	889.2	868.2	846.2	826.6	804.5	796.3	778.9	768.9
17.5°	916.7	890.7	866.3	834.4	801.9	774.6	753.6	732.5	720.0	708.9	703.7
20°	889.2	865.5	831.6	794.4	758.3	728.1	711.1	697.4	683.6	675.9	670.4
22.5°	863.2	832.8	793.5	753.5	717.3	693.6	679.2	665.1	654.0	646.6	639.2
25°	819.7	779.8	738.1	692.3	667.6	647.0	631.5	620.0	613.1	603.6	599.9
27.5°	774.9	726.6	680.6	649.9	624.1	605.3	591.7	583.1	574.4	568.3	563.5
30°	740.5	691.5	650.2	621.0	594.9	579.3	568.3	558.2	551.3	546.3	542.6
32.5°	706.4	657.4	622.8	591.2	570.7	555.4	543.7	536.2	530.8	524.3	522.1
35°	657.1	613.6	583.4	555.0	533.9	520.2	511.0	503.3	498.7	496.8	495.4
37.5°	609.8	574.1	541.7	518.3	499.6	488.8	477.9	474.2	471.0	467.7	469.2
40°	579.7	546.3	517.5	492.8	477.6	465.7	459.3	454.7	451.9	451.9	451.9
42.5°	553.7	521.0	492.9	470.7	455.6	445.6	438.4	434.5	433.6	433.3	435.5
45°	513.3	483.1	454.7	436.4	423.5	413.5	409.4	406.1	406.1	408.0	408.5
47.5°	473.3	445.0	422.2	401.7	389.9	383.7	380.0	378.4	378.6	380.5	382.5
50°	448.8	420.9	398.4	380.0	369.1	363.1	359.9	359.0	359.9	359.9	363.1
52.5°	422.0	397.0	375.0	359.6	347.1	341.5	339.8	338.5	339.1	340.5	341.9
55°	382.8	360.4	339.3	324.7	315.5	311.9	307.7	308.2	307.3	308.2	308.2
57.5°	343.5	323.4	303.8	292.1	284.1	278.8	274.3	275.6	274.2	274.1	273.3
60°	318.2	296.3	280.7	270.2	261.0	256.4	252.3	253.2	251.8	250.9	249.1
62.5°	290.8	272.4	257.6	247.5	240.1	234.8	230.7	229.8	226.6	223.4	219.5
65°	250.9	235.8	222.6	212.9	206.0	201.9	198.7	196.0	189.1	181.8	178.1
67.5°	212.2	201.3	188.9	180.8	175.2	169.8	163.7	159.0	152.6	148.5	146.3
70°	187.3	176.8	166.3	158.4	152.5	147.5	140.6	137.4	132.8	131.0	128.6
72.5°	163.5	153.7	143.9	136.8	130.5	126.6	121.1	118.0	116.0	115.2	113.0
75°	127.3	119.5	112.2	105.8	100.7	98.0	95.7	93.4	92.5	88.3	86.1
77.5°	92.9	87.7	83.2	78.6	75.0	73.2	68.8	66.1	64.6	62.7	62.2
80°	72.3	68.7	64.1	61.4	56.3	54.5	52.7	52.2	51.7	51.3	50.8
82.5°	54.4	50.7	46.1	44.5	43.1	42.0	40.9	40.5	40.0	40.3	40.2
85°	27.5	25.7	25.7	25.2	24.7	24.3	23.8	23.8	23.3	23.8	23.3
87.5°	10.4	10.2	10.4	9.9	10.4	10.6	10.3	10.5	11.0	10.4	10.5
90°	6.3	7.3	8.2	9.0	9.9	10.8	11.5	12.1	12.7	13.4	13.9
92.5°	16.0	17.0	17.7	18.3	18.9	19.5	19.8	20.2	20.7	21.0	21.3
95°	33.4	34.3	35.0	35.8	36.6	37.3	37.6	38.0	38.3	38.7	38.8
97.5°	54.6	55.4	56.3	57.3	58.1	59.1	59.4	59.8	60.2	60.6	60.8
100°	70.5	71.2	72.2	73.2	74.1	75.2	75.3	75.6	75.8	76.0	76.1
102.5°	87.5	88.1	88.9	89.8	90.7	91.6	92.0	92.2	92.6	92.8	93.1
105°	114.9	115.1	115.5	116.0	116.4	116.8	117.2	117.5	117.9	118.2	118.5
107.5°	144.0	144.0	144.0	144.1	144.2	144.3	144.6	144.9	145.2	145.5	145.7
110°	163.9	163.9	163.8	163.8	163.7	163.5	163.3	163.1	162.9	162.6	162.7



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	183.7	183.6	183.4	183.1	183.0	182.8	182.7	182.7	182.6	182.6	182.6
115°	214.1	214.0	213.8	213.5	213.4	213.1	213.0	212.9	212.8	212.7	212.6
117.5°	243.3	243.3	243.1	243.0	242.8	242.7	242.3	241.9	241.6	241.2	240.9
120°	264.0	264.1	263.7	263.4	263.0	262.7	262.2	261.7	261.1	260.5	260.4
122.5°	282.9	283.0	282.8	282.7	282.5	282.4	282.0	281.6	281.3	280.9	280.5
125°	311.9	311.8	311.7	311.6	311.4	311.3	311.1	310.9	310.6	310.5	310.2
127.5°	339.9	340.0	339.8	339.7	339.5	339.3	339.1	338.9	338.7	338.5	338.3
130°	358.8	359.0	359.0	359.0	359.0	359.0	358.8	358.5	358.3	358.1	357.7
132.5°	377.7	377.8	377.7	377.6	377.5	377.5	377.2	377.0	376.8	376.6	376.3
135°	404.8	405.1	405.1	405.1	405.1	405.1	404.9	404.7	404.5	404.2	404.0
137.5°	431.1	431.4	431.5	431.7	431.9	432.0	431.8	431.4	431.2	430.9	430.8
140°	449.2	449.4	449.4	449.4	449.4	449.4	449.2	449.1	449.0	448.9	448.8
142.5°	466.1	466.1	466.1	466.0	465.9	465.8	465.8	465.8	465.8	465.7	465.7
145°	490.3	490.6	490.8	490.9	490.9	491.0	490.9	490.9	490.8	490.6	490.4
147.5°	513.9	514.1	514.0	513.9	513.8	513.8	513.7	513.6	513.5	513.4	513.3
150°	527.7	527.9	527.9	527.9	527.9	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	540.4	540.5	540.6	540.7	540.8	540.9	541.1	541.4	541.7	541.9	541.9
155°	559.8	559.7	559.6	559.6	559.5	559.3	559.7	560.2	560.6	561.1	561.1
157.5°	576.4	576.2	576.2	576.2	576.2	576.1	576.4	576.8	577.1	577.5	577.4
160°	586.9	586.8	586.7	586.6	586.4	586.3	586.7	587.0	587.3	587.6	587.5
162.5°	595.6	595.4	595.3	595.2	595.1	595.0	595.6	596.2	596.8	597.4	597.4
165°	608.1	607.9	607.6	607.4	607.2	607.0	607.6	608.3	608.9	609.6	609.7
167.5°	617.3	617.1	617.1	617.2	617.2	617.2	617.9	618.5	619.1	619.8	619.7
170°	622.4	622.2	622.3	622.4	622.6	622.7	623.4	624.0	624.7	625.3	625.3
172.5°	626.7	626.5	626.5	626.5	626.5	626.6	627.3	628.1	628.9	629.6	629.6
175°	631.8	631.5	631.4	631.3	631.1	631.0	631.8	632.6	633.4	634.0	634.0
177.5°	634.0	633.8	633.8	633.8	633.8	633.8	634.4	635.0	635.6	636.2	636.2
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1084.9	1085.6	1083.1	1082.3	1083.1	1085.6	1084.9	1087.1	1087.4	1090.4	1089.3
5°	1006.5	1005.6	1003.3	1003.8	1003.3	1005.6	1006.5	1010.1	1012.0	1019.3	1018.4
7.5°	939.4	935.9	936.9	933.2	936.9	935.9	939.4	942.7	948.3	951.7	959.4
10°	898.5	893.4	889.2	885.6	889.2	893.4	898.5	900.3	908.0	911.7	919.5
12.5°	842.4	838.1	832.5	833.6	832.5	838.1	842.4	850.4	860.4	868.1	880.3
15°	762.8	756.0	745.0	746.4	745.0	756.0	762.8	768.9	778.9	796.3	804.5
17.5°	695.6	695.7	690.6	691.8	690.6	695.7	695.6	703.7	708.9	720.0	732.5
20°	660.7	657.5	658.0	656.7	658.0	657.5	660.7	670.4	675.9	683.6	697.4
22.5°	636.6	632.7	629.5	626.6	629.5	632.7	636.6	639.2	646.6	654.0	665.1
25°	595.7	593.0	588.8	588.0	588.8	593.0	595.7	599.9	603.6	613.1	620.0
27.5°	559.8	559.3	557.7	555.5	557.7	559.3	559.8	563.5	568.3	574.4	583.1
30°	539.0	538.0	537.1	535.7	537.1	538.0	539.0	542.6	546.3	551.3	558.2
32.5°	520.3	519.7	518.8	518.9	518.8	519.7	520.3	522.1	524.3	530.8	536.2
35°	493.6	493.2	492.2	491.8	492.2	493.2	493.6	495.4	496.8	498.7	503.3
37.5°	468.7	469.9	469.3	469.2	469.3	469.9	468.7	469.2	467.7	471.0	474.2
40°	451.5	451.9	452.9	452.5	452.9	451.9	451.5	451.9	451.9	451.9	454.7
42.5°	437.2	437.3	438.6	437.0	438.6	437.3	437.2	435.5	433.3	433.6	434.5
45°	411.6	414.4	414.0	414.0	414.0	414.4	411.6	408.5	408.0	406.1	406.1
47.5°	383.7	386.1	386.8	386.7	386.8	386.1	383.7	382.5	380.5	378.6	378.4
50°	365.4	364.5	365.8	365.4	365.8	364.5	365.4	363.1	359.9	359.9	359.0
52.5°	343.1	343.3	343.2	342.7	343.2	343.3	343.1	341.9	340.5	339.1	338.5
55°	308.7	309.1	308.2	308.7	308.2	309.1	308.7	308.2	308.2	307.3	308.2
57.5°	271.3	269.1	270.0	268.9	270.0	269.1	271.3	273.3	274.1	274.2	275.6
60°	244.5	240.8	240.0	238.2	240.0	240.8	244.5	249.1	250.9	251.8	253.2
62.5°	214.5	211.9	208.8	210.3	208.8	211.9	214.5	219.5	223.4	226.6	229.8
65°	174.4	172.6	171.3	173.1	171.3	172.6	174.4	178.1	181.8	189.1	196.0
67.5°	144.4	143.4	143.4	142.5	143.4	143.4	144.4	146.3	148.5	152.6	159.0
70°	128.6	127.3	127.3	126.4	127.3	127.3	128.6	128.6	131.0	132.8	137.4
72.5°	112.5	111.2	111.6	111.0	111.6	111.2	112.5	113.0	115.2	116.0	118.0
75°	83.3	81.0	81.0	81.5	81.0	81.0	83.3	86.1	88.3	92.5	93.4
77.5°	62.2	61.7	62.3	61.6	62.3	61.7	62.2	62.2	62.7	64.6	66.1
80°	50.8	50.4	49.9	51.3	49.9	50.4	50.8	50.8	51.3	51.7	52.2
82.5°	39.4	39.3	39.3	41.1	39.3	39.3	39.4	40.2	40.3	40.0	40.5
85°	23.8	22.9	23.8	22.9	23.8	22.9	23.8	23.3	23.8	23.3	23.8
87.5°	11.3	10.9	10.6	11.0	10.6	10.9	11.3	10.5	10.4	11.0	10.5
90°	14.1	14.3	14.6	14.7	14.6	14.3	14.1	13.9	13.4	12.7	12.1
92.5°	21.4	21.5	21.7	21.8	21.7	21.5	21.4	21.3	21.0	20.7	20.2
95°	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.8	38.7	38.3	38.0
97.5°	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.8	60.6	60.2	59.8
100°	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.1	76.0	75.8	75.6
102.5°	93.2	93.2	93.3	93.4	93.3	93.2	93.2	93.1	92.8	92.6	92.2
105°	118.8	119.2	119.5	119.9	119.5	119.2	118.8	118.5	118.2	117.9	117.5
107.5°	145.6	145.6	145.6	145.6	145.6	145.6	145.6	145.7	145.5	145.2	144.9
110°	163.1	163.3	163.7	164.0	163.7	163.3	163.1	162.7	162.6	162.9	163.1



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	182.7	182.7	182.8	182.9	182.8	182.7	182.7	182.6	182.6	182.6	182.7
115°	212.5	212.3	212.2	212.2	212.2	212.3	212.5	212.6	212.7	212.8	212.9
117.5°	240.6	240.5	240.2	240.0	240.2	240.5	240.6	240.9	241.2	241.6	241.9
120°	260.6	260.8	261.1	261.2	261.1	260.8	260.6	260.4	260.5	261.1	261.7
122.5°	280.1	279.7	279.3	279.0	279.3	279.7	280.1	280.5	280.9	281.3	281.6
125°	310.0	309.8	309.6	309.4	309.6	309.8	310.0	310.2	310.5	310.6	310.9
127.5°	338.1	337.9	337.8	337.6	337.8	337.9	338.1	338.3	338.5	338.7	338.9
130°	357.3	356.9	356.5	356.0	356.5	356.9	357.3	357.7	358.1	358.3	358.5
132.5°	376.2	376.0	375.8	375.7	375.8	376.0	376.2	376.3	376.6	376.8	377.0
135°	403.6	403.3	403.0	402.7	403.0	403.3	403.6	404.0	404.2	404.5	404.7
137.5°	430.8	430.9	431.0	431.1	431.0	430.9	430.8	430.8	430.9	431.2	431.4
140°	448.7	448.6	448.5	448.3	448.5	448.6	448.7	448.8	448.9	449.0	449.1
142.5°	465.7	465.7	465.6	465.6	465.6	465.7	465.7	465.7	465.7	465.8	465.8
145°	490.1	489.7	489.4	489.1	489.4	489.7	490.1	490.4	490.6	490.8	490.9
147.5°	513.2	513.1	513.0	512.9	513.0	513.1	513.2	513.3	513.4	513.5	513.6
150°	527.7	527.6	527.5	527.4	527.5	527.6	527.7	527.9	527.9	527.9	527.9
152.5°	541.7	541.3	541.1	540.8	541.1	541.3	541.7	541.9	541.9	541.7	541.4
155°	560.6	560.2	559.7	559.3	559.7	560.2	560.6	561.1	561.1	560.6	560.2
157.5°	577.0	576.7	576.3	575.9	576.3	576.7	577.0	577.4	577.5	577.1	576.8
160°	587.0	586.4	585.9	585.4	585.9	586.4	587.0	587.5	587.6	587.3	587.0
162.5°	596.8	596.2	595.7	595.2	595.7	596.2	596.8	597.4	597.4	596.8	596.2
165°	609.2	608.8	608.4	608.0	608.4	608.8	609.2	609.7	609.6	608.9	608.3
167.5°	619.1	618.5	617.8	617.1	617.8	618.5	619.1	619.7	619.8	619.1	618.5
170°	624.5	623.7	622.9	622.2	622.9	623.7	624.5	625.3	625.3	624.7	624.0
172.5°	628.8	628.0	627.2	626.5	627.2	628.0	628.8	629.6	629.6	628.9	628.1
175°	633.4	632.6	631.8	631.0	631.8	632.6	633.4	634.0	634.0	633.4	632.6
177.5°	635.5	634.8	634.0	633.4	634.0	634.8	635.5	636.2	636.2	635.6	635.0
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1087.1	1089.7	1095.5	1102.1	1107.6	1112.3	1116.0	1121.1	1125.9	1132.5	1138.8
5°	1021.1	1027.5	1036.7	1047.7	1061.4	1070.6	1082.0	1092.1	1106.7	1121.5	1135.7
7.5°	963.3	970.3	983.8	999.0	1015.3	1030.3	1043.9	1061.6	1081.1	1102.3	1126.2
10°	925.9	933.7	949.7	967.1	986.4	1001.0	1019.3	1040.3	1062.4	1088.5	1117.8
12.5°	892.2	899.6	918.9	936.7	956.7	972.8	994.0	1015.5	1044.7	1073.1	1106.4
15°	826.6	846.2	868.2	889.2	913.1	932.8	958.4	980.4	1008.3	1048.2	1086.2
17.5°	753.6	774.6	801.9	834.4	866.3	890.7	916.7	944.0	977.2	1018.0	1061.8
20°	711.1	728.1	758.3	794.4	831.6	865.5	889.2	919.5	953.8	997.8	1043.1
22.5°	679.2	693.6	717.3	753.5	793.5	832.8	863.2	893.1	931.1	975.1	1024.4
25°	631.5	647.0	667.6	692.3	738.1	779.8	819.7	854.0	894.3	938.2	993.2
27.5°	591.7	605.3	624.1	649.9	680.6	726.6	774.9	814.1	855.4	902.6	957.6
30°	568.3	579.3	594.9	621.0	650.2	691.5	740.5	786.3	827.9	876.9	934.1
32.5°	543.7	555.4	570.7	591.2	622.8	657.4	706.4	756.6	800.8	850.9	907.1
35°	511.0	520.2	533.9	555.0	583.4	613.6	657.1	708.9	755.5	809.2	862.7
37.5°	477.9	488.8	499.6	518.3	541.7	574.1	609.8	662.6	714.4	763.3	815.5
40°	459.3	465.7	477.6	492.8	517.5	546.3	579.7	631.5	683.2	731.8	784.4
42.5°	438.4	445.6	455.6	470.7	492.9	521.0	553.7	598.5	652.5	699.5	747.4
45°	409.4	413.5	423.5	436.4	454.7	483.1	513.3	553.2	604.0	648.8	691.0
47.5°	380.0	383.7	389.9	401.7	422.2	445.0	473.3	509.0	553.6	598.5	634.1
50°	359.9	363.1	369.1	380.0	398.4	420.9	448.8	480.8	520.6	563.7	593.5
52.5°	339.8	341.5	347.1	359.6	375.0	397.0	422.0	451.5	488.8	524.5	554.7
55°	307.7	311.9	315.5	324.7	339.3	360.4	382.8	410.8	439.6	469.8	495.4
57.5°	274.3	278.8	284.1	292.1	303.8	323.4	343.5	366.2	390.8	415.9	437.4
60°	252.3	256.4	261.0	270.2	280.7	296.3	318.2	337.9	356.7	379.6	401.1
62.5°	230.7	234.8	240.1	247.5	257.6	272.4	290.8	307.9	327.4	347.4	363.4
65°	198.7	201.9	206.0	212.9	222.6	235.8	250.9	264.2	281.6	296.3	310.9
67.5°	163.7	169.8	175.2	180.8	188.9	201.3	212.2	224.9	236.8	247.6	261.0
70°	140.6	147.5	152.5	158.4	166.3	176.8	187.3	196.0	205.6	216.1	228.1
72.5°	121.1	126.6	130.5	136.8	143.9	153.7	163.5	170.7	178.5	185.7	197.3
75°	95.7	98.0	100.7	105.8	112.2	119.5	127.3	133.7	138.3	144.7	152.9
77.5°	68.8	73.2	75.0	78.6	83.2	87.7	92.9	98.2	102.6	105.0	111.2
80°	52.7	54.5	56.3	61.4	64.1	68.7	72.3	77.4	79.2	81.5	87.5
82.5°	40.9	42.0	43.1	44.5	46.1	50.7	54.4	57.6	59.4	60.3	64.7
85°	23.8	24.3	24.7	25.2	25.7	25.7	27.5	29.8	33.0	33.0	34.4
87.5°	10.3	10.6	10.4	9.9	10.4	10.2	10.4	10.2	11.0	11.9	12.7
90°	11.5	10.8	9.9	9.0	8.2	7.3	6.3	5.1	3.9	2.7	1.5
92.5°	19.8	19.5	18.9	18.3	17.7	17.0	16.0	14.6	13.3	11.9	10.5
95°	37.6	37.3	36.6	35.8	35.0	34.3	33.4	32.4	31.4	30.5	29.4
97.5°	59.4	59.1	58.1	57.3	56.3	55.4	54.6	53.8	53.0	52.3	51.5
100°	75.3	75.2	74.1	73.2	72.2	71.2	70.5	70.1	69.7	69.2	68.7
102.5°	92.0	91.6	90.7	89.8	88.9	88.1	87.5	87.3	87.1	87.0	86.8
105°	117.2	116.8	116.4	116.0	115.5	115.1	114.9	114.8	114.6	114.5	114.4
107.5°	144.6	144.3	144.2	144.1	144.0	144.0	144.0	143.8	143.6	143.5	143.4
110°	163.3	163.5	163.7	163.8	163.8	163.9	163.9	163.7	163.5	163.2	163.1



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	182.7	182.8	183.0	183.1	183.4	183.6	183.7	183.6	183.6	183.5	183.5
115°	213.0	213.1	213.4	213.5	213.8	214.0	214.1	214.1	214.1	214.1	214.1
117.5°	242.3	242.7	242.8	243.0	243.1	243.3	243.3	243.2	243.1	243.1	243.0
120°	262.2	262.7	263.0	263.4	263.7	264.1	264.0	263.6	263.1	262.7	262.3
122.5°	282.0	282.4	282.5	282.7	282.8	283.0	282.9	282.8	282.6	282.4	282.2
125°	311.1	311.3	311.4	311.6	311.7	311.8	311.9	311.9	311.9	311.9	311.9
127.5°	339.1	339.3	339.5	339.7	339.8	340.0	339.9	339.7	339.3	339.0	338.6
130°	358.8	359.0	359.0	359.0	359.0	359.0	358.8	358.5	358.2	357.8	357.5
132.5°	377.2	377.5	377.5	377.6	377.7	377.8	377.7	377.5	377.2	377.0	376.8
135°	404.9	405.1	405.1	405.1	405.1	405.1	404.8	404.2	403.5	402.9	402.2
137.5°	431.8	432.0	431.9	431.7	431.5	431.4	431.1	430.8	430.5	430.2	429.9
140°	449.2	449.4	449.4	449.4	449.4	449.4	449.2	449.0	448.8	448.6	448.3
142.5°	465.8	465.8	465.9	466.0	466.1	466.1	466.1	465.9	465.7	465.5	465.2
145°	490.9	491.0	490.9	490.9	490.8	490.6	490.3	489.9	489.5	489.0	488.6
147.5°	513.7	513.8	513.8	513.9	514.0	514.1	513.9	513.3	512.8	512.3	511.8
150°	527.9	527.9	527.9	527.9	527.9	527.9	527.7	527.3	526.8	526.4	525.9
152.5°	541.1	540.9	540.8	540.7	540.6	540.5	540.4	540.1	539.8	539.6	539.3
155°	559.7	559.3	559.5	559.6	559.6	559.7	559.8	559.8	559.8	559.8	559.8
157.5°	576.4	576.1	576.2	576.2	576.2	576.2	576.4	576.5	576.7	576.9	577.1
160°	586.7	586.3	586.4	586.6	586.7	586.8	586.9	587.0	587.1	587.2	587.3
162.5°	595.6	595.0	595.1	595.2	595.3	595.4	595.6	595.9	596.2	596.5	596.8
165°	607.6	607.0	607.2	607.4	607.6	607.9	608.1	608.5	608.7	609.1	609.4
167.5°	617.9	617.2	617.2	617.2	617.1	617.1	617.3	617.8	618.2	618.7	619.1
170°	623.4	622.7	622.6	622.4	622.3	622.2	622.4	623.0	623.5	624.1	624.7
172.5°	627.3	626.6	626.5	626.5	626.5	626.5	626.7	627.2	627.7	628.1	628.5
175°	631.8	631.0	631.1	631.3	631.4	631.5	631.8	632.3	632.9	633.4	634.0
177.5°	634.4	633.8	633.8	633.8	633.8	633.8	634.0	634.5	634.9	635.3	635.8
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1143.5	1146.8	1150.5	1157.4	1163.3	1165.9	1171.0	1174.7	1173.5	1178.6	1187.5
5°	1148.0	1160.4	1174.6	1189.2	1205.7	1219.4	1230.4	1241.4	1250.1	1260.6	1276.2
7.5°	1147.3	1169.2	1193.2	1219.4	1246.5	1269.8	1291.4	1313.4	1332.9	1354.3	1382.2
10°	1144.4	1173.6	1203.4	1237.8	1272.0	1304.6	1333.9	1361.4	1387.5	1415.4	1450.7
12.5°	1141.0	1174.7	1210.7	1252.0	1294.8	1333.9	1368.3	1407.9	1440.6	1476.6	1517.3
15°	1126.4	1171.8	1220.8	1274.4	1325.7	1378.3	1425.5	1474.0	1519.3	1562.4	1613.7
17.5°	1109.8	1162.1	1219.9	1283.1	1344.8	1408.8	1464.7	1526.0	1572.3	1630.0	1677.7
20°	1096.2	1152.5	1214.4	1285.4	1355.4	1426.4	1488.2	1550.5	1602.7	1660.9	1721.3
22.5°	1079.8	1141.6	1208.5	1282.0	1355.4	1433.0	1501.4	1563.3	1628.0	1693.4	1755.8
25°	1053.2	1117.3	1188.3	1268.9	1353.1	1432.4	1505.6	1582.5	1652.2	1723.1	1779.0
27.5°	1020.6	1087.9	1162.7	1245.9	1332.3	1413.5	1499.8	1581.7	1651.7	1720.1	1768.8
30°	994.5	1065.6	1137.5	1221.7	1311.5	1398.4	1491.0	1573.0	1646.7	1708.1	1735.5
32.5°	967.9	1035.2	1109.2	1194.6	1286.5	1380.2	1471.9	1555.7	1623.9	1660.8	1661.5
35°	921.4	984.5	1061.4	1145.2	1239.6	1341.3	1434.2	1516.6	1558.2	1561.5	1516.6
37.5°	870.6	928.6	1001.2	1085.0	1188.4	1289.5	1384.5	1439.4	1453.3	1406.7	1323.7
40°	834.3	887.9	957.9	1044.0	1146.6	1251.0	1337.6	1377.9	1363.2	1287.6	1195.2
42.5°	796.3	846.1	913.6	998.6	1101.6	1207.0	1280.7	1302.4	1263.6	1176.3	1068.1
45°	734.0	779.8	846.7	932.3	1031.2	1130.1	1186.0	1175.0	1110.4	1006.9	885.6
47.5°	669.3	713.5	773.7	852.9	954.2	1039.6	1077.4	1044.2	952.4	838.5	739.8
50°	626.5	671.8	727.2	802.7	895.2	977.7	1001.9	951.6	849.5	739.9	649.3
52.5°	584.3	623.0	677.3	750.4	838.8	908.4	921.4	863.2	757.9	659.8	579.4
55°	520.2	555.4	601.2	669.9	746.4	805.5	798.6	723.9	628.3	544.5	481.3
57.5°	458.2	484.7	527.0	591.4	658.6	698.2	673.1	609.5	520.3	451.7	398.4
60°	417.2	441.9	481.3	537.6	596.7	619.1	598.1	528.9	458.4	395.6	350.8
62.5°	378.3	400.1	434.0	486.3	534.0	547.3	524.8	464.4	400.9	347.2	310.1
65°	321.9	342.1	370.9	408.0	441.0	447.4	432.7	370.9	322.8	277.9	252.3
67.5°	270.7	283.9	306.4	338.5	356.0	359.7	331.4	292.6	250.2	222.7	203.3
70°	236.3	245.5	266.5	283.9	298.1	298.6	272.4	241.3	208.8	186.4	172.2
72.5°	202.9	211.7	227.6	239.6	250.5	246.9	223.0	198.5	172.2	155.2	144.7
75°	156.6	164.4	172.6	178.1	178.1	173.6	156.2	137.8	122.7	112.6	109.4
77.5°	113.8	120.3	123.0	122.2	120.5	113.4	102.4	90.4	85.0	80.2	77.8
80°	89.3	92.0	93.0	90.7	87.9	79.6	72.3	67.3	62.3	60.4	59.5
82.5°	66.2	68.6	66.2	66.8	60.8	54.1	50.0	48.3	46.1	45.5	44.5
85°	35.3	34.8	33.9	31.6	27.5	26.5	26.1	25.7	24.7	25.2	24.3
87.5°	12.7	11.8	10.5	10.4	10.6	10.1	10.6	10.8	10.9	10.7	11.6
90°	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5	12.1
92.5°	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8	20.2
95°	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6	38.0
97.5°	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4	59.8
100°	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3	75.6
102.5°	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0	92.2
105°	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2	117.5
107.5°	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6	144.9
110°	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3	163.1



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7	182.7
115°	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0	212.9
117.5°	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3	241.9
120°	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2	261.7
122.5°	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0	281.6
125°	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1	310.9
127.5°	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1	338.9
130°	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8	358.5
132.5°	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2	377.0
135°	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9	404.7
137.5°	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8	431.4
140°	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2	449.1
142.5°	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8	465.8
145°	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9	490.9
147.5°	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7	513.6
150°	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1	541.4
155°	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7	560.2
157.5°	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4	576.8
160°	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7	587.0
162.5°	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6	596.2
165°	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6	608.3
167.5°	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9	618.5
170°	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4	624.0
172.5°	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3	628.1
175°	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8	632.6
177.5°	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4	635.0
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5	1136.5
2.5°	1192.2	1193.7	1194.8	1198.4	1198.8	1202.1	1198.8
5°	1290.8	1297.3	1307.3	1317.4	1318.4	1324.7	1313.3
7.5°	1401.4	1416.3	1425.6	1441.8	1448.3	1452.3	1445.7
10°	1477.6	1491.4	1515.7	1527.6	1539.5	1541.4	1535.9
12.5°	1551.3	1573.1	1592.2	1614.8	1614.2	1630.4	1624.4
15°	1649.4	1671.8	1698.4	1723.5	1732.8	1732.8	1740.1
17.5°	1719.3	1760.5	1788.0	1807.8	1829.4	1833.1	1830.6
20°	1766.6	1811.0	1840.4	1866.0	1880.7	1884.7	1884.7
22.5°	1801.8	1839.6	1868.2	1891.3	1903.3	1908.2	1906.8
25°	1826.2	1858.6	1876.0	1882.9	1886.1	1885.2	1876.5
27.5°	1792.8	1791.3	1780.4	1759.3	1743.4	1733.8	1722.9
30°	1729.1	1705.3	1677.8	1647.5	1608.6	1578.9	1569.7
32.5°	1634.2	1580.7	1534.2	1483.8	1442.0	1412.2	1399.7
35°	1450.7	1366.0	1296.8	1236.4	1192.4	1164.9	1155.8
37.5°	1232.9	1150.9	1065.3	1006.7	970.3	942.5	932.1
40°	1094.4	1005.1	930.5	875.6	838.0	811.0	810.5
42.5°	968.0	882.8	812.5	772.9	732.5	714.6	714.5
45°	792.6	724.4	664.9	633.8	609.5	594.9	590.7
47.5°	656.3	599.9	560.2	535.4	515.6	506.3	500.2
50°	579.7	530.3	498.7	477.2	466.1	454.3	453.3
52.5°	516.0	476.0	451.4	433.9	420.0	412.8	413.0
55°	433.6	402.1	384.6	371.3	360.4	354.9	352.6
57.5°	365.3	341.6	329.0	316.8	312.1	307.8	306.6
60°	322.8	306.8	294.9	285.2	278.4	277.1	276.6
62.5°	287.7	270.9	262.7	255.2	250.2	248.1	247.3
65°	237.2	224.8	217.5	211.5	209.7	206.6	206.0
67.5°	191.2	183.8	178.9	174.9	172.4	172.2	172.2
70°	163.0	158.9	154.8	152.5	151.1	150.2	150.2
72.5°	138.9	135.8	132.4	131.2	131.0	130.0	129.7
75°	105.8	102.5	103.1	100.7	98.9	96.6	95.2
77.5°	75.0	72.8	72.2	72.0	70.4	70.2	70.9
80°	58.1	55.9	55.4	55.9	55.4	54.1	54.1
82.5°	44.3	42.3	41.8	41.6	41.2	41.6	40.8
85°	23.8	22.9	22.9	22.9	23.8	23.3	22.9
87.5°	11.0	10.8	11.2	10.8	10.9	10.6	11.0
90°	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	162.9	162.6	162.7	163.1	163.3	163.7	164.0



TEST NUMBER: P332932-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)