

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332935-935

Luminaire Tested: **SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332935-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4526.9 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332935-935
CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	85	78	73	86	79	74	69	70	66	62	61	58	55	52	50	48	44
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	29
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9656	9656	9656
5°	9678	9559	9618
10°	9617	9444	9444
15°	9507	9246	9177
20°	9355	8985	8820
25°	9161	8679	8459
30°	8972	8358	8007
35°	8763	8024	7554
40°	8513	7644	7065
45°	8281	7267	6566
50°	8017	6832	6038
55°	7734	6380	5465
60°	7424	5885	4879
65°	7138	5266	4304
70°	6722	4584	3654
75°	6198	3799	2969
80°	5407	2896	2724
85°	4576	2631	2455



TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	2.5
10°-20°	313.3	6.9
20°-30°	452.4	10.0
30°-40°	512.8	11.3
40°-50°	495.2	10.9
50°-60°	411.8	9.1
60°-70°	284.4	6.3
70°-80°	144.1	3.2
80°-90°	38.9	0.9
90°-100°	41.9	0.9
100°-110°	124.1	2.7
110°-120°	210.6	4.7
120°-130°	277.7	6.1
130°-140°	311.8	6.9
140°-150°	306.4	6.8
150°-160°	257.7	5.7
160°-170°	171.5	3.8
170°-180°	60.0	1.3
0°-30°	878.1	19.4
0°-40°	1390.9	30.7
0°-60°	2297.9	50.8
0°-90°	2765.3	61.1
90°-120°	376.5	8.3
90°-150°	1272.4	28.1
90°-180°	1762.0	38.9
0°-180°	4526.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1194	1190	1180	1188	1187	113
15°	1138	1128	1106	1104	1098	320
25°	1028	1011	974	959	950	474
35°	889	859	814	784	766	555
45°	725	690	636	593	575	559
55°	550	512	453	407	388	491
65°	374	333	276	238	225	369
75°	199	164	122	102	95	210
85°	49	32	28	27	26	56
90°	2	7	11	14	15	4
95°	29	34	37	39	39	33
105°	114	115	117	118	120	121
115°	214	214	213	213	212	211
125°	312	312	311	310	309	278
135°	402	405	405	404	403	311
145°	489	490	491	490	489	306
155°	560	560	559	561	559	257
165°	609	608	607	610	608	172
175°	634	632	631	634	631	60
180°	635	635	635	635	635	



TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1199.0	1198.3	1197.7	1197.0	1196.4	1195.2	1193.3	1191.6	1189.8	1188.0	1189.8
5°	1194.2	1193.4	1192.6	1191.8	1190.9	1189.4	1186.9	1184.5	1182.0	1179.6	1181.6
7.5°	1183.4	1182.6	1181.7	1180.9	1180.0	1178.0	1174.8	1171.6	1168.5	1165.3	1166.6
10°	1173.2	1172.2	1171.1	1170.1	1169.1	1166.7	1163.1	1159.4	1155.8	1152.1	1152.9
12.5°	1159.9	1158.8	1157.6	1156.4	1155.3	1152.5	1148.2	1143.8	1139.5	1135.2	1135.7
15°	1137.5	1135.7	1133.8	1132.0	1130.1	1126.7	1121.5	1116.5	1111.4	1106.3	1105.9
17.5°	1110.2	1107.5	1104.8	1102.3	1099.6	1095.2	1089.1	1083.0	1076.9	1070.7	1069.6
20°	1088.9	1086.2	1083.7	1081.0	1078.3	1073.6	1066.6	1059.7	1052.7	1045.9	1044.2
22.5°	1065.5	1062.5	1059.5	1056.5	1053.6	1048.4	1040.9	1033.5	1026.1	1018.7	1016.3
25°	1028.5	1024.8	1021.1	1017.4	1013.8	1007.8	999.4	991.1	982.7	974.4	970.9
27.5°	989.6	985.1	980.4	975.9	971.2	964.5	955.5	946.7	937.7	928.8	924.5
30°	962.5	957.4	952.4	947.3	942.2	934.9	925.3	915.8	906.1	896.6	891.5
32.5°	933.9	928.2	922.5	916.7	911.0	903.2	893.3	883.4	873.5	863.6	857.7
35°	889.2	882.8	876.2	869.7	863.2	854.9	844.7	834.5	824.3	814.2	807.3
37.5°	841.5	834.7	828.0	821.3	814.6	805.6	794.4	783.1	771.8	760.5	752.8
40°	807.8	801.1	794.4	787.6	780.9	771.7	760.1	748.6	736.9	725.3	716.8
42.5°	775.5	768.4	761.5	754.4	747.3	737.8	725.7	713.6	701.5	689.4	680.7
45°	725.3	717.8	710.2	702.7	695.2	685.4	673.1	660.9	648.7	636.5	626.5
47.5°	673.5	665.7	658.0	650.1	642.4	632.1	619.5	606.7	594.1	581.3	571.0
50°	638.3	630.4	622.4	614.5	606.6	596.1	583.1	570.1	557.0	544.0	533.8
52.5°	602.4	594.7	586.9	579.1	571.4	560.8	547.4	534.1	520.7	507.4	497.1
55°	549.5	541.3	533.2	525.0	516.9	506.3	493.0	479.7	466.6	453.3	442.7
57.5°	497.1	488.6	480.2	471.7	463.2	452.5	439.5	426.5	413.5	400.4	389.7
60°	459.8	451.6	443.5	435.3	427.1	416.6	403.6	390.5	377.5	364.5	353.9
62.5°	426.0	417.6	409.1	400.6	392.2	381.3	367.9	354.6	341.2	327.9	318.1
65°	373.7	364.9	356.1	347.4	338.6	327.8	314.7	301.7	288.7	275.7	266.9
67.5°	319.3	310.9	302.5	294.1	285.7	275.5	263.4	251.3	239.2	227.1	219.6
70°	284.8	276.3	267.7	259.2	250.6	240.6	228.9	217.3	205.8	194.2	187.4
72.5°	248.2	240.5	232.7	225.0	217.2	207.9	197.0	186.0	175.0	164.1	158.3
75°	198.7	191.2	183.7	176.2	168.6	160.1	150.5	140.9	131.4	121.8	117.1
77.5°	148.5	142.2	135.8	129.4	123.0	115.9	108.2	100.5	92.7	85.0	82.2
80°	116.3	110.4	104.5	98.6	92.7	86.7	80.6	74.5	68.4	62.3	61.6
82.5°	88.5	83.1	77.7	72.2	66.8	62.3	58.9	55.4	51.8	48.4	47.9
85°	49.4	45.4	41.3	37.3	33.1	30.8	30.2	29.6	29.0	28.4	28.0
87.5°	17.1	16.1	15.0	13.9	12.9	12.4	12.4	12.4	12.4	12.4	12.4
90°	1.5	2.7	3.9	5.1	6.3	7.3	8.2	9.0	9.9	10.8	11.5
92.5°	10.5	11.9	13.3	14.6	16.0	17.0	17.7	18.3	18.9	19.5	19.8
95°	29.4	30.5	31.4	32.4	33.4	34.3	35.0	35.8	36.6	37.3	37.6
97.5°	51.5	52.3	53.0	53.8	54.6	55.4	56.3	57.3	58.1	59.1	59.4
100°	68.7	69.2	69.7	70.1	70.5	71.2	72.2	73.2	74.1	75.2	75.3
102.5°	86.8	87.0	87.1	87.3	87.5	88.1	88.9	89.8	90.7	91.6	92.0
105°	114.4	114.5	114.6	114.8	114.9	115.1	115.5	116.0	116.4	116.8	117.2
107.5°	143.4	143.5	143.6	143.8	144.0	144.0	144.0	144.1	144.2	144.3	144.6
110°	163.1	163.2	163.5	163.7	163.9	163.9	163.8	163.8	163.7	163.5	163.3



TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	183.5	183.5	183.6	183.6	183.7	183.6	183.4	183.1	183.0	182.8	182.7
115°	214.1	214.1	214.1	214.1	214.1	214.0	213.8	213.5	213.4	213.1	213.0
117.5°	243.0	243.1	243.1	243.2	243.3	243.3	243.1	243.0	242.8	242.7	242.3
120°	262.3	262.7	263.1	263.6	264.0	264.1	263.7	263.4	263.0	262.7	262.2
122.5°	282.2	282.4	282.6	282.8	282.9	283.0	282.8	282.7	282.5	282.4	282.0
125°	311.9	311.9	311.9	311.9	311.9	311.8	311.7	311.6	311.4	311.3	311.1
127.5°	338.6	339.0	339.3	339.7	339.9	340.0	339.8	339.7	339.5	339.3	339.1
130°	357.5	357.8	358.2	358.5	358.8	359.0	359.0	359.0	359.0	359.0	358.8
132.5°	376.8	377.0	377.2	377.5	377.7	377.8	377.7	377.6	377.5	377.5	377.2
135°	402.2	402.9	403.5	404.2	404.8	405.1	405.1	405.1	405.1	405.1	404.9
137.5°	429.9	430.2	430.5	430.8	431.1	431.4	431.5	431.7	431.9	432.0	431.8
140°	448.3	448.6	448.8	449.0	449.2	449.4	449.4	449.4	449.4	449.4	449.2
142.5°	465.2	465.5	465.7	465.9	466.1	466.1	466.1	466.0	465.9	465.8	465.8
145°	488.6	489.0	489.5	489.9	490.3	490.6	490.8	490.9	490.9	491.0	490.9
147.5°	511.8	512.3	512.8	513.3	513.9	514.1	514.0	513.9	513.8	513.8	513.7
150°	525.9	526.4	526.8	527.3	527.7	527.9	527.9	527.9	527.9	527.9	527.9
152.5°	539.3	539.6	539.8	540.1	540.4	540.5	540.6	540.7	540.8	540.9	541.1
155°	559.8	559.8	559.8	559.8	559.8	559.7	559.6	559.6	559.5	559.3	559.7
157.5°	577.1	576.9	576.7	576.5	576.4	576.2	576.2	576.2	576.2	576.1	576.4
160°	587.3	587.2	587.1	587.0	586.9	586.8	586.7	586.6	586.4	586.3	586.7
162.5°	596.8	596.5	596.2	595.9	595.6	595.4	595.3	595.2	595.1	595.0	595.6
165°	609.4	609.1	608.7	608.5	608.1	607.9	607.6	607.4	607.2	607.0	607.6
167.5°	619.1	618.7	618.2	617.8	617.3	617.1	617.1	617.2	617.2	617.2	617.9
170°	624.7	624.1	623.5	623.0	622.4	622.2	622.3	622.4	622.6	622.7	623.4
172.5°	628.5	628.1	627.7	627.2	626.7	626.5	626.5	626.5	626.5	626.6	627.3
175°	634.0	633.4	632.9	632.3	631.8	631.5	631.4	631.3	631.1	631.0	631.8
177.5°	635.8	635.3	634.9	634.5	634.0	633.8	633.8	633.8	633.8	633.8	634.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0



TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1	1196.1
2.5°	1191.6	1193.3	1195.2	1196.0	1195.8	1195.7	1195.5	1195.3
5°	1183.6	1185.7	1187.7	1188.5	1188.1	1187.7	1187.3	1186.9
7.5°	1167.9	1169.2	1170.5	1170.8	1170.2	1169.5	1168.9	1168.2
10°	1153.7	1154.5	1155.4	1155.4	1154.5	1153.7	1152.9	1152.1
12.5°	1136.3	1136.7	1137.2	1136.9	1135.7	1134.6	1133.4	1132.3
15°	1105.5	1105.1	1104.7	1103.8	1102.3	1100.9	1099.5	1098.0
17.5°	1068.5	1067.4	1066.2	1064.5	1062.4	1060.2	1058.1	1055.9
20°	1042.6	1040.9	1039.3	1037.2	1034.6	1031.9	1029.2	1026.7
22.5°	1013.9	1011.4	1009.0	1006.7	1004.5	1002.4	1000.2	998.1
25°	967.5	964.1	960.6	957.9	955.8	953.8	951.7	949.7
27.5°	920.2	916.0	911.7	908.1	905.2	902.2	899.3	896.4
30°	886.4	881.3	876.2	872.0	868.8	865.6	862.3	859.0
32.5°	851.8	845.9	840.0	835.5	832.4	829.3	826.2	823.1
35°	800.3	793.4	786.5	781.2	777.6	773.9	770.2	766.5
37.5°	745.0	737.3	729.5	723.8	720.2	716.5	712.9	709.2
40°	708.3	699.6	691.1	685.0	681.4	677.7	674.1	670.4
42.5°	672.0	663.3	654.6	648.3	644.5	640.7	636.9	633.0
45°	616.6	606.6	596.6	589.8	586.1	582.5	578.8	575.1
47.5°	560.7	550.4	540.0	532.8	528.8	524.8	520.7	516.7
50°	523.7	513.5	503.3	496.3	492.4	488.5	484.7	480.8
52.5°	486.7	476.4	466.0	458.8	454.8	450.7	446.8	442.7
55°	432.1	421.5	411.0	403.8	399.9	396.1	392.2	388.3
57.5°	378.9	368.2	357.4	350.6	347.7	344.7	341.8	338.9
60°	343.4	332.8	322.2	315.2	312.0	308.8	305.5	302.2
62.5°	308.3	298.6	288.8	282.6	280.0	277.4	274.7	272.2
65°	258.1	249.4	240.6	235.1	232.6	230.1	227.7	225.3
67.5°	212.1	204.6	197.0	191.9	189.2	186.5	183.8	181.2
70°	180.7	174.0	167.3	162.9	160.9	158.9	156.8	154.8
72.5°	152.7	146.9	141.1	137.3	135.5	133.6	131.7	129.8
75°	112.4	107.8	103.1	100.1	98.9	97.7	96.4	95.2
77.5°	79.6	76.8	74.0	72.5	72.2	71.8	71.5	71.0
80°	61.0	60.4	59.8	59.4	59.2	59.0	58.8	58.6
82.5°	47.4	47.0	46.6	46.2	46.1	45.8	45.6	45.5
85°	27.6	27.2	26.8	26.5	26.5	26.5	26.5	26.5
87.5°	12.3	12.3	12.3	12.4	12.6	12.8	13.0	13.2
90°	12.1	12.7	13.4	13.9	14.1	14.3	14.6	14.7
92.5°	20.2	20.7	21.0	21.3	21.4	21.5	21.7	21.8
95°	38.0	38.3	38.7	38.8	38.8	38.8	38.8	38.8
97.5°	59.8	60.2	60.6	60.8	60.8	60.8	60.8	60.8
100°	75.6	75.8	76.0	76.1	76.1	76.1	76.1	76.1
102.5°	92.2	92.6	92.8	93.1	93.2	93.2	93.3	93.4
105°	117.5	117.9	118.2	118.5	118.8	119.2	119.5	119.9
107.5°	144.9	145.2	145.5	145.7	145.6	145.6	145.6	145.6
110°	163.1	162.9	162.6	162.7	163.1	163.3	163.7	164.0



TEST NUMBER: P332935-935

CATALOG NUMBER: SA4XXRDIP-C795D590U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	182.7	182.6	182.6	182.6	182.7	182.7	182.8	182.9
115°	212.9	212.8	212.7	212.6	212.5	212.3	212.2	212.2
117.5°	241.9	241.6	241.2	240.9	240.6	240.5	240.2	240.0
120°	261.7	261.1	260.5	260.4	260.6	260.8	261.1	261.2
122.5°	281.6	281.3	280.9	280.5	280.1	279.7	279.3	279.0
125°	310.9	310.6	310.5	310.2	310.0	309.8	309.6	309.4
127.5°	338.9	338.7	338.5	338.3	338.1	337.9	337.8	337.6
130°	358.5	358.3	358.1	357.7	357.3	356.9	356.5	356.0
132.5°	377.0	376.8	376.6	376.3	376.2	376.0	375.8	375.7
135°	404.7	404.5	404.2	404.0	403.6	403.3	403.0	402.7
137.5°	431.4	431.2	430.9	430.8	430.8	430.9	431.0	431.1
140°	449.1	449.0	448.9	448.8	448.7	448.6	448.5	448.3
142.5°	465.8	465.8	465.7	465.7	465.7	465.7	465.6	465.6
145°	490.9	490.8	490.6	490.4	490.1	489.7	489.4	489.1
147.5°	513.6	513.5	513.4	513.3	513.2	513.1	513.0	512.9
150°	527.9	527.9	527.9	527.9	527.7	527.6	527.5	527.4
152.5°	541.4	541.7	541.9	541.9	541.7	541.3	541.1	540.8
155°	560.2	560.6	561.1	561.1	560.6	560.2	559.7	559.3
157.5°	576.8	577.1	577.5	577.4	577.0	576.7	576.3	575.9
160°	587.0	587.3	587.6	587.5	587.0	586.4	585.9	585.4
162.5°	596.2	596.8	597.4	597.4	596.8	596.2	595.7	595.2
165°	608.3	608.9	609.6	609.7	609.2	608.8	608.4	608.0
167.5°	618.5	619.1	619.8	619.7	619.1	618.5	617.8	617.1
170°	624.0	624.7	625.3	625.3	624.5	623.7	622.9	622.2
172.5°	628.1	628.9	629.6	629.6	628.8	628.0	627.2	626.5
175°	632.6	633.4	634.0	634.0	633.4	632.6	631.8	631.0
177.5°	635.0	635.6	636.2	636.2	635.5	634.8	634.0	633.4
180°	635.0	635.0	635.0	635.0	635.0	635.0	635.0	635.0

(END OF REPORT)