

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907645

Luminaire Tested: DFN2DIP-4P3F0-020D050US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907645
REPORT IS A COMBINATION OF REPORTS P900580 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D050US840-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6715.6 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 53.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	88	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	69	61	55	51	48	44	41	35	33	31	24	23	21
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19
5	65	54	46	41	58	48	42	37	38	33	30	28	25	23	19	18	16
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	36	29	25	28	24	20	21	18	16	15	13	12
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	951	951	951
5°	952	936	942
10°	942	917	911
15°	929	886	863
20°	911	843	805
25°	893	796	748
30°	868	748	677
35°	845	695	614
40°	820	642	543
45°	792	582	477
50°	763	522	414
55°	733	458	353
60°	698	391	290
65°	657	323	261
70°	607	259	236
75°	546	227	214
80°	456	189	184
85°	309	123	136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1163 cd/sqm

TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	1.2
10°-20°	214.8	3.2
20°-30°	301.5	4.5
30°-40°	328.7	4.9
40°-50°	302.1	4.5
50°-60°	237.3	3.5
60°-70°	154.4	2.3
70°-80°	79.5	1.2
80°-90°	23.3	0.3
90°-100°	56.2	0.8
100°-110°	209.5	3.1
110°-120°	555.6	8.3
120°-130°	921.4	13.7
130°-140°	978.8	14.6
140°-150°	909.7	13.5
150°-160°	731.3	10.9
160°-170°	471.2	7.0
170°-180°	162.2	2.4
0°-30°	594.5	8.9
0°-40°	923.2	13.7
0°-60°	1462.6	21.8
0°-90°	1719.8	25.6
90°-120°	821.2	12.2
90°-150°	3631.1	54.1
90°-180°	4996.0	74.4
0°-180°	6715.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	1	15	25	31	33	6
95°	80	39	48	54	53	95
105°	375	412	75	89	94	401
115°	709	730	761	190	101	698
125°	1002	1019	1042	1051	1054	894
135°	1240	1260	1271	1284	1281	958
145°	1439	1438	1459	1467	1461	900
155°	1584	1574	1588	1596	1586	730
165°	1670	1662	1666	1674	1666	472
175°	1708	1699	1702	1710	1698	163
180°	1704	1704	1704	1704	1704	

TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	1.2	14.7	24.6	30.9	33.2
92.5°	30.9	26.0	29.6	32.1	33.2
95°	80.1	39.4	48.1	54.3	53.0
97.5°	144.2	43.2	62.8	66.7	67.8
100°	218.3	49.4	70.3	80.1	82.6
102.5°	299.6	297.2	72.8	86.2	90.1
105°	374.9	411.9	75.2	88.8	93.7
107.5°	462.4	493.1	77.8	91.2	96.2
110°	546.3	572.1	215.8	92.5	97.4

TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	625.2	647.3	626.4	94.9	98.7
115°	709.0	729.9	760.8	190.0	101.2
117.5°	781.7	806.4	827.5	651.0	328.0
120°	863.1	881.6	903.8	918.7	752.1
122.5°	932.1	951.9	976.6	984.0	985.3
125°	1002.4	1018.6	1042.0	1050.6	1054.3
127.5°	1066.5	1083.8	1102.5	1114.7	1115.9
130°	1127.0	1146.8	1160.2	1173.9	1172.8
132.5°	1188.7	1204.8	1218.2	1229.4	1228.2
135°	1240.5	1260.3	1271.2	1283.7	1281.2
137.5°	1294.6	1309.5	1321.9	1334.2	1330.6
140°	1347.7	1357.7	1371.1	1382.2	1376.1
142.5°	1392.2	1400.9	1416.8	1426.6	1420.5
145°	1439.1	1437.7	1458.6	1467.3	1461.2
147.5°	1479.7	1475.9	1496.9	1503.1	1498.2
150°	1519.1	1510.6	1530.2	1537.6	1531.5
152.5°	1552.4	1542.6	1561.1	1568.5	1559.8
155°	1584.5	1573.5	1588.2	1595.6	1585.8
157.5°	1610.3	1600.5	1611.6	1620.3	1610.3
160°	1632.6	1625.2	1632.6	1639.9	1631.3
162.5°	1652.2	1645.0	1651.0	1659.7	1648.6
165°	1669.5	1662.2	1665.9	1674.5	1665.9
167.5°	1683.1	1675.7	1679.5	1688.1	1677.0
170°	1694.3	1686.8	1689.3	1697.9	1686.8
172.5°	1701.6	1694.3	1696.8	1705.4	1694.3
175°	1707.8	1699.1	1701.6	1710.2	1697.9
177.5°	1710.2	1701.6	1702.9	1711.5	1700.4
180°	1704.0	1704.0	1704.0	1704.0	1704.0

TEST NUMBER: P907645

CATALOG NUMBER: DFN2DIP-4P3F0-020D050US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.06	4.73	5.21	5.86	7.44	0.03	0.69	1.17	1.82	3.41
	3H	5.73	6.32	6.88	7.46	9.06	1.20	1.79	2.35	2.93	4.53
	4H	6.32	6.89	7.48	8.03	9.63	1.63	2.20	2.80	3.34	4.94
	6H	6.73	7.25	7.90	8.39	10.01	1.94	2.46	3.11	3.60	5.22
	8H	6.85	7.34	8.02	8.50	10.11	2.02	2.52	3.19	3.67	5.28
	12H	6.91	7.37	8.08	8.53	10.15	2.06	2.52	3.23	3.68	5.30
4H	2H	4.06	4.62	5.23	5.76	7.37	0.60	1.16	1.77	2.30	3.91
	3H	5.87	6.34	7.04	7.50	9.12	1.93	2.40	3.10	3.56	5.18
	4H	6.55	6.98	7.73	8.14	9.77	2.46	2.89	3.64	4.05	5.68
	6H	7.05	7.42	8.23	8.60	10.22	2.86	3.23	4.05	4.41	6.03
	8H	7.22	7.57	8.40	8.74	10.38	2.99	3.33	4.17	4.50	6.14
	12H	7.31	7.62	8.50	8.80	10.44	3.04	3.35	4.23	4.53	6.18
8H	4H	6.50	6.85	7.68	8.02	9.66	2.73	3.07	3.91	4.24	5.88
	6H	7.06	7.34	8.26	8.55	10.19	3.23	3.51	4.43	4.72	6.36
	8H	7.27	7.52	8.48	8.71	10.37	3.42	3.66	4.62	4.85	6.51
	12H	7.40	7.62	8.61	8.80	10.49	3.52	3.74	4.73	4.92	6.61
12H	4H	6.45	6.76	7.64	7.94	9.59	2.72	3.04	3.92	4.22	5.86
	6H	7.03	7.28	8.24	8.47	10.13	3.28	3.52	4.48	4.71	6.37
	8H	7.24	7.46	8.45	8.65	10.34	3.47	3.69	4.68	4.88	6.57

END OF REPORT