

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332631-840

Luminaire Tested: **SA4XXDIP-C1020D365U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332631-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5949.0 lumens  
Efficiency: N/A  
Efficacy: 136.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	63				
2	94	86	80	74	89	82	77	72	75	70	66	68	64	61	62	59	56	53				
3	86	76	68	62	81	73	66	60	66	60	56	60	56	52	55	51	48	45				
4	79	67	59	53	75	64	57	51	59	53	48	54	49	44	49	45	41	38				
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33				
6	67	54	46	40	63	52	44	38	48	41	36	44	38	34	40	35	32	29				
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26				
8	58	45	37	31	55	43	35	30	40	33	29	37	31	27	34	29	25	23				
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21				
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	164.1	2.8
10°-20°	462.4	7.8
20°-30°	680.5	11.4
30°-40°	791.1	13.3
40°-50°	791.2	13.3
50°-60°	692.1	11.6
60°-70°	514.0	8.6
70°-80°	292.0	4.9
80°-90°	85.6	1.4
90°-100°	16.3	0.3
100°-110°	104.1	1.7
110°-120°	199.1	3.3
120°-130°	252.7	4.2
130°-140°	270.4	4.5
140°-150°	252.8	4.3
150°-160°	203.9	3.4
160°-170°	131.5	2.2
170°-180°	45.3	0.8
0°-30°	1307.0	22.0
0°-40°	2098.1	35.3
0°-60°	3581.3	60.2
0°-90°	4472.9	75.2
90°-120°	319.5	5.4
90°-150°	1095.3	18.4
90°-180°	1476.0	24.8
0°-180°	5949.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	1	5	8	10	11	5
95°	20	8	8	10	10	25
105°	107	110	111	114	102	112
115°	201	202	201	202	202	197
125°	282	283	283	284	284	252
135°	350	349	351	352	352	269
145°	403	404	404	405	406	252
155°	442	442	442	443	442	204
165°	466	465	465	467	464	132
175°	477	475	475	478	474	45
180°	477	477	477	477	477	



TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.3	29.2	29.1	29.1	29.0	28.9	28.8	28.6	28.5	28.4	28.5
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.7	6.3	7.0	7.6	8.1
95°	19.6	17.0	14.2	11.5	8.9	7.6	7.6	7.7	7.8	7.9	8.3
97.5°	41.7	43.3	45.0	46.8	48.4	44.8	36.0	27.2	18.3	9.4	9.5
100°	58.6	60.0	61.4	62.8	64.2	59.5	48.6	37.6	26.7	15.8	14.3
102.5°	77.4	78.5	79.5	80.5	81.6	81.4	80.0	78.6	77.1	75.6	61.1
105°	107.4	107.9	108.4	108.9	109.4	109.8	110.2	110.6	111.0	111.4	112.1
107.5°	135.3	135.5	135.8	136.0	136.3	136.6	137.2	137.7	138.3	138.9	139.2
110°	154.2	154.4	154.6	154.9	155.1	155.5	155.9	156.4	156.9	157.4	157.5



TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.5	172.9	173.3	173.7	174.2	174.5	174.7	174.9	175.1	175.4	175.3
115°	200.6	200.9	201.1	201.3	201.6	201.6	201.6	201.5	201.4	201.3	201.5
117.5°	225.9	226.2	226.5	226.9	227.2	227.4	227.6	227.8	227.9	228.1	228.1
120°	243.1	243.4	243.7	244.0	244.3	244.4	244.4	244.3	244.2	244.1	244.3
122.5°	259.0	259.2	259.4	259.6	259.8	259.9	260.0	260.1	260.2	260.4	260.4
125°	282.0	282.3	282.6	282.9	283.3	283.3	283.2	283.0	282.9	282.7	282.9
127.5°	303.7	303.8	303.8	303.9	304.0	304.2	304.6	304.9	305.3	305.7	305.6
130°	317.6	317.7	317.8	317.9	318.0	318.1	318.3	318.6	318.8	319.1	319.1
132.5°	330.5	330.6	330.7	330.9	331.0	331.2	331.5	331.8	332.1	332.4	332.5
135°	349.7	349.7	349.6	349.5	349.4	349.5	349.9	350.2	350.5	350.8	351.0
137.5°	366.8	366.9	366.9	366.9	367.0	367.2	367.5	367.8	368.2	368.5	368.7
140°	378.0	378.1	378.3	378.4	378.6	378.7	378.9	379.1	379.2	379.4	379.6
142.5°	388.0	388.2	388.5	388.8	389.1	389.3	389.4	389.5	389.6	389.7	389.8
145°	403.3	403.5	403.7	404.0	404.2	404.3	404.3	404.3	404.3	404.3	404.5
147.5°	415.5	416.0	416.4	416.9	417.3	417.5	417.4	417.3	417.2	417.2	417.2
150°	424.3	424.6	425.0	425.4	425.7	425.8	425.7	425.6	425.5	425.5	425.5
152.5°	431.8	432.0	432.3	432.5	432.8	432.8	432.7	432.5	432.4	432.3	432.4
155°	442.2	442.3	442.3	442.4	442.5	442.4	442.2	441.9	441.7	441.5	441.8
157.5°	451.0	450.9	450.9	450.8	450.8	450.6	450.4	450.1	449.8	449.6	450.0
160°	456.2	455.9	455.7	455.4	455.1	455.0	454.9	454.8	454.7	454.6	455.1
162.5°	460.7	460.4	460.1	459.8	459.5	459.3	459.2	459.1	459.1	459.0	459.5
165°	466.5	466.1	465.6	465.2	464.8	464.6	464.6	464.6	464.6	464.6	465.3
167.5°	471.0	470.6	470.2	469.8	469.4	469.2	469.1	469.1	469.0	469.0	469.7
170°	473.6	473.1	472.6	472.2	471.7	471.5	471.6	471.7	471.7	471.8	472.4
172.5°	475.3	474.8	474.3	473.9	473.4	473.2	473.3	473.4	473.4	473.5	474.1
175°	477.2	476.7	476.3	475.7	475.2	475.0	475.1	475.2	475.3	475.3	476.2
177.5°	478.1	477.6	477.2	476.7	476.3	476.1	476.3	476.4	476.5	476.6	477.2
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	28.6	28.7	28.8	28.8	28.9	28.9	28.9	29.0
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	8.5	9.0	9.5	9.7	9.8	9.8	9.8	9.9
95°	8.8	9.3	9.8	10.0	10.1	10.2	10.3	10.3
97.5°	9.5	9.6	9.6	9.7	9.8	9.8	9.9	10.0
100°	13.0	11.6	10.3	9.7	9.8	9.8	9.9	10.0
102.5°	46.6	32.0	17.5	10.2	10.2	10.2	10.3	10.3
105°	112.8	113.5	114.2	113.1	110.3	107.4	104.5	101.7
107.5°	139.6	139.9	140.3	140.6	140.9	141.2	141.5	141.8
110°	157.7	157.8	158.0	158.2	158.4	158.8	159.0	159.2





TEST NUMBER: P332631-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.3	175.3	175.2	175.4	175.7	176.0	176.3	176.6
115°	201.6	201.8	202.0	202.0	202.0	202.0	202.0	202.0
117.5°	228.0	228.0	228.0	227.9	227.9	227.9	227.9	227.8
120°	244.4	244.6	244.8	244.8	244.6	244.4	244.3	244.1
122.5°	260.5	260.6	260.7	260.7	260.5	260.4	260.2	260.1
125°	283.2	283.4	283.6	283.8	283.9	284.0	284.0	284.1
127.5°	305.6	305.5	305.5	305.4	305.4	305.3	305.2	305.2
130°	319.2	319.3	319.4	319.4	319.4	319.4	319.4	319.4
132.5°	332.6	332.8	332.9	332.9	332.8	332.6	332.6	332.5
135°	351.1	351.3	351.4	351.6	351.7	351.9	352.1	352.2
137.5°	368.9	369.1	369.2	369.3	369.2	369.2	369.1	369.1
140°	379.8	380.1	380.3	380.5	380.6	380.6	380.7	380.8
142.5°	390.0	390.2	390.3	390.4	390.5	390.5	390.5	390.5
145°	404.6	404.7	404.7	404.8	405.0	405.2	405.3	405.5
147.5°	417.3	417.4	417.4	417.5	417.6	417.6	417.7	417.8
150°	425.5	425.5	425.5	425.5	425.6	425.7	425.7	425.8
152.5°	432.5	432.6	432.8	432.8	432.7	432.7	432.7	432.6
155°	442.1	442.4	442.7	442.8	442.5	442.3	442.1	441.8
157.5°	450.4	450.8	451.2	451.2	450.8	450.4	450.0	449.6
160°	455.7	456.2	456.6	456.6	456.2	455.7	455.1	454.6
162.5°	459.9	460.4	460.9	460.8	460.3	459.8	459.2	458.7
165°	466.0	466.6	467.3	467.2	466.5	465.7	465.0	464.3
167.5°	470.4	471.1	471.7	471.7	470.9	470.1	469.3	468.6
170°	473.1	473.7	474.3	474.2	473.5	472.7	471.9	471.1
172.5°	474.8	475.4	476.1	475.9	475.1	474.2	473.4	472.5
175°	476.9	477.6	478.3	478.2	477.2	476.3	475.2	474.3
177.5°	477.7	478.2	478.7	478.5	477.8	477.0	476.3	475.4
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2

(END OF REPORT)