

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332632-840

Luminaire Tested: **SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332632-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5753.1 lumens
Efficiency: N/A
Efficacy: 132.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332632-840
CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332632-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	59	53	75	65	57	51	60	53	48	55	50	45	50	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14067	14067	14067
5°	14109	13940	14041
10°	14021	13827	13896
15°	13852	13630	13665
20°	13626	13387	13399
25°	13370	13109	13071
30°	13055	12781	12665
35°	12728	12439	12275
40°	12390	12052	11830
45°	12036	11669	11445
50°	11645	11328	10977
55°	11222	10888	10534
60°	10798	10393	10077
65°	10323	9922	9522
70°	9788	9293	8932
75°	8971	8537	8319
80°	7987	7657	7466
85°	6984	6725	6595



TEST NUMBER: P332632-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.1	2.9
10°-20°	462.4	8.0
20°-30°	680.5	11.8
30°-40°	791.1	13.8
40°-50°	791.2	13.8
50°-60°	692.1	12.0
60°-70°	514.0	8.9
70°-80°	292.0	5.1
80°-90°	85.6	1.5
90°-100°	30.4	0.5
100°-110°	90.2	1.6
110°-120°	153.0	2.7
120°-130°	201.8	3.5
130°-140°	226.6	3.9
140°-150°	222.7	3.9
150°-160°	187.3	3.3
160°-170°	124.6	2.2
170°-180°	43.6	0.8
0°-30°	1307.0	22.7
0°-40°	2098.1	36.5
0°-60°	3581.3	62.3
0°-90°	4472.9	77.7
90°-120°	273.6	4.8
90°-150°	924.6	16.1
90°-180°	1280.0	22.2
0°-180°	5753.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1742	1742	1742	1742	1742	
5°	1741	1735	1720	1735	1733	165
15°	1657	1651	1631	1638	1635	467
25°	1501	1491	1472	1473	1467	690
35°	1292	1281	1262	1253	1246	807
45°	1054	1044	1022	1007	1002	812
55°	797	792	774	757	748	714
65°	540	533	519	506	498	535
75°	288	281	274	268	267	306
85°	75	75	73	72	71	83
90°	1	5	8	10	11	5
95°	21	25	27	28	28	24
105°	83	84	85	86	87	88
115°	156	156	155	154	154	153
125°	227	227	226	226	225	202
135°	292	294	294	294	293	226
145°	355	356	357	356	356	222
155°	407	407	406	408	406	187
165°	443	442	441	443	442	125
175°	461	459	459	461	459	44
180°	461	461	461	461	461	



TEST NUMBER: P332632-840
 CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1747.0	1746.3	1745.5	1744.7	1744.0	1742.2	1739.5	1736.8	1734.0	1731.3	1733.8
5°	1741.1	1739.9	1738.7	1737.4	1736.2	1733.8	1730.4	1727.0	1723.6	1720.2	1723.6
7.5°	1725.0	1723.6	1722.4	1721.2	1720.0	1717.5	1713.6	1709.9	1706.1	1702.3	1705.1
10°	1710.4	1709.2	1707.9	1706.7	1705.5	1702.8	1698.8	1694.8	1690.7	1686.7	1689.1
12.5°	1691.4	1690.2	1688.9	1687.7	1686.5	1683.6	1679.4	1675.2	1670.8	1666.6	1669.3
15°	1657.4	1656.1	1654.9	1653.7	1652.3	1649.4	1644.8	1640.1	1635.5	1630.8	1632.6
17.5°	1616.3	1614.8	1613.2	1611.6	1610.1	1607.1	1602.7	1598.3	1593.9	1589.5	1590.6
20°	1586.1	1584.6	1583.1	1581.4	1579.9	1576.8	1572.2	1567.5	1562.9	1558.2	1559.1
22.5°	1553.8	1551.7	1549.6	1547.6	1545.6	1542.2	1537.5	1532.9	1528.2	1523.6	1525.3
25°	1501.0	1498.8	1496.6	1494.4	1492.3	1489.0	1484.7	1480.4	1476.0	1471.7	1472.0
27.5°	1440.7	1438.5	1436.1	1433.9	1431.7	1428.6	1424.5	1420.5	1416.4	1412.4	1411.7
30°	1400.5	1398.0	1395.4	1393.0	1390.5	1387.3	1383.2	1379.2	1375.1	1371.1	1369.9
32.5°	1358.0	1355.7	1353.5	1351.3	1349.1	1345.7	1341.5	1337.3	1332.9	1328.7	1327.2
35°	1291.5	1289.4	1287.2	1285.1	1282.8	1279.6	1275.3	1270.9	1266.6	1262.2	1260.0
37.5°	1221.4	1219.4	1217.5	1215.5	1213.5	1210.2	1205.5	1200.8	1196.2	1191.5	1189.2
40°	1175.7	1173.2	1170.6	1168.2	1165.7	1162.2	1157.5	1152.9	1148.2	1143.6	1140.4
42.5°	1126.5	1125.0	1123.5	1122.1	1120.5	1117.2	1112.1	1106.9	1101.8	1096.6	1093.0
45°	1054.2	1052.0	1049.9	1047.6	1045.5	1041.9	1036.9	1032.0	1027.0	1022.1	1018.7
47.5°	978.5	977.0	975.5	974.0	972.5	969.5	964.9	960.3	955.7	951.1	947.3
50°	927.2	925.8	924.6	923.4	922.1	919.4	915.0	910.7	906.4	902.0	897.7
52.5°	876.9	875.4	873.8	872.4	870.9	867.9	863.2	858.7	854.0	849.5	845.7
55°	797.3	796.3	795.4	794.5	793.6	790.9	786.6	782.2	777.9	773.6	769.8
57.5°	721.3	720.2	719.2	718.1	717.1	714.4	710.1	705.9	701.6	697.3	693.8
60°	668.8	667.2	665.7	664.2	662.6	659.8	655.8	651.8	647.7	643.7	640.9
62.5°	617.4	616.1	614.8	613.5	612.2	609.5	605.1	600.9	596.5	592.3	589.8
65°	540.4	538.8	537.2	535.7	534.1	531.8	528.7	525.6	522.5	519.4	516.3
67.5°	462.7	461.3	459.9	458.5	457.0	454.8	451.8	448.9	445.9	442.9	439.9
70°	414.7	412.5	410.3	408.2	406.0	403.6	401.2	398.7	396.3	393.7	391.2
72.5°	363.3	361.1	359.0	356.8	354.7	352.5	350.5	348.6	346.6	344.6	342.6
75°	287.6	286.1	284.5	283.0	281.4	279.8	278.3	276.8	275.2	273.7	272.5
77.5°	215.3	214.6	213.9	213.3	212.6	211.6	210.2	208.8	207.4	206.1	205.7
80°	171.8	170.8	169.9	169.0	168.0	167.2	166.6	166.0	165.4	164.7	164.1
82.5°	129.3	128.9	128.5	127.9	127.5	127.2	127.1	127.0	126.9	126.7	126.4
85°	75.4	75.4	75.4	75.4	75.4	75.1	74.4	73.8	73.2	72.6	72.6
87.5°	29.3	29.2	29.1	29.1	29.0	28.9	28.8	28.6	28.5	28.4	28.5
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	7.7	8.7	9.6	10.6	11.6	12.3	12.8	13.2	13.7	14.1	14.4
95°	21.4	22.1	22.8	23.5	24.2	24.9	25.4	26.1	26.6	27.2	27.4
97.5°	37.4	38.0	38.6	39.1	39.7	40.3	40.9	41.6	42.2	42.9	43.2
100°	50.0	50.3	50.6	50.9	51.2	51.7	52.4	53.2	53.9	54.6	54.7
102.5°	63.1	63.2	63.3	63.5	63.6	64.0	64.6	65.3	65.9	66.6	66.9
105°	83.1	83.2	83.3	83.4	83.4	83.6	84.0	84.3	84.6	84.9	85.1
107.5°	104.2	104.3	104.4	104.5	104.6	104.6	104.7	104.7	104.8	104.8	105.0
110°	118.5	118.7	118.8	119.0	119.1	119.2	119.1	119.0	118.9	118.9	118.7



TEST NUMBER: P332632-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	133.3	133.3	133.4	133.4	133.4	133.4	133.2	133.1	133.0	132.8	132.8
115°	155.6	155.6	155.6	155.6	155.6	155.5	155.3	155.2	155.0	154.9	154.8
117.5°	176.5	176.6	176.7	176.7	176.8	176.8	176.7	176.6	176.4	176.3	176.1
120°	190.6	190.9	191.2	191.5	191.9	191.9	191.7	191.4	191.2	191.0	190.6
122.5°	205.1	205.2	205.4	205.5	205.6	205.6	205.5	205.4	205.3	205.2	204.9
125°	226.6	226.6	226.6	226.6	226.6	226.5	226.5	226.4	226.3	226.2	226.1
127.5°	246.1	246.3	246.6	246.8	247.0	247.1	247.0	246.8	246.7	246.6	246.4
130°	259.8	260.0	260.2	260.5	260.7	260.8	260.8	260.8	260.8	260.8	260.7
132.5°	273.8	274.0	274.1	274.3	274.5	274.5	274.5	274.4	274.4	274.3	274.1
135°	292.3	292.8	293.2	293.7	294.2	294.4	294.4	294.4	294.4	294.4	294.3
137.5°	312.4	312.7	312.9	313.1	313.3	313.5	313.6	313.7	313.9	314.0	313.8
140°	325.8	326.0	326.1	326.3	326.5	326.5	326.5	326.5	326.5	326.5	326.5
142.5°	338.1	338.2	338.4	338.5	338.7	338.8	338.7	338.6	338.6	338.5	338.5
145°	355.1	355.4	355.7	356.0	356.4	356.6	356.6	356.7	356.8	356.9	356.8
147.5°	371.9	372.3	372.6	373.0	373.4	373.5	373.5	373.4	373.4	373.3	373.2
150°	382.2	382.5	382.8	383.1	383.4	383.6	383.6	383.6	383.6	383.6	383.6
152.5°	391.9	392.1	392.2	392.4	392.6	392.7	392.8	392.9	392.9	393.0	393.2
155°	406.8	406.8	406.8	406.8	406.8	406.8	406.7	406.6	406.6	406.5	406.8
157.5°	419.4	419.2	419.1	419.0	418.8	418.7	418.7	418.7	418.7	418.7	418.9
160°	426.8	426.7	426.7	426.6	426.5	426.4	426.4	426.3	426.2	426.1	426.4
162.5°	433.6	433.4	433.2	433.0	432.8	432.7	432.6	432.5	432.4	432.3	432.8
165°	442.8	442.6	442.4	442.1	441.9	441.7	441.5	441.4	441.2	441.1	441.5
167.5°	449.9	449.6	449.3	448.9	448.6	448.4	448.5	448.5	448.5	448.5	449.0
170°	453.9	453.5	453.1	452.7	452.3	452.2	452.2	452.3	452.4	452.5	452.9
172.5°	456.8	456.5	456.1	455.8	455.4	455.2	455.2	455.3	455.3	455.3	455.9
175°	460.7	460.3	459.9	459.5	459.1	458.9	458.8	458.7	458.7	458.6	459.1
177.5°	462.0	461.7	461.3	461.0	460.7	460.6	460.6	460.6	460.6	460.6	461.0
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4



TEST NUMBER: P332632-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5	1742.5
2.5°	1736.3	1738.8	1741.3	1742.4	1742.1	1741.9	1741.6	1741.4
5°	1727.0	1730.4	1733.8	1735.3	1734.6	1733.9	1733.3	1732.7
7.5°	1707.8	1710.5	1713.2	1714.4	1714.0	1713.6	1713.2	1712.9
10°	1691.6	1694.1	1696.6	1697.5	1696.9	1696.3	1695.7	1695.1
12.5°	1672.0	1674.8	1677.5	1678.4	1677.6	1676.7	1675.8	1675.0
15°	1634.6	1636.4	1638.3	1638.7	1637.8	1636.9	1636.0	1635.0
17.5°	1591.9	1593.1	1594.2	1594.5	1593.9	1593.3	1592.7	1592.0
20°	1560.0	1561.0	1562.0	1562.1	1561.5	1560.8	1560.2	1559.6
22.5°	1526.9	1528.6	1530.2	1530.6	1529.4	1528.3	1527.2	1526.1
25°	1472.3	1472.6	1472.9	1472.4	1471.2	1470.0	1468.6	1467.4
27.5°	1411.0	1410.2	1409.5	1408.4	1406.7	1405.2	1403.6	1402.1
30°	1368.7	1367.4	1366.1	1364.7	1363.2	1361.6	1360.1	1358.6
32.5°	1325.6	1324.2	1322.7	1321.2	1319.6	1318.1	1316.6	1314.9
35°	1257.9	1255.7	1253.5	1251.6	1250.1	1248.6	1247.0	1245.5
37.5°	1186.8	1184.5	1182.1	1179.9	1177.9	1175.8	1173.8	1171.7
40°	1137.3	1134.2	1131.1	1128.8	1127.2	1125.7	1124.2	1122.6
42.5°	1089.4	1085.8	1082.2	1079.8	1078.8	1077.7	1076.7	1075.7
45°	1015.2	1011.8	1008.4	1006.2	1005.3	1004.4	1003.4	1002.5
47.5°	943.4	939.6	935.7	932.6	930.3	927.9	925.5	923.2
50°	893.3	889.0	884.6	881.5	879.6	877.8	876.0	874.0
52.5°	841.8	837.9	834.0	831.0	828.6	826.3	823.9	821.5
55°	766.1	762.3	758.6	755.9	754.0	752.1	750.2	748.4
57.5°	690.2	686.7	683.2	680.4	678.6	676.9	675.1	673.3
60°	638.1	635.3	632.5	630.4	628.7	627.2	625.7	624.1
62.5°	587.2	584.6	582.1	580.1	578.6	576.9	575.4	573.9
65°	513.2	510.1	507.0	504.6	503.1	501.6	500.0	498.5
67.5°	437.0	433.9	431.0	429.3	428.8	428.4	428.0	427.6
70°	388.8	386.3	383.8	382.1	381.2	380.2	379.3	378.4
72.5°	340.6	338.6	336.7	335.2	334.3	333.4	332.4	331.4
75°	271.1	269.9	268.7	267.9	267.6	267.3	267.0	266.7
77.5°	205.3	205.0	204.6	204.0	203.2	202.4	201.6	200.8
80°	163.5	162.9	162.3	161.8	161.5	161.2	160.9	160.6
82.5°	126.0	125.6	125.3	124.9	124.6	124.3	124.0	123.7
85°	72.6	72.6	72.6	72.4	72.1	71.8	71.5	71.2
87.5°	28.6	28.7	28.8	28.8	28.9	28.9	28.9	29.0
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	14.7	14.9	15.2	15.5	15.6	15.7	15.8	15.9
95°	27.6	27.9	28.1	28.2	28.2	28.2	28.2	28.2
97.5°	43.4	43.7	44.0	44.1	44.1	44.1	44.1	44.1
100°	54.9	55.0	55.2	55.3	55.3	55.3	55.3	55.3
102.5°	67.1	67.3	67.5	67.7	67.7	67.8	67.8	67.9
105°	85.4	85.6	85.8	86.1	86.3	86.6	86.8	87.1
107.5°	105.3	105.5	105.7	105.8	105.8	105.8	105.8	105.7
110°	118.6	118.4	118.2	118.3	118.5	118.8	119.0	119.2



TEST NUMBER: P332632-840

CATALOG NUMBER: SA4XXDIP-C1020D365U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.8	132.7	132.7	132.7	132.8	132.8	132.8	132.9
115°	154.7	154.6	154.5	154.5	154.4	154.3	154.2	154.2
117.5°	175.8	175.5	175.3	175.1	174.9	174.7	174.6	174.4
120°	190.2	189.8	189.3	189.2	189.3	189.6	189.7	189.9
122.5°	204.7	204.4	204.1	203.8	203.6	203.3	203.0	202.7
125°	225.9	225.8	225.6	225.4	225.3	225.1	225.0	224.8
127.5°	246.3	246.1	245.9	245.8	245.7	245.6	245.4	245.3
130°	260.5	260.3	260.2	259.9	259.6	259.3	259.0	258.7
132.5°	274.0	273.8	273.7	273.5	273.4	273.3	273.2	273.0
135°	294.1	294.0	293.8	293.6	293.4	293.1	292.9	292.7
137.5°	313.6	313.4	313.2	313.1	313.1	313.2	313.2	313.3
140°	326.4	326.3	326.2	326.1	326.1	326.0	325.9	325.8
142.5°	338.5	338.5	338.4	338.4	338.4	338.4	338.4	338.4
145°	356.7	356.6	356.6	356.4	356.2	355.9	355.7	355.5
147.5°	373.2	373.1	373.0	373.0	372.9	372.8	372.7	372.7
150°	383.6	383.6	383.6	383.5	383.5	383.4	383.3	383.2
152.5°	393.4	393.6	393.8	393.7	393.5	393.3	393.1	392.9
155°	407.1	407.4	407.7	407.7	407.4	407.1	406.8	406.5
157.5°	419.1	419.4	419.6	419.6	419.3	419.1	418.8	418.5
160°	426.6	426.8	427.1	427.0	426.6	426.2	425.8	425.4
162.5°	433.2	433.6	434.0	434.0	433.7	433.3	432.9	432.5
165°	442.0	442.5	442.9	443.0	442.7	442.4	442.1	441.8
167.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
170°	453.4	453.9	454.4	454.3	453.8	453.2	452.7	452.1
172.5°	456.5	457.0	457.5	457.5	457.0	456.4	455.9	455.2
175°	459.7	460.2	460.8	460.8	460.2	459.7	459.1	458.6
177.5°	461.4	461.9	462.3	462.3	461.8	461.3	460.8	460.3
180°	461.4	461.4	461.4	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)