

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332704-840

Luminaire Tested: **SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332704-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8784.2 lumens  
Efficiency: N/A  
Efficacy: 131.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332704-840  
CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	82	77	75	72	67	65	63	57	55	54	49
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	48	46	41
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	33	30
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	2.2
10°-20°	534.0	6.1
20°-30°	786.0	8.9
30°-40°	913.7	10.4
40°-50°	913.7	10.4
50°-60°	799.3	9.1
60°-70°	593.6	6.8
70°-80°	337.2	3.8
80°-90°	101.2	1.2
90°-100°	86.0	1.0
100°-110°	254.7	2.9
110°-120°	432.2	4.9
120°-130°	569.9	6.5
130°-140°	640.1	7.3
140°-150°	629.0	7.2
150°-160°	529.0	6.0
160°-170°	352.0	4.0
170°-180°	123.2	1.4
0°-30°	1509.5	17.2
0°-40°	2423.2	27.6
0°-60°	4136.2	47.1
0°-90°	5168.2	58.8
90°-120°	772.9	8.8
90°-150°	2611.8	29.7
90°-180°	3616.0	41.2
0°-180°	8784.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	3	14	22	28	30	8
95°	60	69	77	80	80	67
105°	235	236	240	243	246	249
115°	440	439	438	436	436	433
125°	640	640	639	637	635	570
135°	826	831	832	830	827	638
145°	1003	1007	1008	1007	1004	627
155°	1149	1149	1148	1152	1148	528
165°	1251	1248	1246	1251	1248	352
175°	1301	1297	1295	1302	1295	123
180°	1303	1303	1303	1303	1303	



TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	34.1	34.3	34.5	34.7	34.9	35.1	35.1	35.2	35.3	35.4	35.6
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	21.6	24.4	27.2	30.0	32.8	34.9	36.2	37.4	38.7	39.9	40.7
95°	60.5	62.5	64.5	66.6	68.6	70.3	71.9	73.5	75.0	76.6	77.3
97.5°	105.6	107.2	108.9	110.5	112.1	113.8	115.6	117.4	119.4	121.2	122.0
100°	141.1	142.0	142.9	143.8	144.7	146.1	148.1	150.2	152.2	154.2	154.7
102.5°	178.2	178.5	178.9	179.3	179.7	180.8	182.6	184.4	186.2	188.1	188.7
105°	234.9	235.1	235.3	235.5	235.8	236.3	237.2	238.1	239.0	239.9	240.5
107.5°	294.4	294.6	294.9	295.2	295.4	295.6	295.8	295.9	296.0	296.2	296.8
110°	334.7	335.1	335.6	336.0	336.5	336.6	336.3	336.1	335.9	335.7	335.2



TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.6	376.7	376.8	376.9	377.0	376.8	376.4	376.0	375.6	375.2	375.1
115°	439.5	439.5	439.5	439.5	439.5	439.3	438.8	438.4	437.9	437.5	437.3
117.5°	498.8	499.0	499.1	499.3	499.5	499.4	499.1	498.8	498.5	498.2	497.4
120°	538.3	539.2	540.1	541.0	541.9	542.0	541.3	540.6	540.0	539.3	538.2
122.5°	579.4	579.8	580.1	580.5	580.8	580.9	580.6	580.2	579.9	579.6	578.9
125°	640.1	640.1	640.1	640.1	640.1	640.0	639.7	639.5	639.2	639.0	638.6
127.5°	695.1	695.8	696.4	697.1	697.8	697.9	697.6	697.2	696.9	696.5	696.1
130°	733.8	734.5	735.2	735.8	736.5	736.8	736.8	736.8	736.8	736.8	736.4
132.5°	773.4	773.9	774.3	774.8	775.3	775.5	775.3	775.1	774.9	774.8	774.3
135°	825.6	826.9	828.2	829.6	830.9	831.6	831.6	831.6	831.6	831.6	831.1
137.5°	882.4	883.0	883.6	884.2	884.9	885.3	885.8	886.2	886.5	886.9	886.3
140°	920.3	920.7	921.2	921.6	922.1	922.3	922.3	922.3	922.3	922.3	922.1
142.5°	954.9	955.4	955.8	956.3	956.7	956.8	956.7	956.5	956.3	956.1	956.1
145°	1002.9	1003.8	1004.7	1005.6	1006.5	1007.0	1007.3	1007.5	1007.7	1007.9	1007.7
147.5°	1050.6	1051.6	1052.7	1053.8	1054.8	1055.3	1055.1	1054.9	1054.7	1054.6	1054.4
150°	1079.5	1080.5	1081.4	1082.3	1083.2	1083.6	1083.6	1083.6	1083.6	1083.6	1083.6
152.5°	1107.0	1107.5	1108.0	1108.6	1109.1	1109.4	1109.6	1109.8	1110.0	1110.1	1110.8
155°	1149.1	1149.1	1149.1	1149.1	1149.1	1149.0	1148.7	1148.5	1148.3	1148.1	1149.0
157.5°	1184.6	1184.2	1183.8	1183.4	1183.0	1182.8	1182.7	1182.7	1182.7	1182.6	1183.3
160°	1205.6	1205.3	1205.1	1204.9	1204.7	1204.5	1204.2	1204.0	1203.8	1203.6	1204.2
162.5°	1224.9	1224.4	1223.8	1223.1	1222.5	1222.1	1221.9	1221.7	1221.5	1221.2	1222.4
165°	1250.9	1250.2	1249.6	1248.9	1248.2	1247.7	1247.2	1246.8	1246.3	1245.9	1247.2
167.5°	1270.9	1269.9	1269.0	1268.1	1267.1	1266.7	1266.7	1266.8	1266.8	1266.9	1268.2
170°	1282.1	1281.0	1279.9	1278.8	1277.7	1277.2	1277.5	1277.7	1277.9	1278.1	1279.5
172.5°	1290.2	1289.3	1288.4	1287.4	1286.5	1286.0	1286.1	1286.1	1286.2	1286.2	1287.7
175°	1301.3	1300.2	1299.1	1298.0	1296.9	1296.2	1296.0	1295.7	1295.5	1295.3	1296.9
177.5°	1304.9	1304.0	1303.1	1302.2	1301.3	1300.9	1300.9	1300.9	1300.9	1300.9	1302.1
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3



TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	36.0	36.2	36.5	36.7	36.8	36.9	37.0	37.0
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	41.5	42.3	43.1	43.7	43.9	44.2	44.5	44.7
95°	78.0	78.7	79.3	79.7	79.7	79.7	79.7	79.7
97.5°	122.8	123.6	124.4	124.8	124.8	124.8	124.8	124.8
100°	155.1	155.5	156.0	156.2	156.2	156.2	156.2	156.2
102.5°	189.3	190.0	190.6	191.0	191.2	191.4	191.6	191.7
105°	241.3	242.0	242.6	243.3	243.9	244.6	245.3	245.9
107.5°	297.4	298.0	298.6	298.9	298.9	298.8	298.8	298.7
110°	334.8	334.3	333.9	334.0	334.7	335.3	336.0	336.7





TEST NUMBER: P332704-840

CATALOG NUMBER: SA4XXDIP-C1195D1035U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	375.0	374.9	374.9	374.9	375.0	375.1	375.3	375.4
115°	437.0	436.8	436.6	436.4	436.2	435.9	435.7	435.5
117.5°	496.7	495.8	495.1	494.5	494.0	493.6	493.1	492.7
120°	537.0	535.9	534.8	534.4	534.9	535.3	535.8	536.2
122.5°	578.0	577.3	576.5	575.7	574.9	574.1	573.3	572.5
125°	638.1	637.7	637.2	636.8	636.4	635.9	635.5	635.0
127.5°	695.6	695.2	694.7	694.3	694.0	693.6	693.3	692.9
130°	736.0	735.5	735.1	734.4	733.5	732.6	731.6	730.7
132.5°	773.9	773.4	773.0	772.5	772.1	771.8	771.4	771.1
135°	830.7	830.2	829.8	829.2	828.6	827.9	827.2	826.6
137.5°	885.7	885.0	884.5	884.2	884.4	884.5	884.6	884.8
140°	921.9	921.6	921.4	921.2	921.0	920.7	920.5	920.3
142.5°	956.0	956.0	956.0	955.9	955.9	955.8	955.8	955.7
145°	1007.5	1007.3	1007.0	1006.6	1005.9	1005.3	1004.6	1003.9
147.5°	1054.2	1054.0	1053.8	1053.6	1053.4	1053.2	1053.0	1052.8
150°	1083.6	1083.6	1083.6	1083.5	1083.3	1083.0	1082.8	1082.6
152.5°	1111.3	1111.8	1112.4	1112.4	1111.8	1111.2	1110.5	1109.9
155°	1149.9	1150.7	1151.7	1151.7	1150.7	1149.9	1149.0	1148.1
157.5°	1183.9	1184.6	1185.3	1185.2	1184.5	1183.7	1183.0	1182.1
160°	1204.9	1205.6	1206.2	1206.0	1204.9	1203.8	1202.6	1201.5
162.5°	1223.7	1224.9	1226.1	1226.2	1225.1	1224.0	1222.8	1221.6
165°	1248.6	1249.9	1251.2	1251.4	1250.6	1249.7	1248.8	1247.9
167.5°	1269.5	1270.9	1272.2	1272.2	1270.8	1269.4	1268.0	1266.7
170°	1280.8	1282.1	1283.5	1283.3	1281.8	1280.2	1278.7	1277.1
172.5°	1289.2	1290.7	1292.3	1292.2	1290.7	1289.1	1287.6	1286.0
175°	1298.4	1300.0	1301.5	1301.5	1300.0	1298.4	1296.9	1295.3
177.5°	1303.4	1304.6	1306.0	1305.9	1304.4	1302.9	1301.5	1300.1
180°	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3	1303.3

(END OF REPORT)