

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907690

Luminaire Tested: DFN2DIP-4P3F0-050D020US840-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907690  
REPORT IS A COMBINATION OF REPORTS P899035 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-050D020US840-FLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6786.3 lumens  
Efficiency: N/A  
Efficacy: 105.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 64.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907690  
CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907690

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	74				74
1	103	99	95	91	98	94	90	87	85	82	80	77	74	72	69	67	66	62				62
2	94	86	80	74	89	82	76	71	74	70	66	67	64	61	61	58	55	52				52
3	86	76	68	62	81	72	65	60	66	60	55	59	55	51	54	50	47	44				44
4	79	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38				38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36	33				33
6	67	54	46	40	63	52	44	38	47	41	36	43	38	34	39	35	31	29				29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	36	31	28	26				26
8	57	45	37	31	54	43	35	30	39	33	28	36	31	27	33	29	25	23				23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23	21				21
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19				19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2239	2239	2239
5°	2241	2206	2222
10°	2222	2175	2191
15°	2188	2138	2143
20°	2142	2087	2095
25°	2097	2026	2038
30°	2040	1969	1967
35°	1986	1902	1891
40°	1921	1835	1819
45°	1855	1767	1746
50°	1783	1696	1660
55°	1708	1613	1582
60°	1622	1516	1492
65°	1529	1414	1386
70°	1410	1291	1272
75°	1246	1143	1165
80°	1047	953	963
85°	738	632	630

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1855 cd/sqm



TEST NUMBER: P907690

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.9	2.7
10°-20°	520.3	7.7
20°-30°	764.6	11.3
30°-40°	888.1	13.1
40°-50°	887.0	13.1
50°-60°	773.4	11.4
60°-70°	571.7	8.4
70°-80°	323.5	4.8
80°-90°	87.2	1.3
90°-100°	39.5	0.6
100°-110°	125.6	1.9
110°-120°	214.9	3.2
120°-130°	282.7	4.2
130°-140°	317.3	4.7
140°-150°	311.1	4.6
150°-160°	261.0	3.8
160°-170°	173.1	2.6
170°-180°	60.5	0.9
0°-30°	1469.8	21.7
0°-40°	2357.9	34.7
0°-60°	4018.3	59.2
0°-90°	5000.7	73.7
90°-120°	380.0	5.6
90°-150°	1291.1	19.0
90°-180°	1786.0	26.3
0°-180°	6786.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	1	7	19	18	18	6
95°	28	34	34	34	34	31
105°	116	117	119	120	120	122
115°	216	219	218	217	216	213
125°	314	318	317	315	315	280
135°	406	412	413	412	411	314
145°	493	496	500	500	498	308
155°	563	565	566	569	568	259
165°	613	612	612	616	613	173
175°	638	636	635	639	636	61
180°	639	639	639	639	639	



TEST NUMBER: P907690

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	0.6	7.0	18.9	17.7	18.3
92.5°	11.9	16.2	16.8	17.4	17.4
95°	28.1	33.5	34.4	34.4	33.5
97.5°	46.8	51.8	53.9	53.9	53.9
100°	68.4	72.8	74.3	74.3	73.7
102.5°	91.1	94.3	96.4	97.0	96.4
105°	115.9	117.4	118.7	119.6	119.6
107.5°	140.6	142.9	142.9	143.3	140.6
110°	164.5	167.5	167.5	167.5	166.0



TEST NUMBER: P907690

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	190.3	193.5	193.0	191.4	190.3
115°	215.7	218.7	217.8	217.2	215.7
117.5°	241.0	245.2	242.5	241.0	239.3
120°	266.3	270.5	266.3	266.3	264.6
122.5°	289.4	294.8	292.2	290.6	289.4
125°	313.7	318.5	317.0	315.3	314.7
127.5°	337.4	343.4	341.2	338.9	337.4
130°	359.5	366.5	365.5	364.4	362.2
132.5°	384.4	389.8	390.1	387.5	385.9
135°	405.8	411.7	412.8	412.3	410.7
137.5°	429.6	434.4	435.5	435.1	432.7
140°	450.6	455.4	458.2	458.2	456.1
142.5°	472.2	477.0	478.6	479.1	477.0
145°	492.6	496.4	499.6	500.1	498.0
147.5°	510.9	515.7	518.1	519.0	516.8
150°	529.8	533.0	535.1	536.8	535.1
152.5°	546.5	549.8	552.5	554.6	552.5
155°	563.3	564.8	566.5	569.3	567.5
157.5°	577.7	578.9	579.9	583.7	581.0
160°	590.7	591.8	592.4	595.6	593.3
162.5°	602.6	602.6	603.1	606.8	604.1
165°	612.8	612.2	612.2	616.0	613.4
167.5°	622.0	620.3	620.3	624.1	621.5
170°	628.9	627.4	626.8	630.7	627.4
172.5°	633.8	632.2	631.7	635.5	632.2
175°	637.6	636.1	634.9	638.7	635.5
177.5°	639.7	638.2	637.0	640.3	637.0
180°	638.7	638.7	638.7	638.7	638.7



TEST NUMBER: P907690  
 CATALOG NUMBER: DFN2DIP-4P3F0-050D020US840-FLLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.99	13.11	12.71	13.85	14.74	11.54	12.67	12.27	13.41	14.30
	3H	13.66	14.67	14.40	15.43	16.34	13.17	14.18	13.91	14.94	15.85
	4H	14.26	15.21	15.01	15.97	16.91	13.76	14.72	14.52	15.48	16.41
	6H	14.67	15.55	15.44	16.32	17.27	14.17	15.05	14.94	15.82	16.77
	8H	14.78	15.62	15.56	16.41	17.36	14.28	15.12	15.05	15.91	16.85
	12H	14.83	15.63	15.62	16.42	17.39	14.32	15.12	15.11	15.91	16.88
4H	2H	12.47	13.43	13.23	14.19	15.12	12.12	13.07	12.88	13.84	14.77
	3H	14.36	15.15	15.13	15.95	16.90	13.95	14.75	14.72	15.55	16.49
	4H	15.08	15.80	15.87	16.60	17.58	14.66	15.38	15.44	16.18	17.16
	6H	15.61	16.23	16.41	17.06	18.04	15.17	15.80	15.98	16.62	17.61
	8H	15.76	16.35	16.57	17.16	18.16	15.32	15.91	16.13	16.73	17.72
	12H	15.84	16.37	16.67	17.21	18.21	15.39	15.92	16.22	16.76	17.76
8H	4H	15.29	15.88	16.10	16.70	17.69	14.92	15.50	15.72	16.32	17.32
	6H	15.93	16.42	16.77	17.28	18.27	15.55	16.03	16.38	16.89	17.89
	8H	16.15	16.58	17.00	17.44	18.45	15.76	16.19	16.60	17.05	18.06
	12H	16.29	16.67	17.14	17.52	18.59	15.88	16.26	16.73	17.11	18.18
12H	4H	15.29	15.82	16.12	16.66	17.66	14.92	15.45	15.75	16.29	17.29
	6H	15.96	16.39	16.81	17.25	18.26	15.59	16.02	16.43	16.88	17.89
	8H	16.21	16.59	17.06	17.44	18.51	15.83	16.21	16.68	17.06	18.13