

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907706

Luminaire Tested: DFN2DIP-4P3F0-050D060US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907706
REPORT IS A COMBINATION OF REPORTS P899075 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D060US840-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10361.2 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907706
CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P907706

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	57	48	47	46	41				41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	41	39	34				34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29				29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	28	25				25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	27	24	22	19				19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17				17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15				15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2239	2239	2239
5°	2241	2206	2222
10°	2222	2175	2191
15°	2188	2138	2143
20°	2142	2087	2095
25°	2097	2026	2038
30°	2040	1969	1967
35°	1986	1902	1891
40°	1921	1835	1819
45°	1855	1767	1746
50°	1783	1696	1660
55°	1708	1613	1582
60°	1622	1516	1492
65°	1529	1414	1386
70°	1410	1291	1272
75°	1246	1143	1165
80°	1047	953	963
85°	738	632	630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1919 cd/sqm



TEST NUMBER: P907706

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.8
10°-20°	520.3	5.0
20°-30°	764.6	7.4
30°-40°	888.1	8.6
40°-50°	887.0	8.6
50°-60°	773.4	7.5
60°-70°	571.7	5.5
70°-80°	323.5	3.1
80°-90°	90.8	0.9
90°-100°	118.6	1.1
100°-110°	376.8	3.6
110°-120°	644.8	6.2
120°-130°	848.0	8.2
130°-140°	951.8	9.2
140°-150°	933.4	9.0
150°-160°	783.0	7.6
160°-170°	519.2	5.0
170°-180°	181.5	1.8
0°-30°	1469.8	14.2
0°-40°	2357.9	22.8
0°-60°	4018.3	38.8
0°-90°	5004.3	48.3
90°-120°	1140.1	11.0
90°-150°	3873.3	37.4
90°-180°	5357.0	51.7
0°-180°	10361.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	2	21	57	53	55	10
95°	84	100	103	103	100	94
105°	348	352	356	359	359	367
115°	647	656	653	652	647	640
125°	941	956	951	946	944	841
135°	1217	1235	1239	1237	1232	941
145°	1478	1489	1499	1500	1494	923
155°	1690	1694	1700	1708	1702	778
165°	1838	1836	1836	1848	1840	519
175°	1913	1908	1905	1916	1906	182
180°	1916	1916	1916	1916	1916	



TEST NUMBER: P907706

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	1.7	20.8	56.7	53.1	54.8
92.5°	35.9	48.6	50.3	52.0	52.0
95°	84.3	100.5	103.4	103.4	100.5
97.5°	140.4	155.4	161.8	161.8	161.8
100°	205.1	218.3	223.0	223.0	221.3
102.5°	273.3	283.1	289.4	291.1	289.4
105°	347.8	352.4	355.9	358.8	358.8
107.5°	421.7	428.7	428.7	429.8	421.7
110°	493.4	502.6	502.6	502.6	498.0



TEST NUMBER: P907706

CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.8	580.6	578.9	574.2	570.8
115°	647.0	656.3	653.4	651.7	647.0
117.5°	722.8	735.5	727.3	722.8	718.1
120°	799.0	811.7	799.0	799.0	793.8
122.5°	868.3	884.4	876.4	871.8	868.3
125°	941.1	955.5	950.9	945.7	944.0
127.5°	1012.2	1030.1	1023.7	1016.8	1012.2
130°	1078.6	1099.4	1096.5	1093.1	1086.7
132.5°	1153.2	1169.3	1170.4	1162.4	1157.7
135°	1217.3	1235.2	1238.6	1236.9	1232.2
137.5°	1288.9	1303.3	1306.3	1305.0	1298.2
140°	1351.9	1366.3	1374.4	1374.4	1368.1
142.5°	1416.5	1431.0	1435.6	1437.3	1431.0
145°	1477.8	1489.3	1498.6	1500.4	1494.0
147.5°	1532.7	1547.1	1554.1	1556.9	1550.5
150°	1589.3	1599.1	1605.5	1610.6	1605.5
152.5°	1639.5	1649.4	1657.5	1663.9	1657.5
155°	1689.8	1694.5	1699.6	1707.8	1702.5
157.5°	1733.1	1736.7	1739.5	1751.1	1743.0
160°	1771.9	1775.3	1777.1	1786.9	1780.0
162.5°	1807.7	1807.7	1809.4	1820.4	1812.3
165°	1838.3	1836.5	1836.5	1848.2	1840.1
167.5°	1866.0	1860.9	1860.9	1872.4	1864.3
170°	1886.8	1882.2	1880.5	1892.0	1882.2
172.5°	1901.3	1896.6	1894.9	1906.4	1896.6
175°	1912.8	1908.2	1904.7	1916.3	1906.4
177.5°	1919.1	1914.6	1911.1	1920.9	1911.1
180°	1916.3	1916.3	1916.3	1916.3	1916.3



TEST NUMBER: P907706
 CATALOG NUMBER: DFN2DIP-4P3F0-050D060US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.88	10.72	10.85	11.71	13.00	9.43	10.28	10.40	11.27	12.56
	3H	11.53	12.29	12.52	13.29	14.60	11.04	11.80	12.02	12.80	14.11
	4H	12.12	12.84	13.11	13.83	15.16	11.62	12.34	12.62	13.34	14.66
	6H	12.51	13.17	13.52	14.18	15.52	12.01	12.67	13.02	13.68	15.02
	8H	12.61	13.25	13.63	14.26	15.60	12.11	12.74	13.13	13.76	15.10
	12H	12.66	13.26	13.68	14.27	15.63	12.15	12.75	13.17	13.76	15.12
4H	2H	10.33	11.05	11.33	12.05	13.38	9.98	10.70	10.98	11.69	13.02
	3H	12.19	12.79	13.20	13.82	15.16	11.78	12.38	12.80	13.41	14.75
	4H	12.90	13.45	13.92	14.47	15.83	12.48	13.03	13.50	14.05	15.41
	6H	13.41	13.88	14.44	14.93	16.29	12.98	13.45	14.01	14.50	15.85
	8H	13.56	14.00	14.59	15.04	16.41	13.12	13.56	14.15	14.60	15.97
	12H	13.63	14.03	14.68	15.08	16.46	13.18	13.58	14.23	14.63	16.01
8H	4H	13.09	13.53	14.12	14.57	15.94	12.72	13.16	13.75	14.19	15.57
	6H	13.72	14.08	14.77	15.16	16.53	13.33	13.70	14.39	14.78	16.15
	8H	13.94	14.26	15.00	15.32	16.71	13.54	13.86	14.61	14.93	16.32
	12H	14.06	14.35	15.13	15.40	16.84	13.65	13.94	14.72	14.99	16.42
12H	4H	13.08	13.48	14.13	14.53	15.91	12.71	13.11	13.76	14.16	15.54
	6H	13.75	14.07	14.81	15.13	16.52	13.37	13.70	14.44	14.76	16.15
	8H	13.98	14.27	15.05	15.32	16.76	13.60	13.89	14.67	14.94	16.38