

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332686-840

Luminaire Tested: **SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332686-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7232.7 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332686-840
CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	47	40	35	42	37	33	38	34	30	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	41	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	2.6
10°-20°	534.0	7.4
20°-30°	786.0	10.9
30°-40°	913.7	12.6
40°-50°	913.7	12.6
50°-60°	799.3	11.1
60°-70°	593.6	8.2
70°-80°	337.2	4.7
80°-90°	99.5	1.4
90°-100°	49.1	0.7
100°-110°	145.5	2.0
110°-120°	247.0	3.4
120°-130°	325.7	4.5
130°-140°	365.7	5.1
140°-150°	359.4	5.0
150°-160°	302.3	4.2
160°-170°	201.1	2.8
170°-180°	70.4	1.0
0°-30°	1509.5	20.9
0°-40°	2423.2	33.5
0°-60°	4136.2	57.2
0°-90°	5166.5	71.4
90°-120°	441.6	6.1
90°-150°	1492.4	20.6
90°-180°	2066.0	28.6
0°-180°	7232.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	2	8	13	16	17	7
95°	34	40	44	45	46	38
105°	134	135	137	139	141	142
115°	251	251	250	249	249	248
125°	366	366	365	364	363	326
135°	472	475	475	474	472	365
145°	573	575	576	575	574	358
155°	657	657	656	658	656	302
165°	715	713	712	715	713	201
175°	744	741	740	744	740	71
180°	745	745	745	745	745	



TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	33.9	33.9	33.8	33.8	33.8	33.8	33.7	33.6	33.5	33.5	33.6
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	12.3	13.9	15.6	17.2	18.8	19.9	20.7	21.4	22.1	22.8	23.2
95°	34.5	35.7	36.9	38.0	39.2	40.2	41.1	42.0	42.9	43.7	44.1
97.5°	60.4	61.3	62.2	63.1	64.0	65.0	66.0	67.2	68.2	69.3	69.7
100°	80.6	81.2	81.7	82.2	82.7	83.5	84.6	85.8	86.9	88.2	88.4
102.5°	101.8	102.0	102.2	102.4	102.6	103.3	104.3	105.3	106.4	107.4	107.9
105°	134.2	134.3	134.4	134.6	134.7	135.0	135.5	136.0	136.5	137.0	137.4
107.5°	168.1	168.3	168.4	168.6	168.8	169.0	169.0	169.1	169.2	169.3	169.6
110°	191.3	191.5	191.8	192.0	192.3	192.3	192.2	192.1	192.0	191.8	191.6



TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.2	215.2	215.3	215.3	215.4	215.3	215.1	214.8	214.6	214.4	214.3
115°	251.2	251.2	251.2	251.2	251.2	251.0	250.7	250.4	250.2	249.9	249.8
117.5°	285.0	285.1	285.2	285.3	285.4	285.4	285.2	285.0	284.8	284.7	284.2
120°	307.6	308.1	308.6	309.1	309.6	309.7	309.3	308.9	308.5	308.1	307.5
122.5°	331.0	331.2	331.4	331.6	331.8	331.9	331.7	331.5	331.3	331.2	330.7
125°	365.8	365.8	365.8	365.8	365.8	365.7	365.6	365.5	365.3	365.2	364.9
127.5°	397.2	397.6	398.0	398.4	398.7	398.8	398.6	398.4	398.2	398.0	397.8
130°	419.3	419.7	420.1	420.5	420.8	421.0	421.0	421.0	421.0	421.0	420.8
132.5°	441.9	442.2	442.4	442.7	443.0	443.1	443.0	442.9	442.8	442.7	442.4
135°	471.7	472.5	473.2	474.0	474.8	475.1	475.1	475.1	475.1	475.1	474.9
137.5°	504.2	504.5	504.9	505.2	505.6	505.9	506.1	506.3	506.5	506.8	506.4
140°	525.8	526.1	526.3	526.6	526.8	527.0	527.0	527.0	527.0	527.0	526.8
142.5°	545.6	545.9	546.2	546.4	546.7	546.7	546.6	546.5	546.4	546.3	546.3
145°	573.1	573.6	574.1	574.6	575.1	575.4	575.6	575.7	575.8	575.9	575.8
147.5°	600.3	600.9	601.5	602.1	602.8	603.0	602.9	602.8	602.7	602.6	602.5
150°	616.8	617.4	617.9	618.4	618.9	619.1	619.1	619.1	619.1	619.1	619.1
152.5°	632.6	632.9	633.2	633.5	633.8	634.0	634.1	634.2	634.3	634.4	634.7
155°	656.6	656.6	656.6	656.6	656.6	656.5	656.4	656.3	656.2	656.0	656.5
157.5°	676.9	676.6	676.4	676.2	676.0	675.8	675.8	675.8	675.8	675.7	676.1
160°	688.8	688.7	688.6	688.5	688.3	688.2	688.1	688.0	687.8	687.7	688.1
162.5°	699.9	699.6	699.2	698.9	698.6	698.3	698.2	698.1	698.0	697.8	698.5
165°	714.8	714.4	714.0	713.7	713.3	713.0	712.7	712.5	712.2	712.0	712.7
167.5°	726.2	725.7	725.1	724.6	724.1	723.8	723.8	723.9	723.9	723.9	724.7
170°	732.7	732.1	731.3	730.7	730.0	729.8	729.9	730.0	730.2	730.3	731.1
172.5°	737.2	736.7	736.2	735.7	735.1	734.9	734.9	734.9	734.9	735.0	735.8
175°	743.6	743.0	742.4	741.6	741.0	740.6	740.5	740.4	740.2	740.1	741.0
177.5°	745.7	745.2	744.7	744.2	743.6	743.4	743.4	743.4	743.4	743.4	744.1
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8



TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	33.8	33.9	34.1	34.2	34.2	34.3	34.3	34.4
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	23.7	24.2	24.6	24.9	25.1	25.2	25.4	25.5
95°	44.5	44.9	45.3	45.5	45.5	45.5	45.5	45.5
97.5°	70.2	70.6	71.1	71.3	71.3	71.3	71.3	71.3
100°	88.7	88.9	89.2	89.3	89.3	89.3	89.3	89.3
102.5°	108.2	108.6	108.9	109.2	109.3	109.4	109.5	109.6
105°	137.8	138.3	138.7	139.0	139.4	139.8	140.2	140.6
107.5°	170.0	170.3	170.7	170.9	170.8	170.8	170.8	170.8
110°	191.3	191.1	190.8	190.9	191.3	191.6	192.0	192.4



TEST NUMBER: P332686-840

CATALOG NUMBER: SA4XXDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.3	214.2	214.2	214.2	214.3	214.3	214.4	214.5
115°	249.7	249.6	249.4	249.3	249.2	249.0	248.9	248.8
117.5°	283.8	283.4	282.9	282.6	282.3	282.1	281.8	281.6
120°	306.9	306.2	305.6	305.4	305.7	305.9	306.2	306.4
122.5°	330.3	329.9	329.4	329.0	328.5	328.1	327.6	327.2
125°	364.7	364.4	364.2	363.9	363.7	363.3	363.1	362.8
127.5°	397.5	397.3	397.0	396.8	396.6	396.4	396.2	396.0
130°	420.5	420.3	420.0	419.6	419.1	418.6	418.1	417.6
132.5°	442.2	441.9	441.7	441.4	441.2	441.0	440.8	440.6
135°	474.6	474.4	474.1	473.8	473.4	473.0	472.7	472.3
137.5°	506.0	505.7	505.4	505.2	505.3	505.4	505.5	505.6
140°	526.7	526.6	526.5	526.3	526.2	526.1	526.0	525.8
142.5°	546.3	546.3	546.2	546.2	546.2	546.2	546.1	546.1
145°	575.7	575.6	575.4	575.2	574.8	574.4	574.0	573.7
147.5°	602.4	602.3	602.2	602.1	602.0	601.8	601.7	601.6
150°	619.1	619.1	619.1	619.1	618.9	618.8	618.7	618.6
152.5°	635.0	635.3	635.6	635.6	635.3	634.9	634.6	634.3
155°	657.0	657.5	658.1	658.1	657.5	657.0	656.5	656.0
157.5°	676.5	676.9	677.3	677.2	676.8	676.4	675.9	675.5
160°	688.5	688.8	689.2	689.1	688.5	687.8	687.2	686.6
162.5°	699.2	699.9	700.6	700.6	700.0	699.3	698.7	698.1
165°	713.5	714.2	715.0	715.1	714.6	714.1	713.6	713.1
167.5°	725.4	726.2	727.0	726.9	726.2	725.4	724.6	723.8
170°	731.8	732.7	733.4	733.4	732.5	731.5	730.6	729.7
172.5°	736.7	737.6	738.4	738.4	737.5	736.6	735.7	734.9
175°	741.9	742.9	743.7	743.7	742.9	741.9	741.0	740.1
177.5°	744.8	745.5	746.2	746.2	745.4	744.6	743.7	742.9
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8

(END OF REPORT)