

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907727

Luminaire Tested: DFN2DIP-4P3F0-060D060US840-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P907727  
REPORT IS A COMBINATION OF REPORTS P900597 AND P897473  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-060D060US840-FLLONL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11997.2 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 109.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLLONL

### Luminous Intensity Polar Plot



TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    |    | 20 |    |    |    |    | 20 |    |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    |    | 50 |    |    |    |    | 30 |    |    |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 107 | 107 | 107 | 107 | 99 | 99 | 99 | 99 | 83 | 83 | 83 | 69 | 69 | 69 | 56 | 56 | 56 | 56 | 56 | 50 |
| 1   | 98  | 93  | 90  | 86  | 90 | 86 | 83 | 80 | 73 | 71 | 68 | 61 | 59 | 58 | 50 | 48 | 47 | 47 | 47 | 42 |
| 2   | 89  | 82  | 75  | 70  | 82 | 76 | 70 | 66 | 64 | 60 | 57 | 53 | 51 | 48 | 44 | 42 | 40 | 40 | 40 | 35 |
| 3   | 81  | 72  | 64  | 59  | 75 | 66 | 60 | 55 | 56 | 52 | 48 | 47 | 44 | 41 | 39 | 36 | 34 | 34 | 34 | 30 |
| 4   | 74  | 64  | 56  | 50  | 68 | 59 | 52 | 47 | 50 | 45 | 41 | 42 | 38 | 35 | 35 | 32 | 29 | 29 | 29 | 26 |
| 5   | 68  | 57  | 48  | 42  | 63 | 53 | 45 | 40 | 45 | 39 | 35 | 38 | 34 | 30 | 31 | 28 | 26 | 26 | 26 | 22 |
| 6   | 63  | 51  | 43  | 37  | 58 | 47 | 40 | 35 | 40 | 35 | 31 | 34 | 30 | 27 | 28 | 25 | 23 | 23 | 23 | 20 |
| 7   | 58  | 46  | 38  | 32  | 53 | 43 | 36 | 30 | 37 | 31 | 27 | 31 | 27 | 23 | 26 | 23 | 20 | 20 | 20 | 17 |
| 8   | 54  | 42  | 34  | 29  | 50 | 39 | 32 | 27 | 33 | 28 | 24 | 28 | 24 | 21 | 24 | 20 | 18 | 18 | 18 | 16 |
| 9   | 50  | 38  | 30  | 25  | 46 | 35 | 29 | 24 | 31 | 25 | 21 | 26 | 22 | 19 | 22 | 19 | 16 | 16 | 16 | 14 |
| 10  | 47  | 35  | 28  | 23  | 43 | 33 | 26 | 22 | 28 | 23 | 19 | 24 | 20 | 17 | 20 | 17 | 15 | 15 | 15 | 13 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2687 | 2687 | 2687 |
| 5°  | 2689 | 2648 | 2666 |
| 10° | 2666 | 2610 | 2629 |
| 15° | 2625 | 2565 | 2572 |
| 20° | 2570 | 2504 | 2514 |
| 25° | 2516 | 2431 | 2446 |
| 30° | 2448 | 2363 | 2360 |
| 35° | 2384 | 2282 | 2269 |
| 40° | 2305 | 2201 | 2183 |
| 45° | 2226 | 2120 | 2095 |
| 50° | 2140 | 2035 | 1993 |
| 55° | 2049 | 1936 | 1898 |
| 60° | 1947 | 1819 | 1790 |
| 65° | 1835 | 1697 | 1663 |
| 70° | 1692 | 1549 | 1526 |
| 75° | 1495 | 1371 | 1398 |
| 80° | 1257 | 1144 | 1155 |
| 85° | 884  | 758  | 757  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2226 cd/sqm

TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLLONL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 221.9   | 1.8       |
| 10°-20°   | 624.4   | 5.2       |
| 20°-30°   | 917.5   | 7.6       |
| 30°-40°   | 1065.7  | 8.9       |
| 40°-50°   | 1064.4  | 8.9       |
| 50°-60°   | 928.1   | 7.7       |
| 60°-70°   | 686.1   | 5.7       |
| 70°-80°   | 388.2   | 3.2       |
| 80°-90°   | 106.0   | 0.9       |
| 90°-100°  | 67.4    | 0.6       |
| 100°-110° | 251.4   | 2.1       |
| 110°-120° | 666.7   | 5.6       |
| 120°-130° | 1105.7  | 9.2       |
| 130°-140° | 1174.5  | 9.8       |
| 140°-150° | 1091.6  | 9.1       |
| 150°-160° | 877.6   | 7.3       |
| 160°-170° | 565.5   | 4.7       |
| 170°-180° | 194.6   | 1.6       |
| 0°-30°    | 1763.8  | 14.7      |
| 0°-40°    | 2829.5  | 23.6      |
| 0°-60°    | 4821.9  | 40.2      |
| 0°-90°    | 6002.2  | 50.0      |
| 90°-120°  | 985.5   | 8.2       |
| 90°-150°  | 4357.2  | 36.3      |
| 90°-180°  | 5995.0  | 50.0      |
| 0°-180°   | 11997.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 2358 | 2358  | 2358 | 2358  | 2358 |      |
| 5°   | 2358 | 2349  | 2324 | 2342  | 2337 | 224  |
| 15°  | 2244 | 2231  | 2201 | 2210  | 2199 | 632  |
| 25°  | 2031 | 2013  | 1975 | 1979  | 1975 | 935  |
| 35°  | 1752 | 1730  | 1694 | 1680  | 1668 | 1094 |
| 45°  | 1426 | 1410  | 1376 | 1351  | 1342 | 1101 |
| 55°  | 1079 | 1066  | 1038 | 1011  | 1000 | 965  |
| 65°  | 728  | 714   | 692  | 671   | 660  | 720  |
| 75°  | 381  | 376   | 365  | 351   | 356  | 406  |
| 85°  | 93   | 91    | 88   | 82    | 79   | 104  |
| 90°  | 1    | 18    | 30   | 37    | 40   | 11   |
| 95°  | 96   | 47    | 58   | 65    | 64   | 114  |
| 105° | 450  | 494   | 90   | 106   | 112  | 481  |
| 115° | 851  | 876   | 913  | 228   | 121  | 838  |
| 125° | 1203 | 1222  | 1250 | 1261  | 1265 | 1073 |
| 135° | 1489 | 1512  | 1526 | 1540  | 1537 | 1150 |
| 145° | 1727 | 1725  | 1750 | 1761  | 1753 | 1080 |
| 155° | 1901 | 1888  | 1906 | 1915  | 1903 | 876  |
| 165° | 2004 | 1995  | 1999 | 2009  | 1999 | 566  |
| 175° | 2049 | 2039  | 2042 | 2052  | 2038 | 195  |
| 180° | 2045 | 2045  | 2045 | 2045  | 2045 |      |

TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLLONL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 2357.6 | 2357.6 | 2357.6 | 2357.6 | 2357.6 |
| 2.5°   | 2371.4 | 2360.1 | 2335.0 | 2357.6 | 2353.3 |
| 5°     | 2357.6 | 2348.7 | 2323.7 | 2341.8 | 2337.4 |
| 7.5°   | 2341.8 | 2328.3 | 2303.3 | 2321.6 | 2317.0 |
| 10°    | 2317.0 | 2301.2 | 2273.9 | 2292.0 | 2285.2 |
| 12.5°  | 2282.9 | 2269.4 | 2242.2 | 2253.5 | 2249.0 |
| 15°    | 2244.3 | 2230.9 | 2201.3 | 2210.5 | 2199.2 |
| 17.5°  | 2196.8 | 2183.3 | 2153.7 | 2164.9 | 2153.7 |
| 20°    | 2144.6 | 2131.1 | 2099.3 | 2106.1 | 2097.2 |
| 22.5°  | 2092.6 | 2072.1 | 2042.6 | 2042.6 | 2038.0 |
| 25°    | 2031.2 | 2013.3 | 1974.7 | 1979.0 | 1974.7 |
| 27.5°  | 1963.2 | 1947.3 | 1917.9 | 1911.3 | 1900.0 |
| 30°    | 1895.4 | 1877.0 | 1843.2 | 1836.4 | 1827.3 |
| 32.5°  | 1822.7 | 1809.3 | 1772.9 | 1759.2 | 1750.1 |
| 35°    | 1752.5 | 1729.9 | 1693.5 | 1679.8 | 1668.5 |
| 37.5°  | 1673.1 | 1652.6 | 1616.4 | 1600.4 | 1589.1 |
| 40°    | 1591.5 | 1573.3 | 1537.0 | 1516.8 | 1507.6 |
| 42.5°  | 1512.2 | 1493.9 | 1457.8 | 1435.0 | 1421.5 |
| 45°    | 1426.1 | 1410.2 | 1376.0 | 1351.3 | 1342.1 |
| 47.5°  | 1342.1 | 1326.3 | 1290.0 | 1265.0 | 1251.4 |
| 50°    | 1253.6 | 1242.3 | 1210.6 | 1178.8 | 1167.5 |
| 52.5°  | 1167.5 | 1151.7 | 1122.3 | 1097.3 | 1081.5 |
| 55°    | 1079.2 | 1065.5 | 1038.3 | 1011.2 | 999.9  |
| 57.5°  | 990.8  | 979.5  | 949.9  | 922.7  | 913.5  |
| 60°    | 902.2  | 893.3  | 861.6  | 836.6  | 829.8  |
| 62.5°  | 816.1  | 800.2  | 777.6  | 755.0  | 745.9  |
| 65°    | 727.8  | 714.2  | 691.6  | 671.1  | 659.7  |
| 67.5°  | 637.1  | 625.6  | 605.4  | 589.6  | 580.4  |
| 70°    | 553.2  | 544.1  | 523.6  | 507.8  | 498.9  |
| 72.5°  | 467.1  | 458.0  | 446.7  | 430.8  | 424.0  |
| 75°    | 380.7  | 376.5  | 364.9  | 351.4  | 356.0  |
| 77.5°  | 303.8  | 294.7  | 290.0  | 283.4  | 276.6  |
| 80°    | 226.8  | 224.4  | 219.8  | 213.1  | 208.5  |
| 82.5°  | 154.2  | 154.2  | 152.0  | 142.9  | 142.9  |
| 85°    | 92.8   | 90.7   | 88.5   | 81.5   | 79.4   |
| 87.5°  | 40.9   | 36.4   | 31.7   | 25.0   | 22.6   |
| 90°    | 1.4    | 17.8   | 29.5   | 37.1   | 39.9   |
| 92.5°  | 37.1   | 31.1   | 35.4   | 38.5   | 39.9   |
| 95°    | 96.1   | 47.3   | 57.7   | 65.2   | 63.6   |
| 97.5°  | 173.1  | 51.8   | 75.3   | 80.0   | 81.4   |
| 100°   | 262.0  | 59.2   | 84.3   | 96.1   | 99.1   |
| 102.5° | 359.5  | 356.7  | 87.4   | 103.5  | 108.1  |
| 105°   | 449.8  | 494.2  | 90.3   | 106.4  | 112.5  |
| 107.5° | 554.9  | 591.8  | 93.3   | 109.5  | 115.4  |
| 110°   | 655.6  | 686.5  | 259.0  | 111.1  | 116.8  |



TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLLONL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 750.2  | 776.8  | 751.6  | 113.8  | 118.5  |
| 115°   | 850.8  | 876.0  | 913.0  | 227.9  | 121.4  |
| 117.5° | 938.1  | 967.7  | 992.9  | 781.2  | 393.5  |
| 120°   | 1035.8 | 1057.9 | 1084.7 | 1102.4 | 902.6  |
| 122.5° | 1118.5 | 1142.3 | 1171.9 | 1180.7 | 1182.4 |
| 125°   | 1203.0 | 1222.2 | 1250.3 | 1260.7 | 1265.1 |
| 127.5° | 1279.9 | 1300.6 | 1322.9 | 1337.7 | 1339.1 |
| 130°   | 1352.4 | 1376.1 | 1392.3 | 1408.7 | 1407.2 |
| 132.5° | 1426.4 | 1445.7 | 1461.9 | 1475.2 | 1473.8 |
| 135°   | 1488.6 | 1512.4 | 1525.5 | 1540.4 | 1537.4 |
| 137.5° | 1553.6 | 1571.4 | 1586.3 | 1601.0 | 1596.7 |
| 140°   | 1617.2 | 1629.2 | 1645.4 | 1658.7 | 1651.3 |
| 142.5° | 1670.6 | 1681.0 | 1700.2 | 1711.9 | 1704.6 |
| 145°   | 1726.9 | 1725.3 | 1750.4 | 1760.8 | 1753.4 |
| 147.5° | 1775.5 | 1771.1 | 1796.2 | 1803.6 | 1797.9 |
| 150°   | 1823.0 | 1812.6 | 1836.3 | 1845.1 | 1837.8 |
| 152.5° | 1862.9 | 1851.1 | 1873.2 | 1882.2 | 1871.8 |
| 155°   | 1901.4 | 1888.1 | 1905.9 | 1914.7 | 1902.9 |
| 157.5° | 1932.5 | 1920.7 | 1934.0 | 1944.4 | 1932.5 |
| 160°   | 1959.1 | 1950.2 | 1959.1 | 1967.9 | 1957.6 |
| 162.5° | 1982.7 | 1973.9 | 1981.3 | 1991.7 | 1978.3 |
| 165°   | 2003.5 | 1994.7 | 1999.0 | 2009.4 | 1999.0 |
| 167.5° | 2019.7 | 2010.8 | 2015.4 | 2025.8 | 2012.4 |
| 170°   | 2033.2 | 2024.2 | 2027.2 | 2037.5 | 2024.2 |
| 172.5° | 2041.9 | 2033.2 | 2036.1 | 2046.5 | 2033.2 |
| 175°   | 2049.3 | 2038.9 | 2041.9 | 2052.2 | 2037.5 |
| 177.5° | 2052.2 | 2041.9 | 2043.5 | 2053.9 | 2040.5 |
| 180°   | 2044.9 | 2044.9 | 2044.9 | 2044.9 | 2044.9 |

TEST NUMBER: P907727

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US840-FLONL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 10.68            | 11.54 | 11.63 | 12.51 | 13.78 | 10.23          | 11.09 | 11.19 | 12.06 | 13.34 |
|                 | 3H   | 12.33            | 13.10 | 13.30 | 14.09 | 15.38 | 11.84          | 12.61 | 12.81 | 13.60 | 14.89 |
|                 | 4H   | 12.92            | 13.65 | 13.90 | 14.63 | 15.93 | 12.42          | 13.15 | 13.40 | 14.14 | 15.44 |
|                 | 6H   | 13.31            | 13.99 | 14.31 | 14.98 | 16.29 | 12.81          | 13.49 | 13.81 | 14.48 | 15.79 |
|                 | 8H   | 13.42            | 14.06 | 14.41 | 15.06 | 16.38 | 12.91          | 13.56 | 13.91 | 14.56 | 15.87 |
|                 | 12H  | 13.46            | 14.07 | 14.47 | 15.07 | 16.41 | 12.95          | 13.56 | 13.96 | 14.56 | 15.90 |
| 4H              | 2H   | 11.13            | 11.86 | 12.12 | 12.85 | 14.15 | 10.78          | 11.51 | 11.77 | 12.49 | 13.80 |
|                 | 3H   | 12.99            | 13.60 | 13.99 | 14.62 | 15.93 | 12.59          | 13.20 | 13.58 | 14.21 | 15.53 |
|                 | 4H   | 13.70            | 14.26 | 14.71 | 15.27 | 16.61 | 13.28          | 13.84 | 14.29 | 14.85 | 16.18 |
|                 | 6H   | 14.21            | 14.70 | 15.23 | 15.73 | 17.06 | 13.78          | 14.26 | 14.80 | 15.29 | 16.63 |
|                 | 8H   | 14.36            | 14.81 | 15.38 | 15.84 | 17.19 | 13.93          | 14.37 | 14.94 | 15.40 | 16.75 |
|                 | 12H  | 14.43            | 14.84 | 15.47 | 15.88 | 17.23 | 13.98          | 14.39 | 15.02 | 15.43 | 16.79 |
| 8H              | 4H   | 13.90            | 14.35 | 14.91 | 15.37 | 16.72 | 13.52          | 13.97 | 14.54 | 14.99 | 16.34 |
|                 | 6H   | 14.52            | 14.89 | 15.56 | 15.96 | 17.31 | 14.14          | 14.51 | 15.18 | 15.57 | 16.92 |
|                 | 8H   | 14.74            | 15.07 | 15.79 | 16.12 | 17.48 | 14.35          | 14.67 | 15.40 | 15.72 | 17.09 |
|                 | 12H  | 14.87            | 15.16 | 15.92 | 16.20 | 17.61 | 14.46          | 14.74 | 15.51 | 15.79 | 17.20 |
| 12H             | 4H   | 13.88            | 14.29 | 14.92 | 15.33 | 16.68 | 13.51          | 13.92 | 14.55 | 14.96 | 16.31 |
|                 | 6H   | 14.55            | 14.88 | 15.60 | 15.93 | 17.30 | 14.18          | 14.50 | 15.23 | 15.56 | 16.92 |
|                 | 8H   | 14.79            | 15.08 | 15.84 | 16.12 | 17.53 | 14.41          | 14.70 | 15.46 | 15.74 | 17.15 |

END OF REPORT