

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332696-840

Luminaire Tested: **SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332696-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8089.7 lumens  
Efficiency: N/A  
Efficacy: 133.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332696-840  
CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	95	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	54	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	42	38
4	77	66	57	51	72	62	55	49	55	49	44	48	44	40	42	39	36	33
5	70	59	50	44	66	55	48	42	49	43	38	44	39	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16247	16247	16247
5°	16295	16100	16216
10°	16193	15969	16047
15°	15998	15742	15782
20°	15738	15460	15474
25°	15441	15139	15097
30°	15077	14762	14626
35°	14701	14366	14177
40°	14309	13918	13663
45°	13900	13476	13218
50°	13448	13083	12679
55°	12960	12573	12165
60°	12471	12003	11638
65°	11922	11459	10997
70°	11306	10733	10315
75°	10359	9860	9607
80°	9219	8847	8619
85°	8068	7762	7614



TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	2.3
10°-20°	534.0	6.6
20°-30°	786.0	9.7
30°-40°	913.7	11.3
40°-50°	913.7	11.3
50°-60°	799.3	9.9
60°-70°	593.6	7.3
70°-80°	337.2	4.2
80°-90°	99.5	1.2
90°-100°	290.3	3.6
100°-110°	604.2	7.5
110°-120°	541.2	6.7
120°-130°	455.2	5.6
130°-140°	379.6	4.7
140°-150°	290.0	3.6
150°-160°	203.8	2.5
160°-170°	119.9	1.5
170°-180°	39.0	0.5
0°-30°	1509.5	18.7
0°-40°	2423.2	30.0
0°-60°	4136.2	51.1
0°-90°	5166.5	63.9
90°-120°	1435.7	17.7
90°-150°	2560.4	31.7
90°-180°	2923.0	36.1
0°-180°	8089.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2012	2012	2012	2012	2012	
5°	2011	2004	1987	2003	2001	191
15°	1914	1907	1884	1892	1888	539
25°	1734	1722	1700	1701	1695	797
35°	1492	1480	1458	1447	1438	932
45°	1218	1205	1180	1163	1158	938
55°	921	915	893	875	864	824
65°	624	616	600	584	576	618
75°	332	324	316	310	308	353
85°	87	87	84	84	82	96
90°	1	6	14	16	17	6
95°	26	82	644	319	193	29
105°	92	134	518	1115	1111	99
115°	163	204	462	888	1067	161
125°	227	269	460	755	851	202
135°	269	321	456	670	761	208
145°	310	355	453	565	622	195
155°	353	381	441	499	520	163
165°	385	396	422	447	454	109
175°	401	402	405	411	409	38
180°	402	402	402	402	402	



TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2017.6	2016.8	2015.9	2015.1	2014.2	2012.2	2009.0	2005.9	2002.8	1999.6	2002.5
5°	2010.8	2009.4	2008.0	2006.6	2005.2	2002.5	1998.5	1994.6	1990.6	1986.7	1990.6
7.5°	1992.2	1990.7	1989.3	1987.8	1986.4	1983.6	1979.1	1974.8	1970.4	1966.0	1969.2
10°	1975.4	1974.0	1972.6	1971.1	1969.6	1966.6	1962.0	1957.3	1952.7	1948.0	1950.9
12.5°	1953.5	1952.1	1950.6	1949.1	1947.7	1944.5	1939.6	1934.7	1929.8	1924.8	1927.9
15°	1914.1	1912.7	1911.3	1909.9	1908.3	1905.0	1899.6	1894.2	1888.9	1883.5	1885.6
17.5°	1866.7	1864.9	1863.1	1861.4	1859.6	1856.1	1851.0	1845.9	1840.9	1835.7	1837.1
20°	1831.9	1830.1	1828.3	1826.5	1824.7	1821.1	1815.7	1810.4	1805.0	1799.6	1800.7
22.5°	1794.4	1792.1	1789.8	1787.4	1785.0	1781.1	1775.7	1770.4	1765.0	1759.6	1761.6
25°	1733.5	1731.0	1728.5	1726.0	1723.4	1719.7	1714.6	1709.7	1704.7	1699.6	1700.0
27.5°	1663.9	1661.2	1658.7	1656.1	1653.6	1649.9	1645.3	1640.6	1636.0	1631.2	1630.4
30°	1617.4	1614.6	1611.6	1608.8	1606.0	1602.2	1597.5	1592.9	1588.2	1583.6	1582.2
32.5°	1568.4	1565.8	1563.3	1560.6	1558.0	1554.3	1549.3	1544.4	1539.4	1534.5	1532.8
35°	1491.7	1489.1	1486.6	1484.1	1481.6	1477.8	1472.8	1467.8	1462.8	1457.7	1455.2
37.5°	1410.7	1408.4	1406.1	1403.8	1401.5	1397.7	1392.3	1386.9	1381.5	1376.1	1373.4
40°	1357.8	1354.9	1352.0	1349.2	1346.4	1342.2	1336.9	1331.4	1326.1	1320.7	1317.1
42.5°	1301.0	1299.3	1297.6	1295.9	1294.1	1290.3	1284.3	1278.4	1272.4	1266.5	1262.3
45°	1217.5	1215.0	1212.4	1209.9	1207.5	1203.4	1197.6	1191.8	1186.1	1180.4	1176.5
47.5°	1130.0	1128.3	1126.6	1124.9	1123.2	1119.7	1114.4	1109.1	1103.8	1098.5	1094.1
50°	1070.8	1069.3	1067.8	1066.4	1065.0	1061.8	1056.7	1051.8	1046.7	1041.7	1036.7
52.5°	1012.7	1011.0	1009.3	1007.5	1005.8	1002.3	997.0	991.7	986.4	981.1	976.6
55°	920.8	919.7	918.7	917.6	916.5	913.4	908.4	903.4	898.4	893.3	889.1
57.5°	833.0	831.8	830.6	829.4	828.2	825.1	820.1	815.2	810.2	805.3	801.2
60°	772.4	770.6	768.8	767.1	765.3	762.0	757.4	752.8	748.0	743.4	740.1
62.5°	713.1	711.6	710.0	708.5	707.1	703.9	698.9	694.0	689.0	684.1	681.2
65°	624.1	622.3	620.5	618.6	616.9	614.2	610.7	607.0	603.5	599.9	596.3
67.5°	534.4	532.8	531.1	529.5	527.9	525.2	521.8	518.4	514.9	511.5	508.1
70°	479.0	476.5	473.9	471.4	468.9	466.3	463.3	460.5	457.6	454.7	451.9
72.5°	419.6	417.1	414.5	412.0	409.6	407.2	404.9	402.5	400.3	398.0	395.7
75°	332.1	330.4	328.6	326.8	325.0	323.3	321.4	319.6	317.9	316.1	314.7
77.5°	248.6	247.8	247.1	246.3	245.5	244.3	242.8	241.2	239.6	238.0	237.6
80°	198.3	197.2	196.2	195.1	194.1	193.2	192.5	191.7	191.0	190.3	189.6
82.5°	149.4	148.9	148.3	147.8	147.3	147.0	146.8	146.7	146.5	146.4	146.0
85°	87.1	87.1	87.1	87.1	87.1	86.7	86.0	85.3	84.5	83.8	83.8
87.5°	33.7	33.7	33.9	33.8	33.6	33.3	34.0	33.7	33.7	33.8	33.6
90°	0.8	2.3	4.7	5.6	6.4	6.4	11.0	11.0	12.6	14.2	13.4
92.5°	9.0	13.1	20.5	30.2	41.7	58.1	98.3	159.5	219.2	250.4	208.6
95°	26.1	28.4	36.4	46.6	65.5	98.7	167.4	296.9	485.6	643.6	661.8
97.5°	46.8	46.8	53.5	63.0	79.3	107.0	160.0	266.9	454.5	677.8	831.3
100°	60.0	60.0	65.5	75.0	90.0	115.3	161.9	251.2	412.2	634.9	837.0
102.5°	72.6	73.9	78.8	87.7	102.0	126.0	168.1	246.7	383.7	581.2	789.6
105°	92.4	94.7	98.7	108.2	122.4	145.3	183.2	248.7	359.3	518.0	703.6
107.5°	114.2	115.7	119.7	129.8	143.4	166.0	200.8	260.4	354.9	482.6	634.1
110°	128.8	130.3	134.2	143.7	157.9	179.3	214.0	269.2	356.1	470.6	599.4



TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.6	144.2	148.8	157.6	171.8	193.2	226.6	278.7	359.9	464.9	579.8
115°	162.7	165.0	170.6	178.4	193.5	214.8	246.4	293.8	367.2	461.9	561.4
117.5°	183.5	185.7	190.7	199.3	213.4	235.5	265.5	309.0	375.0	461.1	553.2
120°	197.4	198.9	204.5	213.2	226.6	248.7	278.7	319.8	380.6	461.1	548.8
122.5°	210.1	211.7	217.1	225.2	239.8	261.4	291.3	329.9	386.3	460.5	543.7
125°	226.6	229.7	234.5	243.2	258.2	280.3	308.7	345.1	394.9	459.6	535.3
127.5°	241.4	243.9	249.5	259.4	275.1	297.4	324.9	358.2	401.6	457.9	524.1
130°	249.5	252.7	259.0	270.8	285.9	308.7	335.6	366.4	406.7	457.2	517.3
132.5°	257.7	260.2	268.5	279.7	296.0	317.6	344.5	374.6	411.1	456.6	510.9
135°	269.2	272.5	280.3	293.8	310.3	330.8	356.9	385.4	417.7	455.7	501.4
137.5°	280.8	283.8	292.5	305.3	322.4	342.0	366.4	392.9	421.6	455.4	493.2
140°	289.0	291.3	300.0	313.5	330.0	349.0	372.7	398.0	424.9	454.8	488.8
142.5°	297.8	300.2	308.3	321.0	337.0	355.4	378.4	401.7	427.4	454.8	485.0
145°	310.3	312.7	320.6	331.6	346.7	364.1	384.6	405.9	428.8	453.2	478.5
147.5°	324.4	325.2	332.1	343.5	356.0	371.6	390.9	409.5	429.6	450.4	472.7
150°	333.3	334.1	340.3	349.8	361.6	376.7	394.0	411.4	429.6	448.5	468.3
152.5°	341.4	341.6	347.9	356.8	367.4	381.1	396.6	412.6	428.3	445.4	463.2
155°	352.9	353.8	358.5	366.4	375.1	386.9	400.3	413.7	426.4	440.6	455.7
157.5°	364.2	364.2	368.6	374.8	382.3	391.6	403.0	413.7	424.3	435.8	447.9
160°	371.1	371.1	374.3	379.8	386.2	394.9	404.2	413.7	422.4	431.9	442.2
162.5°	377.5	376.8	379.3	384.3	389.9	396.7	405.6	413.7	420.6	428.2	437.2
165°	384.6	384.6	386.2	390.1	394.0	398.8	405.9	412.2	417.0	422.4	428.8
167.5°	391.6	390.9	391.6	394.7	396.9	400.5	405.8	410.3	413.1	416.8	421.2
170°	394.9	394.0	394.9	397.2	398.8	401.1	405.1	409.0	410.6	412.9	416.2
172.5°	398.0	397.2	397.4	399.1	400.0	401.7	404.5	407.8	408.1	409.2	411.7
175°	401.1	400.3	400.3	401.1	401.9	401.9	403.5	405.9	405.1	405.1	406.7
177.5°	402.5	401.9	401.3	401.9	401.9	401.9	402.5	403.8	402.5	402.5	403.1
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5	2012.5
2.5°	2005.3	2008.2	2011.0	2012.4	2012.1	2011.8	2011.4	2011.1
5°	1994.6	1998.5	2002.5	2004.1	2003.4	2002.7	2002.0	2001.1
7.5°	1972.4	1975.5	1978.6	1980.0	1979.6	1979.1	1978.7	1978.3
10°	1953.7	1956.6	1959.4	1960.6	1959.8	1959.1	1958.3	1957.6
12.5°	1931.1	1934.2	1937.4	1938.4	1937.4	1936.4	1935.4	1934.4
15°	1887.7	1890.0	1892.1	1892.6	1891.6	1890.5	1889.4	1888.3
17.5°	1838.5	1839.9	1841.2	1841.5	1840.8	1840.1	1839.4	1838.7
20°	1801.8	1802.8	1803.9	1804.1	1803.4	1802.7	1802.0	1801.2
22.5°	1763.5	1765.4	1767.4	1767.7	1766.5	1765.1	1763.8	1762.5
25°	1700.4	1700.7	1701.1	1700.5	1699.1	1697.7	1696.3	1694.9
27.5°	1629.5	1628.7	1627.8	1626.5	1624.7	1623.0	1621.1	1619.3
30°	1580.6	1579.2	1577.8	1576.2	1574.4	1572.7	1570.8	1569.0
32.5°	1531.1	1529.3	1527.6	1525.9	1524.1	1522.3	1520.6	1518.7
35°	1452.8	1450.3	1447.7	1445.6	1443.8	1442.0	1440.2	1438.5
37.5°	1370.7	1368.0	1365.2	1362.7	1360.4	1358.0	1355.6	1353.2
40°	1313.5	1309.9	1306.4	1303.6	1301.9	1300.1	1298.3	1296.5
42.5°	1258.2	1254.1	1249.9	1247.2	1246.0	1244.8	1243.5	1242.3
45°	1172.6	1168.6	1164.7	1162.2	1161.0	1159.9	1158.9	1157.8
47.5°	1089.6	1085.2	1080.8	1077.1	1074.4	1071.7	1068.9	1066.2
50°	1031.7	1026.6	1021.7	1018.0	1015.9	1013.8	1011.6	1009.5
52.5°	972.2	967.8	963.3	959.8	957.0	954.3	951.6	948.9
55°	884.7	880.5	876.2	872.9	870.8	868.7	866.5	864.3
57.5°	797.2	793.0	789.0	785.9	783.9	781.7	779.6	777.6
60°	736.9	733.8	730.5	728.0	726.2	724.4	722.7	720.8
62.5°	678.1	675.2	672.3	669.9	668.1	666.3	664.6	662.8
65°	592.7	589.2	585.5	582.9	581.1	579.3	577.4	575.7
67.5°	504.6	501.2	497.8	495.7	495.2	494.7	494.2	493.7
70°	449.0	446.2	443.2	441.3	440.2	439.2	438.1	437.0
72.5°	393.4	391.1	388.8	387.1	386.1	385.0	383.8	382.8
75°	313.2	311.7	310.3	309.4	309.1	308.7	308.3	308.0
77.5°	237.1	236.7	236.3	235.6	234.7	233.8	232.8	231.9
80°	188.8	188.1	187.4	186.9	186.5	186.1	185.8	185.4
82.5°	145.5	145.1	144.7	144.3	143.9	143.6	143.2	142.9
85°	83.8	83.8	83.8	83.7	83.3	82.9	82.6	82.2
87.5°	33.8	33.9	34.1	34.1	34.2	34.4	34.2	34.2
90°	14.2	15.0	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	155.1	116.7	92.9	77.1	67.8	63.5	60.8	60.8
95°	585.1	462.7	356.9	280.3	241.7	217.1	203.0	192.7
97.5°	864.4	819.0	741.7	659.3	602.7	555.1	531.4	515.0
100°	952.3	968.1	929.4	871.0	802.2	754.1	730.4	724.1
102.5°	947.9	1026.2	1037.4	1013.1	971.0	936.0	911.1	906.1
105°	884.4	1021.0	1099.1	1131.6	1133.2	1126.8	1115.8	1111.1
107.5°	794.3	939.7	1049.8	1120.1	1159.2	1177.2	1185.1	1187.1
110°	739.9	876.5	991.0	1077.8	1133.9	1167.1	1181.3	1188.4





TEST NUMBER: P332696-840

CATALOG NUMBER: SA4XXDIP-C1195D810U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	700.1	820.9	929.1	1015.9	1079.5	1119.7	1139.6	1151.1
115°	660.1	757.3	849.6	925.4	987.8	1035.2	1060.5	1066.8
117.5°	640.6	720.9	793.6	857.9	911.1	950.9	976.4	981.4
120°	631.7	705.2	768.3	824.4	869.4	904.1	924.6	933.3
122.5°	624.1	695.0	752.6	801.6	839.7	869.4	886.8	895.4
125°	611.2	679.1	733.6	777.0	808.6	831.5	846.5	851.2
127.5°	595.4	660.2	714.6	755.9	787.6	808.0	820.6	825.4
130°	582.8	645.1	698.8	740.6	773.1	792.8	805.5	810.2
132.5°	569.5	628.0	680.5	722.4	754.1	776.4	788.4	793.1
135°	551.2	602.5	650.7	690.1	721.8	743.9	756.5	761.2
137.5°	534.6	578.0	618.6	654.3	683.8	705.6	716.0	721.8
140°	525.1	562.2	597.7	631.0	658.5	675.9	687.0	693.3
142.5°	516.2	549.0	579.5	608.1	632.7	648.7	658.5	663.0
145°	503.8	530.7	554.3	576.4	596.2	609.6	617.5	621.5
147.5°	493.5	514.8	533.8	551.2	565.7	577.2	583.2	584.6
150°	487.2	505.3	521.2	535.3	548.1	558.3	563.0	563.8
152.5°	480.3	495.8	510.4	522.1	532.8	541.2	544.0	544.8
155°	469.8	482.5	494.3	503.8	511.7	518.0	520.4	520.4
157.5°	458.6	469.2	479.2	486.8	492.7	497.5	498.9	498.9
160°	451.7	460.4	469.1	475.3	480.1	484.8	485.6	485.6
162.5°	444.7	452.1	459.0	464.6	468.1	472.8	473.6	473.0
165°	435.0	439.8	445.4	449.3	452.4	455.7	454.8	454.0
167.5°	425.8	429.4	433.8	436.2	437.8	439.8	439.7	439.0
170°	420.1	422.4	425.7	428.0	429.6	430.3	429.6	429.6
172.5°	415.1	416.8	418.7	420.4	421.3	422.1	421.3	420.1
175°	408.3	409.0	410.6	410.6	410.6	412.2	410.6	409.0
177.5°	403.8	404.5	404.5	405.1	404.5	405.1	403.8	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9

(END OF REPORT)