

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910362

Luminaire Tested: DFN2DIP-4P3F0-020D030US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910362
REPORT IS A COMBINATION OF REPORTS P899039 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-020D030US850-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5140.2 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	983	983	983
5°	984	969	976
10°	976	955	962
15°	961	939	942
20°	941	917	920
25°	921	890	895
30°	896	865	864
35°	873	835	831
40°	844	806	799
45°	815	776	767
50°	783	745	729
55°	750	709	695
60°	713	666	655
65°	671	621	609
70°	619	567	559
75°	547	502	512
80°	460	419	423
85°	323	278	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1058 cd/sqm

TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.6
10°-20°	228.6	4.4
20°-30°	335.9	6.5
30°-40°	390.1	7.6
40°-50°	389.6	7.6
50°-60°	339.7	6.6
60°-70°	251.1	4.9
70°-80°	142.1	2.8
80°-90°	40.5	0.8
90°-100°	65.1	1.3
100°-110°	206.9	4.0
110°-120°	354.0	6.9
120°-130°	465.6	9.1
130°-140°	522.6	10.2
140°-150°	512.5	10.0
150°-160°	429.9	8.4
160°-170°	285.1	5.5
170°-180°	99.7	1.9
0°-30°	645.7	12.6
0°-40°	1035.8	20.2
0°-60°	1765.1	34.3
0°-90°	2198.8	42.8
90°-120°	626.0	12.2
90°-150°	2126.7	41.4
90°-180°	2941.0	57.2
0°-180°	5140.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	863	860	851	857	856	82
15°	822	817	806	809	805	231
25°	744	737	723	724	723	342
35°	642	633	620	615	611	401
45°	522	516	504	495	491	403
55°	395	390	380	370	366	353
65°	266	261	253	246	242	263
75°	139	138	134	129	130	149
85°	34	33	32	30	29	38
90°	1	11	31	29	30	5
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	

TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	863.0	863.0	863.0	863.0	863.0
2.5°	868.0	863.9	854.7	863.0	861.5
5°	863.0	859.8	850.6	857.3	855.6
7.5°	857.3	852.3	843.2	849.8	848.2
10°	848.2	842.4	832.4	839.0	836.5
12.5°	835.6	830.8	820.8	824.9	823.2
15°	821.5	816.7	805.8	809.1	805.0
17.5°	804.1	799.3	788.4	792.5	788.4
20°	785.1	780.1	768.4	771.0	767.6
22.5°	766.0	758.6	747.7	747.7	746.0
25°	743.6	736.9	722.8	724.4	722.8
27.5°	718.6	712.9	702.1	699.7	695.5
30°	693.8	687.1	674.7	672.3	668.8
32.5°	667.2	662.3	649.0	644.0	640.7
35°	641.6	633.2	619.9	614.9	610.7
37.5°	612.5	605.0	591.7	585.9	581.7
40°	582.6	575.9	562.6	555.3	551.8
42.5°	553.5	546.8	533.7	525.3	520.3
45°	522.0	516.2	503.7	494.6	491.3
47.5°	491.3	485.5	472.2	463.0	458.1
50°	458.9	454.8	443.2	431.5	427.4
52.5°	427.4	421.5	410.8	401.7	395.9
55°	395.0	390.0	380.1	370.2	366.0
57.5°	362.6	358.5	347.7	337.8	334.4
60°	330.3	327.0	315.4	306.2	303.8
62.5°	298.8	292.9	284.7	276.4	273.0
65°	266.4	261.4	253.2	245.6	241.5
67.5°	233.2	229.0	221.6	215.8	212.5
70°	202.5	199.2	191.6	185.9	182.7
72.5°	171.0	167.7	163.5	157.7	155.3
75°	139.4	137.8	133.5	128.6	130.3
77.5°	111.2	107.9	106.1	103.7	101.3
80°	83.1	82.2	80.5	78.0	76.3
82.5°	56.4	56.4	55.7	52.3	52.3
85°	33.9	33.2	32.4	29.8	29.1
87.5°	15.0	13.3	11.6	9.2	8.3
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5



TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2

TEST NUMBER: P910362

CATALOG NUMBER: DFN2DIP-4P3F0-020D030US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.47	7.27	7.49	8.30	9.67	6.03	6.83	7.05	7.85	9.22
	3H	8.12	8.84	9.15	9.87	11.27	7.63	8.35	8.66	9.39	10.78
	4H	8.70	9.38	9.74	10.42	11.82	8.21	8.89	9.25	9.93	11.33
	6H	9.10	9.72	10.15	10.77	12.18	8.60	9.22	9.65	10.27	11.68
	8H	9.20	9.80	10.25	10.85	12.26	8.70	9.29	9.75	10.35	11.76
	12H	9.24	9.81	10.30	10.86	12.29	8.74	9.30	9.79	10.35	11.78
4H	2H	6.92	7.60	7.97	8.64	10.04	6.57	7.25	7.61	8.28	9.68
	3H	8.78	9.34	9.83	10.41	11.82	8.37	8.94	9.42	10.00	11.41
	4H	9.48	10.00	10.55	11.06	12.49	9.06	9.58	10.12	10.64	12.07
	6H	9.99	10.44	11.06	11.52	12.95	9.56	10.01	10.63	11.09	12.51
	8H	10.14	10.56	11.21	11.63	13.07	9.70	10.12	10.77	11.19	12.63
	12H	10.21	10.58	11.29	11.67	13.12	9.76	10.14	10.85	11.22	12.67
8H	4H	9.67	10.09	10.74	11.16	12.61	9.30	9.71	10.37	10.78	12.23
	6H	10.30	10.64	11.39	11.75	13.20	9.91	10.26	11.00	11.37	12.81
	8H	10.51	10.81	11.61	11.91	13.37	10.12	10.42	11.22	11.52	12.98
	12H	10.64	10.90	11.74	12.00	13.50	10.23	10.49	11.33	11.59	13.09
12H	4H	9.65	10.03	10.74	11.12	12.57	9.29	9.66	10.37	10.75	12.20
	6H	10.32	10.63	11.42	11.72	13.18	9.95	10.25	11.05	11.35	12.81
	8H	10.56	10.82	11.66	11.92	13.42	10.18	10.44	11.28	11.54	13.04

END OF REPORT