

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910411

Luminaire Tested: DFN2DIP-4P3F0-040D050US850-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P910411  
REPORT IS A COMBINATION OF REPORTS P900583 AND P897473  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-040D050US850-FLLONL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9881.2 lumens  
Efficiency: N/A  
Efficacy: 130.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 75.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910411  
CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P910411  
 CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44			44
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37			37
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31			31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27			27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23			23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20			20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17			17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15			15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14			14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12			12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11			11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1967	1967	1967
5°	1969	1938	1952
10°	1952	1911	1925
15°	1922	1878	1883
20°	1882	1833	1840
25°	1842	1780	1791
30°	1792	1730	1728
35°	1745	1671	1662
40°	1687	1612	1598
45°	1630	1552	1534
50°	1566	1490	1459
55°	1500	1417	1390
60°	1425	1332	1311
65°	1343	1243	1218
70°	1239	1134	1117
75°	1095	1004	1023
80°	920	837	846
85°	648	555	554

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1630 cd/sqm



TEST NUMBER: P910411

CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	1.6
10°-20°	457.1	4.6
20°-30°	671.7	6.8
30°-40°	780.2	7.9
40°-50°	779.2	7.9
50°-60°	679.5	6.9
60°-70°	502.3	5.1
70°-80°	284.2	2.9
80°-90°	78.3	0.8
90°-100°	61.7	0.6
100°-110°	230.0	2.3
110°-120°	610.1	6.2
120°-130°	1011.9	10.2
130°-140°	1074.8	10.9
140°-150°	999.0	10.1
150°-160°	803.1	8.1
160°-170°	517.5	5.2
170°-180°	178.1	1.8
0°-30°	1291.3	13.1
0°-40°	2071.5	21.0
0°-60°	3530.2	35.7
0°-90°	4394.9	44.5
90°-120°	901.9	9.1
90°-150°	3987.5	40.4
90°-180°	5486.0	55.5
0°-180°	9881.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	1	16	27	34	36	9
95°	88	43	53	60	58	104
105°	412	452	83	98	103	440
115°	779	802	836	209	111	767
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1410	1407	1052
145°	1580	1579	1602	1611	1605	988
155°	1740	1728	1744	1752	1742	802
165°	1833	1825	1829	1839	1829	518
175°	1875	1866	1869	1878	1865	178
180°	1871	1871	1871	1871	1871	



TEST NUMBER: P910411

CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	1.3	16.2	27.1	33.9	36.5
92.5°	33.9	28.5	32.5	35.3	36.5
95°	87.9	43.3	52.8	59.7	58.2
97.5°	158.4	47.5	69.0	73.2	74.4
100°	239.8	54.2	77.2	87.9	90.7
102.5°	329.0	326.4	80.0	94.7	98.9
105°	411.7	452.4	82.6	97.5	102.9
107.5°	507.8	541.5	85.4	100.1	105.7
110°	600.0	628.2	237.0	101.6	106.9



TEST NUMBER: P910411

CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	686.6	710.9	687.9	104.2	108.3
115°	778.6	801.6	835.5	208.6	111.1
117.5°	858.5	885.5	908.7	714.9	360.2
120°	947.9	968.2	992.6	1008.9	826.0
122.5°	1023.6	1045.3	1072.5	1080.6	1082.1
125°	1100.8	1118.5	1144.3	1153.7	1157.8
127.5°	1171.2	1190.2	1210.7	1224.1	1225.4
130°	1237.6	1259.4	1274.1	1289.1	1287.9
132.5°	1305.4	1323.0	1337.8	1350.1	1348.8
135°	1362.3	1384.0	1396.0	1409.8	1407.0
137.5°	1421.7	1438.0	1451.7	1465.2	1461.2
140°	1480.0	1490.9	1505.7	1517.9	1511.2
142.5°	1528.9	1538.4	1555.9	1566.7	1559.9
145°	1580.3	1578.9	1601.8	1611.4	1604.6
147.5°	1624.9	1620.8	1643.9	1650.6	1645.3
150°	1668.3	1658.8	1680.5	1688.6	1681.8
152.5°	1704.8	1694.0	1714.3	1722.5	1713.0
155°	1740.0	1727.9	1744.1	1752.2	1741.5
157.5°	1768.4	1757.7	1769.9	1779.4	1768.4
160°	1792.9	1784.7	1792.9	1800.9	1791.5
162.5°	1814.4	1806.5	1813.1	1822.6	1810.4
165°	1833.4	1825.4	1829.4	1838.8	1829.4
167.5°	1848.4	1840.2	1844.4	1853.8	1841.6
170°	1860.6	1852.4	1855.1	1864.6	1852.4
172.5°	1868.7	1860.6	1863.3	1872.8	1860.6
175°	1875.4	1865.9	1868.7	1878.1	1864.6
177.5°	1878.1	1868.7	1870.1	1879.5	1867.3
180°	1871.3	1871.3	1871.3	1871.3	1871.3



TEST NUMBER: P910411  
 CATALOG NUMBER: DFN2DIP-4P3F0-040D050US850-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.06	9.87	10.06	10.88	12.23	8.61	9.43	9.61	10.44	11.79
	3H	10.71	11.44	11.72	12.46	13.83	10.22	10.95	11.23	11.97	13.34
	4H	11.29	11.98	12.32	13.01	14.38	10.80	11.49	11.82	12.51	13.89
	6H	11.68	12.32	12.72	13.35	14.74	11.18	11.82	12.22	12.85	14.24
	8H	11.79	12.39	12.83	13.44	14.82	11.28	11.89	12.33	12.94	14.32
	12H	11.83	12.41	12.88	13.45	14.86	11.32	11.90	12.37	12.94	14.35
4H	2H	9.51	10.20	10.54	11.22	12.60	9.15	9.84	10.19	10.87	12.25
	3H	11.36	11.94	12.40	12.99	14.38	10.96	11.53	12.00	12.59	13.98
	4H	12.07	12.60	13.12	13.65	15.06	11.65	12.18	12.70	13.22	14.63
	6H	12.58	13.03	13.64	14.10	15.51	12.15	12.60	13.21	13.67	15.08
	8H	12.73	13.15	13.79	14.21	15.63	12.29	12.71	13.35	13.78	15.20
	12H	12.80	13.18	13.87	14.25	15.68	12.35	12.73	13.42	13.81	15.23
8H	4H	12.26	12.69	13.32	13.75	15.17	11.88	12.31	12.94	13.37	14.79
	6H	12.88	13.23	13.97	14.34	15.76	12.50	12.85	13.58	13.95	15.37
	8H	13.10	13.41	14.19	14.50	15.93	12.71	13.02	13.80	14.10	15.54
	12H	13.23	13.50	14.32	14.58	16.06	12.82	13.09	13.91	14.17	15.65
12H	4H	12.24	12.63	13.32	13.70	15.13	11.87	12.26	12.95	13.33	14.76
	6H	12.91	13.22	14.00	14.31	15.75	12.54	12.85	13.63	13.93	15.37
	8H	13.15	13.42	14.24	14.50	15.98	12.77	13.04	13.86	14.12	15.60