

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910449

Luminaire Tested: DFN2DIP-4P3F0-060D040US850-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910449
REPORT IS A COMBINATION OF REPORTS P900578 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D040US850-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10047.6 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 91.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910449
CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P910449
 CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49	49	49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42	42	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27	27	27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24	24	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3134	3134	3134
5°	3137	3082	3103
10°	3104	3020	3001
15°	3059	2918	2844
20°	3001	2779	2652
25°	2941	2623	2466
30°	2861	2463	2231
35°	2783	2291	2024
40°	2703	2114	1788
45°	2611	1917	1573
50°	2515	1719	1364
55°	2414	1508	1163
60°	2298	1287	956
65°	2164	1063	859
70°	2002	854	776
75°	1798	748	704
80°	1503	621	607
85°	1019	404	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2611 cd/sqm



TEST NUMBER: P910449

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	2.6
10°-20°	707.6	7.0
20°-30°	993.4	9.9
30°-40°	1082.8	10.8
40°-50°	995.2	9.9
50°-60°	781.6	7.8
60°-70°	508.8	5.1
70°-80°	261.9	2.6
80°-90°	69.5	0.7
90°-100°	49.4	0.5
100°-110°	184.0	1.8
110°-120°	488.1	4.9
120°-130°	809.5	8.1
130°-140°	859.9	8.6
140°-150°	799.2	8.0
150°-160°	642.5	6.4
160°-170°	414.0	4.1
170°-180°	142.5	1.4
0°-30°	1958.7	19.5
0°-40°	3041.5	30.3
0°-60°	4818.4	48.0
0°-90°	5658.6	56.3
90°-120°	721.5	7.2
90°-150°	3190.0	31.7
90°-180°	4389.0	43.7
0°-180°	10047.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	1	13	22	27	29	9
95°	70	35	42	48	47	83
105°	329	362	66	78	82	352
115°	623	641	668	167	89	613
125°	881	895	915	923	926	785
135°	1090	1107	1117	1128	1126	842
145°	1264	1263	1281	1289	1284	791
155°	1392	1382	1395	1402	1393	641
165°	1467	1460	1464	1471	1464	414
175°	1500	1493	1495	1502	1492	143
180°	1497	1497	1497	1497	1497	



TEST NUMBER: P910449

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.0	13.0	21.6	27.2	29.2
92.5°	27.2	22.7	26.0	28.2	29.2
95°	70.3	34.6	42.1	47.7	46.6
97.5°	126.8	37.9	55.2	58.6	59.6
100°	191.7	43.4	61.8	70.3	72.5
102.5°	263.2	261.2	63.9	75.7	79.1
105°	329.3	361.9	66.1	78.0	82.3
107.5°	406.2	433.3	68.3	80.2	84.5
110°	480.0	502.6	189.6	81.3	85.5



TEST NUMBER: P910449

CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	549.3	568.7	550.3	83.4	86.7
115°	622.8	641.2	668.4	166.8	88.9
117.5°	686.8	708.4	726.9	571.9	288.1
120°	758.3	774.5	794.0	807.1	660.9
122.5°	818.9	836.3	858.0	864.5	865.6
125°	880.7	894.9	915.4	923.0	926.2
127.5°	937.0	952.2	968.5	979.4	980.4
130°	990.1	1007.5	1019.3	1031.3	1030.3
132.5°	1044.2	1058.4	1070.3	1080.1	1079.1
135°	1089.8	1107.2	1116.9	1127.7	1125.6
137.5°	1137.4	1150.4	1161.3	1172.1	1168.9
140°	1184.0	1192.7	1204.6	1214.4	1208.9
142.5°	1223.1	1230.7	1244.7	1253.3	1248.0
145°	1264.3	1263.2	1281.4	1289.1	1283.7
147.5°	1299.9	1296.6	1315.1	1320.5	1316.3
150°	1334.6	1327.0	1344.4	1350.9	1345.4
152.5°	1363.8	1355.2	1371.4	1377.9	1370.4
155°	1392.0	1382.4	1395.3	1401.8	1393.1
157.5°	1414.8	1406.1	1416.0	1423.5	1414.8
160°	1434.3	1427.7	1434.3	1440.7	1433.2
162.5°	1451.6	1445.1	1450.6	1458.1	1448.4
165°	1466.8	1460.3	1463.5	1471.1	1463.5
167.5°	1478.7	1472.1	1475.5	1483.1	1473.3
170°	1488.5	1482.0	1484.1	1491.7	1482.0
172.5°	1494.9	1488.5	1490.7	1498.3	1488.5
175°	1500.3	1492.7	1494.9	1502.5	1491.7
177.5°	1502.5	1494.9	1496.0	1503.7	1493.9
180°	1497.2	1497.2	1497.2	1497.2	1497.2



TEST NUMBER: P910449
 CATALOG NUMBER: DFN2DIP-4P3F0-060D040US850-RLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.65	12.54	12.56	13.46	14.64	7.61	8.50	8.52	9.42	10.60
	3H	13.33	14.12	14.25	15.05	16.26	8.80	9.59	9.72	10.52	11.73
	4H	13.94	14.69	14.87	15.62	16.84	9.25	10.00	10.18	10.93	12.15
	6H	14.36	15.05	15.31	15.99	17.22	9.57	10.25	10.51	11.20	12.42
	8H	14.49	15.14	15.44	16.10	17.32	9.66	10.31	10.61	11.27	12.50
	12H	14.55	15.17	15.51	16.12	17.37	9.70	10.32	10.66	11.27	12.52
4H	2H	11.68	12.42	12.62	13.36	14.57	8.21	8.96	9.15	9.90	11.11
	3H	13.50	14.13	14.46	15.09	16.32	9.56	10.18	10.51	11.15	12.38
	4H	14.20	14.76	15.16	15.72	16.98	10.11	10.67	11.07	11.63	12.89
	6H	14.71	15.20	15.68	16.18	17.44	10.52	11.01	11.49	11.99	13.25
	8H	14.88	15.34	15.86	16.32	17.58	10.65	11.10	11.62	12.08	13.35
	12H	14.98	15.39	15.97	16.38	17.66	10.71	11.12	11.70	12.12	13.39
8H	4H	14.17	14.62	15.14	15.60	16.87	10.39	10.84	11.36	11.82	13.09
	6H	14.73	15.10	15.73	16.12	17.39	10.90	11.27	11.90	12.30	13.56
	8H	14.94	15.27	15.95	16.28	17.57	11.09	11.42	12.09	12.43	13.71
	12H	15.08	15.37	16.09	16.37	17.70	11.20	11.49	12.21	12.50	13.83
12H	4H	14.12	14.53	15.11	15.53	16.80	10.39	10.80	11.39	11.80	13.07
	6H	14.70	15.04	15.71	16.04	17.33	10.95	11.28	11.96	12.29	13.57
	8H	14.92	15.21	15.93	16.22	17.55	11.16	11.45	12.17	12.45	13.78