

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332623-840

Luminaire Tested: **SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332623-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7653.5 lumens  
Efficiency: N/A  
Efficacy: 134.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45																			
1	97	92	88	85	88	85	81	78	71	68	66	57	56	54	45	44	43	38																			
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32																			
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27																			
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23																			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20																			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18																			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16																			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14																			
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13																			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.2	1.6
10°-20°	355.7	4.6
20°-30°	523.5	6.8
30°-40°	608.6	8.0
40°-50°	608.7	8.0
50°-60°	532.4	7.0
60°-70°	395.4	5.2
70°-80°	224.6	2.9
80°-90°	69.4	0.9
90°-100°	100.1	1.3
100°-110°	296.4	3.9
110°-120°	503.1	6.6
120°-130°	663.4	8.7
130°-140°	745.0	9.7
140°-150°	732.1	9.6
150°-160°	615.7	8.0
160°-170°	409.7	5.4
170°-180°	143.5	1.9
0°-30°	1005.5	13.1
0°-40°	1614.1	21.1
0°-60°	2755.2	36.0
0°-90°	3444.6	45.0
90°-120°	899.6	11.8
90°-150°	3040.1	39.7
90°-180°	4209.0	55.0
0°-180°	7653.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	4	16	26	33	35	8
95°	70	81	89	92	93	78
105°	273	275	279	283	286	290
115°	512	511	509	508	507	504
125°	745	745	744	741	739	664
135°	961	968	968	966	962	743
145°	1167	1172	1173	1172	1169	730
155°	1338	1337	1336	1340	1336	615
165°	1456	1453	1450	1456	1452	410
175°	1515	1509	1508	1515	1508	144
180°	1517	1517	1517	1517	1517	



TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	23.0	23.4	23.8	24.2	24.5	24.8	25.1	25.3	25.5	25.8	26.1
90°	3.5	6.4	9.3	12.1	14.9	17.5	19.6	21.6	23.7	25.9	27.4
92.5°	25.1	28.4	31.7	34.9	38.3	40.6	42.1	43.5	45.0	46.5	47.4
95°	70.4	72.7	75.1	77.5	79.8	81.9	83.7	85.5	87.4	89.2	90.0
97.5°	123.0	124.8	126.7	128.6	130.5	132.5	134.6	136.7	138.9	141.0	142.0
100°	164.3	165.3	166.3	167.3	168.4	170.2	172.5	174.8	177.1	179.6	180.1
102.5°	207.4	207.8	208.2	208.6	209.1	210.4	212.5	214.7	216.8	218.9	219.6
105°	273.4	273.7	273.9	274.2	274.4	275.1	276.1	277.1	278.2	279.2	280.0
107.5°	342.5	343.0	343.3	343.6	343.9	344.1	344.3	344.4	344.6	344.7	345.5
110°	389.5	390.0	390.5	391.1	391.6	391.7	391.5	391.2	390.9	390.7	390.2



TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	438.3	438.5	438.6	438.7	438.8	438.6	438.1	437.7	437.2	436.7	436.6
115°	511.5	511.5	511.5	511.5	511.5	511.3	510.8	510.3	509.7	509.2	509.0
117.5°	580.6	580.8	581.0	581.2	581.4	581.3	580.9	580.6	580.2	579.9	579.0
120°	626.5	627.5	628.6	629.7	630.7	630.9	630.1	629.2	628.4	627.7	626.4
122.5°	674.4	674.8	675.2	675.6	676.1	676.1	675.7	675.4	675.0	674.6	673.8
125°	745.0	745.0	745.0	745.0	745.0	744.9	744.7	744.4	744.1	743.9	743.4
127.5°	809.1	809.9	810.6	811.4	812.2	812.4	811.9	811.5	811.1	810.7	810.2
130°	854.1	855.0	855.7	856.5	857.3	857.7	857.7	857.7	857.7	857.7	857.2
132.5°	900.1	900.7	901.3	901.8	902.4	902.6	902.4	902.2	902.0	901.8	901.2
135°	960.9	962.5	964.0	965.6	967.1	968.0	968.0	968.0	968.0	968.0	967.5
137.5°	1027.0	1027.8	1028.5	1029.3	1030.0	1030.6	1031.0	1031.4	1031.8	1032.2	1031.6
140°	1071.2	1071.7	1072.3	1072.8	1073.3	1073.5	1073.5	1073.5	1073.5	1073.5	1073.3
142.5°	1111.6	1112.1	1112.6	1113.1	1113.7	1113.8	1113.6	1113.4	1113.2	1113.0	1112.9
145°	1167.4	1168.4	1169.5	1170.5	1171.5	1172.3	1172.5	1172.8	1173.0	1173.3	1173.0
147.5°	1222.7	1224.1	1225.3	1226.5	1227.8	1228.3	1228.1	1227.9	1227.7	1227.5	1227.3
150°	1256.6	1257.6	1258.7	1259.7	1260.7	1261.2	1261.2	1261.2	1261.2	1261.2	1261.2
152.5°	1288.5	1289.1	1289.7	1290.3	1291.0	1291.4	1291.6	1291.8	1292.0	1292.2	1292.8
155°	1337.5	1337.5	1337.5	1337.5	1337.5	1337.4	1337.2	1336.9	1336.6	1336.4	1337.4
157.5°	1378.8	1378.4	1377.9	1377.5	1377.0	1376.6	1376.6	1376.5	1376.5	1376.4	1377.3
160°	1403.2	1403.0	1402.7	1402.4	1402.2	1401.9	1401.7	1401.4	1401.1	1400.9	1401.7
162.5°	1425.7	1425.0	1424.4	1423.7	1423.0	1422.6	1422.3	1422.1	1421.8	1421.5	1422.9
165°	1456.0	1455.2	1454.4	1453.7	1452.9	1452.2	1451.7	1451.2	1450.7	1450.2	1451.7
167.5°	1479.3	1478.1	1477.0	1475.9	1474.9	1474.3	1474.4	1474.4	1474.5	1474.5	1476.1
170°	1492.4	1491.1	1489.8	1488.4	1487.1	1486.6	1486.9	1487.1	1487.4	1487.7	1489.2
172.5°	1501.8	1500.7	1499.5	1498.4	1497.4	1496.8	1496.9	1497.0	1497.0	1497.1	1498.8
175°	1514.7	1513.4	1512.1	1510.8	1509.4	1508.6	1508.4	1508.1	1507.9	1507.6	1509.4
177.5°	1518.9	1517.8	1516.8	1515.8	1514.7	1514.2	1514.2	1514.2	1514.2	1514.2	1515.7
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0



TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	26.5	26.8	27.1	27.3	27.4	27.5	27.6	27.7
90°	29.0	30.5	32.1	33.1	33.6	34.1	34.6	35.2
92.5°	48.4	49.3	50.2	50.8	51.2	51.5	51.8	52.1
95°	90.7	91.5	92.3	92.7	92.7	92.7	92.7	92.7
97.5°	142.9	143.8	144.8	145.2	145.2	145.2	145.2	145.2
100°	180.6	181.1	181.6	181.9	181.9	181.9	181.9	181.9
102.5°	220.4	221.2	221.9	222.3	222.6	222.8	223.0	223.2
105°	280.8	281.6	282.4	283.2	284.0	284.7	285.5	286.3
107.5°	346.2	346.9	347.6	348.0	347.9	347.9	347.8	347.8
110°	389.6	389.1	388.6	388.7	389.5	390.3	391.1	391.8





TEST NUMBER: P332623-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	436.5	436.4	436.3	436.3	436.5	436.6	436.8	437.0
115°	508.7	508.4	508.2	507.9	507.7	507.4	507.2	506.9
117.5°	578.0	577.1	576.2	575.6	575.0	574.5	574.0	573.5
120°	625.1	623.8	622.5	622.1	622.6	623.1	623.7	624.2
122.5°	672.9	672.0	671.1	670.1	669.2	668.3	667.3	666.4
125°	742.8	742.3	741.7	741.2	740.7	740.2	739.6	739.1
127.5°	809.7	809.2	808.6	808.2	807.8	807.3	806.9	806.5
130°	856.6	856.1	855.6	854.7	853.7	852.7	851.6	850.6
132.5°	900.7	900.2	899.7	899.2	898.8	898.4	898.0	897.6
135°	966.9	966.3	965.8	965.2	964.4	963.6	962.8	962.1
137.5°	1030.9	1030.2	1029.6	1029.3	1029.5	1029.6	1029.8	1029.9
140°	1073.0	1072.8	1072.5	1072.3	1072.0	1071.7	1071.5	1071.2
142.5°	1112.9	1112.8	1112.8	1112.7	1112.7	1112.6	1112.6	1112.5
145°	1172.8	1172.5	1172.3	1171.6	1170.9	1170.1	1169.3	1168.6
147.5°	1227.1	1226.9	1226.6	1226.4	1226.2	1225.9	1225.6	1225.4
150°	1261.2	1261.2	1261.2	1261.1	1260.8	1260.6	1260.3	1260.1
152.5°	1293.4	1294.1	1294.7	1294.7	1294.0	1293.3	1292.6	1292.0
155°	1338.5	1339.5	1340.5	1340.5	1339.5	1338.5	1337.4	1336.4
157.5°	1378.1	1378.8	1379.6	1379.6	1378.7	1377.8	1376.8	1376.0
160°	1402.4	1403.2	1404.0	1403.7	1402.4	1401.1	1399.9	1398.6
162.5°	1424.3	1425.7	1427.1	1427.2	1425.9	1424.6	1423.3	1422.0
165°	1453.3	1454.8	1456.4	1456.6	1455.6	1454.6	1453.5	1452.5
167.5°	1477.6	1479.3	1480.8	1480.8	1479.1	1477.5	1475.9	1474.3
170°	1490.9	1492.4	1494.0	1493.8	1492.0	1490.2	1488.3	1486.5
172.5°	1500.7	1502.4	1504.2	1504.2	1502.3	1500.5	1498.6	1496.8
175°	1511.3	1513.1	1514.9	1514.9	1513.1	1511.3	1509.4	1507.6
177.5°	1517.1	1518.6	1520.0	1519.9	1518.2	1516.6	1514.9	1513.3
180°	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0	1517.0

(END OF REPORT)