

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332624-840

Luminaire Tested: **SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332624-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7787.4 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332624-840
CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44																			
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37																			
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36	31																			
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31	26																			
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26	23																			
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23	20																			
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20	17																			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																			
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16	14																			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	15	12																			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10823	10823	10823
5°	10855	10724	10802
10°	10787	10637	10690
15°	10657	10486	10513
20°	10483	10299	10308
25°	10286	10085	10056
30°	10043	9833	9743
35°	9792	9570	9443
40°	9531	9271	9101
45°	9259	8977	8805
50°	8959	8715	8446
55°	8633	8376	8103
60°	8307	7995	7753
65°	7941	7633	7324
70°	7530	7152	6871
75°	6903	6569	6400
80°	6141	5890	5742
85°	5372	5169	5067



TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.2	1.6
10°-20°	355.7	4.6
20°-30°	523.5	6.7
30°-40°	608.6	7.8
40°-50°	608.7	7.8
50°-60°	532.4	6.8
60°-70°	395.4	5.1
70°-80°	224.6	2.9
80°-90°	68.1	0.9
90°-100°	431.4	5.5
100°-110°	897.9	11.5
110°-120°	804.2	10.3
120°-130°	676.5	8.7
130°-140°	564.1	7.2
140°-150°	430.9	5.5
150°-160°	302.9	3.9
160°-170°	178.2	2.3
170°-180°	58.0	0.7
0°-30°	1005.5	12.9
0°-40°	1614.1	20.7
0°-60°	2755.2	35.4
0°-90°	3443.3	44.2
90°-120°	2133.5	27.4
90°-150°	3805.0	48.9
90°-180°	4344.0	55.8
0°-180°	7787.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1341	1341	1341	1341	1341	
5°	1340	1335	1323	1334	1333	127
15°	1275	1270	1255	1260	1258	359
25°	1155	1147	1132	1133	1129	531
35°	994	986	971	964	958	621
45°	811	803	786	775	771	625
55°	613	609	595	583	576	549
65°	416	410	400	389	383	411
75°	221	216	211	206	205	235
85°	58	58	56	56	55	64
90°	1	9	21	23	25	5
95°	39	122	956	474	286	43
105°	137	199	770	1658	1651	146
115°	242	303	686	1319	1585	240
125°	337	400	683	1122	1265	300
135°	400	476	677	996	1131	309
145°	461	528	674	840	924	289
155°	524	566	655	742	773	242
165°	572	589	628	665	675	161
175°	596	597	602	610	608	57
180°	597	597	597	597	597	



TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1344.0	1343.4	1342.8	1342.3	1341.7	1340.4	1338.3	1336.2	1334.0	1332.0	1333.8
5°	1339.5	1338.6	1337.6	1336.7	1335.6	1333.8	1331.2	1328.6	1326.0	1323.3	1326.0
7.5°	1327.1	1326.1	1325.1	1324.1	1323.2	1321.3	1318.4	1315.5	1312.5	1309.6	1311.7
10°	1315.9	1314.9	1313.9	1313.0	1312.0	1310.0	1306.9	1303.8	1300.7	1297.6	1299.5
12.5°	1301.2	1300.3	1299.3	1298.4	1297.5	1295.3	1292.0	1288.7	1285.5	1282.1	1284.2
15°	1275.1	1274.0	1273.1	1272.1	1271.2	1269.0	1265.4	1261.8	1258.2	1254.7	1256.1
17.5°	1243.4	1242.2	1241.0	1239.9	1238.7	1236.4	1233.0	1229.6	1226.2	1222.8	1223.8
20°	1220.2	1219.0	1217.9	1216.7	1215.5	1213.0	1209.5	1205.9	1202.3	1198.8	1199.5
22.5°	1195.4	1193.8	1192.1	1190.6	1189.0	1186.5	1182.9	1179.3	1175.7	1172.2	1173.5
25°	1154.7	1153.1	1151.3	1149.7	1148.0	1145.5	1142.2	1138.8	1135.5	1132.2	1132.4
27.5°	1108.3	1106.6	1104.9	1103.2	1101.5	1099.0	1095.9	1092.9	1089.7	1086.6	1086.0
30°	1077.4	1075.5	1073.6	1071.7	1069.8	1067.2	1064.1	1061.1	1057.9	1054.8	1053.9
32.5°	1044.7	1043.0	1041.3	1039.6	1037.8	1035.3	1032.1	1028.7	1025.5	1022.2	1021.1
35°	993.6	991.9	990.3	988.6	986.9	984.4	981.1	977.8	974.4	971.1	969.4
37.5°	939.7	938.2	936.6	935.1	933.5	931.0	927.5	923.8	920.3	916.7	914.8
40°	904.4	902.5	900.6	898.7	896.8	894.0	890.5	886.9	883.3	879.7	877.4
42.5°	866.7	865.5	864.3	863.2	862.0	859.5	855.6	851.6	847.6	843.6	840.9
45°	811.0	809.3	807.7	806.0	804.4	801.5	797.8	794.0	790.1	786.3	783.7
47.5°	752.8	751.6	750.5	749.3	748.2	745.9	742.4	738.8	735.3	731.7	728.7
50°	713.3	712.3	711.3	710.3	709.4	707.3	704.0	700.6	697.2	693.9	690.5
52.5°	674.6	673.5	672.3	671.2	669.9	667.6	664.1	660.6	657.0	653.5	650.6
55°	613.4	612.6	611.9	611.2	610.5	608.4	605.1	601.8	598.4	595.1	592.2
57.5°	554.9	554.1	553.3	552.5	551.7	549.6	546.3	543.0	539.8	536.4	533.7
60°	514.5	513.3	512.1	511.0	509.8	507.6	504.5	501.4	498.3	495.2	493.0
62.5°	475.0	474.0	473.0	472.0	471.0	468.9	465.5	462.2	459.0	455.7	453.7
65°	415.7	414.5	413.3	412.1	410.9	409.1	406.8	404.3	401.9	399.6	397.2
67.5°	356.0	354.9	353.8	352.6	351.6	349.9	347.6	345.3	343.1	340.7	338.4
70°	319.0	317.4	315.7	314.0	312.4	310.5	308.6	306.7	304.8	303.0	301.0
72.5°	279.5	277.8	276.2	274.5	272.8	271.2	269.7	268.1	266.6	265.1	263.6
75°	221.3	220.0	218.9	217.7	216.5	215.3	214.1	212.9	211.8	210.6	209.5
77.5°	165.6	165.1	164.6	164.1	163.5	162.8	161.7	160.7	159.6	158.5	158.2
80°	132.1	131.4	130.7	130.0	129.3	128.7	128.2	127.7	127.2	126.7	126.2
82.5°	99.5	99.2	98.8	98.5	98.2	98.0	97.9	97.8	97.7	97.6	97.3
85°	58.0	58.0	58.0	58.0	58.0	57.8	57.3	56.9	56.4	55.8	55.8
87.5°	22.6	22.8	23.3	23.4	23.4	23.2	24.4	24.3	24.5	24.8	24.6
90°	1.2	3.5	7.1	8.2	9.4	9.4	16.5	16.5	18.8	21.1	20.0
92.5°	13.3	19.5	30.5	44.8	62.0	86.3	146.0	237.0	325.8	372.2	310.0
95°	38.7	42.2	54.0	69.3	97.4	146.7	248.7	441.2	721.6	956.3	983.4
97.5°	69.5	69.5	79.6	93.6	117.9	159.2	237.7	396.7	675.4	1007.3	1235.5
100°	89.2	89.2	97.4	111.5	133.8	171.4	240.5	373.1	612.6	943.4	1243.9
102.5°	108.0	109.9	117.1	130.3	151.6	187.3	249.9	366.6	570.3	863.6	1173.5
105°	137.3	140.8	146.7	160.8	181.9	215.9	272.3	369.6	533.9	769.8	1045.5
107.5°	169.7	172.0	177.9	192.9	213.1	246.7	298.3	387.0	527.4	717.2	942.3
110°	191.3	193.6	199.4	213.6	234.7	266.4	318.0	400.1	529.3	699.4	890.7



TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	212.0	214.3	221.1	234.2	255.4	287.0	336.8	414.2	534.8	690.9	861.5
115°	241.8	245.3	253.5	265.2	287.5	319.2	366.1	436.6	545.6	686.5	834.4
117.5°	272.7	276.0	283.3	296.2	317.1	349.9	394.6	459.3	557.1	685.3	822.1
120°	293.4	295.7	304.0	316.8	336.8	369.6	414.2	475.2	565.6	685.3	815.6
122.5°	312.1	314.5	322.8	334.7	356.5	388.4	433.0	490.3	574.1	684.4	808.1
125°	336.8	341.4	348.5	361.4	383.7	416.6	458.8	512.8	586.7	683.0	795.6
127.5°	358.6	362.3	370.8	385.6	408.8	441.9	482.7	532.3	596.8	680.3	778.9
130°	370.8	375.5	384.9	402.5	424.7	458.8	498.8	544.5	604.3	679.4	768.6
132.5°	383.0	386.8	399.0	415.7	439.8	472.0	511.9	556.7	610.9	678.5	759.2
135°	400.1	404.9	416.6	436.6	461.2	491.7	530.4	572.7	620.8	677.1	745.2
137.5°	417.3	421.7	434.6	453.6	479.3	508.4	544.5	583.9	626.6	676.8	733.0
140°	429.5	433.0	446.0	465.9	490.5	518.7	553.9	591.4	631.4	675.9	726.4
142.5°	442.6	446.2	458.1	477.2	500.8	528.1	562.3	597.0	635.1	675.9	720.7
145°	461.2	464.7	476.5	492.8	515.1	541.0	571.5	603.2	637.2	673.6	711.1
147.5°	482.0	483.2	493.5	510.5	529.0	552.2	580.9	608.5	638.3	669.3	702.5
150°	495.2	496.3	505.7	519.9	537.5	559.8	585.5	611.4	638.3	666.5	695.9
152.5°	507.4	507.7	517.1	530.2	545.9	566.3	589.4	613.3	636.5	661.9	688.3
155°	524.5	525.7	532.7	544.5	557.4	575.0	594.9	614.9	633.7	654.8	677.1
157.5°	541.2	541.2	547.8	556.9	568.2	582.1	599.0	614.9	630.7	647.5	665.6
160°	551.5	551.5	556.2	564.4	573.8	586.7	600.8	614.9	627.8	641.9	657.1
162.5°	560.9	560.0	563.7	571.0	579.5	589.6	602.7	614.9	625.0	636.2	649.6
165°	571.5	571.5	573.8	579.7	585.5	592.6	603.2	612.6	619.6	627.8	637.2
167.5°	582.1	580.9	582.1	586.5	589.8	595.2	602.9	609.8	614.0	619.4	625.9
170°	586.7	585.5	586.7	590.3	592.6	596.1	602.0	607.8	610.2	613.7	618.4
172.5°	591.4	590.3	590.5	593.1	594.5	597.0	601.1	606.0	606.4	608.0	611.9
175°	596.1	594.9	594.9	596.1	597.3	597.3	599.7	603.2	602.0	602.0	604.3
177.5°	598.2	597.3	596.3	597.3	597.3	597.3	598.2	600.1	598.2	598.2	599.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3



TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6	1340.6
2.5°	1335.7	1337.7	1339.6	1340.5	1340.3	1340.1	1339.9	1339.7
5°	1328.6	1331.2	1333.8	1334.9	1334.4	1334.0	1333.5	1333.0
7.5°	1313.8	1316.0	1318.0	1318.9	1318.7	1318.4	1318.1	1317.8
10°	1301.4	1303.3	1305.3	1306.0	1305.5	1304.9	1304.5	1304.0
12.5°	1286.4	1288.4	1290.5	1291.2	1290.6	1289.9	1289.2	1288.6
15°	1257.5	1258.9	1260.3	1260.7	1260.0	1259.3	1258.6	1257.9
17.5°	1224.7	1225.6	1226.5	1226.7	1226.2	1225.7	1225.3	1224.8
20°	1200.2	1200.9	1201.6	1201.7	1201.2	1200.8	1200.3	1199.8
22.5°	1174.7	1176.0	1177.3	1177.5	1176.6	1175.8	1174.9	1174.1
25°	1132.7	1132.9	1133.2	1132.8	1131.9	1130.8	1129.9	1128.9
27.5°	1085.5	1084.9	1084.3	1083.5	1082.3	1081.1	1079.8	1078.6
30°	1052.9	1052.0	1051.0	1050.0	1048.7	1047.5	1046.3	1045.2
32.5°	1019.9	1018.8	1017.6	1016.4	1015.2	1014.0	1012.8	1011.7
35°	967.8	966.0	964.3	962.9	961.7	960.6	959.4	958.2
37.5°	913.0	911.2	909.5	907.8	906.2	904.6	903.0	901.4
40°	874.9	872.6	870.2	868.4	867.2	866.1	864.8	863.6
42.5°	838.1	835.4	832.5	830.8	830.0	829.2	828.4	827.6
45°	781.0	778.4	775.8	774.2	773.4	772.6	771.9	771.2
47.5°	725.8	722.9	719.8	717.5	715.7	713.9	712.1	710.2
50°	687.2	683.9	680.5	678.1	676.7	675.3	673.9	672.5
52.5°	647.6	644.6	641.7	639.3	637.5	635.7	633.9	632.1
55°	589.4	586.5	583.6	581.5	580.1	578.7	577.1	575.7
57.5°	531.0	528.3	525.5	523.5	522.1	520.7	519.4	518.0
60°	490.9	488.8	486.6	484.9	483.7	482.5	481.3	480.2
62.5°	451.7	449.8	447.9	446.3	445.0	443.8	442.7	441.5
65°	394.9	392.4	390.0	388.3	387.1	385.9	384.7	383.4
67.5°	336.2	333.9	331.5	330.2	329.9	329.6	329.2	328.9
70°	299.1	297.2	295.3	294.0	293.3	292.6	291.9	291.1
72.5°	262.1	260.5	259.0	257.9	257.1	256.4	255.7	255.0
75°	208.6	207.6	206.7	206.1	205.9	205.6	205.4	205.2
77.5°	157.9	157.6	157.4	156.9	156.3	155.7	155.1	154.5
80°	125.8	125.3	124.8	124.5	124.2	124.0	123.8	123.5
82.5°	96.9	96.6	96.3	96.1	95.9	95.6	95.4	95.1
85°	55.8	55.8	55.8	55.7	55.5	55.2	55.0	54.7
87.5°	24.8	25.0	25.3	25.3	25.5	25.8	25.5	25.5
90°	21.1	22.3	23.4	23.4	24.6	25.9	24.6	24.6
92.5°	230.5	173.4	138.0	114.5	100.7	94.3	90.4	90.4
95°	869.5	687.6	530.4	416.6	359.1	322.8	301.5	286.3
97.5°	1284.8	1217.1	1102.4	979.9	895.5	825.0	789.7	765.4
100°	1415.2	1438.7	1381.2	1294.3	1192.2	1120.6	1085.5	1076.1
102.5°	1408.7	1525.0	1541.7	1505.5	1442.9	1391.0	1353.9	1346.5
105°	1314.2	1517.3	1633.5	1681.5	1683.9	1674.6	1658.1	1651.0
107.5°	1180.2	1396.4	1560.0	1664.7	1722.6	1749.4	1761.1	1764.2
110°	1099.5	1302.5	1472.7	1601.7	1685.1	1734.3	1755.5	1766.1



TEST NUMBER: P332624-840

CATALOG NUMBER: SA4XXDIP-C795D1205U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1040.4	1219.9	1380.7	1509.7	1604.4	1664.0	1693.5	1710.7
115°	981.0	1125.4	1262.6	1375.3	1468.0	1538.4	1576.0	1585.4
117.5°	951.9	1071.4	1179.3	1274.9	1353.9	1413.1	1451.1	1458.3
120°	938.8	1047.9	1141.8	1225.1	1292.0	1343.6	1374.1	1387.0
122.5°	927.5	1032.9	1118.3	1191.3	1247.9	1292.0	1317.8	1330.7
125°	908.3	1009.2	1090.1	1154.7	1201.6	1235.7	1258.0	1265.0
127.5°	884.7	981.3	1062.0	1123.3	1170.4	1200.7	1219.5	1226.5
130°	866.1	958.8	1038.5	1100.8	1148.8	1178.1	1196.9	1204.0
132.5°	846.3	933.4	1011.3	1073.5	1120.6	1153.8	1171.5	1178.6
135°	819.1	895.3	966.9	1025.6	1072.6	1105.4	1124.2	1131.3
137.5°	794.5	859.0	919.3	972.3	1016.2	1048.6	1064.1	1072.6
140°	780.3	835.5	888.3	937.6	978.7	1004.5	1020.9	1030.3
142.5°	767.2	815.8	861.1	903.8	940.2	964.1	978.7	985.2
145°	748.7	788.6	823.7	856.7	886.0	905.9	917.7	923.5
147.5°	733.5	765.1	793.2	819.1	840.7	857.8	866.8	868.8
150°	724.1	751.0	774.5	795.6	814.4	829.6	836.7	837.9
152.5°	713.7	736.9	758.5	775.9	791.8	804.3	808.5	809.7
155°	698.2	717.0	734.6	748.7	760.4	769.8	773.4	773.4
157.5°	681.6	697.3	712.1	723.4	732.3	739.3	741.4	741.4
160°	671.3	684.1	697.0	706.4	713.5	720.5	721.6	721.6
162.5°	660.9	672.0	682.1	690.4	695.6	702.7	703.9	702.9
165°	646.6	653.6	661.9	667.7	672.4	677.1	675.9	674.8
167.5°	632.8	638.1	644.7	648.2	650.6	653.6	653.4	652.5
170°	624.3	627.8	632.5	636.0	638.3	639.5	638.3	638.3
172.5°	616.7	619.4	622.2	624.7	626.1	627.3	626.1	624.3
175°	606.7	607.8	610.2	610.2	610.2	612.6	610.2	607.8
177.5°	600.1	601.1	601.1	602.0	601.1	602.0	600.1	598.2
180°	597.3	597.3	597.3	597.3	597.3	597.3	597.3	597.3

(END OF REPORT)