

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332580-840

Luminaire Tested: **SA4XXDIP-C795D365U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332580-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D365U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5054.6 lumens
Efficiency: N/A
Efficacy: 144.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332580-840
CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71	71	71	71	
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60	60	60	60	
2	94	86	80	75	89	82	76	72	74	70	66	66	63	60	59	57	55	51	51	51	51	
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	44	44	44	44	
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41	38	38	38	38	
5	73	61	52	46	68	58	50	45	53	46	42	48	43	39	43	39	36	33	33	33	33	
6	67	55	46	40	63	52	45	39	48	41	37	43	38	34	39	35	32	29	29	29	29	
7	62	50	41	36	59	47	40	35	43	37	32	39	34	30	36	31	28	26	26	26	26	
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23	23	23	23	
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21	21	21	21	
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19	19	19	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10467	10467	10467	10467
5°	12327	10494	9263	10494
10°	14758	10449	8338	10449
15°	17462	10343	7658	10343
20°	19444	10234	7050	10234
25°	19759	10075	6631	10075
30°	16812	9923	6498	9923
35°	12925	9676	6500	9676
40°	10075	9385	6622	9385
45°	8401	8947	6734	8947
50°	7394	8411	6962	8411
55°	6773	7771	7241	7771
60°	6347	7198	7579	7198
65°	5908	6556	7859	6556
70°	5401	5922	8037	5922
75°	4825	5209	7941	5209
80°	4049	4268	7689	4268
85°	2983	3084	7364	3084



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.5
10°-20°	389.3	7.7
20°-30°	617.4	12.2
30°-40°	687.1	13.6
40°-50°	625.4	12.4
50°-60°	511.1	10.1
60°-70°	364.8	7.2
70°-80°	200.9	4.0
80°-90°	56.2	1.1
90°-100°	16.3	0.3
100°-110°	104.1	2.1
110°-120°	199.1	3.9
120°-130°	252.7	5.0
130°-140°	270.4	5.3
140°-150°	252.8	5.0
150°-160°	203.9	4.0
160°-170°	131.5	2.6
170°-180°	45.3	0.9
0°-30°	1133.0	22.4
0°-40°	1820.1	36.0
0°-60°	2956.5	58.5
0°-90°	3578.5	70.8
90°-120°	319.5	6.3
90°-150°	1095.3	21.7
90°-180°	1476.0	29.2
0°-180°	5054.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1297	1297	1297	1297	1297	
5°	1521	1295	1143	1295	1521	155
15°	2089	1238	916	1238	2089	590
25°	2218	1131	744	1131	2218	978
35°	1312	982	660	982	1312	832
45°	736	784	590	784	736	580
55°	481	552	514	552	481	435
65°	309	343	411	343	309	306
75°	155	167	255	167	155	164
85°	32	33	80	33	32	40
90°	11	1	11	1	11	6
95°	10	20	10	20	10	8
105°	102	107	102	107	102	89
115°	202	201	202	201	202	200
125°	284	282	284	282	284	253
135°	352	350	352	350	352	271
145°	406	403	406	403	406	253
155°	442	442	442	442	442	204
165°	464	466	464	466	464	131
175°	474	477	474	477	474	45
180°	477	477	477	477	477	



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1379.9	1379.5	1375.1	1374.3	1371.3	1367.5	1366.5	1359.7	1345.9	1339.5	1337.8
5°	1521.1	1531.8	1517.8	1515.1	1513.5	1495.8	1486.6	1475.9	1451.2	1436.7	1425.4
7.5°	1689.5	1690.7	1684.7	1679.7	1666.1	1650.5	1627.4	1602.7	1573.3	1542.6	1519.5
10°	1800.3	1804.6	1797.7	1796.5	1769.2	1752.0	1717.6	1688.6	1655.3	1618.2	1584.4
12.5°	1917.2	1911.2	1907.6	1884.6	1879.6	1848.3	1808.3	1778.4	1727.1	1684.5	1639.4
15°	2089.3	2077.5	2069.9	2038.2	2022.7	1979.1	1936.7	1904.0	1836.8	1772.9	1724.5
17.5°	2190.2	2202.0	2184.6	2171.6	2131.3	2100.8	2057.5	1988.7	1936.2	1856.8	1795.8
20°	2263.3	2264.3	2254.7	2241.3	2209.6	2170.9	2123.6	2048.4	1985.6	1906.6	1822.9
22.5°	2283.0	2283.3	2279.2	2266.6	2242.6	2211.3	2163.6	2100.8	2024.7	1938.8	1855.1
25°	2218.2	2216.0	2220.9	2234.8	2225.6	2216.0	2188.6	2141.9	2071.0	1980.2	1890.0
27.5°	1977.1	1992.0	2019.2	2053.6	2086.7	2111.9	2119.0	2109.4	2065.5	1990.8	1896.3
30°	1803.5	1821.8	1842.2	1876.5	1943.2	1981.4	2023.2	2054.9	2037.2	1977.5	1889.5
32.5°	1612.8	1617.3	1647.6	1686.7	1747.7	1821.1	1887.4	1951.8	1973.2	1941.9	1868.5
35°	1311.5	1319.1	1351.8	1390.5	1465.2	1554.9	1654.8	1743.9	1817.5	1847.0	1809.5
37.5°	1070.3	1091.9	1115.0	1156.6	1222.3	1303.0	1406.8	1522.2	1631.8	1705.4	1717.8
40°	956.0	969.5	986.1	1017.7	1073.6	1153.2	1242.2	1374.4	1491.0	1596.2	1630.6
42.5°	865.8	873.6	883.8	912.5	955.0	1034.1	1115.5	1231.7	1348.8	1474.6	1532.2
45°	735.8	743.9	761.0	777.7	809.9	864.7	940.4	1036.0	1153.7	1275.1	1381.4
47.5°	642.0	647.1	657.3	675.1	702.5	738.6	800.2	880.1	989.1	1106.9	1220.2
50°	588.7	592.9	601.0	617.1	638.0	670.2	720.7	795.5	880.8	999.6	1110.6
52.5°	546.5	548.3	554.2	565.1	581.8	608.8	650.3	712.1	791.4	897.3	1008.0
55°	481.2	483.4	488.8	496.9	511.3	528.5	560.2	606.3	675.7	767.5	863.6
57.5°	427.5	429.0	433.5	436.7	448.6	462.5	487.0	519.9	572.4	650.3	736.1
60°	393.1	392.0	397.5	400.1	408.2	420.0	438.8	470.5	516.1	579.0	657.9
62.5°	359.6	358.1	362.6	366.2	370.8	380.9	396.3	421.1	458.2	514.9	583.2
65°	309.3	307.2	309.9	314.2	318.5	323.9	335.2	357.2	386.7	427.5	479.6
67.5°	258.8	261.2	261.6	263.7	266.2	273.5	281.2	296.8	317.6	350.3	394.5
70°	228.8	229.3	231.5	231.5	233.1	239.5	246.0	255.1	275.5	305.6	341.5
72.5°	198.7	201.0	200.2	201.9	203.0	207.3	212.1	220.8	238.1	260.4	290.8
75°	154.7	156.3	156.3	156.8	158.4	160.1	163.8	170.3	182.6	199.2	220.3
77.5°	112.8	113.0	113.7	115.7	115.7	118.3	121.1	126.2	132.3	143.7	156.5
80°	87.1	88.1	87.6	88.7	88.7	90.8	91.8	98.3	101.0	108.5	118.7
82.5°	63.8	64.8	64.7	66.2	67.2	67.6	69.1	71.6	74.3	81.0	85.1
85°	32.2	33.3	32.2	33.3	34.9	35.4	37.1	37.6	39.8	41.4	45.1
87.5°	11.6	12.8	12.8	13.2	14.0	14.4	14.7	14.2	15.9	16.2	17.8
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.3	8.8	8.3	7.9	7.2
92.5°	9.9	9.8	9.8	9.8	9.7	9.5	9.0	8.5	8.1	7.6	7.0
95°	10.3	10.3	10.2	10.1	10.0	9.8	9.3	8.8	8.3	7.9	7.8
97.5°	10.0	9.9	9.8	9.8	9.7	9.6	9.6	9.5	9.5	9.4	18.3
100°	10.0	9.9	9.8	9.8	9.7	10.3	11.6	13.0	14.3	15.8	26.7
102.5°	10.3	10.3	10.2	10.2	10.2	17.5	32.0	46.6	61.1	75.6	77.1
105°	101.7	104.5	107.4	110.3	113.1	114.2	113.5	112.8	112.1	111.4	111.0
107.5°	141.8	141.5	141.2	140.9	140.6	140.3	139.9	139.6	139.2	138.9	138.3
110°	159.2	159.0	158.8	158.4	158.2	158.0	157.8	157.7	157.5	157.4	156.9



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.6	176.3	176.0	175.7	175.4	175.2	175.3	175.3	175.3	175.4	175.1
115°	202.0	202.0	202.0	202.0	202.0	202.0	201.8	201.6	201.5	201.3	201.4
117.5°	227.8	227.9	227.9	227.9	227.9	228.0	228.0	228.0	228.1	228.1	227.9
120°	244.1	244.3	244.4	244.6	244.8	244.8	244.6	244.4	244.3	244.1	244.2
122.5°	260.1	260.2	260.4	260.5	260.7	260.7	260.6	260.5	260.4	260.4	260.2
125°	284.1	284.0	284.0	283.9	283.8	283.6	283.4	283.2	282.9	282.7	282.9
127.5°	305.2	305.2	305.3	305.4	305.4	305.5	305.5	305.6	305.6	305.7	305.3
130°	319.4	319.4	319.4	319.4	319.4	319.4	319.3	319.2	319.1	319.1	318.8
132.5°	332.5	332.6	332.6	332.8	332.9	332.9	332.8	332.6	332.5	332.4	332.1
135°	352.2	352.1	351.9	351.7	351.6	351.4	351.3	351.1	351.0	350.8	350.5
137.5°	369.1	369.1	369.2	369.2	369.3	369.2	369.1	368.9	368.7	368.5	368.2
140°	380.8	380.7	380.6	380.6	380.5	380.3	380.1	379.8	379.6	379.4	379.2
142.5°	390.5	390.5	390.5	390.5	390.4	390.3	390.2	390.0	389.8	389.7	389.6
145°	405.5	405.3	405.2	405.0	404.8	404.7	404.7	404.6	404.5	404.3	404.3
147.5°	417.8	417.7	417.6	417.6	417.5	417.4	417.4	417.3	417.2	417.2	417.2
150°	425.8	425.7	425.7	425.6	425.5	425.5	425.5	425.5	425.5	425.5	425.5
152.5°	432.6	432.7	432.7	432.7	432.8	432.8	432.6	432.5	432.4	432.3	432.4
155°	441.8	442.1	442.3	442.5	442.8	442.7	442.4	442.1	441.8	441.5	441.7
157.5°	449.6	450.0	450.4	450.8	451.2	451.2	450.8	450.4	450.0	449.6	449.8
160°	454.6	455.1	455.7	456.2	456.6	456.6	456.2	455.7	455.1	454.6	454.7
162.5°	458.7	459.2	459.8	460.3	460.8	460.9	460.4	459.9	459.5	459.0	459.1
165°	464.3	465.0	465.7	466.5	467.2	467.3	466.6	466.0	465.3	464.6	464.6
167.5°	468.6	469.3	470.1	470.9	471.7	471.7	471.1	470.4	469.7	469.0	469.0
170°	471.1	471.9	472.7	473.5	474.2	474.3	473.7	473.1	472.4	471.8	471.7
172.5°	472.5	473.4	474.2	475.1	475.9	476.1	475.4	474.8	474.1	473.5	473.4
175°	474.3	475.2	476.3	477.2	478.2	478.3	477.6	476.9	476.2	475.3	475.3
177.5°	475.4	476.3	477.0	477.8	478.5	478.7	478.2	477.7	477.2	476.6	476.5
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1338.2	1332.2	1327.9	1324.4	1315.0	1309.4	1305.1	1299.1	1292.2	1285.0	1275.9
5°	1414.1	1395.8	1382.5	1362.0	1342.7	1326.6	1310.0	1294.9	1276.7	1256.8	1242.2
7.5°	1494.0	1466.8	1432.0	1401.8	1367.9	1338.3	1311.9	1284.9	1256.7	1229.4	1204.4
10°	1544.7	1509.7	1471.1	1425.4	1382.5	1344.3	1308.9	1274.6	1241.2	1207.9	1179.4
12.5°	1599.2	1555.7	1498.5	1445.2	1397.0	1346.0	1303.3	1261.2	1221.0	1186.0	1152.8
15°	1672.4	1609.6	1543.6	1472.2	1408.8	1349.2	1290.6	1237.5	1192.3	1146.1	1113.9
17.5°	1717.5	1639.7	1564.2	1489.6	1412.9	1337.7	1274.6	1213.2	1156.7	1110.8	1070.2
20°	1747.2	1669.8	1575.8	1501.2	1409.9	1332.5	1259.5	1191.2	1132.2	1083.3	1041.4
22.5°	1772.9	1683.5	1589.5	1491.3	1400.4	1318.4	1238.4	1169.7	1109.4	1057.9	1017.7
25°	1786.9	1684.3	1582.3	1484.5	1381.4	1284.1	1211.6	1131.1	1066.6	1012.4	969.5
27.5°	1788.4	1678.7	1563.3	1454.6	1348.2	1257.7	1166.1	1094.2	1027.2	969.9	928.6
30°	1783.6	1669.3	1545.2	1427.5	1320.7	1222.4	1143.0	1064.5	996.3	939.4	896.4
32.5°	1768.6	1649.5	1522.0	1397.5	1286.8	1190.6	1108.5	1034.0	967.6	911.4	866.4
35°	1725.2	1607.5	1471.6	1342.2	1228.8	1131.7	1057.5	981.8	915.2	862.0	818.5
37.5°	1657.1	1550.7	1412.6	1278.7	1167.4	1069.8	996.3	927.9	867.8	813.7	769.2
40°	1597.8	1504.4	1365.8	1235.3	1115.0	1022.1	953.3	890.5	830.9	779.8	737.4
42.5°	1529.5	1448.0	1320.3	1182.0	1066.0	972.7	905.6	849.2	793.0	745.9	703.5
45°	1407.7	1354.0	1233.7	1105.9	985.0	897.0	833.0	783.7	736.4	690.1	654.7
47.5°	1267.6	1241.0	1139.7	1018.3	903.6	816.8	761.3	715.7	674.3	635.2	603.9
50°	1173.6	1160.6	1073.1	956.0	846.5	764.8	708.9	669.7	634.3	600.0	570.4
52.5°	1080.8	1080.3	1001.4	894.1	792.7	714.1	658.6	622.1	591.4	563.4	536.8
55°	938.9	953.8	892.1	796.5	705.7	634.8	584.9	552.1	530.7	507.6	487.7
57.5°	808.5	833.4	782.5	698.3	622.6	557.2	513.8	489.2	466.3	452.3	437.9
60°	723.5	747.1	707.3	636.4	565.0	509.2	467.8	445.8	425.9	416.3	406.1
62.5°	647.8	668.9	639.4	573.7	511.7	458.1	423.1	401.9	388.5	378.0	371.2
65°	539.8	557.4	532.3	484.4	431.3	388.3	359.8	343.2	330.3	326.0	318.5
67.5°	436.4	452.4	438.8	398.2	355.6	323.0	300.7	284.8	277.1	273.4	268.0
70°	374.9	391.0	376.5	341.0	308.3	280.9	259.9	250.9	242.8	241.2	233.6
72.5°	322.9	333.9	319.3	291.6	263.6	240.5	224.3	214.7	210.6	207.6	203.6
75°	242.3	251.9	242.3	220.8	200.9	184.8	170.8	167.0	162.2	160.6	157.9
77.5°	171.5	179.9	172.4	159.0	144.1	131.7	124.2	119.4	118.3	115.4	116.7
80°	131.1	136.4	129.5	120.3	108.5	99.9	94.5	91.8	88.7	87.6	89.7
82.5°	94.1	96.4	92.9	86.7	78.0	72.4	68.8	65.6	65.0	65.2	65.2
85°	48.9	48.4	47.8	42.4	39.8	36.0	33.8	33.3	32.7	33.8	34.9
87.5°	17.7	18.0	17.4	15.6	14.0	12.6	12.0	11.4	12.0	12.6	13.2
90°	6.6	6.0	5.4	4.5	3.7	2.8	1.9	1.1	1.9	2.8	3.7
92.5°	6.3	5.7	5.0	4.6	4.6	4.5	4.5	4.5	4.5	4.5	4.6
95°	7.7	7.6	7.6	8.9	11.5	14.2	17.0	19.6	17.0	14.2	11.5
97.5°	27.2	36.0	44.8	48.4	46.8	45.0	43.3	41.7	43.3	45.0	46.8
100°	37.6	48.6	59.5	64.2	62.8	61.4	60.0	58.6	60.0	61.4	62.8
102.5°	78.6	80.0	81.4	81.6	80.5	79.5	78.5	77.4	78.5	79.5	80.5
105°	110.6	110.2	109.8	109.4	108.9	108.4	107.9	107.4	107.9	108.4	108.9
107.5°	137.7	137.2	136.6	136.3	136.0	135.8	135.5	135.3	135.5	135.8	136.0
110°	156.4	155.9	155.5	155.1	154.9	154.6	154.4	154.2	154.4	154.6	154.9



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.9	174.7	174.5	174.2	173.7	173.3	172.9	172.5	172.9	173.3	173.7
115°	201.5	201.6	201.6	201.6	201.3	201.1	200.9	200.6	200.9	201.1	201.3
117.5°	227.8	227.6	227.4	227.2	226.9	226.5	226.2	225.9	226.2	226.5	226.9
120°	244.3	244.4	244.4	244.3	244.0	243.7	243.4	243.1	243.4	243.7	244.0
122.5°	260.1	260.0	259.9	259.8	259.6	259.4	259.2	259.0	259.2	259.4	259.6
125°	283.0	283.2	283.3	283.3	282.9	282.6	282.3	282.0	282.3	282.6	282.9
127.5°	304.9	304.6	304.2	304.0	303.9	303.8	303.8	303.7	303.8	303.8	303.9
130°	318.6	318.3	318.1	318.0	317.9	317.8	317.7	317.6	317.7	317.8	317.9
132.5°	331.8	331.5	331.2	331.0	330.9	330.7	330.6	330.5	330.6	330.7	330.9
135°	350.2	349.9	349.5	349.4	349.5	349.6	349.7	349.7	349.7	349.6	349.5
137.5°	367.8	367.5	367.2	367.0	366.9	366.9	366.9	366.8	366.9	366.9	366.9
140°	379.1	378.9	378.7	378.6	378.4	378.3	378.1	378.0	378.1	378.3	378.4
142.5°	389.5	389.4	389.3	389.1	388.8	388.5	388.2	388.0	388.2	388.5	388.8
145°	404.3	404.3	404.3	404.2	404.0	403.7	403.5	403.3	403.5	403.7	404.0
147.5°	417.3	417.4	417.5	417.3	416.9	416.4	416.0	415.5	416.0	416.4	416.9
150°	425.6	425.7	425.8	425.7	425.4	425.0	424.6	424.3	424.6	425.0	425.4
152.5°	432.5	432.7	432.8	432.8	432.5	432.3	432.0	431.8	432.0	432.3	432.5
155°	441.9	442.2	442.4	442.5	442.4	442.3	442.3	442.2	442.3	442.3	442.4
157.5°	450.1	450.4	450.6	450.8	450.8	450.9	450.9	451.0	450.9	450.9	450.8
160°	454.8	454.9	455.0	455.1	455.4	455.7	455.9	456.2	455.9	455.7	455.4
162.5°	459.1	459.2	459.3	459.5	459.8	460.1	460.4	460.7	460.4	460.1	459.8
165°	464.6	464.6	464.6	464.8	465.2	465.6	466.1	466.5	466.1	465.6	465.2
167.5°	469.1	469.1	469.2	469.4	469.8	470.2	470.6	471.0	470.6	470.2	469.8
170°	471.7	471.6	471.5	471.7	472.2	472.6	473.1	473.6	473.1	472.6	472.2
172.5°	473.4	473.3	473.2	473.4	473.9	474.3	474.8	475.3	474.8	474.3	473.9
175°	475.2	475.1	475.0	475.2	475.7	476.3	476.7	477.2	476.7	476.3	475.7
177.5°	476.4	476.3	476.1	476.3	476.7	477.2	477.6	478.1	477.6	477.2	476.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1271.6	1267.8	1262.1	1254.5	1248.0	1241.1	1239.4	1236.8	1241.9	1237.7	1236.4
5°	1229.9	1218.6	1204.2	1187.5	1177.8	1163.9	1161.1	1155.8	1150.4	1149.9	1144.5
7.5°	1185.8	1169.2	1150.2	1133.3	1117.5	1102.3	1092.4	1090.1	1082.3	1077.6	1072.3
10°	1157.4	1137.0	1115.0	1098.8	1080.7	1064.5	1053.2	1046.8	1041.4	1035.5	1030.2
12.5°	1123.9	1102.2	1084.1	1066.6	1044.9	1032.7	1014.1	1003.0	1001.9	1002.0	988.1
15°	1084.9	1063.4	1035.5	1010.8	999.0	975.3	965.1	952.2	944.2	936.1	929.7
17.5°	1040.4	1013.6	991.8	963.4	940.9	922.1	908.7	900.9	888.8	877.4	869.1
20°	1012.4	983.9	960.9	930.8	906.1	882.9	871.7	860.9	851.8	842.1	833.0
22.5°	984.0	954.3	926.0	896.9	873.8	849.5	838.6	823.9	815.3	809.9	800.8
25°	939.4	907.2	874.9	847.0	823.3	801.8	787.4	776.1	766.4	762.1	756.2
27.5°	890.8	858.8	827.7	796.0	769.1	753.6	741.9	733.5	727.8	722.2	719.5
30°	859.9	826.6	793.2	763.8	739.0	723.5	712.7	706.8	702.5	699.8	697.1
32.5°	828.5	795.7	760.6	733.7	711.6	697.7	689.5	683.6	681.5	680.4	679.5
35°	778.2	745.0	712.7	688.5	667.6	662.3	655.2	652.1	651.0	654.7	656.3
37.5°	729.5	698.6	669.0	645.6	631.9	624.0	621.6	621.8	625.6	628.9	632.8
40°	698.2	668.1	640.3	619.8	606.9	602.1	601.0	603.7	607.9	611.8	616.0
42.5°	667.7	638.0	612.7	593.6	584.6	580.2	580.8	583.5	589.5	594.1	600.6
45°	620.4	595.6	570.9	555.3	547.9	548.9	548.9	553.7	559.7	566.6	573.6
47.5°	575.7	550.9	530.5	517.5	513.5	512.6	515.6	521.9	530.4	539.1	548.8
50°	545.6	522.0	504.3	492.5	488.2	489.8	494.1	500.0	510.2	521.0	531.2
52.5°	515.1	493.7	477.3	466.3	463.3	466.2	470.5	479.8	488.8	500.4	512.7
55°	467.8	449.5	436.7	428.6	427.5	429.1	433.9	444.1	457.1	471.6	483.4
57.5°	420.6	405.4	393.5	388.0	388.5	390.0	398.0	410.1	423.8	439.3	454.5
60°	388.9	374.9	365.3	360.9	361.4	364.7	374.4	385.7	402.8	417.9	433.9
62.5°	358.8	346.5	337.3	333.5	332.6	339.7	349.0	360.7	377.9	394.7	412.0
65°	310.4	300.7	293.3	291.1	292.8	298.1	309.9	325.5	340.0	357.7	376.0
67.5°	263.2	255.2	250.0	251.1	253.0	260.9	270.8	284.2	300.6	319.0	337.1
70°	233.1	225.6	221.3	221.8	225.0	234.7	243.3	256.7	274.5	293.3	308.3
72.5°	202.2	197.2	193.4	195.6	198.8	205.5	216.2	229.6	245.2	262.8	278.6
75°	155.2	155.2	153.1	154.7	159.6	165.9	174.0	187.9	203.6	217.5	230.5
77.5°	115.1	114.0	115.3	117.3	120.1	127.7	136.9	146.9	158.6	172.6	183.3
80°	88.1	88.7	91.3	94.5	95.6	101.5	111.2	120.3	129.5	141.3	151.5
82.5°	66.1	66.8	68.1	72.2	73.2	79.6	85.8	94.9	103.2	111.2	119.7
85°	36.0	36.0	38.7	40.3	42.9	47.3	51.0	56.4	63.9	69.3	77.4
87.5°	14.6	14.8	16.7	17.7	19.1	21.3	22.3	27.1	28.9	31.2	35.1
90°	4.5	5.4	6.0	6.6	7.2	7.9	8.3	8.8	9.3	9.8	10.1
92.5°	4.6	5.0	5.7	6.3	7.0	7.6	8.1	8.5	9.0	9.5	9.7
95°	8.9	7.6	7.6	7.7	7.8	7.9	8.3	8.8	9.3	9.8	10.0
97.5°	48.4	44.8	36.0	27.2	18.3	9.4	9.5	9.5	9.6	9.6	9.7
100°	64.2	59.5	48.6	37.6	26.7	15.8	14.3	13.0	11.6	10.3	9.7
102.5°	81.6	81.4	80.0	78.6	77.1	75.6	61.1	46.6	32.0	17.5	10.2
105°	109.4	109.8	110.2	110.6	111.0	111.4	112.1	112.8	113.5	114.2	113.1
107.5°	136.3	136.6	137.2	137.7	138.3	138.9	139.2	139.6	139.9	140.3	140.6
110°	155.1	155.5	155.9	156.4	156.9	157.4	157.5	157.7	157.8	158.0	158.2



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.2	174.5	174.7	174.9	175.1	175.4	175.3	175.3	175.3	175.2	175.4
115°	201.6	201.6	201.6	201.5	201.4	201.3	201.5	201.6	201.8	202.0	202.0
117.5°	227.2	227.4	227.6	227.8	227.9	228.1	228.1	228.0	228.0	228.0	227.9
120°	244.3	244.4	244.4	244.3	244.2	244.1	244.3	244.4	244.6	244.8	244.8
122.5°	259.8	259.9	260.0	260.1	260.2	260.4	260.4	260.5	260.6	260.7	260.7
125°	283.3	283.3	283.2	283.0	282.9	282.7	282.9	283.2	283.4	283.6	283.8
127.5°	304.0	304.2	304.6	304.9	305.3	305.7	305.6	305.6	305.5	305.5	305.4
130°	318.0	318.1	318.3	318.6	318.8	319.1	319.1	319.2	319.3	319.4	319.4
132.5°	331.0	331.2	331.5	331.8	332.1	332.4	332.5	332.6	332.8	332.9	332.9
135°	349.4	349.5	349.9	350.2	350.5	350.8	351.0	351.1	351.3	351.4	351.6
137.5°	367.0	367.2	367.5	367.8	368.2	368.5	368.7	368.9	369.1	369.2	369.3
140°	378.6	378.7	378.9	379.1	379.2	379.4	379.6	379.8	380.1	380.3	380.5
142.5°	389.1	389.3	389.4	389.5	389.6	389.7	389.8	390.0	390.2	390.3	390.4
145°	404.2	404.3	404.3	404.3	404.3	404.3	404.5	404.6	404.7	404.7	404.8
147.5°	417.3	417.5	417.4	417.3	417.2	417.2	417.2	417.3	417.4	417.4	417.5
150°	425.7	425.8	425.7	425.6	425.5	425.5	425.5	425.5	425.5	425.5	425.5
152.5°	432.8	432.8	432.7	432.5	432.4	432.3	432.4	432.5	432.6	432.8	432.8
155°	442.5	442.4	442.2	441.9	441.7	441.5	441.8	442.1	442.4	442.7	442.8
157.5°	450.8	450.6	450.4	450.1	449.8	449.6	450.0	450.4	450.8	451.2	451.2
160°	455.1	455.0	454.9	454.8	454.7	454.6	455.1	455.7	456.2	456.6	456.6
162.5°	459.5	459.3	459.2	459.1	459.1	459.0	459.5	459.9	460.4	460.9	460.8
165°	464.8	464.6	464.6	464.6	464.6	464.6	465.3	466.0	466.6	467.3	467.2
167.5°	469.4	469.2	469.1	469.1	469.0	469.0	469.7	470.4	471.1	471.7	471.7
170°	471.7	471.5	471.6	471.7	471.7	471.8	472.4	473.1	473.7	474.3	474.2
172.5°	473.4	473.2	473.3	473.4	473.4	473.5	474.1	474.8	475.4	476.1	475.9
175°	475.2	475.0	475.1	475.2	475.3	475.3	476.2	476.9	477.6	478.3	478.2
177.5°	476.3	476.1	476.3	476.4	476.5	476.6	477.2	477.7	478.2	478.7	478.5
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840
 CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1235.5	1234.7	1231.6	1231.2	1231.6	1234.7	1235.5	1236.4	1237.7	1241.9	1236.8
5°	1141.3	1138.6	1137.0	1143.0	1137.0	1138.6	1141.3	1144.5	1149.9	1150.4	1155.8
7.5°	1070.3	1068.1	1063.4	1062.0	1063.4	1068.1	1070.3	1072.3	1077.6	1082.3	1090.1
10°	1024.7	1022.6	1018.3	1017.2	1018.3	1022.6	1024.7	1030.2	1035.5	1041.4	1046.8
12.5°	980.9	976.6	975.7	976.8	975.7	976.6	980.9	988.1	1002.0	1001.9	1003.0
15°	922.7	920.6	914.6	916.3	914.6	920.6	922.7	929.7	936.1	944.2	952.2
17.5°	865.4	862.7	855.6	861.9	855.6	862.7	865.4	869.1	877.4	888.8	900.9
20°	829.3	825.0	821.2	820.6	821.2	825.0	829.3	833.0	842.1	851.8	860.9
22.5°	794.9	791.0	790.7	787.2	790.7	791.0	794.9	800.8	809.9	815.3	823.9
25°	751.9	748.2	747.1	744.4	747.1	748.2	751.9	756.2	762.1	766.4	776.1
27.5°	718.9	717.1	715.2	716.0	715.2	717.1	718.9	719.5	722.2	727.8	733.5
30°	698.7	698.2	697.1	697.1	697.1	698.2	698.7	697.1	699.8	702.5	706.8
32.5°	682.0	681.9	682.6	682.6	682.6	681.9	682.0	679.5	680.4	681.5	683.6
35°	658.4	660.0	661.2	659.5	661.2	660.0	658.4	656.3	654.7	651.0	652.1
37.5°	637.2	638.8	640.4	642.2	640.4	638.8	637.2	632.8	628.9	625.6	621.8
40°	620.9	624.6	625.7	628.4	625.7	624.6	620.9	616.0	611.8	607.9	603.7
42.5°	605.4	609.6	612.4	612.9	612.4	609.6	605.4	600.6	594.1	589.5	583.5
45°	581.7	585.9	589.8	589.8	589.8	585.9	581.7	573.6	566.6	559.7	553.7
47.5°	557.0	563.3	567.0	568.0	567.0	563.3	557.0	548.8	539.1	530.4	521.9
50°	540.3	547.9	551.6	554.3	551.6	547.9	540.3	531.2	521.0	510.2	500.0
52.5°	524.0	531.5	536.5	538.0	536.5	531.5	524.0	512.7	500.4	488.8	479.8
55°	495.7	506.4	512.4	514.5	512.4	506.4	495.7	483.4	471.6	457.1	444.1
57.5°	469.1	479.0	485.8	487.5	485.8	479.0	469.1	454.5	439.3	423.8	410.1
60°	448.5	459.2	467.8	469.4	467.8	459.2	448.5	433.9	417.9	402.8	385.7
62.5°	427.4	438.6	446.4	450.5	446.4	438.6	427.4	412.0	394.7	377.9	360.7
65°	391.0	402.2	409.8	411.4	409.8	402.2	391.0	376.0	357.7	340.0	325.5
67.5°	351.2	362.5	367.5	370.6	367.5	362.5	351.2	337.1	319.0	300.6	284.2
70°	323.4	332.4	337.8	340.5	337.8	332.4	323.4	308.3	293.3	274.5	256.7
72.5°	291.5	301.0	307.3	307.8	307.3	301.0	291.5	278.6	262.8	245.2	229.6
75°	242.8	251.4	254.6	254.6	254.6	251.4	242.8	230.5	217.5	203.6	187.9
77.5°	192.2	196.6	200.7	201.5	200.7	196.6	192.2	183.3	172.6	158.6	146.9
80°	159.6	162.2	165.4	165.4	165.4	162.2	159.6	151.5	141.3	129.5	120.3
82.5°	126.0	128.3	131.5	131.1	131.5	128.3	126.0	119.7	111.2	103.2	94.9
85°	76.2	81.1	80.6	79.5	80.6	81.1	76.2	77.4	69.3	63.9	56.4
87.5°	36.5	36.9	38.2	39.1	38.2	36.9	36.5	35.1	31.2	28.9	27.1
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.3	8.8
92.5°	9.8	9.8	9.8	9.9	9.8	9.8	9.8	9.7	9.5	9.0	8.5
95°	10.1	10.2	10.3	10.3	10.3	10.2	10.1	10.0	9.8	9.3	8.8
97.5°	9.8	9.8	9.9	10.0	9.9	9.8	9.8	9.7	9.6	9.6	9.5
100°	9.8	9.8	9.9	10.0	9.9	9.8	9.8	9.7	10.3	11.6	13.0
102.5°	10.2	10.2	10.3	10.3	10.3	10.2	10.2	10.2	17.5	32.0	46.6
105°	110.3	107.4	104.5	101.7	104.5	107.4	110.3	113.1	114.2	113.5	112.8
107.5°	140.9	141.2	141.5	141.8	141.5	141.2	140.9	140.6	140.3	139.9	139.6
110°	158.4	158.8	159.0	159.2	159.0	158.8	158.4	158.2	158.0	157.8	157.7



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.7	176.0	176.3	176.6	176.3	176.0	175.7	175.4	175.2	175.3	175.3
115°	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	202.0	201.8	201.6
117.5°	227.9	227.9	227.9	227.8	227.9	227.9	227.9	227.9	228.0	228.0	228.0
120°	244.6	244.4	244.3	244.1	244.3	244.4	244.6	244.8	244.8	244.6	244.4
122.5°	260.5	260.4	260.2	260.1	260.2	260.4	260.5	260.7	260.7	260.6	260.5
125°	283.9	284.0	284.0	284.1	284.0	284.0	283.9	283.8	283.6	283.4	283.2
127.5°	305.4	305.3	305.2	305.2	305.2	305.3	305.4	305.4	305.5	305.5	305.6
130°	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.4	319.3	319.2
132.5°	332.8	332.6	332.6	332.5	332.6	332.6	332.8	332.9	332.9	332.8	332.6
135°	351.7	351.9	352.1	352.2	352.1	351.9	351.7	351.6	351.4	351.3	351.1
137.5°	369.2	369.2	369.1	369.1	369.1	369.2	369.2	369.3	369.2	369.1	368.9
140°	380.6	380.6	380.7	380.8	380.7	380.6	380.6	380.5	380.3	380.1	379.8
142.5°	390.5	390.5	390.5	390.5	390.5	390.5	390.5	390.4	390.3	390.2	390.0
145°	405.0	405.2	405.3	405.5	405.3	405.2	405.0	404.8	404.7	404.7	404.6
147.5°	417.6	417.6	417.7	417.8	417.7	417.6	417.6	417.5	417.4	417.4	417.3
150°	425.6	425.7	425.7	425.8	425.7	425.7	425.6	425.5	425.5	425.5	425.5
152.5°	432.7	432.7	432.7	432.6	432.7	432.7	432.7	432.8	432.8	432.6	432.5
155°	442.5	442.3	442.1	441.8	442.1	442.3	442.5	442.8	442.7	442.4	442.1
157.5°	450.8	450.4	450.0	449.6	450.0	450.4	450.8	451.2	451.2	450.8	450.4
160°	456.2	455.7	455.1	454.6	455.1	455.7	456.2	456.6	456.6	456.2	455.7
162.5°	460.3	459.8	459.2	458.7	459.2	459.8	460.3	460.8	460.9	460.4	459.9
165°	466.5	465.7	465.0	464.3	465.0	465.7	466.5	467.2	467.3	466.6	466.0
167.5°	470.9	470.1	469.3	468.6	469.3	470.1	470.9	471.7	471.7	471.1	470.4
170°	473.5	472.7	471.9	471.1	471.9	472.7	473.5	474.2	474.3	473.7	473.1
172.5°	475.1	474.2	473.4	472.5	473.4	474.2	475.1	475.9	476.1	475.4	474.8
175°	477.2	476.3	475.2	474.3	475.2	476.3	477.2	478.2	478.3	477.6	476.9
177.5°	477.8	477.0	476.3	475.4	476.3	477.0	477.8	478.5	478.7	478.2	477.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840
 CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1239.4	1241.1	1248.0	1254.5	1262.1	1267.8	1271.6	1275.9	1285.0	1292.2	1299.1
5°	1161.1	1163.9	1177.8	1187.5	1204.2	1218.6	1229.9	1242.2	1256.8	1276.7	1294.9
7.5°	1092.4	1102.3	1117.5	1133.3	1150.2	1169.2	1185.8	1204.4	1229.4	1256.7	1284.9
10°	1053.2	1064.5	1080.7	1098.8	1115.0	1137.0	1157.4	1179.4	1207.9	1241.2	1274.6
12.5°	1014.1	1032.7	1044.9	1066.6	1084.1	1102.2	1123.9	1152.8	1186.0	1221.0	1261.2
15°	965.1	975.3	999.0	1010.8	1035.5	1063.4	1084.9	1113.9	1146.1	1192.3	1237.5
17.5°	908.7	922.1	940.9	963.4	991.8	1013.6	1040.4	1070.2	1110.8	1156.7	1213.2
20°	871.7	882.9	906.1	930.8	960.9	983.9	1012.4	1041.4	1083.3	1132.2	1191.2
22.5°	838.6	849.5	873.8	896.9	926.0	954.3	984.0	1017.7	1057.9	1109.4	1169.7
25°	787.4	801.8	823.3	847.0	874.9	907.2	939.4	969.5	1012.4	1066.6	1131.1
27.5°	741.9	753.6	769.1	796.0	827.7	858.8	890.8	928.6	969.9	1027.2	1094.2
30°	712.7	723.5	739.0	763.8	793.2	826.6	859.9	896.4	939.4	996.3	1064.5
32.5°	689.5	697.7	711.6	733.7	760.6	795.7	828.5	866.4	911.4	967.6	1034.0
35°	655.2	662.3	667.6	688.5	712.7	745.0	778.2	818.5	862.0	915.2	981.8
37.5°	621.6	624.0	631.9	645.6	669.0	698.6	729.5	769.2	813.7	867.8	927.9
40°	601.0	602.1	606.9	619.8	640.3	668.1	698.2	737.4	779.8	830.9	890.5
42.5°	580.8	580.2	584.6	593.6	612.7	638.0	667.7	703.5	745.9	793.0	849.2
45°	548.9	548.9	547.9	555.3	570.9	595.6	620.4	654.7	690.1	736.4	783.7
47.5°	515.6	512.6	513.5	517.5	530.5	550.9	575.7	603.9	635.2	674.3	715.7
50°	494.1	489.8	488.2	492.5	504.3	522.0	545.6	570.4	600.0	634.3	669.7
52.5°	470.5	466.2	463.3	466.3	477.3	493.7	515.1	536.8	563.4	591.4	622.1
55°	433.9	429.1	427.5	428.6	436.7	449.5	467.8	487.7	507.6	530.7	552.1
57.5°	398.0	390.0	388.5	388.0	393.5	405.4	420.6	437.9	452.3	466.3	489.2
60°	374.4	364.7	361.4	360.9	365.3	374.9	388.9	406.1	416.3	425.9	445.8
62.5°	349.0	339.7	332.6	333.5	337.3	346.5	358.8	371.2	378.0	388.5	401.9
65°	309.9	298.1	292.8	291.1	293.3	300.7	310.4	318.5	326.0	330.3	343.2
67.5°	270.8	260.9	253.0	251.1	250.0	255.2	263.2	268.0	273.4	277.1	284.8
70°	243.3	234.7	225.0	221.8	221.3	225.6	233.1	233.6	241.2	242.8	250.9
72.5°	216.2	205.5	198.8	195.6	193.4	197.2	202.2	203.6	207.6	210.6	214.7
75°	174.0	165.9	159.6	154.7	153.1	155.2	155.2	157.9	160.6	162.2	167.0
77.5°	136.9	127.7	120.1	117.3	115.3	114.0	115.1	116.7	115.4	118.3	119.4
80°	111.2	101.5	95.6	94.5	91.3	88.7	88.1	89.7	87.6	88.7	91.8
82.5°	85.8	79.6	73.2	72.2	68.1	66.8	66.1	65.2	65.2	65.0	65.6
85°	51.0	47.3	42.9	40.3	38.7	36.0	36.0	34.9	33.8	32.7	33.3
87.5°	22.3	21.3	19.1	17.7	16.7	14.8	14.6	13.2	12.6	12.0	11.4
90°	8.3	7.9	7.2	6.6	6.0	5.4	4.5	3.7	2.8	1.9	1.1
92.5°	8.1	7.6	7.0	6.3	5.7	5.0	4.6	4.6	4.5	4.5	4.5
95°	8.3	7.9	7.8	7.7	7.6	7.6	8.9	11.5	14.2	17.0	19.6
97.5°	9.5	9.4	18.3	27.2	36.0	44.8	48.4	46.8	45.0	43.3	41.7
100°	14.3	15.8	26.7	37.6	48.6	59.5	64.2	62.8	61.4	60.0	58.6
102.5°	61.1	75.6	77.1	78.6	80.0	81.4	81.6	80.5	79.5	78.5	77.4
105°	112.1	111.4	111.0	110.6	110.2	109.8	109.4	108.9	108.4	107.9	107.4
107.5°	139.2	138.9	138.3	137.7	137.2	136.6	136.3	136.0	135.8	135.5	135.3
110°	157.5	157.4	156.9	156.4	155.9	155.5	155.1	154.9	154.6	154.4	154.2



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	175.3	175.4	175.1	174.9	174.7	174.5	174.2	173.7	173.3	172.9	172.5
115°	201.5	201.3	201.4	201.5	201.6	201.6	201.6	201.3	201.1	200.9	200.6
117.5°	228.1	228.1	227.9	227.8	227.6	227.4	227.2	226.9	226.5	226.2	225.9
120°	244.3	244.1	244.2	244.3	244.4	244.4	244.3	244.0	243.7	243.4	243.1
122.5°	260.4	260.4	260.2	260.1	260.0	259.9	259.8	259.6	259.4	259.2	259.0
125°	282.9	282.7	282.9	283.0	283.2	283.3	283.3	282.9	282.6	282.3	282.0
127.5°	305.6	305.7	305.3	304.9	304.6	304.2	304.0	303.9	303.8	303.8	303.7
130°	319.1	319.1	318.8	318.6	318.3	318.1	318.0	317.9	317.8	317.7	317.6
132.5°	332.5	332.4	332.1	331.8	331.5	331.2	331.0	330.9	330.7	330.6	330.5
135°	351.0	350.8	350.5	350.2	349.9	349.5	349.4	349.5	349.6	349.7	349.7
137.5°	368.7	368.5	368.2	367.8	367.5	367.2	367.0	366.9	366.9	366.9	366.8
140°	379.6	379.4	379.2	379.1	378.9	378.7	378.6	378.4	378.3	378.1	378.0
142.5°	389.8	389.7	389.6	389.5	389.4	389.3	389.1	388.8	388.5	388.2	388.0
145°	404.5	404.3	404.3	404.3	404.3	404.3	404.2	404.0	403.7	403.5	403.3
147.5°	417.2	417.2	417.2	417.3	417.4	417.5	417.3	416.9	416.4	416.0	415.5
150°	425.5	425.5	425.5	425.6	425.7	425.8	425.7	425.4	425.0	424.6	424.3
152.5°	432.4	432.3	432.4	432.5	432.7	432.8	432.8	432.5	432.3	432.0	431.8
155°	441.8	441.5	441.7	441.9	442.2	442.4	442.5	442.4	442.3	442.3	442.2
157.5°	450.0	449.6	449.8	450.1	450.4	450.6	450.8	450.8	450.9	450.9	451.0
160°	455.1	454.6	454.7	454.8	454.9	455.0	455.1	455.4	455.7	455.9	456.2
162.5°	459.5	459.0	459.1	459.1	459.2	459.3	459.5	459.8	460.1	460.4	460.7
165°	465.3	464.6	464.6	464.6	464.6	464.6	464.8	465.2	465.6	466.1	466.5
167.5°	469.7	469.0	469.0	469.1	469.1	469.2	469.4	469.8	470.2	470.6	471.0
170°	472.4	471.8	471.7	471.7	471.6	471.5	471.7	472.2	472.6	473.1	473.6
172.5°	474.1	473.5	473.4	473.4	473.3	473.2	473.4	473.9	474.3	474.8	475.3
175°	476.2	475.3	475.3	475.2	475.1	475.0	475.2	475.7	476.3	476.7	477.2
177.5°	477.2	476.6	476.5	476.4	476.3	476.1	476.3	476.7	477.2	477.6	478.1
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840
 CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1305.1	1309.4	1315.0	1324.4	1327.9	1332.2	1338.2	1337.8	1339.5	1345.9	1359.7
5°	1310.0	1326.6	1342.7	1362.0	1382.5	1395.8	1414.1	1425.4	1436.7	1451.2	1475.9
7.5°	1311.9	1338.3	1367.9	1401.8	1432.0	1466.8	1494.0	1519.5	1542.6	1573.3	1602.7
10°	1308.9	1344.3	1382.5	1425.4	1471.1	1509.7	1544.7	1584.4	1618.2	1655.3	1688.6
12.5°	1303.3	1346.0	1397.0	1445.2	1498.5	1555.7	1599.2	1639.4	1684.5	1727.1	1778.4
15°	1290.6	1349.2	1408.8	1472.2	1543.6	1609.6	1672.4	1724.5	1772.9	1836.8	1904.0
17.5°	1274.6	1337.7	1412.9	1489.6	1564.2	1639.7	1717.5	1795.8	1856.8	1936.2	1988.7
20°	1259.5	1332.5	1409.9	1501.2	1575.8	1669.8	1747.2	1822.9	1906.6	1985.6	2048.4
22.5°	1238.4	1318.4	1400.4	1491.3	1589.5	1683.5	1772.9	1855.1	1938.8	2024.7	2100.8
25°	1211.6	1284.1	1381.4	1484.5	1582.3	1684.3	1786.9	1890.0	1980.2	2071.0	2141.9
27.5°	1166.1	1257.7	1348.2	1454.6	1563.3	1678.7	1788.4	1896.3	1990.8	2065.5	2109.4
30°	1143.0	1222.4	1320.7	1427.5	1545.2	1669.3	1783.6	1889.5	1977.5	2037.2	2054.9
32.5°	1108.5	1190.6	1286.8	1397.5	1522.0	1649.5	1768.6	1868.5	1941.9	1973.2	1951.8
35°	1057.5	1131.7	1228.8	1342.2	1471.6	1607.5	1725.2	1809.5	1847.0	1817.5	1743.9
37.5°	996.3	1069.8	1167.4	1278.7	1412.6	1550.7	1657.1	1717.8	1705.4	1631.8	1522.2
40°	953.3	1022.1	1115.0	1235.3	1365.8	1504.4	1597.8	1630.6	1596.2	1491.0	1374.4
42.5°	905.6	972.7	1066.0	1182.0	1320.3	1448.0	1529.5	1532.2	1474.6	1348.8	1231.7
45°	833.0	897.0	985.0	1105.9	1233.7	1354.0	1407.7	1381.4	1275.1	1153.7	1036.0
47.5°	761.3	816.8	903.6	1018.3	1139.7	1241.0	1267.6	1220.2	1106.9	989.1	880.1
50°	708.9	764.8	846.5	956.0	1073.1	1160.6	1173.6	1110.6	999.6	880.8	795.5
52.5°	658.6	714.1	792.7	894.1	1001.4	1080.3	1080.8	1008.0	897.3	791.4	712.1
55°	584.9	634.8	705.7	796.5	892.1	953.8	938.9	863.6	767.5	675.7	606.3
57.5°	513.8	557.2	622.6	698.3	782.5	833.4	808.5	736.1	650.3	572.4	519.9
60°	467.8	509.2	565.0	636.4	707.3	747.1	723.5	657.9	579.0	516.1	470.5
62.5°	423.1	458.1	511.7	573.7	639.4	668.9	647.8	583.2	514.9	458.2	421.1
65°	359.8	388.3	431.3	484.4	532.3	557.4	539.8	479.6	427.5	386.7	357.2
67.5°	300.7	323.0	355.6	398.2	438.8	452.4	436.4	394.5	350.3	317.6	296.8
70°	259.9	280.9	308.3	341.0	376.5	391.0	374.9	341.5	305.6	275.5	255.1
72.5°	224.3	240.5	263.6	291.6	319.3	333.9	322.9	290.8	260.4	238.1	220.8
75°	170.8	184.8	200.9	220.8	242.3	251.9	242.3	220.3	199.2	182.6	170.3
77.5°	124.2	131.7	144.1	159.0	172.4	179.9	171.5	156.5	143.7	132.3	126.2
80°	94.5	99.9	108.5	120.3	129.5	136.4	131.1	118.7	108.5	101.0	98.3
82.5°	68.8	72.4	78.0	86.7	92.9	96.4	94.1	85.1	81.0	74.3	71.6
85°	33.8	36.0	39.8	42.4	47.8	48.4	48.9	45.1	41.4	39.8	37.6
87.5°	12.0	12.6	14.0	15.6	17.4	18.0	17.7	17.8	16.2	15.9	14.2
90°	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3	8.8
92.5°	4.5	4.5	4.6	4.6	5.0	5.7	6.3	7.0	7.6	8.1	8.5
95°	17.0	14.2	11.5	8.9	7.6	7.6	7.7	7.8	7.9	8.3	8.8
97.5°	43.3	45.0	46.8	48.4	44.8	36.0	27.2	18.3	9.4	9.5	9.5
100°	60.0	61.4	62.8	64.2	59.5	48.6	37.6	26.7	15.8	14.3	13.0
102.5°	78.5	79.5	80.5	81.6	81.4	80.0	78.6	77.1	75.6	61.1	46.6
105°	107.9	108.4	108.9	109.4	109.8	110.2	110.6	111.0	111.4	112.1	112.8
107.5°	135.5	135.8	136.0	136.3	136.6	137.2	137.7	138.3	138.9	139.2	139.6
110°	154.4	154.6	154.9	155.1	155.5	155.9	156.4	156.9	157.4	157.5	157.7



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	172.9	173.3	173.7	174.2	174.5	174.7	174.9	175.1	175.4	175.3	175.3
115°	200.9	201.1	201.3	201.6	201.6	201.6	201.5	201.4	201.3	201.5	201.6
117.5°	226.2	226.5	226.9	227.2	227.4	227.6	227.8	227.9	228.1	228.1	228.0
120°	243.4	243.7	244.0	244.3	244.4	244.4	244.3	244.2	244.1	244.3	244.4
122.5°	259.2	259.4	259.6	259.8	259.9	260.0	260.1	260.2	260.4	260.4	260.5
125°	282.3	282.6	282.9	283.3	283.3	283.2	283.0	282.9	282.7	282.9	283.2
127.5°	303.8	303.8	303.9	304.0	304.2	304.6	304.9	305.3	305.7	305.6	305.6
130°	317.7	317.8	317.9	318.0	318.1	318.3	318.6	318.8	319.1	319.1	319.2
132.5°	330.6	330.7	330.9	331.0	331.2	331.5	331.8	332.1	332.4	332.5	332.6
135°	349.7	349.6	349.5	349.4	349.5	349.9	350.2	350.5	350.8	351.0	351.1
137.5°	366.9	366.9	366.9	367.0	367.2	367.5	367.8	368.2	368.5	368.7	368.9
140°	378.1	378.3	378.4	378.6	378.7	378.9	379.1	379.2	379.4	379.6	379.8
142.5°	388.2	388.5	388.8	389.1	389.3	389.4	389.5	389.6	389.7	389.8	390.0
145°	403.5	403.7	404.0	404.2	404.3	404.3	404.3	404.3	404.3	404.5	404.6
147.5°	416.0	416.4	416.9	417.3	417.5	417.4	417.3	417.2	417.2	417.2	417.3
150°	424.6	425.0	425.4	425.7	425.8	425.7	425.6	425.5	425.5	425.5	425.5
152.5°	432.0	432.3	432.5	432.8	432.8	432.7	432.5	432.4	432.3	432.4	432.5
155°	442.3	442.3	442.4	442.5	442.4	442.2	441.9	441.7	441.5	441.8	442.1
157.5°	450.9	450.9	450.8	450.8	450.6	450.4	450.1	449.8	449.6	450.0	450.4
160°	455.9	455.7	455.4	455.1	455.0	454.9	454.8	454.7	454.6	455.1	455.7
162.5°	460.4	460.1	459.8	459.5	459.3	459.2	459.1	459.1	459.0	459.5	459.9
165°	466.1	465.6	465.2	464.8	464.6	464.6	464.6	464.6	464.6	465.3	466.0
167.5°	470.6	470.2	469.8	469.4	469.2	469.1	469.1	469.0	469.0	469.7	470.4
170°	473.1	472.6	472.2	471.7	471.5	471.6	471.7	471.7	471.8	472.4	473.1
172.5°	474.8	474.3	473.9	473.4	473.2	473.3	473.4	473.4	473.5	474.1	474.8
175°	476.7	476.3	475.7	475.2	475.0	475.1	475.2	475.3	475.3	476.2	476.9
177.5°	477.6	477.2	476.7	476.3	476.1	476.3	476.4	476.5	476.6	477.2	477.7
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332580-840
 CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6	1296.6
2.5°	1366.5	1367.5	1371.3	1374.3	1375.1	1379.5	1379.9
5°	1486.6	1495.8	1513.5	1515.1	1517.8	1531.8	1521.1
7.5°	1627.4	1650.5	1666.1	1679.7	1684.7	1690.7	1689.5
10°	1717.6	1752.0	1769.2	1796.5	1797.7	1804.6	1800.3
12.5°	1808.3	1848.3	1879.6	1884.6	1907.6	1911.2	1917.2
15°	1936.7	1979.1	2022.7	2038.2	2069.9	2077.5	2089.3
17.5°	2057.5	2100.8	2131.3	2171.6	2184.6	2202.0	2190.2
20°	2123.6	2170.9	2209.6	2241.3	2254.7	2264.3	2263.3
22.5°	2163.6	2211.3	2242.6	2266.6	2279.2	2283.3	2283.0
25°	2188.6	2216.0	2225.6	2234.8	2220.9	2216.0	2218.2
27.5°	2119.0	2111.9	2086.7	2053.6	2019.2	1992.0	1977.1
30°	2023.2	1981.4	1943.2	1876.5	1842.2	1821.8	1803.5
32.5°	1887.4	1821.1	1747.7	1686.7	1647.6	1617.3	1612.8
35°	1654.8	1554.9	1465.2	1390.5	1351.8	1319.1	1311.5
37.5°	1406.8	1303.0	1222.3	1156.6	1115.0	1091.9	1070.3
40°	1242.2	1153.2	1073.6	1017.7	986.1	969.5	956.0
42.5°	1115.5	1034.1	955.0	912.5	883.8	873.6	865.8
45°	940.4	864.7	809.9	777.7	761.0	743.9	735.8
47.5°	800.2	738.6	702.5	675.1	657.3	647.1	642.0
50°	720.7	670.2	638.0	617.1	601.0	592.9	588.7
52.5°	650.3	608.8	581.8	565.1	554.2	548.3	546.5
55°	560.2	528.5	511.3	496.9	488.8	483.4	481.2
57.5°	487.0	462.5	448.6	436.7	433.5	429.0	427.5
60°	438.8	420.0	408.2	400.1	397.5	392.0	393.1
62.5°	396.3	380.9	370.8	366.2	362.6	358.1	359.6
65°	335.2	323.9	318.5	314.2	309.9	307.2	309.3
67.5°	281.2	273.5	266.2	263.7	261.6	261.2	258.8
70°	246.0	239.5	233.1	231.5	231.5	229.3	228.8
72.5°	212.1	207.3	203.0	201.9	200.2	201.0	198.7
75°	163.8	160.1	158.4	156.8	156.3	156.3	154.7
77.5°	121.1	118.3	115.7	115.7	113.7	113.0	112.8
80°	91.8	90.8	88.7	88.7	87.6	88.1	87.1
82.5°	69.1	67.6	67.2	66.2	64.7	64.8	63.8
85°	37.1	35.4	34.9	33.3	32.2	33.3	32.2
87.5°	14.7	14.4	14.0	13.2	12.8	12.8	11.6
90°	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	9.0	9.5	9.7	9.8	9.8	9.8	9.9
95°	9.3	9.8	10.0	10.1	10.2	10.3	10.3
97.5°	9.6	9.6	9.7	9.8	9.8	9.9	10.0
100°	11.6	10.3	9.7	9.8	9.8	9.9	10.0
102.5°	32.0	17.5	10.2	10.2	10.2	10.3	10.3
105°	113.5	114.2	113.1	110.3	107.4	104.5	101.7
107.5°	139.9	140.3	140.6	140.9	141.2	141.5	141.8
110°	157.8	158.0	158.2	158.4	158.8	159.0	159.2



TEST NUMBER: P332580-840

CATALOG NUMBER: SA4XXDIP-C795D365U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	175.3	175.2	175.4	175.7	176.0	176.3	176.6
115°	201.8	202.0	202.0	202.0	202.0	202.0	202.0
117.5°	228.0	228.0	227.9	227.9	227.9	227.9	227.8
120°	244.6	244.8	244.8	244.6	244.4	244.3	244.1
122.5°	260.6	260.7	260.7	260.5	260.4	260.2	260.1
125°	283.4	283.6	283.8	283.9	284.0	284.0	284.1
127.5°	305.5	305.5	305.4	305.4	305.3	305.2	305.2
130°	319.3	319.4	319.4	319.4	319.4	319.4	319.4
132.5°	332.8	332.9	332.9	332.8	332.6	332.6	332.5
135°	351.3	351.4	351.6	351.7	351.9	352.1	352.2
137.5°	369.1	369.2	369.3	369.2	369.2	369.1	369.1
140°	380.1	380.3	380.5	380.6	380.6	380.7	380.8
142.5°	390.2	390.3	390.4	390.5	390.5	390.5	390.5
145°	404.7	404.7	404.8	405.0	405.2	405.3	405.5
147.5°	417.4	417.4	417.5	417.6	417.6	417.7	417.8
150°	425.5	425.5	425.5	425.6	425.7	425.7	425.8
152.5°	432.6	432.8	432.8	432.7	432.7	432.7	432.6
155°	442.4	442.7	442.8	442.5	442.3	442.1	441.8
157.5°	450.8	451.2	451.2	450.8	450.4	450.0	449.6
160°	456.2	456.6	456.6	456.2	455.7	455.1	454.6
162.5°	460.4	460.9	460.8	460.3	459.8	459.2	458.7
165°	466.6	467.3	467.2	466.5	465.7	465.0	464.3
167.5°	471.1	471.7	471.7	470.9	470.1	469.3	468.6
170°	473.7	474.3	474.2	473.5	472.7	471.9	471.1
172.5°	475.4	476.1	475.9	475.1	474.2	473.4	472.5
175°	477.6	478.3	478.2	477.2	476.3	475.2	474.3
177.5°	478.2	478.7	478.5	477.8	477.0	476.3	475.4
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2

(END OF REPORT)