

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913146

Luminaire Tested: DFN2DIP-4P3F0-050D020US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913146
REPORT IS A COMBINATION OF REPORTS P899035 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-050D020US927-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5323.4 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 64.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78
1	103	99	95	91	98	94	90	87	85	82	80		77	74	72		69
2	94	86	80	74	89	82	76	71	74	70	66		67	64	61		61
3	86	76	68	62	81	72	65	60	66	60	55		59	55	51		54
4	79	67	59	53	74	64	57	51	58	52	47		53	48	44		48
5	72	60	52	45	68	57	50	44	52	46	41		48	42	38		43
6	67	54	46	40	63	52	44	38	47	41	36		43	38	34		39
7	62	49	41	35	58	47	39	34	43	37	32		39	34	30		36
8	57	45	37	31	54	43	35	30	39	33	28		36	31	27		33
9	54	41	33	28	51	39	32	27	36	30	26		33	28	24		31
10	50	38	30	25	48	36	29	24	33	27	23		31	26	22		28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1756	1756	1756
5°	1758	1731	1743
10°	1743	1706	1719
15°	1716	1677	1681
20°	1680	1637	1643
25°	1645	1589	1599
30°	1600	1544	1543
35°	1558	1492	1484
40°	1507	1439	1427
45°	1455	1386	1369
50°	1399	1330	1303
55°	1339	1265	1241
60°	1273	1189	1170
65°	1199	1109	1087
70°	1106	1013	997
75°	977	896	914
80°	822	748	755
85°	579	495	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1455 cd/sqm

TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	2.7
10°-20°	408.1	7.7
20°-30°	599.8	11.3
30°-40°	696.6	13.1
40°-50°	695.8	13.1
50°-60°	606.7	11.4
60°-70°	448.5	8.4
70°-80°	253.7	4.8
80°-90°	68.4	1.3
90°-100°	31.0	0.6
100°-110°	98.5	1.9
110°-120°	168.6	3.2
120°-130°	221.7	4.2
130°-140°	248.9	4.7
140°-150°	244.1	4.6
150°-160°	204.7	3.8
160°-170°	135.8	2.6
170°-180°	47.5	0.9
0°-30°	1153.0	21.7
0°-40°	1849.6	34.7
0°-60°	3152.1	59.2
0°-90°	3922.7	73.7
90°-120°	298.1	5.6
90°-150°	1012.8	19.0
90°-180°	1401.0	26.3
0°-180°	5323.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1531	1528	146
15°	1467	1458	1439	1445	1438	413
25°	1328	1316	1291	1294	1291	611
35°	1146	1131	1107	1098	1091	715
45°	932	922	900	883	877	719
55°	706	697	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	0	6	15	14	14	5
95°	22	26	27	27	26	25
105°	91	92	93	94	94	96
115°	169	172	171	170	169	167
125°	246	250	249	247	247	220
135°	318	323	324	323	322	246
145°	386	389	392	392	391	241
155°	442	443	444	447	445	203
165°	481	480	480	483	481	136
175°	500	499	498	501	498	48
180°	501	501	501	501	501	

TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.2	1541.2	1541.2	1541.2	1541.2
2.5°	1550.1	1542.8	1526.5	1541.2	1538.4
5°	1541.2	1535.4	1519.0	1530.8	1528.0
7.5°	1530.8	1522.0	1505.7	1517.7	1514.7
10°	1514.7	1504.3	1486.5	1498.3	1493.9
12.5°	1492.3	1483.5	1465.8	1473.1	1470.1
15°	1467.1	1458.3	1439.0	1445.0	1437.6
17.5°	1436.0	1427.2	1407.9	1415.2	1407.9
20°	1401.9	1393.1	1372.4	1376.7	1370.9
22.5°	1367.9	1354.6	1335.2	1335.2	1332.2
25°	1327.9	1316.1	1290.9	1293.7	1290.9
27.5°	1283.3	1273.0	1253.8	1249.3	1242.0
30°	1239.0	1227.1	1204.9	1200.5	1194.5
32.5°	1191.5	1182.7	1159.0	1150.0	1144.1
35°	1145.6	1130.8	1107.1	1098.1	1090.8
37.5°	1093.7	1080.4	1056.6	1046.2	1038.9
40°	1040.5	1028.5	1004.7	991.5	985.6
42.5°	988.6	976.6	953.0	938.0	929.2
45°	932.2	921.9	899.5	883.4	877.3
47.5°	877.3	867.0	843.3	826.9	818.1
50°	819.5	812.1	791.4	770.6	763.2
52.5°	763.2	752.8	733.6	717.3	706.9
55°	705.5	696.6	678.7	661.0	653.6
57.5°	647.6	640.2	620.9	603.2	597.1
60°	589.8	584.0	563.2	546.8	542.5
62.5°	533.5	523.2	508.3	493.5	487.6
65°	475.8	466.8	452.0	438.7	431.3
67.5°	416.5	409.0	395.8	385.4	379.4
70°	361.6	355.7	342.3	331.9	326.1
72.5°	305.4	299.4	292.0	281.6	277.2
75°	248.9	246.1	238.5	229.7	232.7
77.5°	198.6	192.6	189.6	185.2	180.9
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.8	100.8	99.3	93.4	93.4
85°	60.7	59.3	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.5	5.5	14.8	13.9	14.3
92.5°	9.3	12.7	13.2	13.6	13.6
95°	22.0	26.3	27.0	27.0	26.3
97.5°	36.7	40.6	42.3	42.3	42.3
100°	53.6	57.1	58.3	58.3	57.8
102.5°	71.5	74.0	75.7	76.1	75.7
105°	90.9	92.1	93.1	93.8	93.8
107.5°	110.3	112.1	112.1	112.4	110.3
110°	129.0	131.4	131.4	131.4	130.2



TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	149.2	151.8	151.4	150.1	149.2
115°	169.2	171.6	170.9	170.4	169.2
117.5°	189.0	192.3	190.2	189.0	187.7
120°	208.9	212.2	208.9	208.9	207.6
122.5°	227.0	231.2	229.2	228.0	227.0
125°	246.1	249.9	248.7	247.3	246.8
127.5°	264.7	269.3	267.7	265.9	264.7
130°	282.0	287.5	286.7	285.8	284.2
132.5°	301.5	305.8	306.0	304.0	302.7
135°	318.3	323.0	323.8	323.4	322.2
137.5°	337.0	340.8	341.6	341.3	339.4
140°	353.5	357.3	359.4	359.4	357.7
142.5°	370.4	374.1	375.4	375.8	374.1
145°	386.4	389.4	391.9	392.3	390.6
147.5°	400.8	404.6	406.4	407.1	405.4
150°	415.6	418.1	419.8	421.1	419.8
152.5°	428.7	431.3	433.4	435.1	433.4
155°	441.9	443.1	444.4	446.6	445.2
157.5°	453.2	454.1	454.9	457.9	455.7
160°	463.3	464.2	464.7	467.2	465.4
162.5°	472.7	472.7	473.1	476.0	473.9
165°	480.7	480.2	480.2	483.2	481.2
167.5°	487.9	486.6	486.6	489.6	487.5
170°	493.4	492.2	491.7	494.7	492.2
172.5°	497.2	495.9	495.5	498.5	495.9
175°	500.2	499.0	498.0	501.1	498.5
177.5°	501.8	500.7	499.7	502.2	499.7
180°	501.1	501.1	501.1	501.1	501.1

TEST NUMBER: P913146

CATALOG NUMBER: DFN2DIP-4P3F0-050D020US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.14	12.27	11.87	13.01	13.90	10.70	11.82	11.42	12.57	13.45
	3H	12.82	13.83	13.55	14.58	15.50	12.33	13.34	13.06	14.09	15.01
	4H	13.41	14.37	14.17	15.13	16.06	12.92	13.87	13.68	14.64	15.57
	6H	13.82	14.70	14.59	15.48	16.42	13.32	14.20	14.09	14.98	15.92
	8H	13.93	14.77	14.71	15.57	16.51	13.43	14.27	14.21	15.06	16.01
	12H	13.99	14.79	14.77	15.58	16.55	13.48	14.28	14.26	15.07	16.04
4H	2H	11.63	12.58	12.39	13.35	14.28	11.28	12.23	12.03	12.99	13.92
	3H	13.51	14.31	14.29	15.11	16.06	13.11	13.90	13.88	14.70	15.65
	4H	14.24	14.96	15.02	15.76	16.74	13.81	14.54	14.60	15.34	16.31
	6H	14.76	15.39	15.57	16.21	17.20	14.33	14.96	15.13	15.78	16.76
	8H	14.92	15.50	15.72	16.32	17.32	14.48	15.06	15.29	15.88	16.88
	12H	15.00	15.53	15.83	16.37	17.37	14.55	15.08	15.38	15.92	16.92
8H	4H	14.45	15.04	15.26	15.86	16.85	14.07	14.66	14.88	15.48	16.47
	6H	15.09	15.57	15.92	16.43	17.43	14.70	15.19	15.54	16.05	17.05
	8H	15.31	15.74	16.15	16.60	17.61	14.91	15.35	15.76	16.20	17.22
	12H	15.45	15.83	16.30	16.68	17.75	15.04	15.42	15.89	16.27	17.33
12H	4H	14.45	14.97	15.27	15.82	16.82	14.08	14.61	14.91	15.45	16.45
	6H	15.12	15.55	15.96	16.41	17.42	14.74	15.18	15.59	16.03	17.05
	8H	15.37	15.75	16.22	16.60	17.67	14.99	15.37	15.84	16.22	17.28

END OF REPORT