

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332973-840

Luminaire Tested: **SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332973-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8553.2 lumens
Efficiency: N/A
Efficacy: 141.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	59	47	40	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	34	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	20	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13988	13988	13988	13988
5°	16226	14030	12400	14030
10°	19194	13969	11068	13969
15°	22172	13840	9510	13840
20°	24686	13662	8600	13662
25°	25483	13488	7985	13488
30°	22309	13276	7614	13276
35°	17366	12962	7389	12962
40°	13022	12603	7268	12603
45°	10282	12028	7205	12028
50°	8681	11362	6997	11362
55°	7567	10632	6622	10632
60°	6807	9875	5861	9875
65°	6002	9054	5041	9054
70°	5403	8207	4548	8207
75°	4529	7274	3877	7274
80°	3831	6197	3636	6197
85°	3233	4844	3233	4844



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	2.0
10°-20°	506.4	5.9
20°-30°	792.1	9.3
30°-40°	880.6	10.3
40°-50°	781.3	9.1
50°-60°	608.8	7.1
60°-70°	398.6	4.7
70°-80°	196.0	2.3
80°-90°	52.3	0.6
90°-100°	46.1	0.5
100°-110°	293.9	3.4
110°-120°	562.3	6.6
120°-130°	713.8	8.3
130°-140°	763.7	8.9
140°-150°	714.1	8.3
150°-160°	575.9	6.7
160°-170°	371.4	4.3
170°-180°	128.0	1.5
0°-30°	1466.4	17.1
0°-40°	2347.0	27.4
0°-60°	3737.0	43.7
0°-90°	4383.9	51.3
90°-120°	902.3	10.5
90°-150°	3094.0	36.2
90°-180°	4169.0	48.7
0°-180°	8553.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1733	1733	1733	1733	1733	
5°	2002	1731	1530	1731	2002	203
15°	2653	1656	1138	1656	2653	754
25°	2861	1514	896	1514	2861	1269
35°	1762	1315	750	1315	1762	1105
45°	901	1054	631	1054	901	713
55°	538	755	470	755	538	489
65°	314	474	264	474	314	316
75°	145	233	124	233	145	160
85°	35	52	35	52	35	40
90°	30	3	30	3	30	15
95°	29	55	29	55	29	23
105°	287	304	287	304	287	251
115°	571	566	571	566	571	565
125°	802	796	802	796	802	715
135°	995	988	995	988	995	766
145°	1145	1139	1145	1139	1145	716
155°	1248	1249	1248	1249	1248	575
165°	1312	1318	1312	1318	1312	370
175°	1340	1348	1340	1348	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1827.7	1832.7	1827.7	1827.1	1821.6	1819.9	1817.7	1810.4	1797.0	1789.2	1790.8
5°	2002.3	2019.6	2009.9	2008.5	1993.2	1977.8	1968.0	1945.7	1922.0	1905.9	1892.6
7.5°	2204.1	2214.1	2208.1	2198.3	2173.4	2159.3	2136.7	2107.2	2064.7	2032.1	2002.4
10°	2341.5	2349.9	2347.1	2329.0	2310.8	2273.8	2252.8	2211.7	2157.9	2115.4	2075.5
12.5°	2476.7	2485.6	2461.0	2461.8	2427.5	2398.3	2365.1	2313.3	2251.2	2196.3	2146.5
15°	2652.9	2641.7	2641.7	2627.8	2589.3	2548.9	2514.7	2460.2	2382.0	2316.3	2247.3
17.5°	2790.9	2794.7	2789.0	2756.0	2725.9	2684.0	2621.3	2557.8	2485.2	2397.1	2326.4
20°	2873.5	2873.5	2867.2	2844.9	2805.8	2761.1	2693.4	2624.2	2532.1	2443.5	2363.9
22.5°	2907.0	2909.2	2901.8	2883.4	2848.2	2804.6	2746.9	2676.7	2581.8	2481.9	2383.4
25°	2860.9	2874.2	2875.6	2870.6	2860.2	2833.7	2784.1	2712.2	2627.1	2518.8	2412.7
27.5°	2626.7	2643.4	2658.1	2682.2	2714.3	2731.1	2733.3	2696.7	2622.4	2518.3	2411.5
30°	2393.2	2407.1	2452.6	2511.8	2557.9	2599.8	2636.2	2645.8	2604.0	2510.4	2398.0
32.5°	2134.0	2153.0	2198.4	2262.2	2338.9	2409.9	2491.4	2533.0	2531.9	2475.8	2371.8
35°	1762.1	1776.0	1818.0	1884.9	1977.1	2082.5	2211.7	2312.2	2380.6	2375.7	2312.2
37.5°	1421.1	1436.8	1479.1	1534.8	1624.2	1754.6	1879.7	2018.1	2144.7	2215.7	2194.4
40°	1235.7	1236.4	1277.6	1334.8	1418.6	1532.4	1668.5	1822.1	1963.1	2078.3	2100.6
42.5°	1089.3	1089.4	1116.7	1178.4	1238.8	1345.8	1475.8	1628.3	1793.3	1926.4	1985.6
45°	900.6	906.9	929.2	966.2	1013.7	1104.4	1208.4	1350.2	1535.2	1692.9	1791.4
47.5°	762.7	771.8	786.1	816.3	854.0	914.5	1000.6	1127.9	1278.4	1452.0	1592.1
50°	691.2	692.6	710.6	727.4	760.2	808.4	883.8	990.0	1128.1	1295.1	1450.7
52.5°	629.8	629.4	640.4	661.6	688.2	725.8	786.7	883.2	1005.8	1155.4	1316.1
55°	537.6	541.1	549.5	566.1	586.4	613.0	661.2	733.8	830.1	957.9	1103.8
57.5°	467.5	469.3	475.8	482.9	501.5	520.8	556.9	607.3	688.6	793.2	929.2
60°	421.6	422.3	424.4	434.9	449.6	467.8	492.2	534.7	603.2	698.8	806.4
62.5°	377.0	378.2	381.4	389.1	400.4	413.0	438.6	472.8	529.5	611.2	708.0
65°	314.2	314.9	319.7	322.6	331.6	342.7	361.6	384.7	423.7	492.2	565.5
67.5°	262.5	262.5	262.8	266.5	272.9	280.2	291.5	309.9	339.4	381.4	446.1
70°	228.9	228.9	230.4	232.5	236.0	242.3	248.5	262.5	284.2	318.3	367.9
72.5°	197.7	198.2	199.7	200.1	201.9	207.0	211.7	220.7	236.7	262.5	302.6
75°	145.2	147.3	150.8	153.6	157.0	156.4	161.3	166.8	171.8	187.1	210.2
77.5°	108.1	106.9	107.3	109.8	110.2	110.9	114.3	118.7	122.3	129.6	137.8
80°	82.4	82.4	84.4	85.1	84.4	85.1	88.7	90.8	92.2	94.9	102.6
82.5°	62.3	63.4	62.7	63.4	63.8	64.5	67.5	67.9	69.3	70.4	73.6
85°	34.9	35.6	36.3	34.9	34.9	34.9	36.3	37.0	38.4	37.7	39.1
87.5°	18.4	17.7	18.2	18.1	18.6	17.8	18.1	19.0	17.6	17.9	17.5
90°	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8	23.5	22.2	20.4
92.5°	27.9	27.8	27.7	27.6	27.5	26.8	25.4	24.0	22.7	21.4	19.6
95°	29.2	29.0	28.8	28.6	28.4	27.6	26.3	24.8	23.5	22.2	21.9
97.5°	28.3	28.0	27.8	27.6	27.4	27.2	27.1	26.9	26.8	26.7	51.6
100°	28.3	28.0	27.8	27.6	27.4	29.1	32.9	36.8	40.6	44.3	75.2
102.5°	29.1	29.0	29.0	28.9	28.9	49.4	90.5	131.6	172.6	213.7	217.7
105°	287.3	295.4	303.5	311.5	319.6	322.6	320.5	318.6	316.6	314.6	313.5
107.5°	400.4	399.6	398.7	397.9	397.0	396.1	395.2	394.2	393.1	392.1	390.6
110°	449.6	449.0	448.3	447.6	447.0	446.4	446.0	445.5	445.0	444.5	443.2



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	498.8	498.0	497.2	496.2	495.4	495.0	495.1	495.2	495.3	495.3	494.7
115°	570.6	570.6	570.6	570.6	570.6	570.4	570.0	569.5	569.1	568.6	568.8
117.5°	643.6	643.7	643.8	643.9	644.0	644.0	644.1	644.2	644.3	644.4	643.9
120°	689.5	690.0	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5	689.7
122.5°	734.7	735.2	735.6	736.1	736.5	736.6	736.3	736.1	735.8	735.5	735.2
125°	802.4	802.2	802.0	801.8	801.5	801.1	800.4	799.8	799.1	798.4	798.9
127.5°	861.9	862.1	862.3	862.5	862.6	862.8	862.9	863.1	863.2	863.3	862.3
130°	902.3	902.3	902.3	902.3	902.3	902.1	901.9	901.7	901.5	901.3	900.6
132.5°	939.4	939.6	939.7	939.9	940.1	940.1	939.9	939.6	939.4	939.2	938.3
135°	995.0	994.5	994.1	993.7	993.2	992.8	992.3	991.9	991.4	991.0	990.1
137.5°	1042.6	1042.7	1042.9	1043.0	1043.1	1043.0	1042.5	1042.0	1041.5	1041.0	1040.0
140°	1075.7	1075.4	1075.2	1075.0	1074.8	1074.3	1073.7	1073.0	1072.3	1071.7	1071.2
142.5°	1103.1	1103.1	1103.0	1103.0	1102.9	1102.7	1102.2	1101.7	1101.2	1100.7	1100.3
145°	1145.2	1144.8	1144.3	1143.9	1143.5	1143.1	1142.9	1142.7	1142.5	1142.2	1142.2
147.5°	1180.1	1179.9	1179.6	1179.4	1179.2	1179.0	1178.8	1178.6	1178.5	1178.3	1178.5
150°	1202.6	1202.4	1202.2	1202.0	1201.7	1201.6	1201.6	1201.6	1201.6	1201.6	1201.9
152.5°	1222.0	1222.1	1222.3	1222.4	1222.5	1222.4	1222.1	1221.7	1221.4	1221.0	1221.4
155°	1248.1	1248.7	1249.4	1250.1	1250.7	1250.6	1249.7	1248.8	1247.9	1247.1	1247.7
157.5°	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8	1270.6
160°	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3	1284.5
162.5°	1295.7	1297.2	1298.7	1300.2	1301.7	1301.8	1300.5	1299.1	1297.8	1296.5	1296.7
165°	1311.5	1313.5	1315.6	1317.6	1319.6	1319.7	1318.0	1316.2	1314.3	1312.5	1312.5
167.5°	1323.4	1325.6	1328.0	1330.2	1332.4	1332.5	1330.6	1328.6	1326.7	1324.6	1324.8
170°	1330.7	1332.9	1335.2	1337.5	1339.7	1339.9	1338.1	1336.4	1334.5	1332.7	1332.5
172.5°	1334.7	1337.2	1339.6	1342.0	1344.4	1344.7	1342.9	1341.2	1339.4	1337.6	1337.4
175°	1339.8	1342.5	1345.1	1347.9	1350.5	1350.9	1348.9	1346.9	1344.8	1342.8	1342.6
177.5°	1343.0	1345.1	1347.4	1349.5	1351.6	1352.0	1350.5	1349.1	1347.7	1346.3	1345.8
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1785.2	1777.5	1773.5	1764.5	1753.9	1748.4	1743.3	1736.1	1726.6	1716.6	1709.3
5°	1875.8	1859.1	1838.2	1813.0	1790.7	1769.1	1750.2	1731.3	1709.7	1687.4	1665.1
7.5°	1968.8	1935.9	1900.3	1859.1	1819.1	1782.6	1749.1	1717.0	1680.6	1648.1	1618.5
10°	2033.7	1988.9	1939.3	1887.0	1834.6	1789.3	1744.6	1704.1	1659.4	1619.6	1586.1
12.5°	2086.2	2033.7	1974.0	1908.8	1845.8	1791.0	1739.6	1686.8	1636.0	1592.9	1548.1
15°	2173.2	2101.3	2021.0	1942.9	1861.2	1786.5	1717.4	1656.0	1598.0	1537.3	1494.7
17.5°	2233.1	2147.9	2050.2	1956.3	1859.8	1771.7	1691.9	1618.8	1552.0	1490.0	1439.3
20°	2268.9	2174.6	2066.5	1959.6	1851.4	1757.2	1671.3	1590.3	1521.3	1454.2	1401.8
22.5°	2289.0	2184.7	2066.5	1954.6	1842.5	1740.4	1646.2	1561.9	1486.6	1419.6	1361.6
25°	2295.4	2183.7	2063.0	1934.5	1811.6	1703.4	1605.7	1514.2	1430.5	1363.4	1302.0
27.5°	2286.5	2155.0	2031.2	1899.5	1772.7	1658.6	1556.0	1460.0	1376.0	1304.1	1241.1
30°	2273.1	2132.0	1999.4	1862.6	1734.1	1624.6	1516.3	1424.2	1336.9	1262.2	1198.7
32.5°	2244.0	2104.2	1961.5	1821.3	1691.1	1578.2	1475.5	1382.8	1297.3	1220.9	1153.5
35°	2186.6	2044.8	1889.9	1746.1	1618.2	1501.0	1404.6	1315.2	1233.6	1152.0	1080.7
37.5°	2110.7	1965.9	1811.8	1654.3	1526.4	1415.6	1327.3	1243.3	1163.7	1089.0	1010.2
40°	2039.2	1907.2	1748.1	1591.7	1460.5	1353.6	1272.0	1195.9	1115.6	1041.6	962.7
42.5°	1952.7	1840.3	1679.4	1522.5	1392.9	1290.0	1213.9	1139.4	1066.4	994.7	912.4
45°	1808.2	1722.9	1572.2	1421.4	1290.8	1188.9	1119.1	1053.5	989.3	920.8	843.3
47.5°	1642.5	1584.9	1454.7	1300.3	1179.5	1087.8	1020.4	966.7	912.4	844.0	776.1
50°	1527.5	1490.5	1364.8	1223.9	1108.6	1024.1	955.0	904.7	859.4	793.8	733.1
52.5°	1404.6	1384.9	1278.8	1144.0	1032.7	949.9	890.8	845.6	799.6	745.2	688.3
55°	1217.5	1228.0	1137.9	1021.4	916.7	846.9	793.0	755.4	716.3	670.2	626.2
57.5°	1026.2	1064.5	1004.0	901.7	803.5	739.0	698.5	666.8	634.0	595.8	558.3
60°	911.7	943.8	909.7	819.6	733.8	673.7	636.0	611.6	578.8	543.8	515.2
62.5°	800.0	834.4	814.2	741.4	661.7	610.1	576.8	554.0	529.6	499.2	469.4
65°	659.7	682.1	672.3	622.1	565.5	521.5	490.8	474.0	451.7	429.4	402.8
67.5°	505.3	548.5	542.7	516.0	467.2	432.8	412.7	397.9	377.6	360.9	343.0
70°	415.4	455.1	454.4	432.8	406.3	374.2	360.2	347.7	329.5	313.5	298.8
72.5°	340.0	376.5	381.8	365.3	347.1	322.9	309.4	300.7	283.2	272.2	260.2
75°	238.0	264.6	271.6	271.6	263.2	250.6	238.7	233.2	220.7	210.9	203.9
77.5°	156.1	172.9	183.8	186.2	187.5	183.3	173.6	169.7	160.0	156.5	149.9
80°	110.3	121.5	134.0	138.3	141.7	140.4	136.1	133.3	124.3	120.8	118.0
82.5°	76.2	82.4	92.7	101.9	101.0	104.6	101.0	98.8	91.9	90.6	87.9
85°	39.8	40.5	41.9	48.2	51.7	53.0	53.7	52.3	50.3	50.3	45.3
87.5°	17.2	16.2	17.0	16.6	16.6	18.4	19.5	19.6	18.4	17.3	16.1
90°	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0	5.5	8.0	10.4
92.5°	17.8	16.0	14.2	13.2	13.1	12.9	12.8	12.7	12.8	12.9	13.1
95°	21.7	21.5	21.3	24.9	32.6	40.2	47.9	55.4	47.9	40.2	32.6
97.5°	76.6	101.6	126.6	136.7	132.0	127.2	122.5	117.8	122.5	127.2	132.0
100°	106.2	137.1	168.0	181.5	177.4	173.4	169.4	165.3	169.4	173.4	177.4
102.5°	221.8	225.8	229.8	230.4	227.4	224.5	221.6	218.5	221.6	224.5	227.4
105°	312.3	311.1	310.0	308.8	307.5	306.1	304.8	303.5	304.8	306.1	307.5
107.5°	389.1	387.6	386.1	385.0	384.3	383.6	382.9	382.2	382.9	383.6	384.3
110°	441.9	440.5	439.2	438.2	437.5	436.9	436.2	435.6	436.2	436.9	437.5



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	494.1	493.5	492.9	492.0	490.8	489.6	488.4	487.2	488.4	489.6	490.8
115°	569.1	569.3	569.5	569.3	568.6	567.9	567.2	566.5	567.2	567.9	568.6
117.5°	643.4	642.9	642.4	641.8	640.9	640.0	639.0	638.1	639.0	640.0	640.9
120°	690.0	690.2	690.4	690.1	689.2	688.3	687.4	686.5	687.4	688.3	689.2
122.5°	734.9	734.6	734.3	733.9	733.3	732.8	732.3	731.6	732.3	732.8	733.3
125°	799.3	799.8	800.2	800.0	799.1	798.2	797.3	796.4	797.3	798.2	799.1
127.5°	861.3	860.3	859.2	858.6	858.4	858.2	857.9	857.7	857.9	858.2	858.4
130°	899.9	899.3	898.6	898.1	897.9	897.7	897.5	897.3	897.5	897.7	897.9
132.5°	937.5	936.6	935.7	935.1	934.7	934.3	933.9	933.5	933.9	934.3	934.7
135°	989.2	988.3	987.3	987.0	987.2	987.5	987.7	988.0	987.7	987.5	987.2
137.5°	1039.1	1038.0	1037.0	1036.5	1036.4	1036.3	1036.2	1036.1	1036.2	1036.3	1036.4
140°	1070.8	1070.3	1069.9	1069.3	1068.9	1068.5	1068.0	1067.6	1068.0	1068.5	1068.9
142.5°	1100.1	1099.8	1099.5	1099.0	1098.2	1097.4	1096.6	1095.8	1096.6	1097.4	1098.2
145°	1142.2	1142.2	1142.2	1141.9	1141.1	1140.5	1139.8	1139.1	1139.8	1140.5	1141.1
147.5°	1178.7	1178.9	1179.2	1178.7	1177.4	1176.2	1174.9	1173.7	1174.9	1176.2	1177.4
150°	1202.1	1202.3	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6	1199.5	1200.4	1201.3
152.5°	1221.8	1222.2	1222.6	1222.4	1221.7	1221.0	1220.3	1219.6	1220.3	1221.0	1221.7
155°	1248.4	1249.1	1249.7	1249.9	1249.7	1249.5	1249.3	1249.1	1249.3	1249.5	1249.7
157.5°	1271.3	1272.1	1272.8	1273.3	1273.4	1273.5	1273.7	1273.8	1273.7	1273.5	1273.4
160°	1284.8	1285.1	1285.3	1285.7	1286.4	1287.1	1287.7	1288.4	1287.7	1287.1	1286.4
162.5°	1296.9	1297.1	1297.4	1297.9	1298.7	1299.6	1300.4	1301.3	1300.4	1299.6	1298.7
165°	1312.5	1312.5	1312.5	1313.1	1314.2	1315.3	1316.5	1317.6	1316.5	1315.3	1314.2
167.5°	1324.9	1325.0	1325.2	1325.9	1327.1	1328.2	1329.4	1330.5	1329.4	1328.2	1327.1
170°	1332.3	1332.0	1331.8	1332.4	1333.7	1335.0	1336.5	1337.8	1336.5	1335.0	1333.7
172.5°	1337.2	1336.9	1336.7	1337.3	1338.6	1339.9	1341.3	1342.6	1341.3	1339.9	1338.6
175°	1342.4	1342.1	1341.9	1342.5	1343.8	1345.1	1346.6	1347.9	1346.6	1345.1	1343.8
177.5°	1345.5	1345.1	1344.8	1345.2	1346.6	1347.8	1349.0	1350.3	1349.0	1347.8	1346.6
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1701.4	1695.9	1688.6	1680.2	1670.2	1661.2	1657.4	1660.7	1662.3	1657.9	1657.4
5°	1649.7	1632.2	1618.2	1597.3	1580.5	1566.6	1556.8	1552.7	1554.0	1542.9	1540.0
7.5°	1591.4	1570.7	1547.9	1523.0	1499.9	1479.4	1468.5	1462.7	1450.9	1445.8	1437.3
10°	1554.0	1526.1	1503.8	1474.4	1447.9	1423.5	1411.6	1401.8	1390.0	1384.4	1372.5
12.5°	1515.5	1483.1	1458.5	1428.1	1401.0	1371.5	1360.2	1342.1	1323.5	1311.8	1296.6
15°	1461.2	1422.1	1392.1	1355.7	1323.6	1290.1	1260.1	1226.6	1214.1	1187.5	1172.2
17.5°	1397.7	1358.0	1320.8	1272.1	1222.5	1180.9	1148.9	1116.8	1097.6	1080.7	1072.9
20°	1355.7	1319.5	1267.8	1211.2	1156.1	1110.0	1084.2	1063.3	1042.3	1030.5	1022.1
22.5°	1316.1	1269.7	1209.7	1148.7	1093.6	1057.5	1035.6	1014.1	997.0	985.7	974.6
25°	1249.6	1188.9	1125.4	1055.6	1017.8	986.4	962.7	945.2	934.8	920.1	914.5
27.5°	1181.3	1107.8	1037.7	990.8	951.5	922.8	902.1	889.0	875.8	866.4	859.1
30°	1128.8	1054.2	991.4	946.6	906.9	883.1	866.4	851.0	840.5	832.8	827.3
32.5°	1076.9	1002.2	949.5	901.4	870.0	846.9	829.0	817.5	809.3	799.3	796.0
35°	1001.8	935.4	889.4	846.2	814.1	793.0	779.1	767.2	760.2	757.5	755.4
37.5°	929.6	875.4	825.8	790.3	761.6	745.2	728.7	722.9	718.1	713.1	715.3
40°	883.8	832.8	788.9	751.1	728.1	710.0	700.2	693.3	689.0	689.0	689.0
42.5°	844.1	794.4	751.4	717.7	694.6	679.2	668.4	662.5	661.2	660.6	663.9
45°	782.6	736.5	693.3	665.3	645.8	630.4	624.1	619.2	619.2	622.1	622.7
47.5°	721.5	678.4	643.7	612.4	594.5	584.9	579.5	576.9	577.2	580.0	583.2
50°	684.2	641.6	607.3	579.5	562.7	553.6	548.8	547.3	548.8	548.8	553.6
52.5°	643.4	605.3	571.6	548.2	529.2	520.7	518.0	516.0	516.8	519.2	521.2
55°	583.6	549.5	517.4	494.9	481.0	475.4	469.2	469.8	468.5	469.8	469.8
57.5°	523.7	493.0	463.1	445.5	433.1	425.1	418.2	420.1	418.1	417.8	416.7
60°	485.2	451.7	428.0	411.9	397.9	390.9	384.7	386.1	384.0	382.5	379.8
62.5°	443.3	415.4	392.7	377.3	366.1	358.0	351.7	350.3	345.5	340.7	334.6
65°	382.5	359.5	339.3	324.7	314.2	307.9	303.0	298.8	288.3	277.1	271.6
67.5°	323.6	306.9	288.0	275.6	267.1	258.8	249.5	242.4	232.6	226.5	223.0
70°	285.5	269.4	253.4	241.6	232.5	224.8	214.3	209.4	202.5	199.7	196.2
72.5°	249.2	234.3	219.3	208.6	198.9	193.0	184.7	179.9	176.7	175.6	172.2
75°	194.1	182.2	171.1	161.3	153.6	149.4	145.9	142.4	141.0	134.7	131.3
77.5°	141.6	133.8	126.7	119.8	114.3	111.6	104.8	100.8	98.5	95.5	94.8
80°	110.3	104.7	97.8	93.5	85.8	83.1	80.3	79.6	78.9	78.2	77.5
82.5°	82.9	77.4	70.4	67.9	65.7	64.1	62.4	61.7	61.0	61.4	61.3
85°	41.9	39.1	39.1	38.4	37.7	37.0	36.3	36.3	35.6	36.3	35.6
87.5°	16.6	16.4	16.8	16.0	17.0	17.3	17.0	17.3	18.1	17.3	17.4
90°	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8	26.3	27.6	28.5
92.5°	13.2	14.2	16.0	17.8	19.6	21.4	22.7	24.0	25.4	26.8	27.5
95°	24.9	21.3	21.5	21.7	21.9	22.2	23.5	24.8	26.3	27.6	28.4
97.5°	136.7	126.6	101.6	76.6	51.6	26.7	26.8	26.9	27.1	27.2	27.4
100°	181.5	168.0	137.1	106.2	75.2	44.3	40.6	36.8	32.9	29.1	27.4
102.5°	230.4	229.8	225.8	221.8	217.7	213.7	172.6	131.6	90.5	49.4	28.9
105°	308.8	310.0	311.1	312.3	313.5	314.6	316.6	318.6	320.5	322.6	319.6
107.5°	385.0	386.1	387.6	389.1	390.6	392.1	393.1	394.2	395.2	396.1	397.0
110°	438.2	439.2	440.5	441.9	443.2	444.5	445.0	445.5	446.0	446.4	447.0



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.0	492.9	493.5	494.1	494.7	495.3	495.3	495.2	495.1	495.0	495.4
115°	569.3	569.5	569.3	569.1	568.8	568.6	569.1	569.5	570.0	570.4	570.6
117.5°	641.8	642.4	642.9	643.4	643.9	644.4	644.3	644.2	644.1	644.0	644.0
120°	690.1	690.4	690.2	690.0	689.7	689.5	690.0	690.4	690.8	691.4	691.4
122.5°	733.9	734.3	734.6	734.9	735.2	735.5	735.8	736.1	736.3	736.6	736.5
125°	800.0	800.2	799.8	799.3	798.9	798.4	799.1	799.8	800.4	801.1	801.5
127.5°	858.6	859.2	860.3	861.3	862.3	863.3	863.2	863.1	862.9	862.8	862.6
130°	898.1	898.6	899.3	899.9	900.6	901.3	901.5	901.7	901.9	902.1	902.3
132.5°	935.1	935.7	936.6	937.5	938.3	939.2	939.4	939.6	939.9	940.1	940.1
135°	987.0	987.3	988.3	989.2	990.1	991.0	991.4	991.9	992.3	992.8	993.2
137.5°	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5	1042.0	1042.5	1043.0	1043.1
140°	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3	1073.0	1073.7	1074.3	1074.8
142.5°	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2	1101.7	1102.2	1102.7	1102.9
145°	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5	1142.7	1142.9	1143.1	1143.5
147.5°	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5	1178.6	1178.8	1179.0	1179.2
150°	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6	1201.6	1201.6	1201.6	1201.7
152.5°	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4	1221.7	1222.1	1222.4	1222.5
155°	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9	1248.8	1249.7	1250.6	1250.7
157.5°	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4
160°	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7
162.5°	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8	1299.1	1300.5	1301.8	1301.7
165°	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3	1316.2	1318.0	1319.7	1319.6
167.5°	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7	1328.6	1330.6	1332.5	1332.4
170°	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5	1336.4	1338.1	1339.9	1339.7
172.5°	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4	1341.2	1342.9	1344.7	1344.4
175°	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8	1346.9	1348.9	1350.9	1350.5
177.5°	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7	1349.1	1350.5	1352.0	1351.6
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1654.0	1655.1	1651.2	1650.1	1651.2	1655.1	1654.0	1657.4	1657.9	1662.3	1660.7
5°	1534.5	1533.1	1529.5	1530.2	1529.5	1533.1	1534.5	1540.0	1542.9	1554.0	1552.7
7.5°	1432.3	1426.8	1428.4	1422.8	1428.4	1426.8	1432.3	1437.3	1445.8	1450.9	1462.7
10°	1369.7	1362.0	1355.7	1350.2	1355.7	1362.0	1369.7	1372.5	1384.4	1390.0	1401.8
12.5°	1284.2	1277.7	1269.2	1270.9	1269.2	1277.7	1284.2	1296.6	1311.8	1323.5	1342.1
15°	1163.1	1152.6	1135.9	1137.9	1135.9	1152.6	1163.1	1172.2	1187.5	1214.1	1226.6
17.5°	1060.5	1060.6	1052.9	1054.7	1052.9	1060.6	1060.5	1072.9	1080.7	1097.6	1116.8
20°	1007.4	1002.5	1003.2	1001.1	1003.2	1002.5	1007.4	1022.1	1030.5	1042.3	1063.3
22.5°	970.6	964.5	959.7	955.3	959.7	964.5	970.6	974.6	985.7	997.0	1014.1
25°	908.3	904.0	897.8	896.4	897.8	904.0	908.3	914.5	920.1	934.8	945.2
27.5°	853.5	852.7	850.2	847.0	850.2	852.7	853.5	859.1	866.4	875.8	889.0
30°	821.7	820.3	818.9	816.8	818.9	820.3	821.7	827.3	832.8	840.5	851.0
32.5°	793.2	792.3	790.9	791.1	790.9	792.3	793.2	796.0	799.3	809.3	817.5
35°	752.6	751.8	750.5	749.8	750.5	751.8	752.6	755.4	757.5	760.2	767.2
37.5°	714.6	716.4	715.6	715.4	715.6	716.4	714.6	715.3	713.1	718.1	722.9
40°	688.3	689.0	690.4	689.7	690.4	689.0	688.3	689.0	689.0	689.0	693.3
42.5°	666.6	666.7	668.6	666.3	668.6	666.7	666.6	663.9	660.6	661.2	662.5
45°	627.6	631.8	631.1	631.1	631.1	631.8	627.6	622.7	622.1	619.2	619.2
47.5°	585.0	588.7	589.7	589.5	589.7	588.7	585.0	583.2	580.0	577.2	576.9
50°	557.1	555.7	557.8	557.1	557.8	555.7	557.1	553.6	548.8	548.8	547.3
52.5°	523.0	523.3	523.2	522.5	523.2	523.3	523.0	521.2	519.2	516.8	516.0
55°	470.5	471.2	469.8	470.5	469.8	471.2	470.5	469.8	469.8	468.5	469.8
57.5°	413.5	410.2	411.6	409.9	411.6	410.2	413.5	416.7	417.8	418.1	420.1
60°	372.8	367.2	365.8	363.0	365.8	367.2	372.8	379.8	382.5	384.0	386.1
62.5°	327.0	323.1	318.3	320.5	318.3	323.1	327.0	334.6	340.7	345.5	350.3
65°	266.0	263.2	261.1	263.9	261.1	263.2	266.0	271.6	277.1	288.3	298.8
67.5°	220.2	218.6	218.6	217.2	218.6	218.6	220.2	223.0	226.5	232.6	242.4
70°	196.2	194.1	194.1	192.7	194.1	194.1	196.2	196.2	199.7	202.5	209.4
72.5°	171.6	169.5	170.1	169.3	170.1	169.5	171.6	172.2	175.6	176.7	179.9
75°	127.0	123.6	123.6	124.3	123.6	123.6	127.0	131.3	134.7	141.0	142.4
77.5°	94.8	94.1	95.1	93.8	95.1	94.1	94.8	94.8	95.5	98.5	100.8
80°	77.5	76.7	76.1	78.2	76.1	76.7	77.5	77.5	78.2	78.9	79.6
82.5°	60.2	60.1	59.9	62.5	59.9	60.1	60.2	61.3	61.4	61.0	61.7
85°	36.3	34.9	36.3	34.9	36.3	34.9	36.3	35.6	36.3	35.6	36.3
87.5°	18.6	18.2	17.7	18.4	17.7	18.2	18.6	17.4	17.3	18.1	17.3
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.6	26.3	24.8
92.5°	27.6	27.7	27.8	27.9	27.8	27.7	27.6	27.5	26.8	25.4	24.0
95°	28.6	28.8	29.0	29.2	29.0	28.8	28.6	28.4	27.6	26.3	24.8
97.5°	27.6	27.8	28.0	28.3	28.0	27.8	27.6	27.4	27.2	27.1	26.9
100°	27.6	27.8	28.0	28.3	28.0	27.8	27.6	27.4	29.1	32.9	36.8
102.5°	28.9	29.0	29.0	29.1	29.0	29.0	28.9	28.9	49.4	90.5	131.6
105°	311.5	303.5	295.4	287.3	295.4	303.5	311.5	319.6	322.6	320.5	318.6
107.5°	397.9	398.7	399.6	400.4	399.6	398.7	397.9	397.0	396.1	395.2	394.2
110°	447.6	448.3	449.0	449.6	449.0	448.3	447.6	447.0	446.4	446.0	445.5



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	496.2	497.2	498.0	498.8	498.0	497.2	496.2	495.4	495.0	495.1	495.2
115°	570.6	570.6	570.6	570.6	570.6	570.6	570.6	570.6	570.4	570.0	569.5
117.5°	643.9	643.8	643.7	643.6	643.7	643.8	643.9	644.0	644.0	644.1	644.2
120°	690.8	690.4	690.0	689.5	690.0	690.4	690.8	691.4	691.4	690.8	690.4
122.5°	736.1	735.6	735.2	734.7	735.2	735.6	736.1	736.5	736.6	736.3	736.1
125°	801.8	802.0	802.2	802.4	802.2	802.0	801.8	801.5	801.1	800.4	799.8
127.5°	862.5	862.3	862.1	861.9	862.1	862.3	862.5	862.6	862.8	862.9	863.1
130°	902.3	902.3	902.3	902.3	902.3	902.3	902.3	902.3	902.1	901.9	901.7
132.5°	939.9	939.7	939.6	939.4	939.6	939.7	939.9	940.1	940.1	939.9	939.6
135°	993.7	994.1	994.5	995.0	994.5	994.1	993.7	993.2	992.8	992.3	991.9
137.5°	1043.0	1042.9	1042.7	1042.6	1042.7	1042.9	1043.0	1043.1	1043.0	1042.5	1042.0
140°	1075.0	1075.2	1075.4	1075.7	1075.4	1075.2	1075.0	1074.8	1074.3	1073.7	1073.0
142.5°	1103.0	1103.0	1103.1	1103.1	1103.1	1103.0	1103.0	1102.9	1102.7	1102.2	1101.7
145°	1143.9	1144.3	1144.8	1145.2	1144.8	1144.3	1143.9	1143.5	1143.1	1142.9	1142.7
147.5°	1179.4	1179.6	1179.9	1180.1	1179.9	1179.6	1179.4	1179.2	1179.0	1178.8	1178.6
150°	1202.0	1202.2	1202.4	1202.6	1202.4	1202.2	1202.0	1201.7	1201.6	1201.6	1201.6
152.5°	1222.4	1222.3	1222.1	1222.0	1222.1	1222.3	1222.4	1222.5	1222.4	1222.1	1221.7
155°	1250.1	1249.4	1248.7	1248.1	1248.7	1249.4	1250.1	1250.7	1250.6	1249.7	1248.8
157.5°	1273.3	1272.1	1271.0	1269.8	1271.0	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1
160°	1288.4	1287.1	1285.7	1284.3	1285.7	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1
162.5°	1300.2	1298.7	1297.2	1295.7	1297.2	1298.7	1300.2	1301.7	1301.8	1300.5	1299.1
165°	1317.6	1315.6	1313.5	1311.5	1313.5	1315.6	1317.6	1319.6	1319.7	1318.0	1316.2
167.5°	1330.2	1328.0	1325.6	1323.4	1325.6	1328.0	1330.2	1332.4	1332.5	1330.6	1328.6
170°	1337.5	1335.2	1332.9	1330.7	1332.9	1335.2	1337.5	1339.7	1339.9	1338.1	1336.4
172.5°	1342.0	1339.6	1337.2	1334.7	1337.2	1339.6	1342.0	1344.4	1344.7	1342.9	1341.2
175°	1347.9	1345.1	1342.5	1339.8	1342.5	1345.1	1347.9	1350.5	1350.9	1348.9	1346.9
177.5°	1349.5	1347.4	1345.1	1343.0	1345.1	1347.4	1349.5	1351.6	1352.0	1350.5	1349.1
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1657.4	1661.2	1670.2	1680.2	1688.6	1695.9	1701.4	1709.3	1716.6	1726.6	1736.1
5°	1556.8	1566.6	1580.5	1597.3	1618.2	1632.2	1649.7	1665.1	1687.4	1709.7	1731.3
7.5°	1468.5	1479.4	1499.9	1523.0	1547.9	1570.7	1591.4	1618.5	1648.1	1680.6	1717.0
10°	1411.6	1423.5	1447.9	1474.4	1503.8	1526.1	1554.0	1586.1	1619.6	1659.4	1704.1
12.5°	1360.2	1371.5	1401.0	1428.1	1458.5	1483.1	1515.5	1548.1	1592.9	1636.0	1686.8
15°	1260.1	1290.1	1323.6	1355.7	1392.1	1422.1	1461.2	1494.7	1537.3	1598.0	1656.0
17.5°	1148.9	1180.9	1222.5	1272.1	1320.8	1358.0	1397.7	1439.3	1490.0	1552.0	1618.8
20°	1084.2	1110.0	1156.1	1211.2	1267.8	1319.5	1355.7	1401.8	1454.2	1521.3	1590.3
22.5°	1035.6	1057.5	1093.6	1148.7	1209.7	1269.7	1316.1	1361.6	1419.6	1486.6	1561.9
25°	962.7	986.4	1017.8	1055.6	1125.4	1188.9	1249.6	1302.0	1363.4	1430.5	1514.2
27.5°	902.1	922.8	951.5	990.8	1037.7	1107.8	1181.3	1241.1	1304.1	1376.0	1460.0
30°	866.4	883.1	906.9	946.6	991.4	1054.2	1128.8	1198.7	1262.2	1336.9	1424.2
32.5°	829.0	846.9	870.0	901.4	949.5	1002.2	1076.9	1153.5	1220.9	1297.3	1382.8
35°	779.1	793.0	814.1	846.2	889.4	935.4	1001.8	1080.7	1152.0	1233.6	1315.2
37.5°	728.7	745.2	761.6	790.3	825.8	875.4	929.6	1010.2	1089.0	1163.7	1243.3
40°	700.2	710.0	728.1	751.1	788.9	832.8	883.8	962.7	1041.6	1115.6	1195.9
42.5°	668.4	679.2	694.6	717.7	751.4	794.4	844.1	912.4	994.7	1066.4	1139.4
45°	624.1	630.4	645.8	665.3	693.3	736.5	782.6	843.3	920.8	989.3	1053.5
47.5°	579.5	584.9	594.5	612.4	643.7	678.4	721.5	776.1	844.0	912.4	966.7
50°	548.8	553.6	562.7	579.5	607.3	641.6	684.2	733.1	793.8	859.4	904.7
52.5°	518.0	520.7	529.2	548.2	571.6	605.3	643.4	688.3	745.2	799.6	845.6
55°	469.2	475.4	481.0	494.9	517.4	549.5	583.6	626.2	670.2	716.3	755.4
57.5°	418.2	425.1	433.1	445.5	463.1	493.0	523.7	558.3	595.8	634.0	666.8
60°	384.7	390.9	397.9	411.9	428.0	451.7	485.2	515.2	543.8	578.8	611.6
62.5°	351.7	358.0	366.1	377.3	392.7	415.4	443.3	469.4	499.2	529.6	554.0
65°	303.0	307.9	314.2	324.7	339.3	359.5	382.5	402.8	429.4	451.7	474.0
67.5°	249.5	258.8	267.1	275.6	288.0	306.9	323.6	343.0	360.9	377.6	397.9
70°	214.3	224.8	232.5	241.6	253.4	269.4	285.5	298.8	313.5	329.5	347.7
72.5°	184.7	193.0	198.9	208.6	219.3	234.3	249.2	260.2	272.2	283.2	300.7
75°	145.9	149.4	153.6	161.3	171.1	182.2	194.1	203.9	210.9	220.7	233.2
77.5°	104.8	111.6	114.3	119.8	126.7	133.8	141.6	149.9	156.5	160.0	169.7
80°	80.3	83.1	85.8	93.5	97.8	104.7	110.3	118.0	120.8	124.3	133.3
82.5°	62.4	64.1	65.7	67.9	70.4	77.4	82.9	87.9	90.6	91.9	98.8
85°	36.3	37.0	37.7	38.4	39.1	39.1	41.9	45.3	50.3	50.3	52.3
87.5°	17.0	17.3	17.0	16.0	16.8	16.4	16.6	16.1	17.3	18.4	19.6
90°	23.5	22.2	20.4	18.6	16.8	15.0	12.9	10.4	8.0	5.5	3.0
92.5°	22.7	21.4	19.6	17.8	16.0	14.2	13.2	13.1	12.9	12.8	12.7
95°	23.5	22.2	21.9	21.7	21.5	21.3	24.9	32.6	40.2	47.9	55.4
97.5°	26.8	26.7	51.6	76.6	101.6	126.6	136.7	132.0	127.2	122.5	117.8
100°	40.6	44.3	75.2	106.2	137.1	168.0	181.5	177.4	173.4	169.4	165.3
102.5°	172.6	213.7	217.7	221.8	225.8	229.8	230.4	227.4	224.5	221.6	218.5
105°	316.6	314.6	313.5	312.3	311.1	310.0	308.8	307.5	306.1	304.8	303.5
107.5°	393.1	392.1	390.6	389.1	387.6	386.1	385.0	384.3	383.6	382.9	382.2
110°	445.0	444.5	443.2	441.9	440.5	439.2	438.2	437.5	436.9	436.2	435.6



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	495.3	495.3	494.7	494.1	493.5	492.9	492.0	490.8	489.6	488.4	487.2
115°	569.1	568.6	568.8	569.1	569.3	569.5	569.3	568.6	567.9	567.2	566.5
117.5°	644.3	644.4	643.9	643.4	642.9	642.4	641.8	640.9	640.0	639.0	638.1
120°	690.0	689.5	689.7	690.0	690.2	690.4	690.1	689.2	688.3	687.4	686.5
122.5°	735.8	735.5	735.2	734.9	734.6	734.3	733.9	733.3	732.8	732.3	731.6
125°	799.1	798.4	798.9	799.3	799.8	800.2	800.0	799.1	798.2	797.3	796.4
127.5°	863.2	863.3	862.3	861.3	860.3	859.2	858.6	858.4	858.2	857.9	857.7
130°	901.5	901.3	900.6	899.9	899.3	898.6	898.1	897.9	897.7	897.5	897.3
132.5°	939.4	939.2	938.3	937.5	936.6	935.7	935.1	934.7	934.3	933.9	933.5
135°	991.4	991.0	990.1	989.2	988.3	987.3	987.0	987.2	987.5	987.7	988.0
137.5°	1041.5	1041.0	1040.0	1039.1	1038.0	1037.0	1036.5	1036.4	1036.3	1036.2	1036.1
140°	1072.3	1071.7	1071.2	1070.8	1070.3	1069.9	1069.3	1068.9	1068.5	1068.0	1067.6
142.5°	1101.2	1100.7	1100.3	1100.1	1099.8	1099.5	1099.0	1098.2	1097.4	1096.6	1095.8
145°	1142.5	1142.2	1142.2	1142.2	1142.2	1142.2	1141.9	1141.1	1140.5	1139.8	1139.1
147.5°	1178.5	1178.3	1178.5	1178.7	1178.9	1179.2	1178.7	1177.4	1176.2	1174.9	1173.7
150°	1201.6	1201.6	1201.9	1202.1	1202.3	1202.5	1202.2	1201.3	1200.4	1199.5	1198.6
152.5°	1221.4	1221.0	1221.4	1221.8	1222.2	1222.6	1222.4	1221.7	1221.0	1220.3	1219.6
155°	1247.9	1247.1	1247.7	1248.4	1249.1	1249.7	1249.9	1249.7	1249.5	1249.3	1249.1
157.5°	1271.0	1269.8	1270.6	1271.3	1272.1	1272.8	1273.3	1273.4	1273.5	1273.7	1273.8
160°	1285.7	1284.3	1284.5	1284.8	1285.1	1285.3	1285.7	1286.4	1287.1	1287.7	1288.4
162.5°	1297.8	1296.5	1296.7	1296.9	1297.1	1297.4	1297.9	1298.7	1299.6	1300.4	1301.3
165°	1314.3	1312.5	1312.5	1312.5	1312.5	1312.5	1313.1	1314.2	1315.3	1316.5	1317.6
167.5°	1326.7	1324.6	1324.8	1324.9	1325.0	1325.2	1325.9	1327.1	1328.2	1329.4	1330.5
170°	1334.5	1332.7	1332.5	1332.3	1332.0	1331.8	1332.4	1333.7	1335.0	1336.5	1337.8
172.5°	1339.4	1337.6	1337.4	1337.2	1336.9	1336.7	1337.3	1338.6	1339.9	1341.3	1342.6
175°	1344.8	1342.8	1342.6	1342.4	1342.1	1341.9	1342.5	1343.8	1345.1	1346.6	1347.9
177.5°	1347.7	1346.3	1345.8	1345.5	1345.1	1344.8	1345.2	1346.6	1347.8	1349.0	1350.3
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1743.3	1748.4	1753.9	1764.5	1773.5	1777.5	1785.2	1790.8	1789.2	1797.0	1810.4
5°	1750.2	1769.1	1790.7	1813.0	1838.2	1859.1	1875.8	1892.6	1905.9	1922.0	1945.7
7.5°	1749.1	1782.6	1819.1	1859.1	1900.3	1935.9	1968.8	2002.4	2032.1	2064.7	2107.2
10°	1744.6	1789.3	1834.6	1887.0	1939.3	1988.9	2033.7	2075.5	2115.4	2157.9	2211.7
12.5°	1739.6	1791.0	1845.8	1908.8	1974.0	2033.7	2086.2	2146.5	2196.3	2251.2	2313.3
15°	1717.4	1786.5	1861.2	1942.9	2021.0	2101.3	2173.2	2247.3	2316.3	2382.0	2460.2
17.5°	1691.9	1771.7	1859.8	1956.3	2050.2	2147.9	2233.1	2326.4	2397.1	2485.2	2557.8
20°	1671.3	1757.2	1851.4	1959.6	2066.5	2174.6	2268.9	2363.9	2443.5	2532.1	2624.2
22.5°	1646.2	1740.4	1842.5	1954.6	2066.5	2184.7	2289.0	2383.4	2481.9	2581.8	2676.7
25°	1605.7	1703.4	1811.6	1934.5	2063.0	2183.7	2295.4	2412.7	2518.8	2627.1	2712.2
27.5°	1556.0	1658.6	1772.7	1899.5	2031.2	2155.0	2286.5	2411.5	2518.3	2622.4	2696.7
30°	1516.3	1624.6	1734.1	1862.6	1999.4	2132.0	2273.1	2398.0	2510.4	2604.0	2645.8
32.5°	1475.5	1578.2	1691.1	1821.3	1961.5	2104.2	2244.0	2371.8	2475.8	2531.9	2533.0
35°	1404.6	1501.0	1618.2	1746.1	1889.9	2044.8	2186.6	2312.2	2375.7	2380.6	2312.2
37.5°	1327.3	1415.6	1526.4	1654.3	1811.8	1965.9	2110.7	2194.4	2215.7	2144.7	2018.1
40°	1272.0	1353.6	1460.5	1591.7	1748.1	1907.2	2039.2	2100.6	2078.3	1963.1	1822.1
42.5°	1213.9	1290.0	1392.9	1522.5	1679.4	1840.3	1952.7	1985.6	1926.4	1793.3	1628.3
45°	1119.1	1188.9	1290.8	1421.4	1572.2	1722.9	1808.2	1791.4	1692.9	1535.2	1350.2
47.5°	1020.4	1087.8	1179.5	1300.3	1454.7	1584.9	1642.5	1592.1	1452.0	1278.4	1127.9
50°	955.0	1024.1	1108.6	1223.9	1364.8	1490.5	1527.5	1450.7	1295.1	1128.1	990.0
52.5°	890.8	949.9	1032.7	1144.0	1278.8	1384.9	1404.6	1316.1	1155.4	1005.8	883.2
55°	793.0	846.9	916.7	1021.4	1137.9	1228.0	1217.5	1103.8	957.9	830.1	733.8
57.5°	698.5	739.0	803.5	901.7	1004.0	1064.5	1026.2	929.2	793.2	688.6	607.3
60°	636.0	673.7	733.8	819.6	909.7	943.8	911.7	806.4	698.8	603.2	534.7
62.5°	576.8	610.1	661.7	741.4	814.2	834.4	800.0	708.0	611.2	529.5	472.8
65°	490.8	521.5	565.5	622.1	672.3	682.1	659.7	565.5	492.2	423.7	384.7
67.5°	412.7	432.8	467.2	516.0	542.7	548.5	505.3	446.1	381.4	339.4	309.9
70°	360.2	374.2	406.3	432.8	454.4	455.1	415.4	367.9	318.3	284.2	262.5
72.5°	309.4	322.9	347.1	365.3	381.8	376.5	340.0	302.6	262.5	236.7	220.7
75°	238.7	250.6	263.2	271.6	271.6	264.6	238.0	210.2	187.1	171.8	166.8
77.5°	173.6	183.3	187.5	186.2	183.8	172.9	156.1	137.8	129.6	122.3	118.7
80°	136.1	140.4	141.7	138.3	134.0	121.5	110.3	102.6	94.9	92.2	90.8
82.5°	101.0	104.6	101.0	101.9	92.7	82.4	76.2	73.6	70.4	69.3	67.9
85°	53.7	53.0	51.7	48.2	41.9	40.5	39.8	39.1	37.7	38.4	37.0
87.5°	19.5	18.4	16.6	16.6	17.0	16.2	17.2	17.5	17.9	17.6	19.0
90°	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5	24.8
92.5°	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7	24.0
95°	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5	24.8
97.5°	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8	26.9
100°	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6	36.8
102.5°	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6	131.6
105°	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6	318.6
107.5°	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1	394.2
110°	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0	445.5



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3	495.2
115°	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1	569.5
117.5°	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3	644.2
120°	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0	690.4
122.5°	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8	736.1
125°	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1	799.8
127.5°	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2	863.1
130°	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5	901.7
132.5°	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4	939.6
135°	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4	991.9
137.5°	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5	1042.0
140°	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3	1073.0
142.5°	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2	1101.7
145°	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5	1142.7
147.5°	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5	1178.6
150°	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6	1201.6
152.5°	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4	1221.7
155°	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9	1248.8
157.5°	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0	1272.1
160°	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7	1287.1
162.5°	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8	1299.1
165°	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3	1316.2
167.5°	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7	1328.6
170°	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5	1336.4
172.5°	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4	1341.2
175°	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8	1346.9
177.5°	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7	1349.1
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1817.7	1819.9	1821.6	1827.1	1827.7	1832.7	1827.7
5°	1968.0	1977.8	1993.2	2008.5	2009.9	2019.6	2002.3
7.5°	2136.7	2159.3	2173.4	2198.3	2208.1	2214.1	2204.1
10°	2252.8	2273.8	2310.8	2329.0	2347.1	2349.9	2341.5
12.5°	2365.1	2398.3	2427.5	2461.8	2461.0	2485.6	2476.7
15°	2514.7	2548.9	2589.3	2627.8	2641.7	2641.7	2652.9
17.5°	2621.3	2684.0	2725.9	2756.0	2789.0	2794.7	2790.9
20°	2693.4	2761.1	2805.8	2844.9	2867.2	2873.5	2873.5
22.5°	2746.9	2804.6	2848.2	2883.4	2901.8	2909.2	2907.0
25°	2784.1	2833.7	2860.2	2870.6	2875.6	2874.2	2860.9
27.5°	2733.3	2731.1	2714.3	2682.2	2658.1	2643.4	2626.7
30°	2636.2	2599.8	2557.9	2511.8	2452.6	2407.1	2393.2
32.5°	2491.4	2409.9	2338.9	2262.2	2198.4	2153.0	2134.0
35°	2211.7	2082.5	1977.1	1884.9	1818.0	1776.0	1762.1
37.5°	1879.7	1754.6	1624.2	1534.8	1479.1	1436.8	1421.1
40°	1668.5	1532.4	1418.6	1334.8	1277.6	1236.4	1235.7
42.5°	1475.8	1345.8	1238.8	1178.4	1116.7	1089.4	1089.3
45°	1208.4	1104.4	1013.7	966.2	929.2	906.9	900.6
47.5°	1000.6	914.5	854.0	816.3	786.1	771.8	762.7
50°	883.8	808.4	760.2	727.4	710.6	692.6	691.2
52.5°	786.7	725.8	688.2	661.6	640.4	629.4	629.8
55°	661.2	613.0	586.4	566.1	549.5	541.1	537.6
57.5°	556.9	520.8	501.5	482.9	475.8	469.3	467.5
60°	492.2	467.8	449.6	434.9	424.4	422.3	421.6
62.5°	438.6	413.0	400.4	389.1	381.4	378.2	377.0
65°	361.6	342.7	331.6	322.6	319.7	314.9	314.2
67.5°	291.5	280.2	272.9	266.5	262.8	262.5	262.5
70°	248.5	242.3	236.0	232.5	230.4	228.9	228.9
72.5°	211.7	207.0	201.9	200.1	199.7	198.2	197.7
75°	161.3	156.4	157.0	153.6	150.8	147.3	145.2
77.5°	114.3	110.9	110.2	109.8	107.3	106.9	108.1
80°	88.7	85.1	84.4	85.1	84.4	82.4	82.4
82.5°	67.5	64.5	63.8	63.4	62.7	63.4	62.3
85°	36.3	34.9	34.9	34.9	36.3	35.6	34.9
87.5°	18.1	17.8	18.6	18.1	18.2	17.7	18.4
90°	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	446.0	446.4	447.0	447.6	448.3	449.0	449.6



TEST NUMBER: P332973-840

CATALOG NUMBER: SA4XXRDIP-C1020D1035U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)