

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913169

Luminaire Tested: DFN2DIP-4P3F0-060D020US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913169
REPORT IS A COMBINATION OF REPORTS P900558 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-060D020US927-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5608.6 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913169
CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913169

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66	66	66	66	62
2	95	87	81	76	90	83	78	73	75	71	68	68	65	62	61	59	57	57	57	57	53
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	49	49	49	46
4	80	69	61	55	76	66	59	54	60	54	50	55	50	46	50	46	43	43	43	43	40
5	74	62	54	48	70	59	52	47	54	48	44	50	45	41	45	41	38	38	38	38	35
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34	34	34	34	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	34	30	30	30	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27	27	27	27	25
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25	25	25	25	23
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2239	2239	2239
5°	2241	2202	2216
10°	2217	2157	2144
15°	2185	2084	2031
20°	2143	1985	1894
25°	2101	1873	1762
30°	2044	1759	1593
35°	1988	1637	1446
40°	1931	1510	1277
45°	1865	1370	1124
50°	1796	1228	974
55°	1725	1077	830
60°	1642	919	683
65°	1546	759	614
70°	1430	610	555
75°	1284	534	503
80°	1073	443	434
85°	728	289	321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1865 cd/sqm



TEST NUMBER: P913169

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	3.3
10°-20°	505.4	9.0
20°-30°	709.6	12.7
30°-40°	773.5	13.8
40°-50°	710.9	12.7
50°-60°	558.3	10.0
60°-70°	363.4	6.5
70°-80°	187.1	3.3
80°-90°	48.7	0.9
90°-100°	17.6	0.3
100°-110°	65.7	1.2
110°-120°	174.3	3.1
120°-130°	289.1	5.2
130°-140°	307.1	5.5
140°-150°	285.4	5.1
150°-160°	229.5	4.1
160°-170°	147.9	2.6
170°-180°	50.9	0.9
0°-30°	1399.1	24.9
0°-40°	2172.6	38.7
0°-60°	3441.9	61.4
0°-90°	4041.1	72.1
90°-120°	257.7	4.6
90°-150°	1139.3	20.3
90°-180°	1568.0	28.0
0°-180°	5608.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1956	1932	1948	1943	186
15°	1868	1849	1788	1755	1737	527
25°	1696	1639	1522	1449	1422	780
35°	1461	1371	1214	1102	1063	915
45°	1195	1076	889	763	720	923
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	203	142	130	128	346
85°	76	39	34	34	34	88
90°	0	5	8	10	10	5
95°	25	12	15	17	17	30
105°	118	129	24	28	29	126
115°	222	229	239	60	32	219
125°	315	320	327	330	331	281
135°	389	396	399	403	402	301
145°	452	451	458	460	458	282
155°	497	494	498	501	498	229
165°	524	522	523	526	523	148
175°	536	533	534	537	533	51
180°	535	535	535	535	535	



TEST NUMBER: P913169

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.5	1964.5	1964.5	1964.5	1964.5
2.5°	1973.3	1964.5	1944.8	1962.7	1959.1
5°	1964.5	1955.6	1932.4	1948.4	1943.1
7.5°	1948.4	1937.8	1913.0	1919.9	1911.1
10°	1927.1	1914.6	1879.2	1873.7	1863.1
12.5°	1900.5	1884.4	1836.4	1825.8	1806.2
15°	1868.4	1848.8	1788.4	1754.7	1736.9
17.5°	1831.1	1802.6	1727.9	1688.9	1660.4
20°	1788.4	1752.8	1664.0	1619.6	1580.4
22.5°	1742.2	1701.3	1598.1	1537.8	1511.2
25°	1696.1	1639.1	1521.8	1449.0	1422.2
27.5°	1641.0	1580.4	1450.6	1367.1	1326.2
30°	1582.3	1514.6	1372.4	1281.8	1233.7
32.5°	1525.3	1443.5	1297.9	1191.1	1146.6
35°	1461.4	1370.7	1214.3	1102.2	1063.0
37.5°	1399.2	1301.2	1136.1	1013.3	968.9
40°	1333.3	1226.8	1054.2	928.0	881.8
42.5°	1265.8	1152.1	972.5	840.8	796.5
45°	1194.7	1075.5	889.0	762.6	719.9
47.5°	1127.2	1001.0	809.0	682.6	643.6
50°	1052.5	926.3	730.7	607.9	570.8
52.5°	979.5	846.1	656.0	538.7	504.9
55°	908.4	769.8	577.7	471.2	437.4
57.5°	835.6	693.3	508.5	408.9	380.4
60°	760.9	618.7	435.5	345.0	316.5
62.5°	688.1	545.9	373.3	288.0	273.9
65°	613.4	469.3	309.3	249.0	243.5
67.5°	542.2	398.2	249.0	218.6	213.3
70°	467.5	328.9	206.1	188.5	181.3
72.5°	396.5	264.8	172.4	158.3	154.6
75°	327.1	202.6	142.2	129.8	128.1
77.5°	257.9	143.9	112.0	104.9	101.3
80°	193.7	103.1	85.2	78.3	78.3
82.5°	135.1	69.4	58.6	55.1	55.1
85°	76.4	39.1	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.4	4.7	7.7	9.7	10.5
92.5°	9.7	8.2	9.3	10.1	10.5
95°	25.1	12.4	15.1	17.0	16.6
97.5°	45.2	13.5	19.7	20.9	21.3
100°	68.5	15.4	22.0	25.1	25.9
102.5°	94.0	93.2	22.8	27.1	28.3
105°	117.6	129.2	23.6	27.8	29.4
107.5°	145.1	154.7	24.4	28.6	30.2
110°	171.4	179.5	67.7	29.1	30.6



TEST NUMBER: P913169

CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	196.1	203.1	196.5	29.8	31.0
115°	222.4	229.0	238.8	59.6	31.8
117.5°	245.3	253.0	259.6	204.3	102.9
120°	270.8	276.6	283.6	288.3	236.0
122.5°	292.5	298.7	306.4	308.7	309.2
125°	314.6	319.6	326.9	329.6	330.8
127.5°	334.7	340.1	345.9	349.7	350.1
130°	353.6	359.8	364.1	368.4	368.0
132.5°	373.0	378.0	382.2	385.7	385.4
135°	389.3	395.5	398.9	402.8	402.0
137.5°	406.2	410.9	414.8	418.7	417.5
140°	422.9	426.0	430.2	433.7	431.8
142.5°	436.8	439.6	444.6	447.7	445.7
145°	451.5	451.1	457.7	460.4	458.5
147.5°	464.3	463.1	469.7	471.6	470.1
150°	476.7	474.0	480.1	482.4	480.5
152.5°	487.1	484.0	489.8	492.2	489.4
155°	497.2	493.7	498.4	500.7	497.6
157.5°	505.3	502.2	505.7	508.4	505.3
160°	512.3	509.9	512.3	514.6	511.9
162.5°	518.4	516.1	518.1	520.8	517.3
165°	523.9	521.6	522.7	525.5	522.7
167.5°	528.1	525.8	527.0	529.7	526.2
170°	531.6	529.3	530.0	532.7	529.3
172.5°	533.9	531.6	532.4	535.1	531.6
175°	535.8	533.1	533.9	536.6	532.7
177.5°	536.6	533.9	534.3	537.0	533.5
180°	534.7	534.7	534.7	534.7	534.7



TEST NUMBER: P913169
 CATALOG NUMBER: DFN2DIP-4P3F0-060D020US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.76	12.81	12.51	13.58	14.50	7.73	8.78	8.47	9.54	10.46
	3H	13.45	14.39	14.22	15.17	16.12	8.92	9.86	9.69	10.64	11.59
	4H	14.07	14.95	14.85	15.74	16.70	9.38	10.27	10.16	11.05	12.01
	6H	14.50	15.31	15.29	16.11	17.08	9.71	10.52	10.50	11.32	12.29
	8H	14.63	15.41	15.43	16.22	17.19	9.80	10.58	10.60	11.39	12.37
	12H	14.70	15.44	15.50	16.24	17.24	9.85	10.59	10.66	11.39	12.40
4H	2H	11.81	12.69	12.59	13.48	14.44	8.34	9.23	9.13	10.01	10.98
	3H	13.65	14.39	14.45	15.20	16.18	9.71	10.44	10.50	11.26	12.24
	4H	14.35	15.01	15.16	15.83	16.84	10.26	10.93	11.07	11.74	12.75
	6H	14.87	15.45	15.70	16.29	17.30	10.68	11.26	11.51	12.10	13.12
	8H	15.05	15.59	15.88	16.42	17.45	10.81	11.35	11.64	12.19	13.21
	12H	15.15	15.63	16.00	16.49	17.52	10.88	11.37	11.73	12.23	13.26
8H	4H	14.33	14.87	15.16	15.71	16.73	10.55	11.09	11.38	11.93	12.95
	6H	14.90	15.34	15.76	16.22	17.25	11.07	11.51	11.93	12.39	13.42
	8H	15.11	15.51	15.98	16.38	17.43	11.26	11.65	12.13	12.53	13.57
	12H	15.26	15.61	16.13	16.47	17.57	11.38	11.73	12.25	12.59	13.69
12H	4H	14.29	14.77	15.14	15.63	16.66	10.57	11.05	11.42	11.91	12.94
	6H	14.87	15.27	15.74	16.15	17.19	11.12	11.51	11.99	12.39	13.43
	8H	15.10	15.45	15.97	16.32	17.41	11.33	11.68	12.21	12.55	13.65