

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332966-840

Luminaire Tested: **SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332966-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6347.2 lumens  
Efficiency: N/A  
Efficacy: 130.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	102	98	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	44	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36	42	37	33	37	33	30	27
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.3	2.7
10°-20°	477.7	7.5
20°-30°	689.8	10.9
30°-40°	781.8	12.3
40°-50°	755.0	11.9
50°-60°	627.8	9.9
60°-70°	433.5	6.8
70°-80°	219.7	3.5
80°-90°	58.0	0.9
90°-100°	211.8	3.3
100°-110°	440.8	6.9
110°-120°	394.8	6.2
120°-130°	332.1	5.2
130°-140°	276.9	4.4
140°-150°	211.5	3.3
150°-160°	148.7	2.3
160°-170°	87.5	1.4
170°-180°	28.5	0.4
0°-30°	1338.7	21.1
0°-40°	2120.6	33.4
0°-60°	3503.4	55.2
0°-90°	4214.7	66.4
90°-120°	1047.4	16.5
90°-150°	1868.0	29.4
90°-180°	2133.0	33.6
0°-180°	6347.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	1	5	10	12	12	5
95°	19	60	470	232	141	21
105°	67	98	378	814	810	72
115°	119	149	337	648	778	118
125°	165	196	335	551	621	147
135°	196	234	332	489	555	152
145°	226	259	331	412	453	142
155°	258	278	321	364	380	119
165°	280	289	308	326	331	79
175°	293	293	296	300	298	28
180°	293	293	293	293	293	



TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	25.9	24.0	22.4	20.5	18.7	17.6	18.0	17.8	17.8	17.7	17.4
90°	0.6	1.7	3.4	4.0	4.6	4.6	8.1	8.1	9.2	10.4	9.8
92.5°	6.6	9.6	14.9	22.0	30.4	42.4	71.7	116.3	160.0	182.7	152.2
95°	19.0	20.7	26.5	34.0	47.8	72.0	122.1	216.6	354.3	469.5	482.7
97.5°	34.1	34.1	39.1	45.9	57.9	78.2	116.7	194.7	331.6	494.5	606.5
100°	43.8	43.8	47.8	54.7	65.6	84.1	118.1	183.2	300.7	463.1	610.7
102.5°	53.0	53.9	57.5	63.9	74.4	91.9	122.7	180.0	279.9	424.0	576.0
105°	67.4	69.2	72.0	79.0	89.3	106.0	133.6	181.5	262.2	377.9	513.3
107.5°	83.3	84.4	87.4	94.7	104.6	121.1	146.4	190.0	258.9	352.1	462.6
110°	93.9	95.0	98.0	104.8	115.2	130.8	156.1	196.4	259.8	343.4	437.3



TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	104.0	105.2	108.6	115.0	125.3	140.9	165.3	203.4	262.6	339.2	422.9
115°	118.7	120.4	124.4	130.2	141.2	156.7	179.8	214.3	267.9	337.0	409.6
117.5°	133.9	135.5	139.1	145.4	155.6	171.8	193.7	225.5	273.5	336.4	403.6
120°	144.0	145.2	149.2	155.5	165.3	181.5	203.4	233.3	277.7	336.4	400.4
122.5°	153.2	154.4	158.4	164.3	175.0	190.7	212.6	240.7	281.9	336.0	396.7
125°	165.3	167.6	171.1	177.4	188.3	204.5	225.2	251.8	288.0	335.3	390.6
127.5°	176.0	177.9	182.1	189.2	200.7	216.9	237.0	261.4	293.0	334.0	382.4
130°	182.1	184.3	188.9	197.6	208.5	225.2	244.8	267.3	296.7	333.6	377.3
132.5°	188.0	189.9	195.9	204.1	215.9	231.7	251.3	273.3	299.9	333.1	372.7
135°	196.4	198.7	204.5	214.3	226.4	241.4	260.3	281.1	304.8	332.3	365.8
137.5°	204.9	207.0	213.4	222.7	235.3	249.5	267.3	286.7	307.6	332.2	359.8
140°	210.9	212.6	218.9	228.7	240.8	254.6	272.0	290.3	309.9	331.8	356.6
142.5°	217.3	219.0	224.9	234.2	245.9	259.2	276.1	293.1	311.7	331.8	353.9
145°	226.4	228.1	233.9	242.0	252.9	265.6	280.5	296.1	312.9	330.6	349.1
147.5°	236.6	237.2	242.3	250.5	259.7	271.1	285.2	298.7	313.4	328.6	344.9
150°	243.1	243.7	248.3	255.2	263.9	274.8	287.5	300.1	313.4	327.2	341.6
152.5°	249.1	249.2	253.8	260.2	268.0	278.0	289.3	301.0	312.5	324.9	337.9
155°	257.5	258.1	261.6	267.3	273.7	282.3	292.1	301.8	311.0	321.4	332.3
157.5°	265.7	265.7	268.9	273.4	278.9	285.7	294.1	301.8	309.6	317.9	326.8
160°	270.7	270.7	273.1	277.1	281.7	288.0	295.0	301.8	308.2	315.1	322.7
162.5°	275.4	274.9	276.7	280.3	284.5	289.4	295.9	301.8	306.8	312.4	318.9
165°	280.5	280.5	281.7	284.6	287.5	290.9	296.1	300.7	304.2	308.2	312.9
167.5°	285.7	285.2	285.7	287.9	289.5	292.2	296.0	299.3	301.4	304.1	307.3
170°	288.0	287.5	288.0	289.7	290.9	292.7	295.5	298.4	299.5	301.2	303.6
172.5°	290.3	289.7	289.8	291.1	291.9	293.1	295.1	297.5	297.7	298.5	300.3
175°	292.7	292.1	292.1	292.7	293.3	293.3	294.4	296.1	295.5	295.5	296.7
177.5°	293.7	293.3	292.8	293.3	293.3	293.3	293.7	294.6	293.7	293.7	294.2
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3



TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	17.2	17.1	17.0	17.0	17.3	17.7	17.8	18.1
90°	10.4	10.9	11.5	11.5	12.1	12.6	12.1	12.1
92.5°	113.1	85.1	67.8	56.2	49.4	46.4	44.3	44.3
95°	426.9	337.6	260.3	204.5	176.3	158.4	148.0	140.6
97.5°	630.7	597.5	541.2	481.0	439.7	405.0	387.7	375.7
100°	694.8	706.3	678.0	635.4	585.3	550.2	532.9	528.3
102.5°	691.6	748.7	756.9	739.1	708.3	682.9	664.7	661.0
105°	645.2	744.9	801.9	825.6	826.7	822.0	814.0	810.5
107.5°	579.5	685.5	765.9	817.2	845.7	858.8	864.5	866.1
110°	539.8	639.4	723.0	786.4	827.3	851.4	861.8	867.0





TEST NUMBER: P332966-840

CATALOG NUMBER: SA4XXRDIP-C1020D590U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	510.8	598.8	677.8	741.1	787.6	816.9	831.4	839.8
115°	481.6	552.5	619.9	675.2	720.6	755.3	773.7	778.3
117.5°	467.3	525.9	579.0	625.8	664.7	693.7	712.4	716.0
120°	460.9	514.4	560.5	601.4	634.3	659.6	674.6	681.0
122.5°	455.3	507.1	549.0	584.8	612.6	634.3	646.9	653.3
125°	445.9	495.4	535.1	566.8	589.9	606.6	617.5	621.0
127.5°	434.3	481.7	521.4	551.4	574.6	589.5	598.6	602.1
130°	425.2	470.7	509.8	540.4	564.0	578.3	587.6	591.1
132.5°	415.5	458.2	496.4	526.9	550.2	566.4	575.1	578.7
135°	402.1	439.6	474.6	503.5	526.5	542.7	551.9	555.3
137.5°	390.0	421.7	451.3	477.4	498.9	514.8	522.4	526.5
140°	383.0	410.2	436.1	460.3	480.5	493.1	501.2	505.8
142.5°	376.7	400.5	422.7	443.7	461.5	473.3	480.5	483.6
145°	367.5	387.1	404.5	420.5	434.9	444.7	450.5	453.3
147.5°	360.0	375.6	389.4	402.1	412.7	421.1	425.5	426.6
150°	355.5	368.7	380.2	390.6	399.8	407.3	410.7	411.3
152.5°	350.3	361.7	372.3	380.9	388.7	394.9	396.9	397.5
155°	342.7	351.9	360.6	367.5	373.3	377.9	379.6	379.6
157.5°	334.6	342.3	349.5	355.1	359.5	362.9	364.0	364.0
160°	329.5	335.9	342.1	346.8	350.2	353.8	354.3	354.3
162.5°	324.5	329.8	334.8	339.0	341.5	345.0	345.6	345.1
165°	317.4	320.8	324.9	327.8	330.1	332.3	331.8	331.2
167.5°	310.6	313.3	316.5	318.2	319.4	320.8	320.7	320.3
170°	306.5	308.2	310.5	312.3	313.4	314.0	313.4	313.4
172.5°	302.8	304.1	305.5	306.7	307.4	308.0	307.4	306.5
175°	297.8	298.4	299.5	299.5	299.5	300.7	299.5	298.4
177.5°	294.6	295.1	295.1	295.5	295.1	295.5	294.6	293.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3

(END OF REPORT)