

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915835

Luminaire Tested: DFN2DIP-4P3F0-030D020US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915835
REPORT IS A COMBINATION OF REPORTS P900551 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US930-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4035.7 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1085	1085	1085
5°	1086	1069	1076
10°	1076	1054	1061
15°	1060	1036	1038
20°	1038	1011	1015
25°	1016	981	987
30°	988	954	953
35°	962	921	916
40°	930	889	881
45°	899	856	846
50°	864	821	804
55°	827	781	766
60°	786	734	723
65°	741	685	671
70°	683	625	616
75°	603	554	564
80°	507	462	466
85°	357	306	305

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 899 cd/sqm

TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.2
10°-20°	252.0	6.2
20°-30°	370.4	9.2
30°-40°	430.2	10.7
40°-50°	429.7	10.6
50°-60°	374.6	9.3
60°-70°	277.0	6.9
70°-80°	156.7	3.9
80°-90°	42.3	1.0
90°-100°	18.1	0.4
100°-110°	67.6	1.7
110°-120°	179.4	4.4
120°-130°	297.6	7.4
130°-140°	316.1	7.8
140°-150°	293.8	7.3
150°-160°	236.2	5.9
160°-170°	152.2	3.8
170°-180°	52.4	1.3
0°-30°	712.0	17.6
0°-40°	1142.2	28.3
0°-60°	1946.5	48.2
0°-90°	2422.4	60.0
90°-120°	265.2	6.6
90°-150°	1172.6	29.1
90°-180°	1613.0	40.0
0°-180°	4035.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	0	5	8	10	11	4
95°	26	13	16	18	17	31
105°	121	133	24	29	30	129
115°	229	236	246	61	33	225
125°	324	329	336	339	340	289
135°	401	407	410	415	414	309
145°	465	464	471	474	472	291
155°	512	508	513	515	512	236
165°	539	537	538	541	538	152
175°	552	549	550	552	548	52
180°	550	550	550	550	550	

TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	0.4	4.8	7.9	9.9	10.8
92.5°	9.9	8.4	9.5	10.4	10.8
95°	25.8	12.7	15.5	17.5	17.1
97.5°	46.6	13.9	20.3	21.5	21.9
100°	70.5	15.9	22.7	25.8	26.7
102.5°	96.8	96.0	23.5	27.9	29.1
105°	121.1	133.0	24.3	28.6	30.2
107.5°	149.4	159.2	25.1	29.4	31.1
110°	176.4	184.7	69.7	29.9	31.5



TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.9	209.0	202.3	30.7	31.9
115°	228.9	235.7	245.7	61.3	32.7
117.5°	252.4	260.4	267.2	210.3	105.9
120°	278.8	284.7	291.9	296.7	242.9
122.5°	301.0	307.4	315.4	317.7	318.2
125°	323.8	328.9	336.5	339.2	340.5
127.5°	344.5	350.0	356.0	360.0	360.4
130°	363.9	370.3	374.7	379.1	378.7
132.5°	383.8	389.1	393.4	397.0	396.6
135°	400.6	407.0	410.5	414.6	413.8
137.5°	418.1	422.9	426.9	430.9	429.7
140°	435.2	438.5	442.8	446.4	444.4
142.5°	449.6	452.4	457.5	460.7	458.7
145°	464.7	464.3	471.1	473.9	471.9
147.5°	477.8	476.6	483.4	485.3	483.8
150°	490.6	487.8	494.2	496.5	494.6
152.5°	501.3	498.1	504.1	506.5	503.7
155°	511.7	508.1	512.9	515.3	512.1
157.5°	520.1	516.9	520.5	523.3	520.1
160°	527.3	524.8	527.3	529.6	526.8
162.5°	533.5	531.2	533.2	536.0	532.4
165°	539.2	536.8	537.9	540.8	537.9
167.5°	543.6	541.1	542.3	545.2	541.5
170°	547.1	544.7	545.5	548.3	544.7
172.5°	549.5	547.1	548.0	550.7	547.1
175°	551.5	548.7	549.5	552.3	548.3
177.5°	552.3	549.5	549.9	552.7	549.1
180°	550.3	550.3	550.3	550.3	550.3

TEST NUMBER: P915835

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.40	9.36	9.26	10.24	11.36	7.95	8.91	8.82	9.80	10.92
	3H	10.06	10.92	10.94	11.82	12.96	9.57	10.43	10.45	11.33	12.47
	4H	10.65	11.46	11.54	12.37	13.52	10.16	10.97	11.05	11.87	13.03
	6H	11.05	11.80	11.96	12.71	13.88	10.55	11.30	11.46	12.21	13.38
	8H	11.16	11.87	12.07	12.80	13.97	10.66	11.37	11.57	12.30	13.47
	12H	11.21	11.89	12.13	12.81	14.00	10.70	11.38	11.62	12.30	13.49
4H	2H	8.87	9.68	9.77	10.58	11.74	8.51	9.33	9.41	10.23	11.38
	3H	10.74	11.41	11.65	12.35	13.52	10.33	11.01	11.24	11.94	13.11
	4H	11.45	12.07	12.37	13.00	14.20	11.03	11.65	11.95	12.58	13.77
	6H	11.97	12.50	12.90	13.46	14.65	11.54	12.07	12.47	13.02	14.22
	8H	12.12	12.62	13.05	13.56	14.78	11.68	12.18	12.62	13.13	14.34
	12H	12.19	12.64	13.15	13.61	14.83	11.74	12.19	12.70	13.16	14.38
8H	4H	11.65	12.15	12.59	13.10	14.31	11.27	11.77	12.21	12.72	13.93
	6H	12.28	12.69	13.24	13.68	14.89	11.90	12.31	12.86	13.30	14.51
	8H	12.50	12.86	13.47	13.84	15.07	12.11	12.47	13.08	13.45	14.68
	12H	12.63	12.95	13.61	13.93	15.20	12.22	12.54	13.20	13.51	14.79
12H	4H	11.64	12.09	12.60	13.06	14.27	11.27	11.72	12.23	12.69	13.91
	6H	12.31	12.68	13.28	13.65	14.88	11.94	12.30	12.91	13.28	14.51
	8H	12.55	12.87	13.53	13.85	15.12	12.17	12.49	13.15	13.47	14.74