

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333006-840

Luminaire Tested: **SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P333006-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9039.0 lumens  
Efficiency: N/A  
Efficacy: 135.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54				54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46				46
2	90	83	77	72	84	77	72	68	66	62	59	56	54	51	47	45	43	39				39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33				33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29				29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25				25
6	64	52	44	38	59	49	42	36	42	37	33	37	32	29	31	28	25	22				22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20				20
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20	18				18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16				16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15				15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.8	2.2
10°-20°	551.7	6.1
20°-30°	796.6	8.8
30°-40°	903.0	10.0
40°-50°	872.0	9.6
50°-60°	725.1	8.0
60°-70°	500.7	5.5
70°-80°	253.8	2.8
80°-90°	69.0	0.8
90°-100°	46.1	0.5
100°-110°	293.9	3.3
110°-120°	562.3	6.2
120°-130°	713.8	7.9
130°-140°	763.7	8.4
140°-150°	714.1	7.9
150°-160°	575.9	6.4
160°-170°	371.4	4.1
170°-180°	128.0	1.4
0°-30°	1546.1	17.1
0°-40°	2449.1	27.1
0°-60°	4046.2	44.8
0°-90°	4869.7	53.9
90°-120°	902.3	10.0
90°-150°	3094.0	34.2
90°-180°	4169.0	46.1
0°-180°	9039.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	3	14	22	28	30	7
95°	55	23	22	28	29	71
105°	304	309	315	321	287	317
115°	566	569	569	570	571	557
125°	796	800	798	801	802	711
135°	988	987	991	993	995	761
145°	1139	1142	1142	1143	1145	712
155°	1249	1250	1247	1251	1248	576
165°	1318	1313	1312	1320	1312	372
175°	1348	1342	1343	1351	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.3	28.5	26.7	24.8	23.0	22.2	22.3	22.3	22.4	22.5	22.5
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	12.7	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7
95°	55.4	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5
97.5°	117.8	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8
100°	165.3	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6
102.5°	218.5	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6
105°	303.5	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6
107.5°	382.2	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1
110°	435.6	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0



TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3
115°	566.5	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1
117.5°	638.1	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3
120°	686.5	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0
122.5°	731.6	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8
125°	796.4	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1
127.5°	857.7	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2
130°	897.3	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5
132.5°	933.5	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4
135°	988.0	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4
137.5°	1036.1	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5
140°	1067.6	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3
142.5°	1095.8	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2
145°	1139.1	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
147.5°	1173.7	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5
150°	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6
152.5°	1219.6	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4
155°	1249.1	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9
157.5°	1273.8	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0
160°	1288.4	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7
162.5°	1301.3	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8
165°	1317.6	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3
167.5°	1330.5	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7
170°	1337.8	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5
172.5°	1342.6	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4
175°	1347.9	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8
177.5°	1350.3	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	22.4	22.4	22.4	22.6	23.0	23.3	23.7	24.1
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	24.0	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	24.8	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	26.9	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	36.8	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	131.6	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	318.6	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	394.2	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	445.5	446.0	446.4	447.0	447.6	448.3	449.0	449.6





TEST NUMBER: P333006-840

CATALOG NUMBER: SA4XXRDIP-C1195D1035U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.2	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	569.5	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.2	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.1	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	799.8	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	863.1	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.7	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.6	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	991.9	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.0	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.0	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1101.7	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.7	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.6	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1221.7	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1248.8	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1299.1	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1316.2	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1328.6	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1336.4	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1341.2	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1346.9	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1349.1	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)