

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915855

Luminaire Tested: DFN2DIP-4P3F0-040D020US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915855
REPORT IS A COMBINATION OF REPORTS P900553 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-040D020US930-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4842.9 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 53
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1446	1446	1446
5°	1447	1425	1435
10°	1435	1405	1415
15°	1413	1381	1384
20°	1383	1348	1353
25°	1354	1308	1316
30°	1318	1272	1270
35°	1283	1228	1222
40°	1240	1185	1175
45°	1198	1141	1128
50°	1152	1095	1072
55°	1103	1042	1022
60°	1048	979	964
65°	988	913	895
70°	911	834	821
75°	805	738	752
80°	676	616	622
85°	477	408	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1198 cd/sqm

TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.5
10°-20°	336.0	6.9
20°-30°	493.8	10.2
30°-40°	573.6	11.8
40°-50°	572.9	11.8
50°-60°	499.5	10.3
60°-70°	369.3	7.6
70°-80°	208.9	4.3
80°-90°	56.1	1.2
90°-100°	18.1	0.4
100°-110°	67.6	1.4
110°-120°	179.4	3.7
120°-130°	297.6	6.1
130°-140°	316.1	6.5
140°-150°	293.8	6.1
150°-160°	236.2	4.9
160°-170°	152.2	3.1
170°-180°	52.4	1.1
0°-30°	949.3	19.6
0°-40°	1522.9	31.4
0°-60°	2595.3	53.6
0°-90°	3229.6	66.7
90°-120°	265.2	5.5
90°-150°	1172.6	24.2
90°-180°	1613.0	33.3
0°-180°	4842.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	0	5	8	10	11	4
95°	26	13	16	18	17	31
105°	121	133	24	29	30	129
115°	229	236	246	61	33	225
125°	324	329	336	339	340	289
135°	401	407	410	415	414	309
145°	465	464	471	474	472	291
155°	512	508	513	515	512	236
165°	539	537	538	541	538	152
175°	552	549	550	552	548	52
180°	550	550	550	550	550	

TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.4	4.8	7.9	9.9	10.8
92.5°	9.9	8.4	9.5	10.4	10.8
95°	25.8	12.7	15.5	17.5	17.1
97.5°	46.6	13.9	20.3	21.5	21.9
100°	70.5	15.9	22.7	25.8	26.7
102.5°	96.8	96.0	23.5	27.9	29.1
105°	121.1	133.0	24.3	28.6	30.2
107.5°	149.4	159.2	25.1	29.4	31.1
110°	176.4	184.7	69.7	29.9	31.5

TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.9	209.0	202.3	30.7	31.9
115°	228.9	235.7	245.7	61.3	32.7
117.5°	252.4	260.4	267.2	210.3	105.9
120°	278.8	284.7	291.9	296.7	242.9
122.5°	301.0	307.4	315.4	317.7	318.2
125°	323.8	328.9	336.5	339.2	340.5
127.5°	344.5	350.0	356.0	360.0	360.4
130°	363.9	370.3	374.7	379.1	378.7
132.5°	383.8	389.1	393.4	397.0	396.6
135°	400.6	407.0	410.5	414.6	413.8
137.5°	418.1	422.9	426.9	430.9	429.7
140°	435.2	438.5	442.8	446.4	444.4
142.5°	449.6	452.4	457.5	460.7	458.7
145°	464.7	464.3	471.1	473.9	471.9
147.5°	477.8	476.6	483.4	485.3	483.8
150°	490.6	487.8	494.2	496.5	494.6
152.5°	501.3	498.1	504.1	506.5	503.7
155°	511.7	508.1	512.9	515.3	512.1
157.5°	520.1	516.9	520.5	523.3	520.1
160°	527.3	524.8	527.3	529.6	526.8
162.5°	533.5	531.2	533.2	536.0	532.4
165°	539.2	536.8	537.9	540.8	537.9
167.5°	543.6	541.1	542.3	545.2	541.5
170°	547.1	544.7	545.5	548.3	544.7
172.5°	549.5	547.1	548.0	550.7	547.1
175°	551.5	548.7	549.5	552.3	548.3
177.5°	552.3	549.5	549.9	552.7	549.1
180°	550.3	550.3	550.3	550.3	550.3

TEST NUMBER: P915855

CATALOG NUMBER: DFN2DIP-4P3F0-040D020US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.93	10.97	10.73	11.79	12.80	9.49	10.52	10.29	11.34	12.36
	3H	11.60	12.53	12.41	13.36	14.40	11.11	12.04	11.92	12.87	13.91
	4H	12.19	13.07	13.02	13.91	14.96	11.70	12.58	12.53	13.42	14.47
	6H	12.60	13.41	13.44	14.26	15.32	12.10	12.91	12.94	13.76	14.82
	8H	12.71	13.48	13.56	14.34	15.41	12.21	12.98	13.06	13.84	14.91
	12H	12.76	13.50	13.62	14.35	15.45	12.25	12.99	13.11	13.85	14.94
4H	2H	10.41	11.29	11.24	12.13	13.18	10.06	10.93	10.89	11.77	12.82
	3H	12.29	13.02	13.13	13.89	14.96	11.88	12.61	12.72	13.48	14.55
	4H	13.00	13.67	13.86	14.54	15.64	12.58	13.25	13.44	14.12	15.21
	6H	13.53	14.10	14.40	15.00	16.09	13.09	13.67	13.97	14.56	15.66
	8H	13.68	14.22	14.55	15.11	16.22	13.24	13.78	14.12	14.67	15.78
	12H	13.76	14.24	14.65	15.15	16.27	13.31	13.79	14.20	14.70	15.82
8H	4H	13.21	13.75	14.09	14.64	15.75	12.83	13.37	13.71	14.26	15.37
	6H	13.84	14.29	14.75	15.22	16.33	13.46	13.91	14.36	14.84	15.95
	8H	14.06	14.46	14.98	15.38	16.51	13.67	14.07	14.58	14.99	16.12
	12H	14.20	14.55	15.12	15.46	16.64	13.79	14.14	14.71	15.05	16.23
12H	4H	13.20	13.69	14.10	14.60	15.71	12.84	13.32	13.73	14.23	15.35
	6H	13.87	14.27	14.79	15.19	16.32	13.50	13.90	14.42	14.82	15.95
	8H	14.12	14.47	15.04	15.38	16.56	13.74	14.09	14.66	15.00	16.18

END OF REPORT