

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332995-840

Luminaire Tested: **SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332995-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6934.2 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60				
2	94	86	80	75	89	82	77	72	74	69	66	66	63	60	59	57	54	51				
3	86	76	69	63	81	73	66	61	65	60	56	59	55	51	53	49	47	43				
4	79	68	60	54	74	65	57	52	58	53	48	53	48	44	47	44	41	38				
5	73	61	52	46	68	58	50	45	52	46	42	47	42	39	43	39	36	33				
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	31	29				
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	36	31	28	26				
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21				
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.8	2.9
10°-20°	551.7	8.0
20°-30°	796.6	11.5
30°-40°	903.0	13.0
40°-50°	872.0	12.6
50°-60°	725.1	10.5
60°-70°	500.7	7.2
70°-80°	253.8	3.7
80°-90°	67.3	1.0
90°-100°	49.1	0.7
100°-110°	145.5	2.1
110°-120°	247.0	3.6
120°-130°	325.7	4.7
130°-140°	365.7	5.3
140°-150°	359.4	5.2
150°-160°	302.3	4.4
160°-170°	201.1	2.9
170°-180°	70.4	1.0
0°-30°	1546.1	22.3
0°-40°	2449.1	35.3
0°-60°	4046.2	58.4
0°-90°	4868.0	70.2
90°-120°	441.6	6.4
90°-150°	1492.4	21.5
90°-180°	2066.0	29.8
0°-180°	6934.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	2	8	13	16	17	6
95°	34	40	44	45	46	38
105°	134	135	137	139	141	142
115°	251	251	250	249	249	248
125°	366	366	365	364	363	326
135°	472	475	475	474	472	365
145°	573	575	576	575	574	358
155°	657	657	656	658	656	302
165°	715	713	712	715	713	201
175°	744	741	740	744	740	71
180°	745	745	745	745	745	



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	30.0	28.0	26.0	23.9	22.0	20.9	20.8	20.8	20.7	20.6	20.5
90°	1.7	3.1	4.5	6.0	7.4	8.6	9.6	10.6	11.6	12.6	13.4
92.5°	12.3	13.9	15.6	17.2	18.8	19.9	20.7	21.4	22.1	22.8	23.2
95°	34.5	35.7	36.9	38.0	39.2	40.2	41.1	42.0	42.9	43.7	44.1
97.5°	60.4	61.3	62.2	63.1	64.0	65.0	66.0	67.2	68.2	69.3	69.7
100°	80.6	81.2	81.7	82.2	82.7	83.5	84.6	85.8	86.9	88.2	88.4
102.5°	101.8	102.0	102.2	102.4	102.6	103.3	104.3	105.3	106.4	107.4	107.9
105°	134.2	134.3	134.4	134.6	134.7	135.0	135.5	136.0	136.5	137.0	137.4
107.5°	168.1	168.3	168.4	168.6	168.8	169.0	169.0	169.1	169.2	169.3	169.6
110°	191.3	191.5	191.8	192.0	192.3	192.3	192.2	192.1	192.0	191.8	191.6



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	215.2	215.2	215.3	215.3	215.4	215.3	215.1	214.8	214.6	214.4	214.3
115°	251.2	251.2	251.2	251.2	251.2	251.0	250.7	250.4	250.2	249.9	249.8
117.5°	285.0	285.1	285.2	285.3	285.4	285.4	285.2	285.0	284.8	284.7	284.2
120°	307.6	308.1	308.6	309.1	309.6	309.7	309.3	308.9	308.5	308.1	307.5
122.5°	331.0	331.2	331.4	331.6	331.8	331.9	331.7	331.5	331.3	331.2	330.7
125°	365.8	365.8	365.8	365.8	365.8	365.7	365.6	365.5	365.3	365.2	364.9
127.5°	397.2	397.6	398.0	398.4	398.7	398.8	398.6	398.4	398.2	398.0	397.8
130°	419.3	419.7	420.1	420.5	420.8	421.0	421.0	421.0	421.0	421.0	420.8
132.5°	441.9	442.2	442.4	442.7	443.0	443.1	443.0	442.9	442.8	442.7	442.4
135°	471.7	472.5	473.2	474.0	474.8	475.1	475.1	475.1	475.1	475.1	474.9
137.5°	504.2	504.5	504.9	505.2	505.6	505.9	506.1	506.3	506.5	506.8	506.4
140°	525.8	526.1	526.3	526.6	526.8	527.0	527.0	527.0	527.0	527.0	526.8
142.5°	545.6	545.9	546.2	546.4	546.7	546.7	546.6	546.5	546.4	546.3	546.3
145°	573.1	573.6	574.1	574.6	575.1	575.4	575.6	575.7	575.8	575.9	575.8
147.5°	600.3	600.9	601.5	602.1	602.8	603.0	602.9	602.8	602.7	602.6	602.5
150°	616.8	617.4	617.9	618.4	618.9	619.1	619.1	619.1	619.1	619.1	619.1
152.5°	632.6	632.9	633.2	633.5	633.8	634.0	634.1	634.2	634.3	634.4	634.7
155°	656.6	656.6	656.6	656.6	656.6	656.5	656.4	656.3	656.2	656.0	656.5
157.5°	676.9	676.6	676.4	676.2	676.0	675.8	675.8	675.8	675.8	675.7	676.1
160°	688.8	688.7	688.6	688.5	688.3	688.2	688.1	688.0	687.8	687.7	688.1
162.5°	699.9	699.6	699.2	698.9	698.6	698.3	698.2	698.1	698.0	697.8	698.5
165°	714.8	714.4	714.0	713.7	713.3	713.0	712.7	712.5	712.2	712.0	712.7
167.5°	726.2	725.7	725.1	724.6	724.1	723.8	723.8	723.9	723.9	723.9	724.7
170°	732.7	732.1	731.3	730.7	730.0	729.8	729.9	730.0	730.2	730.3	731.1
172.5°	737.2	736.7	736.2	735.7	735.1	734.9	734.9	734.9	734.9	735.0	735.8
175°	743.6	743.0	742.4	741.6	741.0	740.6	740.5	740.4	740.2	740.1	741.0
177.5°	745.7	745.2	744.7	744.2	743.6	743.4	743.4	743.4	743.4	743.4	744.1
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	20.3	20.2	20.1	20.2	20.5	20.8	21.2	21.5
90°	14.2	14.9	15.8	16.3	16.6	16.8	17.1	17.3
92.5°	23.7	24.2	24.6	24.9	25.1	25.2	25.4	25.5
95°	44.5	44.9	45.3	45.5	45.5	45.5	45.5	45.5
97.5°	70.2	70.6	71.1	71.3	71.3	71.3	71.3	71.3
100°	88.7	88.9	89.2	89.3	89.3	89.3	89.3	89.3
102.5°	108.2	108.6	108.9	109.2	109.3	109.4	109.5	109.6
105°	137.8	138.3	138.7	139.0	139.4	139.8	140.2	140.6
107.5°	170.0	170.3	170.7	170.9	170.8	170.8	170.8	170.8
110°	191.3	191.1	190.8	190.9	191.3	191.6	192.0	192.4



TEST NUMBER: P332995-840

CATALOG NUMBER: SA4XXRDIP-C1195D590U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.3	214.2	214.2	214.2	214.3	214.3	214.4	214.5
115°	249.7	249.6	249.4	249.3	249.2	249.0	248.9	248.8
117.5°	283.8	283.4	282.9	282.6	282.3	282.1	281.8	281.6
120°	306.9	306.2	305.6	305.4	305.7	305.9	306.2	306.4
122.5°	330.3	329.9	329.4	329.0	328.5	328.1	327.6	327.2
125°	364.7	364.4	364.2	363.9	363.7	363.3	363.1	362.8
127.5°	397.5	397.3	397.0	396.8	396.6	396.4	396.2	396.0
130°	420.5	420.3	420.0	419.6	419.1	418.6	418.1	417.6
132.5°	442.2	441.9	441.7	441.4	441.2	441.0	440.8	440.6
135°	474.6	474.4	474.1	473.8	473.4	473.0	472.7	472.3
137.5°	506.0	505.7	505.4	505.2	505.3	505.4	505.5	505.6
140°	526.7	526.6	526.5	526.3	526.2	526.1	526.0	525.8
142.5°	546.3	546.3	546.2	546.2	546.2	546.2	546.1	546.1
145°	575.7	575.6	575.4	575.2	574.8	574.4	574.0	573.7
147.5°	602.4	602.3	602.2	602.1	602.0	601.8	601.7	601.6
150°	619.1	619.1	619.1	619.1	618.9	618.8	618.7	618.6
152.5°	635.0	635.3	635.6	635.6	635.3	634.9	634.6	634.3
155°	657.0	657.5	658.1	658.1	657.5	657.0	656.5	656.0
157.5°	676.5	676.9	677.3	677.2	676.8	676.4	675.9	675.5
160°	688.5	688.8	689.2	689.1	688.5	687.8	687.2	686.6
162.5°	699.2	699.9	700.6	700.6	700.0	699.3	698.7	698.1
165°	713.5	714.2	715.0	715.1	714.6	714.1	713.6	713.1
167.5°	725.4	726.2	727.0	726.9	726.2	725.4	724.6	723.8
170°	731.8	732.7	733.4	733.4	732.5	731.5	730.6	729.7
172.5°	736.7	737.6	738.4	738.4	737.5	736.6	735.7	734.9
175°	741.9	742.9	743.7	743.7	742.9	741.9	741.0	740.1
177.5°	744.8	745.5	746.2	746.2	745.4	744.6	743.7	742.9
180°	744.8	744.8	744.8	744.8	744.8	744.8	744.8	744.8

(END OF REPORT)