

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332870-840

Luminaire Tested: **SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332870-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2764.6 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332870-840
CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332870-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52				
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42	38				
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32				
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28				
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24				
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22				
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19				
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17				
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16				
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332870-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	2.1
10°-20°	163.5	5.9
20°-30°	236.1	8.5
30°-40°	267.7	9.7
40°-50°	258.5	9.3
50°-60°	214.9	7.8
60°-70°	148.4	5.4
70°-80°	75.2	2.7
80°-90°	20.3	0.7
90°-100°	131.2	4.7
100°-110°	273.1	9.9
110°-120°	244.6	8.8
120°-130°	205.8	7.4
130°-140°	171.6	6.2
140°-150°	131.1	4.7
150°-160°	92.1	3.3
160°-170°	54.2	2.0
170°-180°	17.6	0.6
0°-30°	458.3	16.6
0°-40°	726.0	26.3
0°-60°	1199.4	43.4
0°-90°	1443.3	52.2
90°-120°	648.9	23.5
90°-150°	1157.3	41.9
90°-180°	1321.0	47.8
0°-180°	2764.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	0	3	6	7	8	2
95°	12	37	291	144	87	13
105°	42	60	234	504	502	45
115°	74	92	209	401	482	73
125°	102	122	208	341	385	91
135°	122	145	206	303	344	94
145°	140	161	205	256	281	88
155°	160	172	199	226	235	74
165°	174	179	191	202	205	49
175°	181	182	183	186	185	17
180°	182	182	182	182	182	



TEST NUMBER: P332870-840
 CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	8.9	8.3	7.9	7.3	6.7	6.3	6.6	6.6	6.6	6.7	6.5
90°	0.4	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.8	6.5	6.1
92.5°	4.0	6.0	9.3	13.6	18.9	26.3	44.4	72.1	99.1	113.2	94.3
95°	11.8	12.8	16.5	21.1	29.6	44.6	75.6	134.2	219.5	290.8	299.1
97.5°	21.1	21.1	24.2	28.5	35.9	48.4	72.3	120.7	205.4	306.4	375.8
100°	27.2	27.2	29.6	33.9	40.7	52.1	73.2	113.5	186.3	287.0	378.3
102.5°	32.8	33.4	35.6	39.6	46.2	57.0	76.0	111.5	173.5	262.7	356.9
105°	41.8	42.8	44.6	48.9	55.3	65.6	82.8	112.4	162.4	234.1	318.0
107.5°	51.6	52.3	54.1	58.7	64.8	75.0	90.7	117.8	160.4	218.1	286.6
110°	58.2	58.9	60.7	64.9	71.4	81.0	96.7	121.7	161.0	212.7	270.9



TEST NUMBER: P332870-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.4	65.1	67.3	71.2	77.7	87.3	102.4	126.0	162.7	210.2	262.1
115°	73.5	74.6	77.1	80.7	87.5	97.0	111.4	132.8	165.9	208.8	253.8
117.5°	82.9	83.9	86.1	90.1	96.4	106.4	120.0	139.7	169.5	208.4	250.0
120°	89.3	90.0	92.4	96.3	102.4	112.4	126.0	144.5	172.1	208.4	248.0
122.5°	94.9	95.6	98.2	101.8	108.5	118.2	131.7	149.2	174.6	208.1	245.8
125°	102.4	103.8	106.0	110.0	116.7	126.7	139.6	155.9	178.4	207.7	242.0
127.5°	109.1	110.2	112.8	117.2	124.3	134.4	146.8	161.9	181.6	206.9	236.9
130°	112.8	114.2	117.0	122.4	129.2	139.6	151.7	165.6	183.8	206.6	233.8
132.5°	116.5	117.6	121.4	126.4	133.8	143.5	155.7	169.4	185.8	206.4	231.0
135°	121.7	123.1	126.7	132.8	140.3	149.6	161.3	174.2	188.8	205.9	226.6
137.5°	126.9	128.3	132.2	137.9	145.7	154.6	165.6	177.6	190.6	205.9	223.0
140°	130.7	131.7	135.6	141.7	149.2	157.7	168.4	179.9	192.0	205.6	221.0
142.5°	134.6	135.7	139.4	145.1	152.3	160.6	171.1	181.6	193.2	205.6	219.2
145°	140.3	141.4	144.9	149.9	156.7	164.5	173.8	183.5	193.8	204.9	216.3
147.5°	146.6	146.9	150.2	155.2	160.9	167.9	176.6	185.1	194.2	203.6	213.7
150°	150.6	151.0	153.8	158.1	163.5	170.3	178.1	185.9	194.2	202.7	211.7
152.5°	154.3	154.4	157.2	161.3	166.0	172.3	179.3	186.5	193.6	201.3	209.3
155°	159.6	159.9	162.1	165.6	169.6	174.9	181.0	187.0	192.8	199.1	205.9
157.5°	164.6	164.6	166.6	169.4	172.8	177.0	182.2	187.0	191.8	196.9	202.5
160°	167.7	167.7	169.2	171.7	174.5	178.4	182.8	187.0	191.0	195.2	199.9
162.5°	170.6	170.4	171.5	173.7	176.2	179.4	183.3	187.0	190.1	193.5	197.6
165°	173.8	173.8	174.5	176.3	178.1	180.3	183.5	186.3	188.4	191.0	193.8
167.5°	177.0	176.6	177.0	178.3	179.4	181.1	183.4	185.4	186.7	188.3	190.4
170°	178.4	178.1	178.4	179.6	180.3	181.3	183.1	184.9	185.6	186.6	188.1
172.5°	179.9	179.6	179.6	180.4	180.8	181.6	182.8	184.3	184.5	184.9	186.1
175°	181.3	181.0	181.0	181.3	181.7	181.7	182.4	183.5	183.1	183.1	183.8
177.5°	182.0	181.7	181.4	181.7	181.7	181.7	182.0	182.5	182.0	182.0	182.3
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7



TEST NUMBER: P332870-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	6.5	6.5	6.5	6.5	6.6	6.8	6.8	6.9
90°	6.5	6.8	7.2	7.2	7.5	7.9	7.5	7.5
92.5°	70.1	52.7	42.0	34.8	30.6	28.7	27.5	27.5
95°	264.5	209.1	161.3	126.7	109.2	98.2	91.7	87.1
97.5°	390.7	370.2	335.3	298.0	272.4	251.0	240.2	232.8
100°	430.4	437.6	420.1	393.6	362.6	340.8	330.1	327.3
102.5°	428.5	463.8	468.9	457.9	438.9	423.1	411.8	409.5
105°	399.7	461.5	496.9	511.5	512.2	509.3	504.3	502.2
107.5°	359.0	424.7	474.4	506.3	523.9	532.1	535.6	536.5
110°	334.5	396.2	448.0	487.2	512.5	527.6	533.9	537.1



TEST NUMBER: P332870-840

CATALOG NUMBER: SA4XXRDIP-C350D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.4	371.0	419.9	459.2	488.0	506.1	515.1	520.3
115°	298.4	342.2	384.1	418.3	446.5	467.9	479.4	482.2
117.5°	289.5	325.9	358.7	387.8	411.8	429.8	441.3	443.5
120°	285.5	318.7	347.3	372.6	392.9	408.7	418.0	421.9
122.5°	282.1	314.2	340.1	362.3	379.5	392.9	400.8	404.8
125°	276.3	306.9	331.5	351.2	365.5	375.9	382.6	384.8
127.5°	269.1	298.4	323.1	341.6	356.0	365.2	370.9	373.0
130°	263.4	291.6	315.9	334.8	349.4	358.3	364.1	366.2
132.5°	257.4	283.9	307.6	326.5	340.8	350.9	356.4	358.5
135°	249.1	272.4	294.1	311.9	326.2	336.2	341.9	344.1
137.5°	241.7	261.3	279.6	295.7	309.1	318.9	323.7	326.2
140°	237.3	254.1	270.1	285.2	297.7	305.5	310.5	313.4
142.5°	233.4	248.1	261.9	274.9	286.0	293.3	297.7	299.6
145°	227.7	239.8	250.5	260.5	269.4	275.5	279.1	280.8
147.5°	223.1	232.7	241.3	249.1	255.7	260.9	263.6	264.3
150°	220.3	228.4	235.6	242.0	247.7	252.4	254.5	254.8
152.5°	217.1	224.2	230.8	236.0	240.9	244.6	245.9	246.3
155°	212.4	218.0	223.4	227.7	231.3	234.1	235.2	235.2
157.5°	207.3	212.1	216.6	220.0	222.7	224.9	225.5	225.5
160°	204.2	208.0	212.0	214.9	217.0	219.1	219.5	219.5
162.5°	201.1	204.4	207.4	210.1	211.6	213.7	214.1	213.8
165°	196.6	198.8	201.3	203.1	204.5	205.9	205.6	205.2
167.5°	192.5	194.1	196.1	197.1	197.8	198.8	198.7	198.4
170°	189.9	191.0	192.4	193.5	194.2	194.5	194.2	194.2
172.5°	187.6	188.3	189.2	190.1	190.5	190.8	190.5	189.9
175°	184.5	184.9	185.6	185.6	185.6	186.3	185.6	184.9
177.5°	182.5	182.8	182.8	183.1	182.8	183.1	182.5	182.0
180°	181.7	181.7	181.7	181.7	181.7	181.7	181.7	181.7

(END OF REPORT)