

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332945-840

Luminaire Tested: **SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332945-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7104.6 lumens  
Efficiency: N/A  
Efficacy: 136.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41				41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35				35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30				30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26				26
5	69	58	50	44	63	53	46	41	46	40	36	38	34	31	31	28	26	23				23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15				15
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13				13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	1.8
10°-20°	389.6	5.5
20°-30°	609.4	8.6
30°-40°	677.4	9.5
40°-50°	601.0	8.5
50°-60°	468.4	6.6
60°-70°	306.6	4.3
70°-80°	150.8	2.1
80°-90°	40.0	0.6
90°-100°	370.6	5.2
100°-110°	771.4	10.9
110°-120°	690.9	9.7
120°-130°	581.2	8.2
130°-140°	484.6	6.8
140°-150°	370.2	5.2
150°-160°	260.2	3.7
160°-170°	153.1	2.2
170°-180°	49.8	0.7
0°-30°	1128.1	15.9
0°-40°	1805.6	25.4
0°-60°	2875.0	40.5
0°-90°	3372.5	47.5
90°-120°	1833.0	25.8
90°-150°	3269.0	46.0
90°-180°	3732.0	52.5
0°-180°	7104.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	21	1	21	1	21	18
95°	246	33	246	33	246	382
105°	1418	118	1418	118	1418	1402
115°	1362	208	1362	208	1362	1352
125°	1087	289	1087	289	1087	988
135°	972	344	972	344	972	750
145°	794	396	794	396	794	503
155°	664	451	664	451	664	310
165°	580	491	580	491	580	166
175°	522	512	522	512	522	51
180°	513	513	513	513	513	



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	13.7	13.2	13.9	13.7	13.9	13.5	13.7	14.3	13.3	13.9	13.5
90°	21.2	21.2	22.2	21.2	20.2	20.2	19.2	18.2	17.2	18.2	16.2
92.5°	77.7	77.7	81.1	86.5	98.4	118.6	149.1	198.0	266.4	319.8	279.8
95°	246.0	259.1	277.2	308.5	357.9	455.7	590.8	747.0	844.9	821.6	620.1
97.5°	657.5	678.5	708.7	769.4	841.8	947.1	1045.6	1103.8	1061.4	865.4	580.3
100°	924.5	932.5	962.8	1024.3	1112.0	1186.6	1236.0	1215.9	1068.6	810.5	526.2
102.5°	1156.8	1163.3	1195.1	1239.6	1293.4	1324.5	1310.2	1210.2	1008.1	742.0	490.0
105°	1418.5	1424.5	1438.7	1446.7	1444.7	1403.3	1303.5	1129.1	898.3	661.4	458.7
107.5°	1515.7	1513.1	1503.0	1480.0	1430.2	1340.3	1199.7	1014.0	809.5	616.2	453.0
110°	1517.3	1508.2	1490.1	1447.7	1376.1	1265.3	1119.0	944.6	765.2	600.9	454.6



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1469.7	1455.0	1429.6	1378.4	1297.1	1186.2	1048.0	893.8	740.2	593.6	459.5
115°	1362.0	1353.9	1321.7	1261.2	1181.5	1084.8	966.8	842.8	716.8	589.8	468.8
117.5°	1252.9	1246.7	1214.1	1163.3	1095.3	1013.2	920.5	817.8	706.3	588.8	478.7
120°	1191.6	1180.5	1154.4	1109.9	1052.5	981.0	900.3	806.5	700.6	588.8	485.9
122.5°	1143.3	1132.2	1109.9	1072.1	1023.5	960.8	887.4	796.9	694.2	587.9	493.2
125°	1086.8	1080.8	1061.6	1032.4	992.0	936.5	867.0	780.3	683.6	586.7	504.1
127.5°	1053.7	1047.6	1031.6	1005.5	965.0	912.4	843.0	760.1	669.2	584.5	512.7
130°	1034.4	1028.3	1012.2	986.9	945.6	892.2	823.6	744.1	660.4	583.7	519.2
132.5°	1012.6	1006.5	991.2	962.8	922.3	868.8	801.9	727.1	652.3	582.9	524.8
135°	971.9	965.8	949.7	921.5	881.1	830.7	769.2	703.7	640.2	581.7	533.3
137.5°	921.5	914.2	900.9	873.0	835.4	789.8	738.0	682.6	629.7	581.5	538.4
140°	885.1	877.1	863.0	840.8	805.5	763.2	717.8	670.4	624.1	580.7	542.4
142.5°	846.5	840.8	828.3	807.7	776.5	739.8	700.8	659.1	619.2	580.7	545.6
145°	793.5	788.4	778.3	761.1	736.0	707.7	677.5	643.2	611.0	578.7	547.4
147.5°	746.4	744.7	737.0	722.3	703.7	681.6	657.3	630.1	603.5	575.0	548.5
150°	719.8	718.8	712.8	699.6	683.6	665.4	645.2	622.1	597.8	572.6	548.5
152.5°	695.6	694.6	690.9	680.3	666.6	651.7	633.1	613.2	591.4	568.6	546.8
155°	664.4	664.4	661.4	653.3	643.2	631.1	616.0	599.9	581.7	562.6	544.4
157.5°	636.9	636.9	635.1	629.0	621.5	611.8	599.1	585.5	571.8	556.3	541.8
160°	620.1	620.1	619.0	613.0	606.9	598.8	587.7	576.6	564.6	551.5	539.4
162.5°	603.9	604.7	603.7	597.6	593.2	585.9	577.2	567.7	558.2	546.6	536.9
165°	579.7	580.7	581.7	577.6	573.6	568.6	561.6	555.5	547.4	539.4	532.3
167.5°	560.6	561.4	561.6	559.0	556.9	553.9	548.3	543.6	537.8	532.1	527.5
170°	548.5	548.5	549.5	548.5	546.4	543.4	539.4	536.3	531.3	527.3	524.2
172.5°	536.3	538.0	539.0	538.0	536.7	534.5	532.1	529.9	525.6	522.4	521.0
175°	522.2	524.2	526.2	524.2	524.2	524.2	522.2	521.2	519.2	517.2	517.2
177.5°	513.9	515.5	517.2	516.3	517.2	516.3	516.3	515.5	514.7	513.9	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	13.1	12.7	12.3	12.3	12.6	14.1	14.7	14.8	13.9	13.2	12.1
90°	14.1	14.1	8.1	8.1	7.1	6.1	3.0	1.0	3.0	6.1	7.1
92.5°	203.7	125.4	74.2	53.2	38.5	26.3	16.8	11.5	16.8	26.3	38.5
95°	379.1	213.7	126.0	83.7	59.5	46.4	36.3	33.2	36.3	46.4	59.5
97.5°	340.7	204.3	136.7	101.2	80.5	68.4	59.7	59.7	59.7	68.4	80.5
100°	320.6	206.7	147.2	114.9	95.7	83.7	76.6	76.6	76.6	83.7	95.7
102.5°	315.0	214.7	160.9	130.3	111.9	100.6	94.3	92.7	94.3	100.6	111.9
105°	317.6	233.9	185.5	156.2	138.1	126.0	121.0	118.0	121.0	126.0	138.1
107.5°	332.4	256.3	211.9	183.1	165.7	152.8	147.8	145.8	147.8	152.8	165.7
110°	343.8	273.2	228.8	201.7	183.5	171.4	166.3	164.3	166.3	171.4	183.5





TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.9	289.3	246.6	219.3	201.3	190.0	184.1	182.1	184.1	190.0	201.3
115°	375.1	314.6	274.2	247.0	227.8	217.7	210.7	207.7	210.7	217.7	227.8
117.5°	394.6	338.9	300.6	272.4	254.5	243.4	237.1	234.3	237.1	243.4	254.5
120°	408.3	355.9	317.6	289.3	272.2	261.2	254.1	252.1	254.1	261.2	272.2
122.5°	421.2	372.0	333.7	306.3	287.5	277.2	270.1	268.2	270.1	277.2	287.5
125°	440.6	394.2	357.9	329.6	310.5	299.4	293.4	289.3	293.4	299.4	310.5
127.5°	457.3	414.8	379.7	351.2	331.2	318.6	311.3	308.1	311.3	318.6	331.2
130°	467.8	428.5	394.2	365.0	345.8	330.6	322.7	318.6	322.7	330.6	345.8
132.5°	478.3	439.8	405.5	377.9	357.1	342.7	332.2	329.0	332.2	342.7	357.1
135°	492.0	455.7	422.4	396.2	375.1	357.9	347.8	343.8	347.8	357.9	375.1
137.5°	501.7	467.8	436.8	411.7	389.7	373.4	362.3	358.5	362.3	373.4	389.7
140°	508.1	475.8	445.7	421.4	400.2	383.1	372.0	369.0	372.0	383.1	400.2
142.5°	512.9	483.1	453.6	430.3	409.9	393.5	383.3	380.3	383.3	393.5	409.9
145°	518.2	491.0	464.7	442.6	423.4	409.3	399.2	396.2	399.2	409.3	423.4
147.5°	522.8	499.1	474.4	454.4	438.6	424.0	415.2	414.1	415.2	424.0	438.6
150°	525.2	503.1	480.9	461.7	446.7	434.5	426.5	425.5	426.5	434.5	446.7
152.5°	526.8	506.3	486.6	469.0	455.4	444.2	436.2	436.0	436.2	444.2	455.4
155°	528.3	511.1	494.0	478.9	467.8	457.7	451.6	450.6	451.6	457.7	467.8
157.5°	528.3	514.5	500.1	488.2	478.5	470.6	464.9	464.9	464.9	470.6	478.5
160°	528.3	516.1	504.1	493.0	484.9	477.9	473.8	473.8	473.8	477.9	484.9
162.5°	528.3	517.8	506.5	497.9	490.6	484.3	481.1	481.9	481.1	484.3	490.6
165°	526.2	518.2	509.1	503.1	498.1	493.0	491.0	491.0	491.0	493.0	498.1
167.5°	523.8	518.0	511.3	506.8	503.9	500.1	499.1	500.1	499.1	500.1	503.9
170°	522.2	517.2	512.1	509.1	507.2	504.1	503.1	504.1	503.1	504.1	507.2
172.5°	520.6	516.3	512.9	510.7	509.5	507.3	507.2	508.1	507.2	507.3	509.5
175°	518.2	515.1	513.1	513.1	512.1	511.1	511.1	512.1	511.1	511.1	512.1
177.5°	515.5	513.9	513.1	513.1	513.1	512.3	513.1	513.9	513.1	512.3	513.1
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	12.3	11.9	13.1	12.3	13.1	13.5	12.9	13.1	13.7	13.0	13.0
90°	8.1	8.1	14.1	14.1	16.2	18.2	17.2	18.2	19.2	20.2	20.2
92.5°	53.2	74.2	125.4	203.7	279.8	319.8	266.4	198.0	149.1	118.6	98.4
95°	83.7	126.0	213.7	379.1	620.1	821.6	844.9	747.0	590.8	455.7	357.9
97.5°	101.2	136.7	204.3	340.7	580.3	865.4	1061.4	1103.8	1045.6	947.1	841.8
100°	114.9	147.2	206.7	320.6	526.2	810.5	1068.6	1215.9	1236.0	1186.6	1112.0
102.5°	130.3	160.9	214.7	315.0	490.0	742.0	1008.1	1210.2	1310.2	1324.5	1293.4
105°	156.2	185.5	233.9	317.6	458.7	661.4	898.3	1129.1	1303.5	1403.3	1444.7
107.5°	183.1	211.9	256.3	332.4	453.0	616.2	809.5	1014.0	1199.7	1340.3	1430.2
110°	201.7	228.8	273.2	343.8	454.6	600.9	765.2	944.6	1119.0	1265.3	1376.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	219.3	246.6	289.3	355.9	459.5	593.6	740.2	893.8	1048.0	1186.2	1297.1
115°	247.0	274.2	314.6	375.1	468.8	589.8	716.8	842.8	966.8	1084.8	1181.5
117.5°	272.4	300.6	338.9	394.6	478.7	588.8	706.3	817.8	920.5	1013.2	1095.3
120°	289.3	317.6	355.9	408.3	485.9	588.8	700.6	806.5	900.3	981.0	1052.5
122.5°	306.3	333.7	372.0	421.2	493.2	587.9	694.2	796.9	887.4	960.8	1023.5
125°	329.6	357.9	394.2	440.6	504.1	586.7	683.6	780.3	867.0	936.5	992.0
127.5°	351.2	379.7	414.8	457.3	512.7	584.5	669.2	760.1	843.0	912.4	965.0
130°	365.0	394.2	428.5	467.8	519.2	583.7	660.4	744.1	823.6	892.2	945.6
132.5°	377.9	405.5	439.8	478.3	524.8	582.9	652.3	727.1	801.9	868.8	922.3
135°	396.2	422.4	455.7	492.0	533.3	581.7	640.2	703.7	769.2	830.7	881.1
137.5°	411.7	436.8	467.8	501.7	538.4	581.5	629.7	682.6	738.0	789.8	835.4
140°	421.4	445.7	475.8	508.1	542.4	580.7	624.1	670.4	717.8	763.2	805.5
142.5°	430.3	453.6	483.1	512.9	545.6	580.7	619.2	659.1	700.8	739.8	776.5
145°	442.6	464.7	491.0	518.2	547.4	578.7	611.0	643.2	677.5	707.7	736.0
147.5°	454.4	474.4	499.1	522.8	548.5	575.0	603.5	630.1	657.3	681.6	703.7
150°	461.7	480.9	503.1	525.2	548.5	572.6	597.8	622.1	645.2	665.4	683.6
152.5°	469.0	486.6	506.3	526.8	546.8	568.6	591.4	613.2	633.1	651.7	666.6
155°	478.9	494.0	511.1	528.3	544.4	562.6	581.7	599.9	616.0	631.1	643.2
157.5°	488.2	500.1	514.5	528.3	541.8	556.3	571.8	585.5	599.1	611.8	621.5
160°	493.0	504.1	516.1	528.3	539.4	551.5	564.6	576.6	587.7	598.8	606.9
162.5°	497.9	506.5	517.8	528.3	536.9	546.6	558.2	567.7	577.2	585.9	593.2
165°	503.1	509.1	518.2	526.2	532.3	539.4	547.4	555.5	561.6	568.6	573.6
167.5°	506.8	511.3	518.0	523.8	527.5	532.1	537.8	543.6	548.3	553.9	556.9
170°	509.1	512.1	517.2	522.2	524.2	527.3	531.3	536.3	539.4	543.4	546.4
172.5°	510.7	512.9	516.3	520.6	521.0	522.4	525.6	529.9	532.1	534.5	536.7
175°	513.1	513.1	515.1	518.2	517.2	517.2	519.2	521.2	522.2	524.2	524.2
177.5°	513.1	513.1	513.9	515.5	513.9	513.9	514.7	515.5	516.3	516.3	517.2
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	14.1	13.9	13.2	13.7	13.2	13.9	14.1	13.0	13.0	13.7	13.1
90°	21.2	22.2	21.2	21.2	21.2	22.2	21.2	20.2	20.2	19.2	18.2
92.5°	86.5	81.1	77.7	77.7	77.7	81.1	86.5	98.4	118.6	149.1	198.0
95°	308.5	277.2	259.1	246.0	259.1	277.2	308.5	357.9	455.7	590.8	747.0
97.5°	769.4	708.7	678.5	657.5	678.5	708.7	769.4	841.8	947.1	1045.6	1103.8
100°	1024.3	962.8	932.5	924.5	932.5	962.8	1024.3	1112.0	1186.6	1236.0	1215.9
102.5°	1239.6	1195.1	1163.3	1156.8	1163.3	1195.1	1239.6	1293.4	1324.5	1310.2	1210.2
105°	1446.7	1438.7	1424.5	1418.5	1424.5	1438.7	1446.7	1444.7	1403.3	1303.5	1129.1
107.5°	1480.0	1503.0	1513.1	1515.7	1513.1	1503.0	1480.0	1430.2	1340.3	1199.7	1014.0
110°	1447.7	1490.1	1508.2	1517.3	1508.2	1490.1	1447.7	1376.1	1265.3	1119.0	944.6



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1378.4	1429.6	1455.0	1469.7	1455.0	1429.6	1378.4	1297.1	1186.2	1048.0	893.8
115°	1261.2	1321.7	1353.9	1362.0	1353.9	1321.7	1261.2	1181.5	1084.8	966.8	842.8
117.5°	1163.3	1214.1	1246.7	1252.9	1246.7	1214.1	1163.3	1095.3	1013.2	920.5	817.8
120°	1109.9	1154.4	1180.5	1191.6	1180.5	1154.4	1109.9	1052.5	981.0	900.3	806.5
122.5°	1072.1	1109.9	1132.2	1143.3	1132.2	1109.9	1072.1	1023.5	960.8	887.4	796.9
125°	1032.4	1061.6	1080.8	1086.8	1080.8	1061.6	1032.4	992.0	936.5	867.0	780.3
127.5°	1005.5	1031.6	1047.6	1053.7	1047.6	1031.6	1005.5	965.0	912.4	843.0	760.1
130°	986.9	1012.2	1028.3	1034.4	1028.3	1012.2	986.9	945.6	892.2	823.6	744.1
132.5°	962.8	991.2	1006.5	1012.6	1006.5	991.2	962.8	922.3	868.8	801.9	727.1
135°	921.5	949.7	965.8	971.9	965.8	949.7	921.5	881.1	830.7	769.2	703.7
137.5°	873.0	900.9	914.2	921.5	914.2	900.9	873.0	835.4	789.8	738.0	682.6
140°	840.8	863.0	877.1	885.1	877.1	863.0	840.8	805.5	763.2	717.8	670.4
142.5°	807.7	828.3	840.8	846.5	840.8	828.3	807.7	776.5	739.8	700.8	659.1
145°	761.1	778.3	788.4	793.5	788.4	778.3	761.1	736.0	707.7	677.5	643.2
147.5°	722.3	737.0	744.7	746.4	744.7	737.0	722.3	703.7	681.6	657.3	630.1
150°	699.6	712.8	718.8	719.8	718.8	712.8	699.6	683.6	665.4	645.2	622.1
152.5°	680.3	690.9	694.6	695.6	694.6	690.9	680.3	666.6	651.7	633.1	613.2
155°	653.3	661.4	664.4	664.4	664.4	661.4	653.3	643.2	631.1	616.0	599.9
157.5°	629.0	635.1	636.9	636.9	636.9	635.1	629.0	621.5	611.8	599.1	585.5
160°	613.0	619.0	620.1	620.1	620.1	619.0	613.0	606.9	598.8	587.7	576.6
162.5°	597.6	603.7	604.7	603.9	604.7	603.7	597.6	593.2	585.9	577.2	567.7
165°	577.6	581.7	580.7	579.7	580.7	581.7	577.6	573.6	568.6	561.6	555.5
167.5°	559.0	561.6	561.4	560.6	561.4	561.6	559.0	556.9	553.9	548.3	543.6
170°	548.5	549.5	548.5	548.5	548.5	549.5	548.5	546.4	543.4	539.4	536.3
172.5°	538.0	539.0	538.0	536.3	538.0	539.0	538.0	536.7	534.5	532.1	529.9
175°	524.2	526.2	524.2	522.2	524.2	526.2	524.2	524.2	524.2	522.2	521.2
177.5°	516.3	517.2	515.5	513.9	515.5	517.2	516.3	517.2	516.3	516.3	515.5
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	12.9	13.5	13.1	12.3	13.1	11.9	12.3	12.1	13.2	13.9	14.8
90°	17.2	18.2	16.2	14.1	14.1	8.1	8.1	7.1	6.1	3.0	1.0
92.5°	266.4	319.8	279.8	203.7	125.4	74.2	53.2	38.5	26.3	16.8	11.5
95°	844.9	821.6	620.1	379.1	213.7	126.0	83.7	59.5	46.4	36.3	33.2
97.5°	1061.4	865.4	580.3	340.7	204.3	136.7	101.2	80.5	68.4	59.7	59.7
100°	1068.6	810.5	526.2	320.6	206.7	147.2	114.9	95.7	83.7	76.6	76.6
102.5°	1008.1	742.0	490.0	315.0	214.7	160.9	130.3	111.9	100.6	94.3	92.7
105°	898.3	661.4	458.7	317.6	233.9	185.5	156.2	138.1	126.0	121.0	118.0
107.5°	809.5	616.2	453.0	332.4	256.3	211.9	183.1	165.7	152.8	147.8	145.8
110°	765.2	600.9	454.6	343.8	273.2	228.8	201.7	183.5	171.4	166.3	164.3



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	740.2	593.6	459.5	355.9	289.3	246.6	219.3	201.3	190.0	184.1	182.1
115°	716.8	589.8	468.8	375.1	314.6	274.2	247.0	227.8	217.7	210.7	207.7
117.5°	706.3	588.8	478.7	394.6	338.9	300.6	272.4	254.5	243.4	237.1	234.3
120°	700.6	588.8	485.9	408.3	355.9	317.6	289.3	272.2	261.2	254.1	252.1
122.5°	694.2	587.9	493.2	421.2	372.0	333.7	306.3	287.5	277.2	270.1	268.2
125°	683.6	586.7	504.1	440.6	394.2	357.9	329.6	310.5	299.4	293.4	289.3
127.5°	669.2	584.5	512.7	457.3	414.8	379.7	351.2	331.2	318.6	311.3	308.1
130°	660.4	583.7	519.2	467.8	428.5	394.2	365.0	345.8	330.6	322.7	318.6
132.5°	652.3	582.9	524.8	478.3	439.8	405.5	377.9	357.1	342.7	332.2	329.0
135°	640.2	581.7	533.3	492.0	455.7	422.4	396.2	375.1	357.9	347.8	343.8
137.5°	629.7	581.5	538.4	501.7	467.8	436.8	411.7	389.7	373.4	362.3	358.5
140°	624.1	580.7	542.4	508.1	475.8	445.7	421.4	400.2	383.1	372.0	369.0
142.5°	619.2	580.7	545.6	512.9	483.1	453.6	430.3	409.9	393.5	383.3	380.3
145°	611.0	578.7	547.4	518.2	491.0	464.7	442.6	423.4	409.3	399.2	396.2
147.5°	603.5	575.0	548.5	522.8	499.1	474.4	454.4	438.6	424.0	415.2	414.1
150°	597.8	572.6	548.5	525.2	503.1	480.9	461.7	446.7	434.5	426.5	425.5
152.5°	591.4	568.6	546.8	526.8	506.3	486.6	469.0	455.4	444.2	436.2	436.0
155°	581.7	562.6	544.4	528.3	511.1	494.0	478.9	467.8	457.7	451.6	450.6
157.5°	571.8	556.3	541.8	528.3	514.5	500.1	488.2	478.5	470.6	464.9	464.9
160°	564.6	551.5	539.4	528.3	516.1	504.1	493.0	484.9	477.9	473.8	473.8
162.5°	558.2	546.6	536.9	528.3	517.8	506.5	497.9	490.6	484.3	481.1	481.9
165°	547.4	539.4	532.3	526.2	518.2	509.1	503.1	498.1	493.0	491.0	491.0
167.5°	537.8	532.1	527.5	523.8	518.0	511.3	506.8	503.9	500.1	499.1	500.1
170°	531.3	527.3	524.2	522.2	517.2	512.1	509.1	507.2	504.1	503.1	504.1
172.5°	525.6	522.4	521.0	520.6	516.3	512.9	510.7	509.5	507.3	507.2	508.1
175°	519.2	517.2	517.2	518.2	515.1	513.1	513.1	512.1	511.1	511.1	512.1
177.5°	514.7	513.9	513.9	515.5	513.9	513.1	513.1	513.1	512.3	513.1	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	14.7	14.1	12.6	12.3	12.3	12.7	13.1	13.5	13.9	13.3	14.3
90°	3.0	6.1	7.1	8.1	8.1	14.1	14.1	16.2	18.2	17.2	18.2
92.5°	16.8	26.3	38.5	53.2	74.2	125.4	203.7	279.8	319.8	266.4	198.0
95°	36.3	46.4	59.5	83.7	126.0	213.7	379.1	620.1	821.6	844.9	747.0
97.5°	59.7	68.4	80.5	101.2	136.7	204.3	340.7	580.3	865.4	1061.4	1103.8
100°	76.6	83.7	95.7	114.9	147.2	206.7	320.6	526.2	810.5	1068.6	1215.9
102.5°	94.3	100.6	111.9	130.3	160.9	214.7	315.0	490.0	742.0	1008.1	1210.2
105°	121.0	126.0	138.1	156.2	185.5	233.9	317.6	458.7	661.4	898.3	1129.1
107.5°	147.8	152.8	165.7	183.1	211.9	256.3	332.4	453.0	616.2	809.5	1014.0
110°	166.3	171.4	183.5	201.7	228.8	273.2	343.8	454.6	600.9	765.2	944.6





TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	184.1	190.0	201.3	219.3	246.6	289.3	355.9	459.5	593.6	740.2	893.8
115°	210.7	217.7	227.8	247.0	274.2	314.6	375.1	468.8	589.8	716.8	842.8
117.5°	237.1	243.4	254.5	272.4	300.6	338.9	394.6	478.7	588.8	706.3	817.8
120°	254.1	261.2	272.2	289.3	317.6	355.9	408.3	485.9	588.8	700.6	806.5
122.5°	270.1	277.2	287.5	306.3	333.7	372.0	421.2	493.2	587.9	694.2	796.9
125°	293.4	299.4	310.5	329.6	357.9	394.2	440.6	504.1	586.7	683.6	780.3
127.5°	311.3	318.6	331.2	351.2	379.7	414.8	457.3	512.7	584.5	669.2	760.1
130°	322.7	330.6	345.8	365.0	394.2	428.5	467.8	519.2	583.7	660.4	744.1
132.5°	332.2	342.7	357.1	377.9	405.5	439.8	478.3	524.8	582.9	652.3	727.1
135°	347.8	357.9	375.1	396.2	422.4	455.7	492.0	533.3	581.7	640.2	703.7
137.5°	362.3	373.4	389.7	411.7	436.8	467.8	501.7	538.4	581.5	629.7	682.6
140°	372.0	383.1	400.2	421.4	445.7	475.8	508.1	542.4	580.7	624.1	670.4
142.5°	383.3	393.5	409.9	430.3	453.6	483.1	512.9	545.6	580.7	619.2	659.1
145°	399.2	409.3	423.4	442.6	464.7	491.0	518.2	547.4	578.7	611.0	643.2
147.5°	415.2	424.0	438.6	454.4	474.4	499.1	522.8	548.5	575.0	603.5	630.1
150°	426.5	434.5	446.7	461.7	480.9	503.1	525.2	548.5	572.6	597.8	622.1
152.5°	436.2	444.2	455.4	469.0	486.6	506.3	526.8	546.8	568.6	591.4	613.2
155°	451.6	457.7	467.8	478.9	494.0	511.1	528.3	544.4	562.6	581.7	599.9
157.5°	464.9	470.6	478.5	488.2	500.1	514.5	528.3	541.8	556.3	571.8	585.5
160°	473.8	477.9	484.9	493.0	504.1	516.1	528.3	539.4	551.5	564.6	576.6
162.5°	481.1	484.3	490.6	497.9	506.5	517.8	528.3	536.9	546.6	558.2	567.7
165°	491.0	493.0	498.1	503.1	509.1	518.2	526.2	532.3	539.4	547.4	555.5
167.5°	499.1	500.1	503.9	506.8	511.3	518.0	523.8	527.5	532.1	537.8	543.6
170°	503.1	504.1	507.2	509.1	512.1	517.2	522.2	524.2	527.3	531.3	536.3
172.5°	507.2	507.3	509.5	510.7	512.9	516.3	520.6	521.0	522.4	525.6	529.9
175°	511.1	511.1	512.1	513.1	513.1	515.1	518.2	517.2	517.2	519.2	521.2
177.5°	513.1	512.3	513.1	513.1	513.1	513.9	515.5	513.9	513.9	514.7	515.5
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1	513.1



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	13.7	13.5	13.9	13.7	13.9	13.2	13.7
90°	19.2	20.2	20.2	21.2	22.2	21.2	21.2
92.5°	149.1	118.6	98.4	86.5	81.1	77.7	77.7
95°	590.8	455.7	357.9	308.5	277.2	259.1	246.0
97.5°	1045.6	947.1	841.8	769.4	708.7	678.5	657.5
100°	1236.0	1186.6	1112.0	1024.3	962.8	932.5	924.5
102.5°	1310.2	1324.5	1293.4	1239.6	1195.1	1163.3	1156.8
105°	1303.5	1403.3	1444.7	1446.7	1438.7	1424.5	1418.5
107.5°	1199.7	1340.3	1430.2	1480.0	1503.0	1513.1	1515.7
110°	1119.0	1265.3	1376.1	1447.7	1490.1	1508.2	1517.3



TEST NUMBER: P332945-840

CATALOG NUMBER: SA4XXRDIP-C795D1035U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1048.0	1186.2	1297.1	1378.4	1429.6	1455.0	1469.7
115°	966.8	1084.8	1181.5	1261.2	1321.7	1353.9	1362.0
117.5°	920.5	1013.2	1095.3	1163.3	1214.1	1246.7	1252.9
120°	900.3	981.0	1052.5	1109.9	1154.4	1180.5	1191.6
122.5°	887.4	960.8	1023.5	1072.1	1109.9	1132.2	1143.3
125°	867.0	936.5	992.0	1032.4	1061.6	1080.8	1086.8
127.5°	843.0	912.4	965.0	1005.5	1031.6	1047.6	1053.7
130°	823.6	892.2	945.6	986.9	1012.2	1028.3	1034.4
132.5°	801.9	868.8	922.3	962.8	991.2	1006.5	1012.6
135°	769.2	830.7	881.1	921.5	949.7	965.8	971.9
137.5°	738.0	789.8	835.4	873.0	900.9	914.2	921.5
140°	717.8	763.2	805.5	840.8	863.0	877.1	885.1
142.5°	700.8	739.8	776.5	807.7	828.3	840.8	846.5
145°	677.5	707.7	736.0	761.1	778.3	788.4	793.5
147.5°	657.3	681.6	703.7	722.3	737.0	744.7	746.4
150°	645.2	665.4	683.6	699.6	712.8	718.8	719.8
152.5°	633.1	651.7	666.6	680.3	690.9	694.6	695.6
155°	616.0	631.1	643.2	653.3	661.4	664.4	664.4
157.5°	599.1	611.8	621.5	629.0	635.1	636.9	636.9
160°	587.7	598.8	606.9	613.0	619.0	620.1	620.1
162.5°	577.2	585.9	593.2	597.6	603.7	604.7	603.9
165°	561.6	568.6	573.6	577.6	581.7	580.7	579.7
167.5°	548.3	553.9	556.9	559.0	561.6	561.4	560.6
170°	539.4	543.4	546.4	548.5	549.5	548.5	548.5
172.5°	532.1	534.5	536.7	538.0	539.0	538.0	536.3
175°	522.2	524.2	524.2	524.2	526.2	524.2	522.2
177.5°	516.3	516.3	517.2	516.3	517.2	515.5	513.9
180°	513.1	513.1	513.1	513.1	513.1	513.1	513.1

(END OF REPORT)