

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915912

Luminaire Tested: DFN2DIP-4P3F0-060D060US930-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P915912  
REPORT IS A COMBINATION OF REPORTS P899078 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-060D060US930-RLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8487.2 lumens  
Efficiency: N/A  
Efficacy: 77.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 109.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9963  
Total Harmonic Distortion (THDi): 0.065  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P915912  
CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P915912

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2304	2304	2304
5°	2306	2266	2281
10°	2282	2220	2206
15°	2249	2145	2091
20°	2206	2043	1949
25°	2162	1928	1813
30°	2103	1810	1640
35°	2046	1684	1488
40°	1987	1554	1314
45°	1919	1410	1156
50°	1849	1264	1003
55°	1775	1109	855
60°	1690	946	703
65°	1591	781	632
70°	1472	627	570
75°	1322	550	517
80°	1104	456	447
85°	749	297	331

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1919 cd/sqm



TEST NUMBER: P915912

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	2.2
10°-20°	520.2	6.1
20°-30°	730.3	8.6
30°-40°	796.1	9.4
40°-50°	731.7	8.6
50°-60°	574.6	6.8
60°-70°	374.0	4.4
70°-80°	192.5	2.3
80°-90°	53.5	0.6
90°-100°	95.7	1.1
100°-110°	304.2	3.6
110°-120°	520.6	6.1
120°-130°	684.6	8.1
130°-140°	768.4	9.1
140°-150°	753.5	8.9
150°-160°	632.1	7.4
160°-170°	419.2	4.9
170°-180°	146.5	1.7
0°-30°	1439.9	17.0
0°-40°	2236.0	26.3
0°-60°	3542.3	41.7
0°-90°	4162.4	49.0
90°-120°	920.5	10.8
90°-150°	3127.0	36.8
90°-180°	4325.0	51.0
0°-180°	8487.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	1	17	46	43	44	8
95°	68	81	84	84	81	76
105°	281	284	287	290	290	296
115°	522	530	528	526	522	517
125°	760	771	768	764	762	679
135°	983	997	1000	999	995	760
145°	1193	1202	1210	1211	1206	745
155°	1364	1368	1372	1379	1374	628
165°	1484	1483	1483	1492	1486	419
175°	1544	1541	1538	1547	1539	147
180°	1547	1547	1547	1547	1547	



TEST NUMBER: P915912

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	1.4	16.8	45.7	42.9	44.3
92.5°	28.9	39.2	40.6	42.0	42.0
95°	68.1	81.1	83.5	83.5	81.1
97.5°	113.3	125.5	130.6	130.6	130.6
100°	165.6	176.3	180.0	180.0	178.6
102.5°	220.6	228.5	233.7	235.1	233.7
105°	280.8	284.5	287.3	289.7	289.7
107.5°	340.5	346.1	346.1	347.0	340.5
110°	398.4	405.8	405.8	405.8	402.0



TEST NUMBER: P915912

CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	460.8	468.7	467.3	463.6	460.8
115°	522.4	529.9	527.5	526.1	522.4
117.5°	583.5	593.8	587.2	583.5	579.8
120°	645.1	655.3	645.1	645.1	640.8
122.5°	701.0	714.0	707.5	703.8	701.0
125°	759.8	771.4	767.7	763.5	762.1
127.5°	817.2	831.6	826.5	820.9	817.2
130°	870.8	887.6	885.3	882.5	877.3
132.5°	931.0	944.0	944.9	938.4	934.7
135°	982.8	997.2	1000.0	998.6	994.8
137.5°	1040.6	1052.2	1054.6	1053.6	1048.1
140°	1091.4	1103.1	1109.6	1109.6	1104.5
142.5°	1143.6	1155.3	1159.0	1160.4	1155.3
145°	1193.1	1202.4	1209.9	1211.3	1206.2
147.5°	1237.4	1249.0	1254.7	1256.9	1251.8
150°	1283.1	1291.0	1296.2	1300.3	1296.2
152.5°	1323.6	1331.6	1338.1	1343.3	1338.1
155°	1364.2	1368.0	1372.1	1378.8	1374.5
157.5°	1399.2	1402.1	1404.4	1413.7	1407.2
160°	1430.5	1433.3	1434.7	1442.6	1437.0
162.5°	1459.4	1459.4	1460.8	1469.7	1463.1
165°	1484.1	1482.7	1482.7	1492.1	1485.6
167.5°	1506.5	1502.4	1502.4	1511.6	1505.1
170°	1523.3	1519.6	1518.2	1527.5	1519.6
172.5°	1535.0	1531.2	1529.8	1539.1	1531.2
175°	1544.3	1540.6	1537.7	1547.1	1539.1
177.5°	1549.4	1545.7	1542.9	1550.8	1542.9
180°	1547.1	1547.1	1547.1	1547.1	1547.1



TEST NUMBER: P915912  
 CATALOG NUMBER: DFN2DIP-4P3F0-060D060US930-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.92	10.74	10.89	11.72	13.01	5.88	6.71	6.85	7.69	8.97
	3H	11.59	12.33	12.58	13.32	14.63	7.06	7.80	8.05	8.79	10.10
	4H	12.20	12.89	13.20	13.89	15.21	7.51	8.21	8.51	9.20	10.52
	6H	12.62	13.26	13.62	14.26	15.59	7.82	8.46	8.83	9.46	10.79
	8H	12.74	13.35	13.75	14.36	15.69	7.91	8.52	8.93	9.54	10.86
	12H	12.80	13.38	13.82	14.39	15.74	7.95	8.53	8.97	9.54	10.89
4H	2H	9.94	10.63	10.94	11.63	12.94	6.47	7.17	7.48	8.16	9.48
	3H	11.76	12.34	12.77	13.36	14.69	7.82	8.40	8.83	9.42	10.75
	4H	12.45	12.98	13.47	13.99	15.35	8.36	8.89	9.38	9.90	11.26
	6H	12.96	13.41	13.99	14.45	15.80	8.77	9.23	9.80	10.26	11.62
	8H	13.13	13.55	14.16	14.59	15.95	8.90	9.32	9.93	10.35	11.72
	12H	13.22	13.61	14.27	14.65	16.02	8.96	9.34	10.01	10.39	11.76
8H	4H	12.41	12.84	13.44	13.87	15.24	8.64	9.06	9.67	10.09	11.46
	6H	12.97	13.32	14.03	14.40	15.76	9.15	9.50	10.20	10.57	11.93
	8H	13.19	13.50	14.25	14.55	15.94	9.33	9.64	10.39	10.70	12.08
	12H	13.32	13.59	14.39	14.65	16.07	9.45	9.72	10.51	10.77	12.19
12H	4H	12.37	12.75	13.41	13.79	15.17	8.64	9.02	9.69	10.07	11.44
	6H	12.95	13.26	14.01	14.32	15.70	9.19	9.50	10.26	10.56	11.94
	8H	13.17	13.44	14.23	14.49	15.92	9.40	9.67	10.46	10.72	12.15