

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918560

Luminaire Tested: DFN2DIP-4P3F0-020D060US935-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P918560  
REPORT IS A COMBINATION OF REPORTS P899070 AND P895917  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P3F0-020D060US935-RLLFLL  
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6035.6 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 62.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918560  
CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°



TEST NUMBER: P918560  
 CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13				13
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12	9				9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11	8				8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	811	811	811
5°	812	798	803
10°	803	781	777
15°	792	755	736
20°	777	719	686
25°	761	679	638
30°	740	637	577
35°	720	593	524
40°	699	547	463
45°	676	496	407
50°	651	445	353
55°	625	390	301
60°	595	333	247
65°	560	275	223
70°	518	221	201
75°	465	194	182
80°	389	161	157
85°	263	105	116

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1639 cd/sqm



TEST NUMBER: P918560

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.7	1.1
10°-20°	183.1	3.0
20°-30°	257.1	4.3
30°-40°	280.2	4.6
40°-50°	257.6	4.3
50°-60°	202.3	3.4
60°-70°	131.7	2.2
70°-80°	67.8	1.1
80°-90°	21.9	0.4
90°-100°	101.1	1.7
100°-110°	321.2	5.3
110°-120°	549.7	9.1
120°-130°	723.0	12.0
130°-140°	811.5	13.4
140°-150°	795.8	13.2
150°-160°	667.5	11.1
160°-170°	442.7	7.3
170°-180°	154.7	2.6
0°-30°	506.9	8.4
0°-40°	787.1	13.0
0°-60°	1247.0	20.7
0°-90°	1468.3	24.3
90°-120°	972.0	16.1
90°-150°	3302.3	54.7
90°-180°	4567.0	75.7
0°-180°	6035.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	712	712	712	712	712	
5°	712	708	700	706	704	67
15°	677	670	648	636	629	191
25°	614	594	551	525	515	283
35°	529	497	440	399	385	331
45°	433	390	322	276	261	334
55°	329	279	209	171	158	294
65°	222	170	112	90	88	220
75°	118	73	52	47	46	125
85°	28	14	12	12	12	32
90°	2	18	48	45	47	6
95°	72	86	88	88	86	80
105°	296	300	303	306	306	313
115°	552	560	557	556	552	546
125°	802	815	811	806	805	717
135°	1038	1053	1056	1055	1051	802
145°	1260	1270	1278	1279	1274	787
155°	1441	1445	1449	1456	1452	663
165°	1567	1566	1566	1576	1569	442
175°	1631	1627	1624	1634	1625	155
180°	1634	1634	1634	1634	1634	



TEST NUMBER: P918560

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	711.7	711.7	711.7	711.7	711.7
2.5°	714.9	711.7	704.6	711.1	709.8
5°	711.7	708.5	700.1	705.9	704.0
7.5°	705.9	702.1	693.0	695.6	692.3
10°	698.2	693.6	680.8	678.8	675.0
12.5°	688.5	682.7	665.3	661.5	654.4
15°	676.9	669.8	647.9	635.7	629.3
17.5°	663.4	653.1	626.0	611.8	601.6
20°	647.9	635.0	602.9	586.8	572.6
22.5°	631.2	616.4	579.0	557.2	547.5
25°	614.5	593.8	551.3	525.0	515.2
27.5°	594.5	572.6	525.6	495.2	480.4
30°	573.3	548.7	497.2	464.4	446.9
32.5°	552.6	523.0	470.2	431.5	415.4
35°	529.4	496.6	440.0	399.3	385.1
37.5°	506.9	471.4	411.6	367.1	351.0
40°	483.0	444.4	381.9	336.2	319.4
42.5°	458.6	417.4	352.3	304.6	288.6
45°	432.8	389.6	322.1	276.3	260.8
47.5°	408.4	362.7	293.1	247.3	233.2
50°	381.3	335.6	264.8	220.2	206.8
52.5°	354.8	306.5	237.6	195.2	183.0
55°	329.1	278.9	209.3	170.7	158.4
57.5°	302.7	251.2	184.3	148.2	137.8
60°	275.7	224.1	157.8	125.0	114.7
62.5°	249.3	197.8	135.3	104.4	99.2
65°	222.2	170.0	112.1	90.2	88.3
67.5°	196.5	144.2	90.2	79.2	77.3
70°	169.4	119.2	74.6	68.3	65.7
72.5°	143.6	95.9	62.4	57.3	56.1
75°	118.5	73.4	51.5	47.0	46.4
77.5°	93.4	52.2	40.6	38.0	36.7
80°	70.2	37.4	30.9	28.3	28.3
82.5°	48.9	25.1	21.3	20.0	20.0
85°	27.6	14.1	12.2	12.2	12.2
87.5°	10.3	5.2	5.2	4.5	4.5
90°	1.5	17.7	48.3	45.3	46.8
92.5°	30.6	41.4	42.9	44.3	44.3
95°	71.9	85.7	88.2	88.2	85.7
97.5°	119.7	132.5	137.9	137.9	137.9
100°	174.9	186.1	190.1	190.1	188.6
102.5°	233.0	241.3	246.8	248.2	246.8
105°	296.5	300.5	303.4	305.9	305.9
107.5°	359.6	365.5	365.5	366.4	359.6
110°	420.7	428.5	428.5	428.5	424.6



TEST NUMBER: P918560

CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	486.6	495.0	493.5	489.6	486.6
115°	551.6	559.6	557.1	555.6	551.6
117.5°	616.2	627.1	620.1	616.2	612.3
120°	681.2	692.1	681.2	681.2	676.7
122.5°	740.3	754.1	747.2	743.3	740.3
125°	802.4	814.7	810.7	806.3	804.9
127.5°	863.0	878.2	872.8	866.9	863.0
130°	919.6	937.4	934.9	931.9	926.5
132.5°	983.2	996.9	997.9	991.0	987.0
135°	1037.8	1053.1	1056.0	1054.6	1050.6
137.5°	1098.9	1111.2	1113.7	1112.7	1106.8
140°	1152.6	1164.9	1171.8	1171.8	1166.4
142.5°	1207.7	1220.0	1224.0	1225.5	1220.0
145°	1260.0	1269.8	1277.7	1279.2	1273.8
147.5°	1306.7	1319.0	1325.0	1327.4	1322.0
150°	1355.0	1363.4	1368.8	1373.2	1368.8
152.5°	1397.8	1406.3	1413.2	1418.6	1413.2
155°	1440.7	1444.7	1449.1	1456.0	1451.6
157.5°	1477.6	1480.7	1483.1	1493.0	1486.1
160°	1510.7	1513.6	1515.1	1523.4	1517.6
162.5°	1541.2	1541.2	1542.6	1552.0	1545.1
165°	1567.3	1565.8	1565.8	1575.7	1568.8
167.5°	1591.0	1586.6	1586.6	1596.4	1589.5
170°	1608.7	1604.7	1603.3	1613.1	1604.7
172.5°	1621.0	1617.0	1615.6	1625.4	1617.0
175°	1630.8	1626.9	1623.9	1633.8	1625.4
177.5°	1636.2	1632.4	1629.4	1637.7	1629.4
180°	1633.8	1633.8	1633.8	1633.8	1633.8



TEST NUMBER: P918560  
 CATALOG NUMBER: DFN2DIP-4P3F0-020D060US935-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.30	3.96	4.46	5.10	6.69	0.00	0.00	0.42	1.06	2.66
	3H	4.96	5.55	6.12	6.70	8.31	0.43	1.02	1.59	2.17	3.78
	4H	5.56	6.12	6.73	7.26	8.88	0.87	1.43	2.04	2.58	4.19
	6H	5.97	6.48	7.14	7.63	9.26	1.18	1.69	2.35	2.84	4.47
	8H	6.09	6.57	7.27	7.74	9.36	1.26	1.75	2.44	2.91	4.53
	12H	6.14	6.60	7.32	7.76	9.40	1.29	1.76	2.48	2.91	4.56
4H	2H	3.30	3.85	4.47	5.00	6.62	0.00	0.39	1.01	1.54	3.16
	3H	5.10	5.57	6.29	6.74	8.37	1.16	1.63	2.34	2.80	4.43
	4H	5.79	6.21	6.97	7.37	9.02	1.70	2.12	2.88	3.29	4.93
	6H	6.29	6.65	7.48	7.84	9.47	2.10	2.46	3.29	3.65	5.29
	8H	6.46	6.80	7.64	7.97	9.63	2.22	2.56	3.41	3.74	5.39
	12H	6.54	6.85	7.74	8.03	9.69	2.27	2.58	3.48	3.77	5.43
8H	4H	5.74	6.08	6.93	7.25	8.91	1.96	2.30	3.15	3.48	5.13
	6H	6.29	6.57	7.50	7.79	9.44	2.46	2.75	3.67	3.96	5.61
	8H	6.51	6.75	7.72	7.94	9.62	2.65	2.89	3.86	4.09	5.76
	12H	6.63	6.85	7.85	8.04	9.74	2.76	2.97	3.97	4.16	5.86
12H	4H	5.68	5.99	6.88	7.18	8.84	1.96	2.27	3.16	3.45	5.11
	6H	6.27	6.51	7.48	7.71	9.38	2.51	2.76	3.72	3.95	5.62
	8H	6.48	6.69	7.69	7.88	9.59	2.71	2.92	3.92	4.12	5.82