

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918564

Luminaire Tested: DFN2DIP-4P3F0-030D020US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918564
REPORT IS A COMBINATION OF REPORTS P899032 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US935-RLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3719.5 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1217	1217	1217
5°	1218	1197	1204
10°	1205	1172	1165
15°	1188	1133	1104
20°	1165	1078	1029
25°	1142	1018	957
30°	1111	956	866
35°	1080	889	786
40°	1049	821	694
45°	1013	744	611
50°	976	667	529
55°	937	585	451
60°	892	500	371
65°	840	413	333
70°	777	331	301
75°	698	290	273
80°	583	241	235
85°	396	157	174

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1013 cd/sqm

TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	2.7
10°-20°	274.7	7.4
20°-30°	385.6	10.4
30°-40°	420.3	11.3
40°-50°	386.3	10.4
50°-60°	303.4	8.2
60°-70°	197.5	5.3
70°-80°	101.7	2.7
80°-90°	27.5	0.7
90°-100°	33.7	0.9
100°-110°	107.1	2.9
110°-120°	183.2	4.9
120°-130°	241.0	6.5
130°-140°	270.5	7.3
140°-150°	265.3	7.1
150°-160°	222.5	6.0
160°-170°	147.6	4.0
170°-180°	51.6	1.4
0°-30°	760.3	20.4
0°-40°	1180.7	31.7
0°-60°	1870.4	50.3
0°-90°	2197.1	59.1
90°-120°	324.0	8.7
90°-150°	1100.8	29.6
90°-180°	1522.0	40.9
0°-180°	3719.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	0	6	16	15	16	4
95°	24	29	29	29	29	27
105°	99	100	101	102	102	104
115°	184	186	186	185	184	182
125°	267	272	270	269	268	239
135°	346	351	352	352	350	267
145°	420	423	426	426	425	262
155°	480	482	483	485	484	221
165°	522	522	522	525	523	147
175°	544	542	541	545	542	52
180°	545	545	545	545	545	

TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	0.5	5.9	16.1	15.1	15.6
92.5°	10.2	13.8	14.3	14.8	14.8
95°	23.9	28.6	29.4	29.4	28.6
97.5°	39.9	44.2	46.0	46.0	46.0
100°	58.3	62.1	63.4	63.4	62.9
102.5°	77.7	80.4	82.2	82.7	82.2
105°	98.8	100.1	101.2	101.9	101.9
107.5°	119.9	121.8	121.8	122.2	119.9
110°	140.3	142.8	142.8	142.8	141.5



TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	162.2	165.0	164.5	163.2	162.2
115°	183.9	186.5	185.7	185.2	183.9
117.5°	205.4	209.1	206.7	205.4	204.1
120°	227.0	230.7	227.0	227.0	225.6
122.5°	246.8	251.3	249.1	247.8	246.8
125°	267.4	271.6	270.3	268.8	268.3
127.5°	287.7	292.7	290.9	289.0	287.7
130°	306.5	312.5	311.6	310.6	308.8
132.5°	327.7	332.3	332.6	330.4	329.0
135°	345.9	351.0	352.0	351.5	350.2
137.5°	366.3	370.4	371.3	370.9	368.9
140°	384.2	388.3	390.6	390.6	388.8
142.5°	402.6	406.6	408.0	408.5	406.6
145°	420.0	423.3	425.9	426.4	424.6
147.5°	435.6	439.7	441.7	442.5	440.7
150°	451.7	454.4	456.2	457.7	456.2
152.5°	466.0	468.7	471.1	472.9	471.1
155°	480.3	481.6	483.0	485.3	483.9
157.5°	492.6	493.5	494.4	497.7	495.3
160°	503.6	504.5	505.1	507.8	505.8
162.5°	513.8	513.8	514.2	517.4	515.0
165°	522.5	521.9	521.9	525.2	523.0
167.5°	530.3	528.8	528.8	532.1	529.9
170°	536.2	534.9	534.4	537.7	534.9
172.5°	540.4	539.0	538.6	541.8	539.0
175°	543.6	542.3	541.3	544.6	541.8
177.5°	545.4	544.2	543.1	545.9	543.1
180°	544.6	544.6	544.6	544.6	544.6

TEST NUMBER: P918564

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.51	9.48	10.41	11.55	4.56	5.47	5.44	6.37	7.51
	3H	10.28	11.09	11.17	12.00	13.17	5.75	6.56	6.64	7.47	8.63
	4H	10.89	11.66	11.80	12.57	13.74	6.20	6.97	7.11	7.88	9.05
	6H	11.31	12.02	12.23	12.94	14.12	6.52	7.22	7.44	8.14	9.33
	8H	11.44	12.11	12.37	13.05	14.23	6.61	7.28	7.54	8.22	9.40
	12H	11.50	12.14	12.43	13.07	14.28	6.65	7.29	7.59	8.22	9.43
4H	2H	8.63	9.40	9.54	10.31	11.48	5.16	5.93	6.08	6.85	8.02
	3H	10.46	11.10	11.38	12.04	13.23	6.51	7.15	7.44	8.10	9.28
	4H	11.15	11.73	12.09	12.67	13.88	7.06	7.64	8.00	8.58	9.79
	6H	11.66	12.17	12.61	13.13	14.34	7.48	7.98	8.43	8.94	10.15
	8H	11.84	12.31	12.79	13.26	14.49	7.60	8.07	8.55	9.03	10.26
	12H	11.93	12.36	12.91	13.33	14.56	7.67	8.09	8.64	9.06	10.30
8H	4H	11.12	11.59	12.07	12.55	13.77	7.34	7.81	8.29	8.77	9.99
	6H	11.69	12.07	12.66	13.07	14.30	7.86	8.24	8.83	9.24	10.47
	8H	11.90	12.24	12.89	13.23	14.47	8.04	8.38	9.03	9.37	10.62
	12H	12.04	12.34	13.03	13.32	14.61	8.16	8.46	9.15	9.44	10.73
12H	4H	11.08	11.50	12.05	12.47	13.71	7.35	7.77	8.32	8.75	9.98
	6H	11.66	12.00	12.65	12.99	14.23	7.90	8.24	8.89	9.23	10.48
	8H	11.88	12.18	12.87	13.16	14.45	8.11	8.41	9.10	9.39	10.69