

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918565

Luminaire Tested: DFN2DIP-4P3F0-030D020US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918565
REPORT IS A COMBINATION OF REPORTS P900552 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US935-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3900.3 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1217	1217	1217
5°	1218	1197	1204
10°	1205	1172	1165
15°	1188	1133	1104
20°	1165	1078	1029
25°	1142	1018	957
30°	1111	956	866
35°	1080	889	786
40°	1049	821	694
45°	1013	744	611
50°	976	667	529
55°	937	585	451
60°	892	500	371
65°	840	413	333
70°	777	331	301
75°	698	290	273
80°	583	241	235
85°	396	157	174

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1013 cd/sqm

TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	2.6
10°-20°	274.7	7.0
20°-30°	385.6	9.9
30°-40°	420.3	10.8
40°-50°	386.3	9.9
50°-60°	303.4	7.8
60°-70°	197.5	5.1
70°-80°	101.7	2.6
80°-90°	27.0	0.7
90°-100°	19.2	0.5
100°-110°	71.4	1.8
110°-120°	189.5	4.9
120°-130°	314.2	8.1
130°-140°	333.8	8.6
140°-150°	310.2	8.0
150°-160°	249.4	6.4
160°-170°	160.7	4.1
170°-180°	55.3	1.4
0°-30°	760.3	19.5
0°-40°	1180.7	30.3
0°-60°	1870.4	48.0
0°-90°	2196.5	56.3
90°-120°	280.0	7.2
90°-150°	1238.3	31.7
90°-180°	1704.0	43.7
0°-180°	3900.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	0	5	8	10	11	4
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P918565

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.37	9.25	9.27	10.17	11.35	4.32	5.21	5.23	6.13	7.31
	3H	10.04	10.83	10.96	11.77	12.97	5.51	6.30	6.43	7.23	8.44
	4H	10.65	11.40	11.59	12.33	13.55	5.96	6.71	6.90	7.64	8.86
	6H	11.07	11.76	12.02	12.70	13.93	6.28	6.97	7.22	7.91	9.14
	8H	11.20	11.85	12.15	12.81	14.04	6.37	7.02	7.32	7.98	9.21
	12H	11.26	11.88	12.22	12.83	14.08	6.41	7.03	7.37	7.98	9.24
4H	2H	8.39	9.14	9.33	10.07	11.29	4.93	5.67	5.87	6.61	7.82
	3H	10.22	10.84	11.17	11.81	13.03	6.27	6.89	7.22	7.86	9.09
	4H	10.91	11.47	11.87	12.44	13.69	6.82	7.38	7.78	8.35	9.60
	6H	11.42	11.91	12.39	12.89	14.15	7.23	7.72	8.21	8.70	9.96
	8H	11.60	12.05	12.57	13.03	14.30	7.36	7.81	8.33	8.79	10.06
	12H	11.69	12.10	12.68	13.10	14.37	7.42	7.83	8.42	8.83	10.10
8H	4H	10.88	11.33	11.85	12.31	13.58	7.10	7.55	8.07	8.53	9.80
	6H	11.44	11.82	12.44	12.84	14.10	7.61	7.99	8.61	9.01	10.27
	8H	11.65	11.99	12.66	12.99	14.28	7.80	8.13	8.81	9.14	10.42
	12H	11.79	12.08	12.80	13.09	14.42	7.91	8.21	8.92	9.21	10.54
12H	4H	10.83	11.24	11.83	12.24	13.51	7.11	7.52	8.10	8.51	9.78
	6H	11.42	11.75	12.42	12.76	14.04	7.66	7.99	8.67	9.00	10.28
	8H	11.64	11.93	12.65	12.93	14.26	7.87	8.16	8.88	9.16	10.49