

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332661-940

Luminaire Tested: **SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332661-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8394.9 lumens  
Efficiency: N/A  
Efficacy: 128.4 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332661-940  
CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18	16
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12013	12013	12013	12013
5°	14148	12044	10631	12044
10°	16939	11992	9571	11992
15°	20042	11870	8790	11870
20°	22317	11747	8092	11747
25°	22678	11564	7611	11564
30°	19296	11389	7458	11389
35°	14836	11106	7460	11106
40°	11564	10771	7600	10771
45°	9642	10268	7728	10268
50°	8485	9654	7989	9654
55°	7773	8919	8313	8919
60°	7285	8262	8699	8262
65°	6783	7524	9020	7524
70°	6198	6793	9224	6793
75°	5536	5979	9114	5979
80°	4644	4900	8824	4900
85°	3427	3548	8448	3548



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.0	1.7
10°-20°	446.9	5.3
20°-30°	708.6	8.4
30°-40°	788.6	9.4
40°-50°	717.8	8.6
50°-60°	586.6	7.0
60°-70°	418.8	5.0
70°-80°	230.6	2.7
80°-90°	67.0	0.8
90°-100°	47.4	0.6
100°-110°	302.1	3.6
110°-120°	577.9	6.9
120°-130°	733.6	8.7
130°-140°	784.9	9.3
140°-150°	734.0	8.7
150°-160°	591.9	7.1
160°-170°	381.8	4.5
170°-180°	131.6	1.6
0°-30°	1300.4	15.5
0°-40°	2089.0	24.9
0°-60°	3393.4	40.4
0°-90°	4109.7	49.0
90°-120°	927.4	11.0
90°-150°	3179.9	37.9
90°-180°	4285.0	51.0
0°-180°	8394.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1488	1488	1488	1488	1488	
5°	1746	1486	1312	1486	1746	178
15°	2398	1420	1052	1420	2398	678
25°	2546	1298	854	1298	2546	1122
35°	1505	1127	757	1127	1505	956
45°	844	899	677	899	844	665
55°	552	634	591	634	552	499
65°	355	394	472	394	355	352
75°	178	192	292	192	178	189
85°	37	38	91	38	37	46
90°	31	3	31	3	31	15
95°	30	57	30	57	30	24
105°	295	312	295	312	295	258
115°	586	582	586	582	586	580
125°	825	818	825	818	825	734
135°	1023	1015	1023	1015	1023	787
145°	1177	1171	1177	1171	1177	736
155°	1283	1284	1283	1284	1283	591
165°	1348	1354	1348	1354	1348	381
175°	1377	1385	1377	1385	1377	131
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1583.8	1583.3	1578.3	1577.3	1573.9	1569.5	1568.5	1560.6	1544.8	1537.4	1535.4
5°	1745.8	1758.1	1742.0	1739.0	1737.1	1716.8	1706.3	1694.0	1665.6	1649.0	1636.0
7.5°	1939.1	1940.5	1933.6	1927.9	1912.2	1894.4	1867.9	1839.5	1805.7	1770.6	1744.0
10°	2066.4	2071.3	2063.2	2062.0	2030.6	2010.8	1971.4	1938.1	1899.9	1857.3	1818.6
12.5°	2200.5	2193.5	2189.5	2163.1	2157.3	2121.3	2075.5	2041.2	1982.3	1933.3	1881.6
15°	2398.0	2384.4	2375.8	2339.4	2321.6	2271.6	2222.9	2185.3	2108.3	2034.9	1979.4
17.5°	2513.8	2527.5	2507.5	2492.5	2446.3	2411.3	2361.5	2282.6	2222.3	2131.2	2061.2
20°	2597.7	2598.9	2587.8	2572.4	2536.0	2491.7	2437.4	2351.1	2279.0	2188.3	2092.2
22.5°	2620.4	2620.6	2615.9	2601.5	2574.0	2538.0	2483.3	2411.3	2323.9	2225.4	2129.2
25°	2545.9	2543.4	2549.0	2565.0	2554.6	2543.4	2512.0	2458.4	2377.0	2272.8	2169.3
27.5°	2269.2	2286.3	2317.6	2357.1	2395.0	2424.0	2432.1	2421.2	2370.7	2285.0	2176.6
30°	2070.0	2091.0	2114.4	2153.8	2230.3	2274.0	2322.2	2358.5	2338.2	2269.8	2168.6
32.5°	1851.1	1856.3	1891.1	1935.9	2005.9	2090.1	2166.3	2240.2	2264.7	2228.8	2144.5
35°	1505.4	1513.9	1551.6	1596.0	1681.7	1784.6	1899.3	2001.6	2086.1	2120.0	2076.8
37.5°	1228.4	1253.2	1279.8	1327.5	1402.9	1495.6	1614.7	1747.1	1873.0	1957.3	1971.7
40°	1097.3	1112.7	1131.8	1168.1	1232.3	1323.5	1425.8	1577.5	1711.3	1832.1	1871.5
42.5°	993.7	1002.7	1014.4	1047.3	1096.2	1186.9	1280.3	1413.7	1548.0	1692.5	1758.6
45°	844.5	853.8	873.5	892.6	929.6	992.5	1079.4	1189.1	1324.1	1463.5	1585.5
47.5°	736.7	742.7	754.4	774.9	806.3	847.7	918.5	1010.1	1135.2	1270.5	1400.5
50°	675.6	680.6	689.8	708.3	732.4	769.3	827.2	912.9	1010.9	1147.2	1274.8
52.5°	627.3	629.3	636.1	648.6	667.7	698.8	746.4	817.3	908.4	1029.8	1156.9
55°	552.3	554.8	561.0	570.2	586.8	606.5	642.9	696.0	775.5	880.9	991.2
57.5°	490.7	492.4	497.6	501.1	514.9	530.9	558.8	596.7	657.0	746.4	844.9
60°	451.2	450.0	456.2	459.2	468.5	482.1	503.6	540.0	592.4	664.5	755.1
62.5°	412.8	411.1	416.3	420.3	425.6	437.2	454.8	483.3	525.8	591.0	669.3
65°	355.1	352.6	355.7	360.6	365.5	371.8	384.7	409.9	443.8	490.7	550.5
67.5°	297.1	299.7	300.2	302.6	305.5	313.9	322.8	340.6	364.5	402.1	452.7
70°	262.6	263.2	265.7	265.7	267.5	274.9	282.3	292.8	316.2	350.8	392.1
72.5°	228.1	230.7	229.7	231.7	233.0	237.9	243.3	253.3	273.3	299.0	333.9
75°	177.5	179.4	179.4	180.0	181.8	183.7	188.0	195.4	209.6	228.7	252.7
77.5°	129.5	129.7	130.5	132.8	132.8	135.7	138.9	144.9	151.9	165.0	179.6
80°	99.9	101.1	100.5	101.7	101.7	104.2	105.4	112.8	115.9	124.5	136.3
82.5°	73.2	74.5	74.4	76.1	77.0	77.6	79.3	82.2	85.3	92.9	97.7
85°	37.0	38.3	37.0	38.3	40.0	40.7	42.5	43.2	45.7	47.4	51.8
87.5°	17.0	18.5	18.4	18.7	19.6	20.0	20.2	19.4	21.1	21.3	22.9
90°	31.1	30.6	30.1	29.7	29.2	28.4	26.9	25.6	24.2	22.8	21.0
92.5°	28.6	28.5	28.4	28.4	28.3	27.5	26.1	24.7	23.4	21.9	20.2
95°	30.1	29.8	29.6	29.3	29.2	28.4	26.9	25.6	24.2	22.8	22.6
97.5°	29.0	28.8	28.5	28.4	28.1	27.9	27.7	27.6	27.5	27.4	53.1
100°	29.0	28.8	28.5	28.4	28.1	30.0	33.9	37.7	41.6	45.6	77.4
102.5°	29.9	29.8	29.8	29.7	29.7	50.7	93.0	135.2	177.5	219.6	223.8
105°	295.3	303.6	311.8	320.1	328.4	331.5	329.5	327.4	325.4	323.2	322.1
107.5°	411.5	410.6	409.8	408.9	408.0	407.1	406.1	405.1	404.0	403.1	401.4
110°	462.1	461.5	460.7	460.0	459.3	458.8	458.3	457.9	457.4	456.9	455.6



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	512.6	511.8	511.0	510.1	509.2	508.8	508.9	509.0	509.1	509.2	508.5
115°	586.5	586.5	586.5	586.5	586.5	586.2	585.8	585.3	584.9	584.3	584.6
117.5°	661.5	661.6	661.6	661.7	661.8	661.9	662.0	662.1	662.2	662.3	661.8
120°	708.7	709.2	709.6	710.1	710.5	710.5	710.1	709.6	709.2	708.7	708.9
122.5°	755.1	755.5	756.1	756.5	757.0	757.1	756.8	756.5	756.3	756.0	755.6
125°	824.7	824.6	824.3	824.0	823.9	823.4	822.7	822.0	821.3	820.6	821.1
127.5°	885.9	886.1	886.3	886.4	886.6	886.8	886.9	887.1	887.2	887.3	886.3
130°	927.3	927.3	927.3	927.3	927.3	927.2	927.0	926.8	926.5	926.3	925.6
132.5°	965.5	965.6	965.8	966.0	966.2	966.2	966.0	965.7	965.5	965.3	964.4
135°	1022.6	1022.2	1021.7	1021.3	1020.8	1020.4	1019.8	1019.4	1019.0	1018.5	1017.6
137.5°	1071.6	1071.7	1071.8	1072.0	1072.1	1071.9	1071.4	1070.9	1070.4	1069.9	1068.9
140°	1105.5	1105.3	1105.1	1104.8	1104.7	1104.2	1103.5	1102.8	1102.1	1101.4	1100.9
142.5°	1133.7	1133.7	1133.6	1133.6	1133.5	1133.3	1132.7	1132.3	1131.8	1131.2	1131.0
145°	1177.1	1176.6	1176.1	1175.6	1175.2	1174.8	1174.7	1174.4	1174.2	1173.9	1173.9
147.5°	1212.9	1212.6	1212.5	1212.2	1211.9	1211.7	1211.6	1211.4	1211.2	1211.0	1211.2
150°	1236.1	1235.9	1235.6	1235.4	1235.2	1235.0	1235.0	1235.0	1235.0	1235.0	1235.3
152.5°	1256.0	1256.2	1256.2	1256.4	1256.5	1256.4	1256.1	1255.7	1255.4	1255.0	1255.4
155°	1282.7	1283.4	1284.1	1284.8	1285.5	1285.4	1284.4	1283.5	1282.6	1281.7	1282.4
157.5°	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1	1305.9
160°	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0	1320.3
162.5°	1331.6	1333.2	1334.8	1336.3	1337.9	1338.0	1336.6	1335.2	1333.8	1332.5	1332.7
165°	1348.0	1350.1	1352.1	1354.2	1356.3	1356.4	1354.6	1352.7	1350.9	1349.1	1349.1
167.5°	1360.2	1362.5	1364.9	1367.2	1369.4	1369.6	1367.5	1365.6	1363.5	1361.5	1361.6
170°	1367.7	1370.0	1372.3	1374.6	1376.9	1377.2	1375.3	1373.4	1371.6	1369.8	1369.5
172.5°	1371.8	1374.3	1376.8	1379.3	1381.8	1382.1	1380.3	1378.4	1376.5	1374.8	1374.5
175°	1377.0	1379.7	1382.5	1385.3	1388.0	1388.4	1386.3	1384.3	1382.2	1380.1	1379.9
177.5°	1380.4	1382.5	1384.7	1387.0	1389.2	1389.6	1388.0	1386.6	1385.1	1383.7	1383.3
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940  
 CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1536.0	1529.0	1524.1	1520.2	1509.3	1502.9	1498.0	1491.0	1483.2	1474.8	1464.5
5°	1623.1	1602.1	1586.7	1563.3	1541.1	1522.6	1503.5	1486.2	1465.3	1442.5	1425.8
7.5°	1714.7	1683.6	1643.6	1608.9	1569.9	1536.1	1505.7	1474.6	1442.3	1411.0	1382.3
10°	1772.9	1732.9	1688.5	1636.0	1586.7	1542.9	1502.3	1462.9	1424.6	1386.3	1353.7
12.5°	1835.5	1785.6	1720.0	1658.8	1603.5	1545.0	1495.8	1447.5	1401.4	1361.2	1323.1
15°	1919.6	1847.4	1771.7	1689.7	1616.9	1548.5	1481.3	1420.3	1368.5	1315.5	1278.5
17.5°	1971.3	1882.0	1795.4	1709.7	1621.6	1535.3	1462.9	1392.4	1327.6	1275.0	1228.3
20°	2005.3	1916.6	1808.7	1723.0	1618.2	1529.4	1445.6	1367.3	1299.5	1243.4	1195.2
22.5°	2034.9	1932.3	1824.4	1711.6	1607.3	1513.1	1421.4	1342.6	1273.4	1214.2	1168.1
25°	2050.9	1933.1	1816.1	1703.9	1585.5	1473.9	1390.7	1298.2	1224.2	1162.0	1112.7
27.5°	2052.6	1926.7	1794.2	1669.6	1547.4	1443.5	1338.5	1255.8	1179.0	1113.2	1065.9
30°	2047.2	1915.9	1773.5	1638.5	1515.8	1403.0	1311.8	1221.8	1143.5	1078.2	1028.9
32.5°	2030.0	1893.2	1746.9	1604.0	1476.9	1366.5	1272.4	1186.8	1110.4	1046.1	994.3
35°	1980.0	1845.0	1689.1	1540.5	1410.4	1298.9	1213.8	1126.9	1050.4	989.4	939.5
37.5°	1902.0	1779.9	1621.4	1467.7	1339.9	1227.8	1143.5	1065.0	996.0	934.1	882.9
40°	1833.9	1726.6	1567.6	1417.8	1279.8	1173.1	1094.2	1022.1	953.7	895.1	846.4
42.5°	1755.5	1662.1	1515.4	1356.6	1223.5	1116.4	1039.5	974.7	910.3	856.1	807.4
45°	1615.7	1554.1	1415.9	1269.3	1130.6	1029.5	956.1	899.4	845.2	792.1	751.4
47.5°	1454.9	1424.3	1308.1	1168.8	1037.1	937.5	873.9	821.4	773.9	729.0	693.1
50°	1346.9	1332.1	1231.6	1097.3	971.5	877.8	813.7	768.7	728.0	688.6	654.7
52.5°	1240.4	1239.9	1149.3	1026.3	909.9	819.7	756.0	714.0	678.7	646.7	616.2
55°	1077.5	1094.8	1024.0	914.2	810.0	728.6	671.3	633.7	609.0	582.6	559.7
57.5°	928.0	956.6	898.1	801.5	714.6	639.6	589.7	561.4	535.2	519.2	502.6
60°	830.4	857.5	811.9	730.5	648.5	584.4	536.9	511.7	488.8	477.8	466.0
62.5°	743.6	767.8	734.0	658.5	587.4	525.7	485.6	461.4	445.9	433.8	426.1
65°	619.6	639.9	610.9	556.1	495.0	445.7	413.0	393.9	379.2	374.2	365.5
67.5°	500.8	519.3	503.6	457.0	408.0	370.8	345.2	326.8	318.1	313.8	307.6
70°	430.3	448.8	432.1	391.5	353.8	322.4	298.4	287.8	278.7	276.8	268.1
72.5°	370.6	383.2	366.6	334.7	302.6	276.1	257.4	246.5	241.7	238.4	233.6
75°	278.0	289.1	278.0	253.3	230.5	212.0	196.0	191.7	186.2	184.3	181.2
77.5°	196.8	206.3	197.9	182.4	165.4	151.1	142.5	137.0	135.7	132.5	134.0
80°	150.4	156.6	148.6	138.1	124.5	114.7	108.5	105.4	101.7	100.5	102.9
82.5°	108.0	110.8	106.6	99.6	89.5	83.1	78.9	75.3	74.5	74.8	74.8
85°	56.1	55.5	54.8	48.7	45.7	41.3	38.9	38.3	37.6	38.9	40.0
87.5°	22.6	22.6	21.8	19.4	17.4	15.4	14.4	13.5	14.4	15.4	16.4
90°	19.1	17.3	15.4	13.2	10.7	8.2	5.6	3.1	5.6	8.2	10.7
92.5°	18.3	16.4	14.6	13.6	13.5	13.4	13.2	13.0	13.2	13.4	13.5
95°	22.3	22.1	21.8	25.7	33.5	41.3	49.1	57.0	49.1	41.3	33.5
97.5°	78.7	104.4	130.1	140.5	135.6	130.8	125.9	121.0	125.9	130.8	135.6
100°	109.1	140.9	172.7	186.5	182.4	178.3	174.1	170.0	174.1	178.3	182.4
102.5°	227.9	232.1	236.2	236.7	233.7	230.7	227.7	224.6	227.7	230.7	233.7
105°	320.9	319.9	318.7	317.4	316.0	314.6	313.3	311.8	313.3	314.6	316.0
107.5°	399.9	398.3	396.8	395.7	394.9	394.3	393.6	392.9	393.6	394.3	394.9
110°	454.1	452.8	451.4	450.4	449.7	449.0	448.3	447.6	448.3	449.0	449.7





TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	507.8	507.2	506.6	505.6	504.4	503.1	501.9	500.7	501.9	503.1	504.4
115°	584.9	585.1	585.3	585.1	584.3	583.7	583.0	582.3	583.0	583.7	584.3
117.5°	661.3	660.8	660.2	659.5	658.6	657.7	656.7	655.9	656.7	657.7	658.6
120°	709.2	709.4	709.6	709.3	708.4	707.5	706.5	705.6	706.5	707.5	708.4
122.5°	755.3	755.0	754.7	754.2	753.7	753.1	752.6	752.0	752.6	753.1	753.7
125°	821.5	822.0	822.4	822.2	821.3	820.4	819.5	818.5	819.5	820.4	821.3
127.5°	885.2	884.1	883.1	882.4	882.3	882.0	881.7	881.5	881.7	882.0	882.3
130°	924.9	924.3	923.5	923.1	922.8	922.7	922.4	922.1	922.4	922.7	922.8
132.5°	963.5	962.6	961.8	961.1	960.7	960.3	959.8	959.5	959.8	960.3	960.7
135°	1016.6	1015.7	1014.9	1014.5	1014.7	1014.9	1015.2	1015.4	1015.2	1014.9	1014.7
137.5°	1067.9	1066.8	1065.9	1065.3	1065.2	1065.1	1065.1	1065.0	1065.1	1065.1	1065.2
140°	1100.5	1100.0	1099.6	1099.1	1098.7	1098.1	1097.7	1097.3	1097.7	1098.1	1098.7
142.5°	1130.7	1130.4	1130.2	1129.6	1128.7	1127.9	1127.1	1126.2	1127.1	1127.9	1128.7
145°	1173.9	1173.9	1173.9	1173.6	1172.9	1172.2	1171.5	1170.8	1171.5	1172.2	1172.9
147.5°	1211.5	1211.7	1211.9	1211.4	1210.1	1208.8	1207.6	1206.2	1207.6	1208.8	1210.1
150°	1235.6	1235.7	1236.0	1235.6	1234.8	1233.8	1232.9	1232.0	1232.9	1233.8	1234.8
152.5°	1255.8	1256.2	1256.6	1256.4	1255.7	1255.0	1254.3	1253.5	1254.3	1255.0	1255.7
155°	1283.1	1283.8	1284.4	1284.7	1284.4	1284.2	1284.0	1283.8	1284.0	1284.2	1284.4
157.5°	1306.7	1307.4	1308.2	1308.7	1308.9	1308.9	1309.1	1309.2	1309.1	1308.9	1308.9
160°	1320.4	1320.7	1321.0	1321.4	1322.1	1322.8	1323.5	1324.2	1323.5	1322.8	1322.1
162.5°	1332.9	1333.1	1333.4	1333.9	1334.8	1335.7	1336.6	1337.4	1336.6	1335.7	1334.8
165°	1349.1	1349.1	1349.1	1349.6	1350.8	1351.9	1353.1	1354.2	1353.1	1351.9	1350.8
167.5°	1361.7	1361.9	1362.0	1362.7	1363.9	1365.1	1366.3	1367.4	1366.3	1365.1	1363.9
170°	1369.3	1369.0	1368.9	1369.4	1370.8	1372.2	1373.6	1374.9	1373.6	1372.2	1370.8
172.5°	1374.3	1374.0	1373.8	1374.4	1375.7	1377.2	1378.5	1379.9	1378.5	1377.2	1375.7
175°	1379.7	1379.4	1379.2	1379.7	1381.2	1382.5	1383.9	1385.3	1383.9	1382.5	1381.2
177.5°	1382.9	1382.5	1382.2	1382.6	1383.9	1385.2	1386.5	1387.8	1386.5	1385.2	1383.9
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1459.5	1455.1	1448.7	1439.8	1432.4	1424.5	1422.5	1419.5	1425.5	1420.5	1419.1
5°	1411.7	1398.7	1382.1	1363.0	1351.8	1335.9	1332.8	1326.6	1320.4	1319.8	1313.7
7.5°	1361.0	1342.0	1320.2	1300.7	1282.7	1265.2	1253.7	1251.2	1242.2	1236.8	1230.7
10°	1328.5	1305.0	1279.8	1261.2	1240.3	1221.8	1208.9	1201.5	1195.2	1188.5	1182.3
12.5°	1289.9	1265.1	1244.2	1224.2	1199.4	1185.3	1164.0	1151.1	1150.0	1150.0	1134.0
15°	1245.2	1220.6	1188.5	1160.1	1146.6	1119.5	1107.8	1093.0	1083.7	1074.4	1067.1
17.5°	1194.1	1163.3	1138.4	1105.8	1079.9	1058.3	1042.9	1034.0	1020.1	1007.0	997.6
20°	1162.0	1129.4	1102.8	1068.3	1039.9	1013.4	1000.5	988.2	977.7	966.6	956.1
22.5°	1129.4	1095.3	1062.8	1029.3	1003.0	975.0	962.5	945.7	935.8	929.6	919.1
25°	1078.2	1041.2	1004.2	972.1	945.0	920.3	903.7	890.7	879.7	874.8	868.0
27.5°	1022.4	985.7	949.9	913.6	882.8	864.9	851.6	841.8	835.4	828.8	825.8
30°	986.9	948.7	910.5	876.6	848.2	830.4	818.1	811.3	806.3	803.3	800.1
32.5°	950.9	913.2	873.0	842.0	816.6	800.8	791.4	784.6	782.1	781.0	779.9
35°	893.2	855.0	818.1	790.3	766.2	760.1	752.1	748.3	747.2	751.4	753.3
37.5°	837.4	801.9	767.9	740.9	725.2	716.2	713.5	713.6	718.0	721.8	726.3
40°	801.4	766.9	734.8	711.4	696.6	691.1	689.8	692.9	697.9	702.1	707.0
42.5°	766.3	732.4	703.2	681.3	670.9	665.8	666.6	669.7	676.6	681.9	689.3
45°	712.0	683.7	655.3	637.4	628.7	630.0	630.0	635.5	642.3	650.3	658.4
47.5°	660.8	632.2	608.9	593.9	589.4	588.4	591.8	599.1	608.8	618.7	629.9
50°	626.3	599.1	578.8	565.3	560.4	562.2	567.1	573.9	585.6	598.0	609.7
52.5°	591.3	566.6	547.8	535.2	531.7	535.1	540.0	550.7	561.0	574.3	588.4
55°	536.9	515.9	501.1	492.0	490.7	492.6	498.1	509.8	524.6	541.3	554.8
57.5°	482.8	465.3	451.7	445.3	445.9	447.6	456.8	470.7	486.5	504.3	521.7
60°	446.3	430.3	419.2	414.3	414.8	418.6	429.6	442.6	462.4	479.6	498.1
62.5°	411.8	397.7	387.1	382.7	381.8	389.9	400.6	414.0	433.7	453.0	473.0
65°	356.3	345.2	336.6	334.1	336.0	342.1	355.7	373.5	390.2	410.5	431.5
67.5°	302.0	292.9	287.0	288.1	290.3	299.4	310.9	326.2	345.1	366.1	386.9
70°	267.5	258.9	254.0	254.6	258.3	269.4	279.3	294.6	315.0	336.6	353.8
72.5°	232.0	226.3	221.9	224.5	228.2	235.9	248.2	263.6	281.5	301.6	319.8
75°	178.2	178.2	175.7	177.5	183.1	190.5	199.7	215.8	233.6	249.7	264.5
77.5°	132.2	130.8	132.4	134.6	137.9	146.6	157.2	168.6	182.1	198.1	210.4
80°	101.1	101.7	104.8	108.5	109.8	116.5	127.6	138.1	148.6	162.1	173.8
82.5°	76.0	76.6	78.2	82.8	84.1	91.4	98.5	109.0	118.5	127.6	137.3
85°	41.3	41.3	44.4	46.2	49.3	54.2	58.6	64.7	73.4	79.5	88.7
87.5°	18.5	18.9	21.2	22.6	24.4	27.3	28.5	34.2	36.5	39.2	43.8
90°	13.2	15.4	17.3	19.1	21.0	22.8	24.2	25.6	26.9	28.4	29.2
92.5°	13.6	14.6	16.4	18.3	20.2	21.9	23.4	24.7	26.1	27.5	28.3
95°	25.7	21.8	22.1	22.3	22.6	22.8	24.2	25.6	26.9	28.4	29.2
97.5°	140.5	130.1	104.4	78.7	53.1	27.4	27.5	27.6	27.7	27.9	28.1
100°	186.5	172.7	140.9	109.1	77.4	45.6	41.6	37.7	33.9	30.0	28.1
102.5°	236.7	236.2	232.1	227.9	223.8	219.6	177.5	135.2	93.0	50.7	29.7
105°	317.4	318.7	319.9	320.9	322.1	323.2	325.4	327.4	329.5	331.5	328.4
107.5°	395.7	396.8	398.3	399.9	401.4	403.1	404.0	405.1	406.1	407.1	408.0
110°	450.4	451.4	452.8	454.1	455.6	456.9	457.4	457.9	458.3	458.8	459.3



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	505.6	506.6	507.2	507.8	508.5	509.2	509.1	509.0	508.9	508.8	509.2
115°	585.1	585.3	585.1	584.9	584.6	584.3	584.9	585.3	585.8	586.2	586.5
117.5°	659.5	660.2	660.8	661.3	661.8	662.3	662.2	662.1	662.0	661.9	661.8
120°	709.3	709.6	709.4	709.2	708.9	708.7	709.2	709.6	710.1	710.5	710.5
122.5°	754.2	754.7	755.0	755.3	755.6	756.0	756.3	756.5	756.8	757.1	757.0
125°	822.2	822.4	822.0	821.5	821.1	820.6	821.3	822.0	822.7	823.4	823.9
127.5°	882.4	883.1	884.1	885.2	886.3	887.3	887.2	887.1	886.9	886.8	886.6
130°	923.1	923.5	924.3	924.9	925.6	926.3	926.5	926.8	927.0	927.2	927.3
132.5°	961.1	961.8	962.6	963.5	964.4	965.3	965.5	965.7	966.0	966.2	966.2
135°	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0	1019.4	1019.8	1020.4	1020.8
137.5°	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4	1070.9	1071.4	1071.9	1072.1
140°	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1	1102.8	1103.5	1104.2	1104.7
142.5°	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8	1132.3	1132.7	1133.3	1133.5
145°	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2	1174.4	1174.7	1174.8	1175.2
147.5°	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2	1211.4	1211.6	1211.7	1211.9
150°	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0	1235.0	1235.0	1235.0	1235.2
152.5°	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4	1255.7	1256.1	1256.4	1256.5
155°	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6	1283.5	1284.4	1285.4	1285.5
157.5°	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9
160°	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5
162.5°	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8	1335.2	1336.6	1338.0	1337.9
165°	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9	1352.7	1354.6	1356.4	1356.3
167.5°	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5	1365.6	1367.5	1369.6	1369.4
170°	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6	1373.4	1375.3	1377.2	1376.9
172.5°	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5	1378.4	1380.3	1382.1	1381.8
175°	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2	1384.3	1386.3	1388.4	1388.0
177.5°	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1	1386.6	1388.0	1389.6	1389.2
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940  
 CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1418.1	1417.1	1413.6	1413.2	1413.6	1417.1	1418.1	1419.1	1420.5	1425.5	1419.5
5°	1309.9	1306.9	1305.0	1311.8	1305.0	1306.9	1309.9	1313.7	1319.8	1320.4	1326.6
7.5°	1228.4	1226.0	1220.6	1218.9	1220.6	1226.0	1228.4	1230.7	1236.8	1242.2	1251.2
10°	1176.2	1173.7	1168.8	1167.5	1168.8	1173.7	1176.2	1182.3	1188.5	1195.2	1201.5
12.5°	1125.9	1121.0	1120.0	1121.1	1120.0	1121.0	1125.9	1134.0	1150.0	1150.0	1151.1
15°	1059.1	1056.6	1049.8	1051.7	1049.8	1056.6	1059.1	1067.1	1074.4	1083.7	1093.0
17.5°	993.2	990.2	982.0	989.3	982.0	990.2	993.2	997.6	1007.0	1020.1	1034.0
20°	951.8	946.8	942.5	941.9	942.5	946.8	951.8	956.1	966.6	977.7	988.2
22.5°	912.3	907.9	907.5	903.5	907.5	907.9	912.3	919.1	929.6	935.8	945.7
25°	863.0	858.7	857.5	854.4	857.5	858.7	863.0	868.0	874.8	879.7	890.7
27.5°	825.2	823.0	820.8	821.8	820.8	823.0	825.2	825.8	828.8	835.4	841.8
30°	802.0	801.4	800.1	800.1	800.1	801.4	802.0	800.1	803.3	806.3	811.3
32.5°	782.7	782.7	783.4	783.4	783.4	782.7	782.7	779.9	781.0	782.1	784.6
35°	755.7	757.6	758.8	757.0	758.8	757.6	755.7	753.3	751.4	747.2	748.3
37.5°	731.4	733.2	734.9	737.0	734.9	733.2	731.4	726.3	721.8	718.0	713.6
40°	712.6	716.9	718.2	721.2	718.2	716.9	712.6	707.0	702.1	697.9	692.9
42.5°	694.8	699.6	702.8	703.5	702.8	699.6	694.8	689.3	681.9	676.6	669.7
45°	667.6	672.5	676.9	676.9	676.9	672.5	667.6	658.4	650.3	642.3	635.5
47.5°	639.4	646.5	650.9	651.9	650.9	646.5	639.4	629.9	618.7	608.8	599.1
50°	620.2	628.7	633.1	636.1	633.1	628.7	620.2	609.7	598.0	585.6	573.9
52.5°	601.4	610.0	615.8	617.4	615.8	610.0	601.4	588.4	574.3	561.0	550.7
55°	569.0	581.3	588.1	590.6	588.1	581.3	569.0	554.8	541.3	524.6	509.8
57.5°	538.4	549.7	557.7	559.5	557.7	549.7	538.4	521.7	504.3	486.5	470.7
60°	514.7	527.1	536.9	538.8	536.9	527.1	514.7	498.1	479.6	462.4	442.6
62.5°	490.5	503.4	512.3	517.1	512.3	503.4	490.5	473.0	453.0	433.7	414.0
65°	448.8	461.7	470.4	472.2	470.4	461.7	448.8	431.5	410.5	390.2	373.5
67.5°	403.1	416.1	421.8	425.3	421.8	416.1	403.1	386.9	366.1	345.1	326.2
70°	371.1	381.6	387.7	390.8	387.7	381.6	371.1	353.8	336.6	315.0	294.6
72.5°	334.6	345.5	352.8	353.4	352.8	345.5	334.6	319.8	301.6	281.5	263.6
75°	278.7	288.5	292.2	292.2	292.2	288.5	278.7	264.5	249.7	233.6	215.8
77.5°	220.5	225.6	230.3	231.3	230.3	225.6	220.5	210.4	198.1	182.1	168.6
80°	183.1	186.2	189.8	189.8	189.8	186.2	183.1	173.8	162.1	148.6	138.1
82.5°	144.6	147.2	150.9	150.4	150.9	147.2	144.6	137.3	127.6	118.5	109.0
85°	87.6	93.1	92.5	91.2	92.5	93.1	87.6	88.7	79.5	73.4	64.7
87.5°	45.4	46.0	47.5	48.6	47.5	46.0	45.4	43.8	39.2	36.5	34.2
90°	29.7	30.1	30.6	31.1	30.6	30.1	29.7	29.2	28.4	26.9	25.6
92.5°	28.4	28.4	28.5	28.6	28.5	28.4	28.4	28.3	27.5	26.1	24.7
95°	29.3	29.6	29.8	30.1	29.8	29.6	29.3	29.2	28.4	26.9	25.6
97.5°	28.4	28.5	28.8	29.0	28.8	28.5	28.4	28.1	27.9	27.7	27.6
100°	28.4	28.5	28.8	29.0	28.8	28.5	28.4	28.1	30.0	33.9	37.7
102.5°	29.7	29.8	29.8	29.9	29.8	29.8	29.7	29.7	50.7	93.0	135.2
105°	320.1	311.8	303.6	295.3	303.6	311.8	320.1	328.4	331.5	329.5	327.4
107.5°	408.9	409.8	410.6	411.5	410.6	409.8	408.9	408.0	407.1	406.1	405.1
110°	460.0	460.7	461.5	462.1	461.5	460.7	460.0	459.3	458.8	458.3	457.9



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	510.1	511.0	511.8	512.6	511.8	511.0	510.1	509.2	508.8	508.9	509.0
115°	586.5	586.5	586.5	586.5	586.5	586.5	586.5	586.5	586.2	585.8	585.3
117.5°	661.7	661.6	661.6	661.5	661.6	661.6	661.7	661.8	661.9	662.0	662.1
120°	710.1	709.6	709.2	708.7	709.2	709.6	710.1	710.5	710.5	710.1	709.6
122.5°	756.5	756.1	755.5	755.1	755.5	756.1	756.5	757.0	757.1	756.8	756.5
125°	824.0	824.3	824.6	824.7	824.6	824.3	824.0	823.9	823.4	822.7	822.0
127.5°	886.4	886.3	886.1	885.9	886.1	886.3	886.4	886.6	886.8	886.9	887.1
130°	927.3	927.3	927.3	927.3	927.3	927.3	927.3	927.3	927.2	927.0	926.8
132.5°	966.0	965.8	965.6	965.5	965.6	965.8	966.0	966.2	966.2	966.0	965.7
135°	1021.3	1021.7	1022.2	1022.6	1022.2	1021.7	1021.3	1020.8	1020.4	1019.8	1019.4
137.5°	1072.0	1071.8	1071.7	1071.6	1071.7	1071.8	1072.0	1072.1	1071.9	1071.4	1070.9
140°	1104.8	1105.1	1105.3	1105.5	1105.3	1105.1	1104.8	1104.7	1104.2	1103.5	1102.8
142.5°	1133.6	1133.6	1133.7	1133.7	1133.7	1133.6	1133.6	1133.5	1133.3	1132.7	1132.3
145°	1175.6	1176.1	1176.6	1177.1	1176.6	1176.1	1175.6	1175.2	1174.8	1174.7	1174.4
147.5°	1212.2	1212.5	1212.6	1212.9	1212.6	1212.5	1212.2	1211.9	1211.7	1211.6	1211.4
150°	1235.4	1235.6	1235.9	1236.1	1235.9	1235.6	1235.4	1235.2	1235.0	1235.0	1235.0
152.5°	1256.4	1256.2	1256.2	1256.0	1256.2	1256.2	1256.4	1256.5	1256.4	1256.1	1255.7
155°	1284.8	1284.1	1283.4	1282.7	1283.4	1284.1	1284.8	1285.5	1285.4	1284.4	1283.5
157.5°	1308.7	1307.5	1306.3	1305.1	1306.3	1307.5	1308.7	1309.9	1309.9	1308.7	1307.5
160°	1324.2	1322.8	1321.4	1320.0	1321.4	1322.8	1324.2	1325.5	1325.5	1324.2	1322.8
162.5°	1336.3	1334.8	1333.2	1331.6	1333.2	1334.8	1336.3	1337.9	1338.0	1336.6	1335.2
165°	1354.2	1352.1	1350.1	1348.0	1350.1	1352.1	1354.2	1356.3	1356.4	1354.6	1352.7
167.5°	1367.2	1364.9	1362.5	1360.2	1362.5	1364.9	1367.2	1369.4	1369.6	1367.5	1365.6
170°	1374.6	1372.3	1370.0	1367.7	1370.0	1372.3	1374.6	1376.9	1377.2	1375.3	1373.4
172.5°	1379.3	1376.8	1374.3	1371.8	1374.3	1376.8	1379.3	1381.8	1382.1	1380.3	1378.4
175°	1385.3	1382.5	1379.7	1377.0	1379.7	1382.5	1385.3	1388.0	1388.4	1386.3	1384.3
177.5°	1387.0	1384.7	1382.5	1380.4	1382.5	1384.7	1387.0	1389.2	1389.6	1388.0	1386.6
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940  
 CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1422.5	1424.5	1432.4	1439.8	1448.7	1455.1	1459.5	1464.5	1474.8	1483.2	1491.0
5°	1332.8	1335.9	1351.8	1363.0	1382.1	1398.7	1411.7	1425.8	1442.5	1465.3	1486.2
7.5°	1253.7	1265.2	1282.7	1300.7	1320.2	1342.0	1361.0	1382.3	1411.0	1442.3	1474.6
10°	1208.9	1221.8	1240.3	1261.2	1279.8	1305.0	1328.5	1353.7	1386.3	1424.6	1462.9
12.5°	1164.0	1185.3	1199.4	1224.2	1244.2	1265.1	1289.9	1323.1	1361.2	1401.4	1447.5
15°	1107.8	1119.5	1146.6	1160.1	1188.5	1220.6	1245.2	1278.5	1315.5	1368.5	1420.3
17.5°	1042.9	1058.3	1079.9	1105.8	1138.4	1163.3	1194.1	1228.3	1275.0	1327.6	1392.4
20°	1000.5	1013.4	1039.9	1068.3	1102.8	1129.4	1162.0	1195.2	1243.4	1299.5	1367.3
22.5°	962.5	975.0	1003.0	1029.3	1062.8	1095.3	1129.4	1168.1	1214.2	1273.4	1342.6
25°	903.7	920.3	945.0	972.1	1004.2	1041.2	1078.2	1112.7	1162.0	1224.2	1298.2
27.5°	851.6	864.9	882.8	913.6	949.9	985.7	1022.4	1065.9	1113.2	1179.0	1255.8
30°	818.1	830.4	848.2	876.6	910.5	948.7	986.9	1028.9	1078.2	1143.5	1221.8
32.5°	791.4	800.8	816.6	842.0	873.0	913.2	950.9	994.3	1046.1	1110.4	1186.8
35°	752.1	760.1	766.2	790.3	818.1	855.0	893.2	939.5	989.4	1050.4	1126.9
37.5°	713.5	716.2	725.2	740.9	767.9	801.9	837.4	882.9	934.1	996.0	1065.0
40°	689.8	691.1	696.6	711.4	734.8	766.9	801.4	846.4	895.1	953.7	1022.1
42.5°	666.6	665.8	670.9	681.3	703.2	732.4	766.3	807.4	856.1	910.3	974.7
45°	630.0	630.0	628.7	637.4	655.3	683.7	712.0	751.4	792.1	845.2	899.4
47.5°	591.8	588.4	589.4	593.9	608.9	632.2	660.8	693.1	729.0	773.9	821.4
50°	567.1	562.2	560.4	565.3	578.8	599.1	626.3	654.7	688.6	728.0	768.7
52.5°	540.0	535.1	531.7	535.2	547.8	566.6	591.3	616.2	646.7	678.7	714.0
55°	498.1	492.6	490.7	492.0	501.1	515.9	536.9	559.7	582.6	609.0	633.7
57.5°	456.8	447.6	445.9	445.3	451.7	465.3	482.8	502.6	519.2	535.2	561.4
60°	429.6	418.6	414.8	414.3	419.2	430.3	446.3	466.0	477.8	488.8	511.7
62.5°	400.6	389.9	381.8	382.7	387.1	397.7	411.8	426.1	433.8	445.9	461.4
65°	355.7	342.1	336.0	334.1	336.6	345.2	356.3	365.5	374.2	379.2	393.9
67.5°	310.9	299.4	290.3	288.1	287.0	292.9	302.0	307.6	313.8	318.1	326.8
70°	279.3	269.4	258.3	254.6	254.0	258.9	267.5	268.1	276.8	278.7	287.8
72.5°	248.2	235.9	228.2	224.5	221.9	226.3	232.0	233.6	238.4	241.7	246.5
75°	199.7	190.5	183.1	177.5	175.7	178.2	178.2	181.2	184.3	186.2	191.7
77.5°	157.2	146.6	137.9	134.6	132.4	130.8	132.2	134.0	132.5	135.7	137.0
80°	127.6	116.5	109.8	108.5	104.8	101.7	101.1	102.9	100.5	101.7	105.4
82.5°	98.5	91.4	84.1	82.8	78.2	76.6	76.0	74.8	74.8	74.5	75.3
85°	58.6	54.2	49.3	46.2	44.4	41.3	41.3	40.0	38.9	37.6	38.3
87.5°	28.5	27.3	24.4	22.6	21.2	18.9	18.5	16.4	15.4	14.4	13.5
90°	24.2	22.8	21.0	19.1	17.3	15.4	13.2	10.7	8.2	5.6	3.1
92.5°	23.4	21.9	20.2	18.3	16.4	14.6	13.6	13.5	13.4	13.2	13.0
95°	24.2	22.8	22.6	22.3	22.1	21.8	25.7	33.5	41.3	49.1	57.0
97.5°	27.5	27.4	53.1	78.7	104.4	130.1	140.5	135.6	130.8	125.9	121.0
100°	41.6	45.6	77.4	109.1	140.9	172.7	186.5	182.4	178.3	174.1	170.0
102.5°	177.5	219.6	223.8	227.9	232.1	236.2	236.7	233.7	230.7	227.7	224.6
105°	325.4	323.2	322.1	320.9	319.9	318.7	317.4	316.0	314.6	313.3	311.8
107.5°	404.0	403.1	401.4	399.9	398.3	396.8	395.7	394.9	394.3	393.6	392.9
110°	457.4	456.9	455.6	454.1	452.8	451.4	450.4	449.7	449.0	448.3	447.6



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	509.1	509.2	508.5	507.8	507.2	506.6	505.6	504.4	503.1	501.9	500.7
115°	584.9	584.3	584.6	584.9	585.1	585.3	585.1	584.3	583.7	583.0	582.3
117.5°	662.2	662.3	661.8	661.3	660.8	660.2	659.5	658.6	657.7	656.7	655.9
120°	709.2	708.7	708.9	709.2	709.4	709.6	709.3	708.4	707.5	706.5	705.6
122.5°	756.3	756.0	755.6	755.3	755.0	754.7	754.2	753.7	753.1	752.6	752.0
125°	821.3	820.6	821.1	821.5	822.0	822.4	822.2	821.3	820.4	819.5	818.5
127.5°	887.2	887.3	886.3	885.2	884.1	883.1	882.4	882.3	882.0	881.7	881.5
130°	926.5	926.3	925.6	924.9	924.3	923.5	923.1	922.8	922.7	922.4	922.1
132.5°	965.5	965.3	964.4	963.5	962.6	961.8	961.1	960.7	960.3	959.8	959.5
135°	1019.0	1018.5	1017.6	1016.6	1015.7	1014.9	1014.5	1014.7	1014.9	1015.2	1015.4
137.5°	1070.4	1069.9	1068.9	1067.9	1066.8	1065.9	1065.3	1065.2	1065.1	1065.1	1065.0
140°	1102.1	1101.4	1100.9	1100.5	1100.0	1099.6	1099.1	1098.7	1098.1	1097.7	1097.3
142.5°	1131.8	1131.2	1131.0	1130.7	1130.4	1130.2	1129.6	1128.7	1127.9	1127.1	1126.2
145°	1174.2	1173.9	1173.9	1173.9	1173.9	1173.9	1173.6	1172.9	1172.2	1171.5	1170.8
147.5°	1211.2	1211.0	1211.2	1211.5	1211.7	1211.9	1211.4	1210.1	1208.8	1207.6	1206.2
150°	1235.0	1235.0	1235.3	1235.6	1235.7	1236.0	1235.6	1234.8	1233.8	1232.9	1232.0
152.5°	1255.4	1255.0	1255.4	1255.8	1256.2	1256.6	1256.4	1255.7	1255.0	1254.3	1253.5
155°	1282.6	1281.7	1282.4	1283.1	1283.8	1284.4	1284.7	1284.4	1284.2	1284.0	1283.8
157.5°	1306.3	1305.1	1305.9	1306.7	1307.4	1308.2	1308.7	1308.9	1308.9	1309.1	1309.2
160°	1321.4	1320.0	1320.3	1320.4	1320.7	1321.0	1321.4	1322.1	1322.8	1323.5	1324.2
162.5°	1333.8	1332.5	1332.7	1332.9	1333.1	1333.4	1333.9	1334.8	1335.7	1336.6	1337.4
165°	1350.9	1349.1	1349.1	1349.1	1349.1	1349.1	1349.6	1350.8	1351.9	1353.1	1354.2
167.5°	1363.5	1361.5	1361.6	1361.7	1361.9	1362.0	1362.7	1363.9	1365.1	1366.3	1367.4
170°	1371.6	1369.8	1369.5	1369.3	1369.0	1368.9	1369.4	1370.8	1372.2	1373.6	1374.9
172.5°	1376.5	1374.8	1374.5	1374.3	1374.0	1373.8	1374.4	1375.7	1377.2	1378.5	1379.9
175°	1382.2	1380.1	1379.9	1379.7	1379.4	1379.2	1379.7	1381.2	1382.5	1383.9	1385.3
177.5°	1385.1	1383.7	1383.3	1382.9	1382.5	1382.2	1382.6	1383.9	1385.2	1386.5	1387.8
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1498.0	1502.9	1509.3	1520.2	1524.1	1529.0	1536.0	1535.4	1537.4	1544.8	1560.6
5°	1503.5	1522.6	1541.1	1563.3	1586.7	1602.1	1623.1	1636.0	1649.0	1665.6	1694.0
7.5°	1505.7	1536.1	1569.9	1608.9	1643.6	1683.6	1714.7	1744.0	1770.6	1805.7	1839.5
10°	1502.3	1542.9	1586.7	1636.0	1688.5	1732.9	1772.9	1818.6	1857.3	1899.9	1938.1
12.5°	1495.8	1545.0	1603.5	1658.8	1720.0	1785.6	1835.5	1881.6	1933.3	1982.3	2041.2
15°	1481.3	1548.5	1616.9	1689.7	1771.7	1847.4	1919.6	1979.4	2034.9	2108.3	2185.3
17.5°	1462.9	1535.3	1621.6	1709.7	1795.4	1882.0	1971.3	2061.2	2131.2	2222.3	2282.6
20°	1445.6	1529.4	1618.2	1723.0	1808.7	1916.6	2005.3	2092.2	2188.3	2279.0	2351.1
22.5°	1421.4	1513.1	1607.3	1711.6	1824.4	1932.3	2034.9	2129.2	2225.4	2323.9	2411.3
25°	1390.7	1473.9	1585.5	1703.9	1816.1	1933.1	2050.9	2169.3	2272.8	2377.0	2458.4
27.5°	1338.5	1443.5	1547.4	1669.6	1794.2	1926.7	2052.6	2176.6	2285.0	2370.7	2421.2
30°	1311.8	1403.0	1515.8	1638.5	1773.5	1915.9	2047.2	2168.6	2269.8	2338.2	2358.5
32.5°	1272.4	1366.5	1476.9	1604.0	1746.9	1893.2	2030.0	2144.5	2228.8	2264.7	2240.2
35°	1213.8	1298.9	1410.4	1540.5	1689.1	1845.0	1980.0	2076.8	2120.0	2086.1	2001.6
37.5°	1143.5	1227.8	1339.9	1467.7	1621.4	1779.9	1902.0	1971.7	1957.3	1873.0	1747.1
40°	1094.2	1173.1	1279.8	1417.8	1567.6	1726.6	1833.9	1871.5	1832.1	1711.3	1577.5
42.5°	1039.5	1116.4	1223.5	1356.6	1515.4	1662.1	1755.5	1758.6	1692.5	1548.0	1413.7
45°	956.1	1029.5	1130.6	1269.3	1415.9	1554.1	1615.7	1585.5	1463.5	1324.1	1189.1
47.5°	873.9	937.5	1037.1	1168.8	1308.1	1424.3	1454.9	1400.5	1270.5	1135.2	1010.1
50°	813.7	877.8	971.5	1097.3	1231.6	1332.1	1346.9	1274.8	1147.2	1010.9	912.9
52.5°	756.0	819.7	909.9	1026.3	1149.3	1239.9	1240.4	1156.9	1029.8	908.4	817.3
55°	671.3	728.6	810.0	914.2	1024.0	1094.8	1077.5	991.2	880.9	775.5	696.0
57.5°	589.7	639.6	714.6	801.5	898.1	956.6	928.0	844.9	746.4	657.0	596.7
60°	536.9	584.4	648.5	730.5	811.9	857.5	830.4	755.1	664.5	592.4	540.0
62.5°	485.6	525.7	587.4	658.5	734.0	767.8	743.6	669.3	591.0	525.8	483.3
65°	413.0	445.7	495.0	556.1	610.9	639.9	619.6	550.5	490.7	443.8	409.9
67.5°	345.2	370.8	408.0	457.0	503.6	519.3	500.8	452.7	402.1	364.5	340.6
70°	298.4	322.4	353.8	391.5	432.1	448.8	430.3	392.1	350.8	316.2	292.8
72.5°	257.4	276.1	302.6	334.7	366.6	383.2	370.6	333.9	299.0	273.3	253.3
75°	196.0	212.0	230.5	253.3	278.0	289.1	278.0	252.7	228.7	209.6	195.4
77.5°	142.5	151.1	165.4	182.4	197.9	206.3	196.8	179.6	165.0	151.9	144.9
80°	108.5	114.7	124.5	138.1	148.6	156.6	150.4	136.3	124.5	115.9	112.8
82.5°	78.9	83.1	89.5	99.6	106.6	110.8	108.0	97.7	92.9	85.3	82.2
85°	38.9	41.3	45.7	48.7	54.8	55.5	56.1	51.8	47.4	45.7	43.2
87.5°	14.4	15.4	17.4	19.4	21.8	22.6	22.6	22.9	21.3	21.1	19.4
90°	5.6	8.2	10.7	13.2	15.4	17.3	19.1	21.0	22.8	24.2	25.6
92.5°	13.2	13.4	13.5	13.6	14.6	16.4	18.3	20.2	21.9	23.4	24.7
95°	49.1	41.3	33.5	25.7	21.8	22.1	22.3	22.6	22.8	24.2	25.6
97.5°	125.9	130.8	135.6	140.5	130.1	104.4	78.7	53.1	27.4	27.5	27.6
100°	174.1	178.3	182.4	186.5	172.7	140.9	109.1	77.4	45.6	41.6	37.7
102.5°	227.7	230.7	233.7	236.7	236.2	232.1	227.9	223.8	219.6	177.5	135.2
105°	313.3	314.6	316.0	317.4	318.7	319.9	320.9	322.1	323.2	325.4	327.4
107.5°	393.6	394.3	394.9	395.7	396.8	398.3	399.9	401.4	403.1	404.0	405.1
110°	448.3	449.0	449.7	450.4	451.4	452.8	454.1	455.6	456.9	457.4	457.9





TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	501.9	503.1	504.4	505.6	506.6	507.2	507.8	508.5	509.2	509.1	509.0
115°	583.0	583.7	584.3	585.1	585.3	585.1	584.9	584.6	584.3	584.9	585.3
117.5°	656.7	657.7	658.6	659.5	660.2	660.8	661.3	661.8	662.3	662.2	662.1
120°	706.5	707.5	708.4	709.3	709.6	709.4	709.2	708.9	708.7	709.2	709.6
122.5°	752.6	753.1	753.7	754.2	754.7	755.0	755.3	755.6	756.0	756.3	756.5
125°	819.5	820.4	821.3	822.2	822.4	822.0	821.5	821.1	820.6	821.3	822.0
127.5°	881.7	882.0	882.3	882.4	883.1	884.1	885.2	886.3	887.3	887.2	887.1
130°	922.4	922.7	922.8	923.1	923.5	924.3	924.9	925.6	926.3	926.5	926.8
132.5°	959.8	960.3	960.7	961.1	961.8	962.6	963.5	964.4	965.3	965.5	965.7
135°	1015.2	1014.9	1014.7	1014.5	1014.9	1015.7	1016.6	1017.6	1018.5	1019.0	1019.4
137.5°	1065.1	1065.1	1065.2	1065.3	1065.9	1066.8	1067.9	1068.9	1069.9	1070.4	1070.9
140°	1097.7	1098.1	1098.7	1099.1	1099.6	1100.0	1100.5	1100.9	1101.4	1102.1	1102.8
142.5°	1127.1	1127.9	1128.7	1129.6	1130.2	1130.4	1130.7	1131.0	1131.2	1131.8	1132.3
145°	1171.5	1172.2	1172.9	1173.6	1173.9	1173.9	1173.9	1173.9	1173.9	1174.2	1174.4
147.5°	1207.6	1208.8	1210.1	1211.4	1211.9	1211.7	1211.5	1211.2	1211.0	1211.2	1211.4
150°	1232.9	1233.8	1234.8	1235.6	1236.0	1235.7	1235.6	1235.3	1235.0	1235.0	1235.0
152.5°	1254.3	1255.0	1255.7	1256.4	1256.6	1256.2	1255.8	1255.4	1255.0	1255.4	1255.7
155°	1284.0	1284.2	1284.4	1284.7	1284.4	1283.8	1283.1	1282.4	1281.7	1282.6	1283.5
157.5°	1309.1	1308.9	1308.9	1308.7	1308.2	1307.4	1306.7	1305.9	1305.1	1306.3	1307.5
160°	1323.5	1322.8	1322.1	1321.4	1321.0	1320.7	1320.4	1320.3	1320.0	1321.4	1322.8
162.5°	1336.6	1335.7	1334.8	1333.9	1333.4	1333.1	1332.9	1332.7	1332.5	1333.8	1335.2
165°	1353.1	1351.9	1350.8	1349.6	1349.1	1349.1	1349.1	1349.1	1349.1	1350.9	1352.7
167.5°	1366.3	1365.1	1363.9	1362.7	1362.0	1361.9	1361.7	1361.6	1361.5	1363.5	1365.6
170°	1373.6	1372.2	1370.8	1369.4	1368.9	1369.0	1369.3	1369.5	1369.8	1371.6	1373.4
172.5°	1378.5	1377.2	1375.7	1374.4	1373.8	1374.0	1374.3	1374.5	1374.8	1376.5	1378.4
175°	1383.9	1382.5	1381.2	1379.7	1379.2	1379.4	1379.7	1379.9	1380.1	1382.2	1384.3
177.5°	1386.5	1385.2	1383.9	1382.6	1382.2	1382.5	1382.9	1383.3	1383.7	1385.1	1386.6
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1	1488.1
2.5°	1568.5	1569.5	1573.9	1577.3	1578.3	1583.3	1583.8
5°	1706.3	1716.8	1737.1	1739.0	1742.0	1758.1	1745.8
7.5°	1867.9	1894.4	1912.2	1927.9	1933.6	1940.5	1939.1
10°	1971.4	2010.8	2030.6	2062.0	2063.2	2071.3	2066.4
12.5°	2075.5	2121.3	2157.3	2163.1	2189.5	2193.5	2200.5
15°	2222.9	2271.6	2321.6	2339.4	2375.8	2384.4	2398.0
17.5°	2361.5	2411.3	2446.3	2492.5	2507.5	2527.5	2513.8
20°	2437.4	2491.7	2536.0	2572.4	2587.8	2598.9	2597.7
22.5°	2483.3	2538.0	2574.0	2601.5	2615.9	2620.6	2620.4
25°	2512.0	2543.4	2554.6	2565.0	2549.0	2543.4	2545.9
27.5°	2432.1	2424.0	2395.0	2357.1	2317.6	2286.3	2269.2
30°	2322.2	2274.0	2230.3	2153.8	2114.4	2091.0	2070.0
32.5°	2166.3	2090.1	2005.9	1935.9	1891.1	1856.3	1851.1
35°	1899.3	1784.6	1681.7	1596.0	1551.6	1513.9	1505.4
37.5°	1614.7	1495.6	1402.9	1327.5	1279.8	1253.2	1228.4
40°	1425.8	1323.5	1232.3	1168.1	1131.8	1112.7	1097.3
42.5°	1280.3	1186.9	1096.2	1047.3	1014.4	1002.7	993.7
45°	1079.4	992.5	929.6	892.6	873.5	853.8	844.5
47.5°	918.5	847.7	806.3	774.9	754.4	742.7	736.7
50°	827.2	769.3	732.4	708.3	689.8	680.6	675.6
52.5°	746.4	698.8	667.7	648.6	636.1	629.3	627.3
55°	642.9	606.5	586.8	570.2	561.0	554.8	552.3
57.5°	558.8	530.9	514.9	501.1	497.6	492.4	490.7
60°	503.6	482.1	468.5	459.2	456.2	450.0	451.2
62.5°	454.8	437.2	425.6	420.3	416.3	411.1	412.8
65°	384.7	371.8	365.5	360.6	355.7	352.6	355.1
67.5°	322.8	313.9	305.5	302.6	300.2	299.7	297.1
70°	282.3	274.9	267.5	265.7	265.7	263.2	262.6
72.5°	243.3	237.9	233.0	231.7	229.7	230.7	228.1
75°	188.0	183.7	181.8	180.0	179.4	179.4	177.5
77.5°	138.9	135.7	132.8	132.8	130.5	129.7	129.5
80°	105.4	104.2	101.7	101.7	100.5	101.1	99.9
82.5°	79.3	77.6	77.0	76.1	74.4	74.5	73.2
85°	42.5	40.7	40.0	38.3	37.0	38.3	37.0
87.5°	20.2	20.0	19.6	18.7	18.4	18.5	17.0
90°	26.9	28.4	29.2	29.7	30.1	30.6	31.1
92.5°	26.1	27.5	28.3	28.4	28.4	28.5	28.6
95°	26.9	28.4	29.2	29.3	29.6	29.8	30.1
97.5°	27.7	27.9	28.1	28.4	28.5	28.8	29.0
100°	33.9	30.0	28.1	28.4	28.5	28.8	29.0
102.5°	93.0	50.7	29.7	29.7	29.8	29.8	29.9
105°	329.5	331.5	328.4	320.1	311.8	303.6	295.3
107.5°	406.1	407.1	408.0	408.9	409.8	410.6	411.5
110°	458.3	458.8	459.3	460.0	460.7	461.5	462.1



TEST NUMBER: P332661-940

CATALOG NUMBER: SA4XXDIP-C1020D1205U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	508.9	508.8	509.2	510.1	511.0	511.8	512.6
115°	585.8	586.2	586.5	586.5	586.5	586.5	586.5
117.5°	662.0	661.9	661.8	661.7	661.6	661.6	661.5
120°	710.1	710.5	710.5	710.1	709.6	709.2	708.7
122.5°	756.8	757.1	757.0	756.5	756.1	755.5	755.1
125°	822.7	823.4	823.9	824.0	824.3	824.6	824.7
127.5°	886.9	886.8	886.6	886.4	886.3	886.1	885.9
130°	927.0	927.2	927.3	927.3	927.3	927.3	927.3
132.5°	966.0	966.2	966.2	966.0	965.8	965.6	965.5
135°	1019.8	1020.4	1020.8	1021.3	1021.7	1022.2	1022.6
137.5°	1071.4	1071.9	1072.1	1072.0	1071.8	1071.7	1071.6
140°	1103.5	1104.2	1104.7	1104.8	1105.1	1105.3	1105.5
142.5°	1132.7	1133.3	1133.5	1133.6	1133.6	1133.7	1133.7
145°	1174.7	1174.8	1175.2	1175.6	1176.1	1176.6	1177.1
147.5°	1211.6	1211.7	1211.9	1212.2	1212.5	1212.6	1212.9
150°	1235.0	1235.0	1235.2	1235.4	1235.6	1235.9	1236.1
152.5°	1256.1	1256.4	1256.5	1256.4	1256.2	1256.2	1256.0
155°	1284.4	1285.4	1285.5	1284.8	1284.1	1283.4	1282.7
157.5°	1308.7	1309.9	1309.9	1308.7	1307.5	1306.3	1305.1
160°	1324.2	1325.5	1325.5	1324.2	1322.8	1321.4	1320.0
162.5°	1336.6	1338.0	1337.9	1336.3	1334.8	1333.2	1331.6
165°	1354.6	1356.4	1356.3	1354.2	1352.1	1350.1	1348.0
167.5°	1367.5	1369.6	1369.4	1367.2	1364.9	1362.5	1360.2
170°	1375.3	1377.2	1376.9	1374.6	1372.3	1370.0	1367.7
172.5°	1380.3	1382.1	1381.8	1379.3	1376.8	1374.3	1371.8
175°	1386.3	1388.4	1388.0	1385.3	1382.5	1379.7	1377.0
177.5°	1388.0	1389.6	1389.2	1387.0	1384.7	1382.5	1380.4
180°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3

(END OF REPORT)