

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332641-940

Luminaire Tested: **SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332641-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5774.8 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332641-940
CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68				
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	58				
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48				
3	85	75	67	61	80	71	64	59	63	58	54	57	52	49	50	47	44	41				
4	78	66	58	52	73	63	56	50	56	50	46	51	46	42	45	41	38	35				
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30				
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27				
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24				
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21				
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19				
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.9	2.5
10°-20°	408.3	7.1
20°-30°	600.9	10.4
30°-40°	698.6	12.1
40°-50°	698.6	12.1
50°-60°	611.1	10.6
60°-70°	453.8	7.9
70°-80°	257.8	4.5
80°-90°	76.4	1.3
90°-100°	43.4	0.8
100°-110°	128.5	2.2
110°-120°	218.1	3.8
120°-130°	287.6	5.0
130°-140°	322.9	5.6
140°-150°	317.3	5.5
150°-160°	266.9	4.6
160°-170°	177.6	3.1
170°-180°	62.2	1.1
0°-30°	1154.1	20.0
0°-40°	1852.6	32.1
0°-60°	3162.3	54.8
0°-90°	3950.4	68.4
90°-120°	389.9	6.8
90°-150°	1317.8	22.8
90°-180°	1824.0	31.6
0°-180°	5774.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	2	7	11	14	15	5
95°	30	35	39	40	40	34
105°	118	119	121	123	124	126
115°	222	222	221	220	220	219
125°	323	323	322	321	320	288
135°	416	419	420	419	417	322
145°	506	508	508	508	507	317
155°	580	580	579	581	579	267
165°	631	630	629	631	630	178
175°	657	654	654	657	654	62
180°	658	658	658	658	658	



TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	25.9	25.9	26.0	26.0	26.0	26.0	26.0	25.9	25.9	25.9	26.0
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	10.9	12.3	13.7	15.2	16.6	17.6	18.3	18.9	19.5	20.2	20.5
95°	30.5	31.6	32.5	33.5	34.6	35.5	36.3	37.1	37.9	38.6	39.0
97.5°	53.3	54.1	54.9	55.7	56.5	57.4	58.3	59.3	60.2	61.2	61.5
100°	71.2	71.7	72.1	72.6	73.0	73.7	74.7	75.8	76.8	77.8	78.0
102.5°	89.9	90.1	90.2	90.4	90.6	91.2	92.1	93.0	94.0	94.9	95.2
105°	118.5	118.6	118.7	118.9	119.0	119.2	119.7	120.1	120.6	121.0	121.4
107.5°	148.5	148.6	148.7	148.9	149.1	149.2	149.2	149.3	149.4	149.5	149.7
110°	168.9	169.1	169.3	169.5	169.8	169.8	169.7	169.6	169.5	169.3	169.2



TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	190.0	190.0	190.1	190.1	190.2	190.1	189.9	189.7	189.5	189.3	189.2
115°	221.8	221.8	221.8	221.8	221.8	221.6	221.4	221.1	221.0	220.7	220.6
117.5°	251.6	251.7	251.8	251.9	252.0	252.0	251.8	251.6	251.5	251.4	250.9
120°	271.6	272.1	272.5	273.0	273.4	273.5	273.1	272.8	272.4	272.1	271.5
122.5°	292.3	292.5	292.7	292.8	293.0	293.1	292.9	292.7	292.6	292.5	292.0
125°	323.0	323.0	323.0	323.0	323.0	322.9	322.8	322.7	322.5	322.4	322.2
127.5°	350.7	351.1	351.4	351.8	352.0	352.1	352.0	351.8	351.6	351.4	351.2
130°	370.2	370.6	371.0	371.3	371.6	371.8	371.8	371.8	371.8	371.8	371.6
132.5°	390.2	390.5	390.7	390.9	391.2	391.3	391.2	391.1	391.0	390.9	390.7
135°	416.5	417.2	417.9	418.6	419.3	419.5	419.5	419.5	419.5	419.5	419.4
137.5°	445.2	445.5	445.9	446.1	446.5	446.7	446.9	447.1	447.3	447.5	447.2
140°	464.3	464.6	464.8	465.0	465.2	465.4	465.4	465.4	465.4	465.4	465.2
142.5°	481.8	482.1	482.3	482.5	482.8	482.8	482.7	482.6	482.5	482.4	482.4
145°	506.0	506.5	506.9	507.4	507.8	508.1	508.3	508.4	508.5	508.5	508.5
147.5°	530.0	530.6	531.1	531.6	532.3	532.4	532.4	532.3	532.2	532.1	532.0
150°	544.7	545.2	545.6	546.1	546.5	546.7	546.7	546.7	546.7	546.7	546.7
152.5°	558.6	558.8	559.1	559.4	559.6	559.8	559.9	560.0	560.1	560.2	560.4
155°	579.8	579.8	579.8	579.8	579.8	579.7	579.6	579.5	579.4	579.3	579.7
157.5°	597.7	597.4	597.3	597.1	596.9	596.7	596.7	596.7	596.7	596.6	597.0
160°	608.2	608.1	608.1	608.0	607.8	607.7	607.6	607.5	607.3	607.3	607.6
162.5°	618.0	617.8	617.4	617.2	616.9	616.6	616.5	616.4	616.4	616.2	616.8
165°	631.2	630.8	630.4	630.2	629.8	629.5	629.3	629.1	628.8	628.7	629.3
167.5°	641.2	640.8	640.2	639.8	639.4	639.1	639.1	639.2	639.2	639.2	639.9
170°	646.9	646.4	645.8	645.2	644.6	644.4	644.5	644.6	644.8	644.9	645.6
172.5°	650.9	650.5	650.1	649.6	649.1	648.9	648.9	648.9	648.9	649.0	649.7
175°	656.6	656.0	655.5	654.9	654.3	654.0	653.9	653.8	653.6	653.5	654.3
177.5°	658.4	658.0	657.5	657.1	656.6	656.4	656.4	656.4	656.4	656.4	657.0
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6



TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	26.2	26.3	26.5	26.6	26.6	26.7	26.7	26.8
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	21.0	21.4	21.8	22.0	22.2	22.3	22.5	22.6
95°	39.3	39.7	40.0	40.2	40.2	40.2	40.2	40.2
97.5°	62.0	62.3	62.8	63.0	63.0	63.0	63.0	63.0
100°	78.3	78.5	78.7	78.8	78.8	78.8	78.8	78.8
102.5°	95.5	95.9	96.1	96.4	96.5	96.6	96.7	96.8
105°	121.7	122.1	122.4	122.7	123.1	123.4	123.8	124.1
107.5°	150.1	150.3	150.7	150.9	150.8	150.8	150.8	150.8
110°	168.9	168.7	168.4	168.5	168.9	169.2	169.5	169.9



TEST NUMBER: P332641-940

CATALOG NUMBER: SA4XXDIP-C1020D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	189.2	189.1	189.1	189.1	189.2	189.2	189.3	189.4
115°	220.5	220.4	220.3	220.2	220.1	219.9	219.8	219.7
117.5°	250.6	250.2	249.8	249.5	249.2	249.1	248.8	248.6
120°	271.0	270.4	269.8	269.7	269.9	270.1	270.4	270.5
122.5°	291.7	291.3	290.9	290.5	290.1	289.7	289.3	288.9
125°	322.0	321.7	321.6	321.3	321.1	320.8	320.7	320.4
127.5°	351.0	350.8	350.5	350.4	350.2	350.0	349.8	349.6
130°	371.3	371.1	370.9	370.5	370.1	369.6	369.2	368.7
132.5°	390.5	390.2	390.0	389.8	389.6	389.4	389.2	389.1
135°	419.1	418.9	418.7	418.4	418.0	417.7	417.4	417.1
137.5°	446.8	446.6	446.3	446.1	446.2	446.3	446.4	446.5
140°	465.1	465.0	464.9	464.8	464.7	464.6	464.5	464.3
142.5°	482.4	482.4	482.3	482.3	482.3	482.3	482.2	482.2
145°	508.4	508.3	508.1	507.9	507.6	507.2	506.8	506.6
147.5°	531.9	531.8	531.7	531.6	531.5	531.4	531.3	531.2
150°	546.7	546.7	546.7	546.7	546.5	546.4	546.4	546.3
152.5°	560.7	561.0	561.2	561.2	561.0	560.6	560.4	560.1
155°	580.1	580.6	581.1	581.1	580.6	580.1	579.7	579.3
157.5°	597.4	597.7	598.1	598.0	597.6	597.3	596.8	596.5
160°	608.0	608.2	608.6	608.5	608.0	607.3	606.8	606.3
162.5°	617.4	618.0	618.7	618.7	618.1	617.5	617.0	616.4
165°	630.0	630.6	631.3	631.4	631.0	630.5	630.1	629.6
167.5°	640.5	641.2	641.9	641.9	641.2	640.5	639.8	639.1
170°	646.2	646.9	647.6	647.6	646.8	646.0	645.2	644.4
172.5°	650.5	651.3	652.0	652.0	651.2	650.4	649.6	648.9
175°	655.1	655.9	656.7	656.7	655.9	655.1	654.3	653.5
177.5°	657.6	658.3	658.9	658.9	658.2	657.5	656.7	655.9
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6

(END OF REPORT)