

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332699-940

Luminaire Tested: **SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332699-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8039.7 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	42
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	45	66	55	48	43	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	44	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13875	13875	13875	13875
5°	16339	13910	12277	13910
10°	19563	13849	11053	13849
15°	23147	13709	10151	13709
20°	25775	13566	9346	13566
25°	26191	13356	8790	13356
30°	22287	13154	8614	13154
35°	17134	12827	8615	12827
40°	13355	12440	8778	12440
45°	11136	11860	8926	11860
50°	9800	11150	9229	11150
55°	8978	10301	9600	10301
60°	8414	9541	10046	9541
65°	7834	8692	10418	8692
70°	7159	7848	10655	7848
75°	6394	6906	10524	6906
80°	5360	5658	10195	5658
85°	3955	4085	9763	4085



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.4	2.1
10°-20°	516.1	6.4
20°-30°	818.4	10.2
30°-40°	910.7	11.3
40°-50°	829.0	10.3
50°-60°	677.5	8.4
60°-70°	483.6	6.0
70°-80°	266.3	3.3
80°-90°	75.2	0.9
90°-100°	327.3	4.1
100°-110°	681.1	8.5
110°-120°	610.1	7.6
120°-130°	513.2	6.4
130°-140°	427.9	5.3
140°-150°	326.9	4.1
150°-160°	229.8	2.9
160°-170°	135.2	1.7
170°-180°	44.0	0.5
0°-30°	1501.9	18.7
0°-40°	2412.6	30.0
0°-60°	3919.1	48.7
0°-90°	4744.3	59.0
90°-120°	1618.5	20.1
90°-150°	2886.5	35.9
90°-180°	3295.0	41.0
0°-180°	8039.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1719	1719	1719	1719	1719	
5°	2016	1716	1515	1716	2016	205
15°	2770	1640	1215	1640	2770	782
25°	2940	1499	987	1499	2940	1296
35°	1739	1302	874	1302	1739	1104
45°	975	1039	782	1039	975	768
55°	638	732	682	732	638	576
65°	410	455	545	455	410	406
75°	205	221	337	221	205	218
85°	43	44	105	44	43	52
90°	19	1	19	1	19	17
95°	217	29	217	29	217	337
105°	1252	104	1252	104	1252	1238
115°	1203	183	1203	183	1203	1194
125°	960	256	960	256	960	872
135°	858	304	858	304	858	662
145°	701	350	701	350	701	444
155°	587	398	587	398	587	274
165°	512	434	512	434	512	147
175°	461	452	461	452	461	45
180°	453	453	453	453	453	



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1829.2	1828.5	1822.9	1821.8	1817.8	1812.7	1811.5	1802.4	1784.1	1775.6	1773.3
5°	2016.2	2030.5	2012.0	2008.4	2006.3	1982.8	1970.7	1956.4	1923.7	1904.5	1889.5
7.5°	2239.5	2241.2	2233.1	2226.6	2208.5	2188.0	2157.2	2124.5	2085.4	2044.9	2014.3
10°	2386.5	2392.2	2382.9	2381.5	2345.2	2322.4	2276.8	2238.4	2194.2	2145.1	2100.2
12.5°	2541.4	2533.4	2528.7	2498.2	2491.5	2450.0	2397.0	2357.4	2289.4	2232.8	2173.2
15°	2769.5	2753.9	2743.9	2701.9	2681.2	2623.5	2567.3	2523.9	2434.9	2350.2	2286.1
17.5°	2903.3	2919.0	2895.9	2878.7	2825.3	2784.9	2727.4	2636.3	2566.6	2461.4	2380.5
20°	3000.2	3001.6	2988.7	2971.0	2929.0	2877.7	2815.0	2715.3	2632.1	2527.5	2416.4
22.5°	3026.4	3026.6	3021.2	3004.6	2972.8	2931.2	2868.0	2784.9	2684.0	2570.2	2459.1
25°	2940.3	2937.5	2943.9	2962.4	2950.3	2937.5	2901.2	2839.3	2745.3	2624.9	2505.4
27.5°	2620.8	2640.4	2676.6	2722.2	2766.1	2799.5	2809.0	2796.2	2738.0	2639.1	2513.7
30°	2390.8	2414.9	2442.0	2487.5	2575.9	2626.4	2681.9	2723.9	2700.5	2621.5	2504.6
32.5°	2137.9	2143.9	2184.0	2235.8	2316.7	2414.0	2502.0	2587.2	2615.6	2574.1	2476.7
35°	1738.6	1748.6	1792.0	1843.3	1942.2	2061.1	2193.5	2311.7	2409.2	2448.4	2398.5
37.5°	1418.8	1447.4	1478.0	1533.1	1620.2	1727.3	1864.9	2017.9	2163.2	2260.6	2277.1
40°	1267.3	1285.0	1307.2	1349.2	1423.2	1528.6	1646.7	1821.9	1976.4	2115.9	2161.5
42.5°	1147.6	1158.1	1171.6	1209.6	1266.0	1370.8	1478.7	1632.8	1787.9	1954.7	2031.0
45°	975.4	986.1	1008.8	1030.9	1073.6	1146.2	1246.6	1373.3	1529.3	1690.1	1831.1
47.5°	851.0	857.7	871.3	894.9	931.2	979.1	1060.8	1166.6	1311.2	1467.3	1617.6
50°	780.3	786.0	796.7	818.1	845.8	888.5	955.5	1054.4	1167.6	1324.9	1472.3
52.5°	724.5	726.7	734.6	749.1	771.2	807.1	862.0	943.9	1049.1	1189.4	1336.2
55°	637.9	640.8	647.9	658.5	677.8	700.5	742.5	803.8	895.6	1017.4	1144.8
57.5°	566.7	568.7	574.7	578.8	594.6	613.1	645.4	689.2	758.8	862.0	975.8
60°	521.1	519.7	526.8	530.4	541.1	556.8	581.7	623.7	684.2	767.5	872.2
62.5°	476.7	474.7	480.7	485.4	491.5	504.9	525.3	558.2	607.3	682.6	773.0
65°	410.1	407.2	410.8	416.5	422.2	429.3	444.3	473.4	512.6	566.7	635.8
67.5°	343.1	346.2	346.7	349.6	352.8	362.6	372.7	393.4	421.1	464.3	522.9
70°	303.3	304.0	306.8	306.8	309.0	317.5	326.1	338.1	365.2	405.1	452.8
72.5°	263.4	266.4	265.3	267.5	269.1	274.8	281.1	292.6	315.7	345.3	385.6
75°	205.0	207.1	207.1	207.9	210.0	212.1	217.1	225.7	242.1	264.1	291.9
77.5°	149.5	149.8	150.8	153.4	153.4	156.8	160.5	167.3	175.4	190.6	207.5
80°	115.3	116.7	116.0	117.4	117.4	120.3	121.7	130.3	133.8	143.8	157.3
82.5°	84.6	86.0	85.9	87.8	89.0	89.5	91.6	95.0	98.5	107.4	112.9
85°	42.7	44.1	42.7	44.1	46.3	47.0	49.1	49.8	52.7	54.8	59.8
87.5°	16.2	18.0	18.2	18.5	19.5	20.1	20.5	19.7	21.8	22.6	24.5
90°	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1	15.2	16.1	14.3
92.5°	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9	235.2	282.4	247.1
95°	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6	746.0	725.5	547.5
97.5°	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6	937.2	764.1	512.4
100°	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6	943.6	715.7	464.7
102.5°	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6	890.2	655.2	432.7
105°	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0	793.2	584.0	405.0
107.5°	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4	714.8	544.1	400.0
110°	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1	675.6	530.6	401.4



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3	653.6	524.1	405.7
115°	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2	632.9	520.8	413.9
117.5°	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1	623.7	519.9	422.7
120°	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1	618.7	519.9	429.1
122.5°	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6	613.0	519.2	435.5
125°	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0	603.6	518.1	445.1
127.5°	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2	590.9	516.1	452.7
130°	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0	583.1	515.4	458.4
132.5°	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0	576.0	514.7	463.4
135°	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3	565.3	513.6	470.9
137.5°	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7	556.0	513.4	475.4
140°	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0	551.1	512.7	478.9
142.5°	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0	546.8	512.7	481.8
145°	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9	539.5	511.0	483.4
147.5°	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3	532.9	507.7	484.3
150°	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3	527.9	505.6	484.3
152.5°	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4	522.2	502.0	482.9
155°	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7	513.6	496.8	480.7
157.5°	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0	504.9	491.2	478.4
160°	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2	498.6	487.0	476.3
162.5°	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3	492.8	482.7	474.1
165°	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5	483.4	476.3	470.0
167.5°	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0	474.8	469.8	465.7
170°	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6	469.1	465.6	462.9
172.5°	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9	464.1	461.3	460.0
175°	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2	458.4	456.6	456.6
177.5°	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2	454.5	453.8	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1773.9	1765.9	1760.2	1755.7	1743.1	1735.7	1730.0	1722.1	1713.0	1703.3	1691.3
5°	1874.6	1850.4	1832.6	1805.5	1779.9	1758.5	1736.4	1716.5	1692.3	1666.0	1646.7
7.5°	1980.4	1944.4	1898.2	1858.2	1813.2	1774.1	1739.0	1703.2	1665.8	1629.7	1596.5
10°	2047.5	2001.3	1950.0	1889.5	1832.6	1782.0	1735.0	1689.4	1645.3	1601.2	1563.4
12.5°	2120.0	2062.3	1986.5	1915.8	1851.9	1784.3	1727.6	1671.8	1618.5	1572.2	1528.1
15°	2217.1	2133.7	2046.1	1951.4	1867.4	1788.4	1710.8	1640.3	1580.6	1519.3	1476.6
17.5°	2276.7	2173.6	2073.5	1974.5	1872.9	1773.2	1689.4	1608.2	1533.3	1472.5	1418.6
20°	2316.0	2213.5	2088.8	1989.9	1868.8	1766.4	1669.6	1579.1	1500.8	1436.0	1380.5
22.5°	2350.2	2231.7	2107.1	1976.8	1856.4	1747.6	1641.6	1550.6	1470.6	1402.4	1349.2
25°	2368.7	2232.7	2097.4	1967.8	1831.1	1702.3	1606.1	1499.4	1413.9	1342.0	1285.0
27.5°	2370.7	2225.3	2072.2	1928.2	1787.2	1667.1	1545.8	1450.4	1361.6	1285.7	1231.0
30°	2364.4	2212.8	2048.3	1892.4	1750.7	1620.4	1515.0	1411.1	1320.7	1245.2	1188.2
32.5°	2344.5	2186.6	2017.5	1852.5	1705.7	1578.2	1469.5	1370.6	1282.5	1208.2	1148.3
35°	2286.8	2130.8	1950.7	1779.1	1629.0	1500.1	1401.9	1301.5	1213.2	1142.7	1085.0
37.5°	2196.6	2055.7	1872.6	1695.1	1547.5	1418.1	1320.7	1229.9	1150.4	1078.8	1019.7
40°	2118.1	1994.2	1810.5	1637.4	1478.0	1354.9	1263.7	1180.4	1101.4	1033.8	977.5
42.5°	2027.5	1919.6	1750.2	1566.8	1413.1	1289.3	1200.5	1125.7	1051.2	988.7	932.6
45°	1866.0	1794.8	1635.4	1465.9	1305.7	1188.9	1104.2	1038.8	976.1	914.9	867.9
47.5°	1680.3	1645.0	1510.7	1349.9	1197.7	1082.7	1009.2	948.8	893.8	842.0	800.5
50°	1555.6	1538.6	1422.5	1267.3	1122.0	1013.8	939.8	887.8	840.8	795.2	756.1
52.5°	1432.6	1432.0	1327.4	1185.3	1050.9	946.6	873.2	824.6	783.9	746.8	711.7
55°	1244.5	1264.4	1182.6	1055.8	935.5	841.5	775.3	731.9	703.4	672.8	646.5
57.5°	1071.7	1104.8	1037.3	925.7	825.3	738.7	681.1	648.5	618.1	599.6	580.4
60°	959.0	990.3	937.6	843.6	748.9	674.9	620.1	590.9	564.5	551.8	538.2
62.5°	858.7	886.6	847.7	760.5	678.3	607.2	560.9	532.8	515.1	501.1	492.1
65°	715.5	739.0	705.5	642.2	571.7	514.8	477.0	455.0	437.8	432.1	422.2
67.5°	578.4	599.8	581.7	527.8	471.3	428.2	398.7	377.5	367.4	362.4	355.3
70°	497.0	518.3	499.1	452.1	408.7	372.4	344.6	332.5	321.8	319.7	309.7
72.5°	428.0	442.6	423.3	386.6	349.5	318.8	297.3	284.6	279.1	275.3	269.8
75°	321.1	333.9	321.1	292.6	266.3	245.0	226.4	221.4	215.0	212.9	209.3
77.5°	227.3	238.4	228.5	210.7	191.1	174.6	164.6	158.2	156.8	153.1	154.8
80°	173.7	180.8	171.6	159.4	143.8	132.4	125.3	121.7	117.4	116.0	118.9
82.5°	124.8	127.9	123.1	115.0	103.3	95.9	91.1	87.0	86.1	86.4	86.4
85°	64.8	64.1	63.4	56.3	52.7	47.7	44.9	44.1	43.4	44.9	46.3
87.5°	24.2	24.7	23.1	20.8	18.9	17.0	15.9	15.0	15.9	17.0	17.7
90°	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9	2.7	5.4	6.2
92.5°	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2	14.8	23.2	34.0
95°	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3	32.0	40.9	52.5
97.5°	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7	52.7	60.4	71.1
100°	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7	67.7	73.9	84.5
102.5°	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9	83.3	88.8	98.8
105°	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2	106.8	111.3	122.0
107.5°	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8	130.5	134.9	146.3
110°	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1	146.9	151.3	162.0



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8	162.6	167.7	177.7
115°	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4	186.0	192.3	201.2
117.5°	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9	209.4	214.9	224.7
120°	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6	224.4	230.6	240.3
122.5°	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8	238.5	244.8	253.9
125°	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5	259.0	264.4	274.2
127.5°	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1	274.9	281.3	292.5
130°	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3	284.9	291.9	305.3
132.5°	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5	293.4	302.6	315.3
135°	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5	307.1	316.0	331.2
137.5°	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6	319.9	329.8	344.1
140°	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8	328.5	338.3	353.4
142.5°	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8	338.5	347.5	361.9
145°	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8	352.5	361.4	373.9
147.5°	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7	366.6	374.4	387.3
150°	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7	376.6	383.7	394.4
152.5°	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0	385.1	392.3	402.2
155°	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9	398.8	404.1	413.0
157.5°	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5	410.5	415.5	422.5
160°	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4	418.4	422.0	428.2
162.5°	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5	424.8	427.7	433.2
165°	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5	433.5	435.3	439.8
167.5°	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6	440.7	441.6	445.0
170°	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1	444.3	445.1	447.8
172.5°	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6	447.8	447.9	449.9
175°	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2	451.3	451.3	452.2
177.5°	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8	453.1	452.4	453.1
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1685.6	1680.5	1673.1	1662.9	1654.3	1645.2	1642.9	1639.5	1646.3	1640.7	1638.9
5°	1630.4	1615.4	1596.2	1574.1	1561.3	1542.8	1539.3	1532.1	1525.0	1524.3	1517.2
7.5°	1571.8	1549.9	1524.7	1502.2	1481.4	1461.2	1448.0	1445.1	1434.6	1428.4	1421.3
10°	1534.3	1507.2	1478.0	1456.7	1432.4	1411.1	1396.2	1387.6	1380.5	1372.6	1365.6
12.5°	1489.9	1461.1	1437.0	1413.9	1385.2	1369.0	1344.3	1329.5	1328.1	1328.2	1309.7
15°	1438.2	1409.7	1372.6	1339.9	1324.2	1292.9	1279.3	1262.3	1251.6	1240.9	1232.4
17.5°	1379.0	1343.6	1314.6	1277.1	1247.2	1222.3	1204.5	1194.3	1178.1	1163.1	1152.1
20°	1342.0	1304.3	1273.7	1233.8	1201.0	1170.5	1155.5	1141.3	1129.2	1116.3	1104.2
22.5°	1304.4	1265.0	1227.5	1188.8	1158.3	1126.1	1111.6	1092.3	1080.8	1073.6	1061.5
25°	1245.2	1202.5	1159.8	1122.8	1091.5	1062.9	1043.7	1028.8	1015.9	1010.2	1002.5
27.5°	1180.8	1138.4	1097.2	1055.1	1019.5	998.9	983.5	972.2	964.8	957.3	953.8
30°	1139.9	1095.7	1051.6	1012.4	979.6	959.0	944.8	936.9	931.2	927.6	924.1
32.5°	1098.2	1054.7	1008.3	972.5	943.2	924.8	914.0	906.2	903.3	902.1	900.8
35°	1031.6	987.5	944.8	912.8	884.9	877.8	868.6	864.3	862.9	867.9	870.0
37.5°	967.1	926.1	886.8	855.8	837.6	827.2	824.0	824.1	829.3	833.7	838.8
40°	925.5	885.6	848.6	821.6	804.5	798.1	796.7	800.2	805.9	810.9	816.6
42.5°	885.1	845.8	812.2	786.8	774.9	769.0	769.9	773.5	781.4	787.6	796.1
45°	822.3	789.5	756.8	736.2	726.2	727.6	727.6	734.1	741.8	751.1	760.4
47.5°	763.2	730.2	703.3	685.9	680.7	679.5	683.5	691.9	703.1	714.5	727.5
50°	723.4	692.1	668.5	652.8	647.2	649.3	655.0	662.8	676.4	690.6	704.1
52.5°	682.9	654.4	632.7	618.1	614.1	618.0	623.7	636.1	647.9	663.3	679.7
55°	620.1	595.9	578.8	568.1	566.7	568.8	575.2	588.8	605.8	625.1	640.8
57.5°	557.6	537.3	521.7	514.3	515.1	517.0	527.5	543.7	561.9	582.4	602.6
60°	515.4	497.0	484.1	478.4	479.1	483.4	496.2	511.2	534.0	553.9	575.2
62.5°	475.5	459.3	447.1	442.0	441.0	450.4	462.6	478.1	501.0	523.2	546.2
65°	411.5	398.7	388.7	385.8	388.0	395.1	410.8	431.4	450.7	474.1	498.4
67.5°	348.8	338.3	331.4	332.8	335.4	345.9	359.0	376.7	398.6	422.9	446.8
70°	309.0	299.0	293.3	294.0	298.3	311.1	322.5	340.3	363.8	388.7	408.7
72.5°	268.0	261.4	256.3	259.3	263.6	272.4	286.6	304.4	325.1	348.3	369.3
75°	205.7	205.7	202.9	205.0	211.4	220.0	230.7	249.1	269.8	288.4	305.4
77.5°	152.7	151.1	152.9	155.5	159.2	169.3	181.6	194.7	210.4	228.8	242.9
80°	116.7	117.4	121.0	125.3	126.7	134.6	147.4	159.4	171.6	187.3	200.8
82.5°	87.7	88.5	90.2	95.7	97.1	105.5	113.8	125.9	136.9	147.4	158.6
85°	47.7	47.7	51.3	53.4	57.0	62.7	67.6	74.7	84.7	91.8	102.5
87.5°	19.6	19.6	23.0	24.2	26.2	29.4	30.4	36.8	39.2	42.3	47.4
90°	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1	16.9	17.8	17.8
92.5°	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9	131.6	104.7	86.9
95°	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6	521.7	402.3	316.0
97.5°	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6	923.3	836.2	743.3
100°	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6	1091.4	1047.8	981.9
102.5°	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6	1156.9	1169.6	1142.1
105°	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0	1151.0	1239.1	1275.7
107.5°	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4	1059.4	1183.5	1262.8
110°	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1	988.1	1117.2	1215.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3	925.4	1047.4	1145.3
115°	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2	853.7	957.9	1043.3
117.5°	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1	812.8	894.7	967.1
120°	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1	795.0	866.2	929.3
122.5°	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6	783.5	848.4	903.7
125°	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0	765.5	827.0	875.9
127.5°	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2	744.4	805.7	852.1
130°	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0	727.3	787.8	835.0
132.5°	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0	708.1	767.1	814.4
135°	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3	679.2	733.5	778.0
137.5°	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7	651.7	697.4	737.6
140°	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0	633.8	673.9	711.2
142.5°	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0	618.8	653.3	685.6
145°	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9	598.2	624.9	649.9
147.5°	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3	580.4	601.8	621.3
150°	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3	569.7	587.5	603.6
152.5°	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4	559.0	575.4	588.6
155°	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7	543.9	557.2	567.9
157.5°	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0	529.0	540.2	548.8
160°	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2	519.0	528.8	535.9
162.5°	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3	509.7	517.4	523.8
165°	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5	495.9	502.0	506.5
167.5°	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0	484.1	489.1	491.8
170°	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6	476.3	479.8	482.5
172.5°	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9	469.8	472.0	473.9
175°	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2	461.1	462.9	462.9
177.5°	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2	455.9	455.9	456.6
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1637.8	1636.6	1632.6	1632.1	1632.6	1636.6	1637.8	1638.9	1640.7	1646.3	1639.5
5°	1512.9	1509.3	1507.2	1515.0	1507.2	1509.3	1512.9	1517.2	1524.3	1525.0	1532.1
7.5°	1418.8	1415.9	1409.7	1407.7	1409.7	1415.9	1418.8	1421.3	1428.4	1434.6	1445.1
10°	1358.4	1355.6	1349.9	1348.4	1349.9	1355.6	1358.4	1365.6	1372.6	1380.5	1387.6
12.5°	1300.3	1294.6	1293.5	1294.9	1293.5	1294.6	1300.3	1309.7	1328.2	1328.1	1329.5
15°	1223.2	1220.3	1212.5	1214.6	1212.5	1220.3	1223.2	1232.4	1240.9	1251.6	1262.3
17.5°	1147.1	1143.7	1134.2	1142.5	1134.2	1143.7	1147.1	1152.1	1163.1	1178.1	1194.3
20°	1099.2	1093.6	1088.6	1087.9	1088.6	1093.6	1099.2	1104.2	1116.3	1129.2	1141.3
22.5°	1053.6	1048.6	1048.1	1043.5	1048.1	1048.6	1053.6	1061.5	1073.6	1080.8	1092.3
25°	996.8	991.8	990.3	986.8	990.3	991.8	996.8	1002.5	1010.2	1015.9	1028.8
27.5°	953.1	950.6	948.1	949.1	948.1	950.6	953.1	953.8	957.3	964.8	972.2
30°	926.2	925.5	924.1	924.1	924.1	925.5	926.2	924.1	927.6	931.2	936.9
32.5°	904.0	903.9	904.7	904.7	904.7	903.9	904.0	900.8	902.1	903.3	906.2
35°	872.9	874.9	876.4	874.2	876.4	874.9	872.9	870.0	867.9	862.9	864.3
37.5°	844.6	846.8	848.8	851.2	848.8	846.8	844.6	838.8	833.7	829.3	824.1
40°	823.0	828.0	829.4	832.9	829.4	828.0	823.0	816.6	810.9	805.9	800.2
42.5°	802.5	808.1	811.7	812.4	811.7	808.1	802.5	796.1	787.6	781.4	773.5
45°	771.1	776.8	781.8	781.8	781.8	776.8	771.1	760.4	751.1	741.8	734.1
47.5°	738.4	746.7	751.7	753.0	751.7	746.7	738.4	727.5	714.5	703.1	691.9
50°	716.2	726.2	731.2	734.8	731.2	726.2	716.2	704.1	690.6	676.4	662.8
52.5°	694.6	704.5	711.2	713.1	711.2	704.5	694.6	679.7	663.3	647.9	636.1
55°	657.1	671.4	679.2	682.1	679.2	671.4	657.1	640.8	625.1	605.8	588.8
57.5°	621.8	634.9	644.0	646.1	644.0	634.9	621.8	602.6	582.4	561.9	543.7
60°	594.5	608.7	620.1	622.2	620.1	608.7	594.5	575.2	553.9	534.0	511.2
62.5°	566.6	581.4	591.7	597.2	591.7	581.4	566.6	546.2	523.2	501.0	478.1
65°	518.3	533.2	543.2	545.4	543.2	533.2	518.3	498.4	474.1	450.7	431.4
67.5°	465.7	480.5	487.1	491.2	487.1	480.5	465.7	446.8	422.9	398.6	376.7
70°	428.6	440.7	447.8	451.4	447.8	440.7	428.6	408.7	388.7	363.8	340.3
72.5°	386.5	399.1	407.4	408.0	407.4	399.1	386.5	369.3	348.3	325.1	304.4
75°	321.8	333.2	337.4	337.4	337.4	333.2	321.8	305.4	288.4	269.8	249.1
77.5°	254.8	260.6	266.0	267.2	266.0	260.6	254.8	242.9	228.8	210.4	194.7
80°	211.4	215.0	219.3	219.3	219.3	215.0	211.4	200.8	187.3	171.6	159.4
82.5°	167.0	170.0	174.3	173.7	174.3	170.0	167.0	158.6	147.4	136.9	125.9
85°	101.1	107.5	106.8	105.4	106.8	107.5	101.1	102.5	91.8	84.7	74.7
87.5°	49.3	50.0	51.5	52.7	51.5	50.0	49.3	47.4	42.3	39.2	36.8
90°	18.7	19.6	18.7	18.7	18.7	19.6	18.7	17.8	17.8	16.9	16.1
92.5°	76.4	71.6	68.6	68.6	68.6	71.6	76.4	86.9	104.7	131.6	174.9
95°	272.4	244.8	228.8	217.2	228.8	244.8	272.4	316.0	402.3	521.7	659.6
97.5°	679.4	625.8	599.1	580.6	599.1	625.8	679.4	743.3	836.2	923.3	974.6
100°	904.5	850.2	823.4	816.4	823.4	850.2	904.5	981.9	1047.8	1091.4	1073.6
102.5°	1094.6	1055.3	1027.2	1021.5	1027.2	1055.3	1094.6	1142.1	1169.6	1156.9	1068.6
105°	1277.5	1270.3	1257.8	1252.5	1257.8	1270.3	1277.5	1275.7	1239.1	1151.0	997.0
107.5°	1306.8	1327.1	1336.1	1338.4	1336.1	1327.1	1306.8	1262.8	1183.5	1059.4	895.4
110°	1278.4	1315.7	1331.8	1339.8	1331.8	1315.7	1278.4	1215.1	1117.2	988.1	834.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1217.1	1262.3	1284.8	1297.7	1284.8	1262.3	1217.1	1145.3	1047.4	925.4	789.3
115°	1113.7	1167.1	1195.5	1202.7	1195.5	1167.1	1113.7	1043.3	957.9	853.7	744.2
117.5°	1027.2	1072.0	1100.8	1106.3	1100.8	1072.0	1027.2	967.1	894.7	812.8	722.1
120°	980.1	1019.3	1042.4	1052.2	1042.4	1019.3	980.1	929.3	866.2	795.0	712.1
122.5°	946.6	980.1	999.7	1009.5	999.7	980.1	946.6	903.7	848.4	783.5	703.6
125°	911.6	937.4	954.3	959.7	954.3	937.4	911.6	875.9	827.0	765.5	689.0
127.5°	887.9	910.9	925.1	930.4	925.1	910.9	887.9	852.1	805.7	744.4	671.2
130°	871.5	893.8	908.0	913.4	908.0	893.8	871.5	835.0	787.8	727.3	657.0
132.5°	850.2	875.2	888.8	894.1	888.8	875.2	850.2	814.4	767.1	708.1	642.0
135°	813.7	838.6	852.8	858.2	852.8	838.6	813.7	778.0	733.5	679.2	621.3
137.5°	770.9	795.5	807.3	813.7	807.3	795.5	770.9	737.6	697.4	651.7	602.7
140°	742.4	762.1	774.5	781.6	774.5	762.1	742.4	711.2	673.9	633.8	592.0
142.5°	713.2	731.4	742.4	747.4	742.4	731.4	713.2	685.6	653.3	618.8	582.0
145°	672.1	687.2	696.2	700.6	696.2	687.2	672.1	649.9	624.9	598.2	567.9
147.5°	637.8	650.8	657.5	659.1	657.5	650.8	637.8	621.3	601.8	580.4	556.3
150°	617.8	629.4	634.7	635.6	634.7	629.4	617.8	603.6	587.5	569.7	549.3
152.5°	600.7	610.1	613.3	614.2	613.3	610.1	600.7	588.6	575.4	559.0	541.4
155°	576.8	584.0	586.7	586.7	586.7	584.0	576.8	567.9	557.2	543.9	529.7
157.5°	555.4	560.8	562.4	562.4	562.4	560.8	555.4	548.8	540.2	529.0	517.0
160°	541.3	546.6	547.5	547.5	547.5	546.6	541.3	535.9	528.8	519.0	509.2
162.5°	527.7	533.1	534.0	533.2	534.0	533.1	527.7	523.8	517.4	509.7	501.3
165°	510.1	513.6	512.7	511.8	512.7	513.6	510.1	506.5	502.0	495.9	490.5
167.5°	493.6	495.9	495.7	495.0	495.7	495.9	493.6	491.8	489.1	484.1	480.0
170°	484.3	485.2	484.3	484.3	484.3	485.2	484.3	482.5	479.8	476.3	473.6
172.5°	475.0	475.9	475.0	473.6	475.0	475.9	475.0	473.9	472.0	469.8	467.9
175°	462.9	464.7	462.9	461.1	462.9	464.7	462.9	462.9	462.9	461.1	460.2
177.5°	455.9	456.6	455.2	453.8	455.2	456.6	455.9	456.6	455.9	455.9	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1642.9	1645.2	1654.3	1662.9	1673.1	1680.5	1685.6	1691.3	1703.3	1713.0	1722.1
5°	1539.3	1542.8	1561.3	1574.1	1596.2	1615.4	1630.4	1646.7	1666.0	1692.3	1716.5
7.5°	1448.0	1461.2	1481.4	1502.2	1524.7	1549.9	1571.8	1596.5	1629.7	1665.8	1703.2
10°	1396.2	1411.1	1432.4	1456.7	1478.0	1507.2	1534.3	1563.4	1601.2	1645.3	1689.4
12.5°	1344.3	1369.0	1385.2	1413.9	1437.0	1461.1	1489.9	1528.1	1572.2	1618.5	1671.8
15°	1279.3	1292.9	1324.2	1339.9	1372.6	1409.7	1438.2	1476.6	1519.3	1580.6	1640.3
17.5°	1204.5	1222.3	1247.2	1277.1	1314.6	1343.6	1379.0	1418.6	1472.5	1533.3	1608.2
20°	1155.5	1170.5	1201.0	1233.8	1273.7	1304.3	1342.0	1380.5	1436.0	1500.8	1579.1
22.5°	1111.6	1126.1	1158.3	1188.8	1227.5	1265.0	1304.4	1349.2	1402.4	1470.6	1550.6
25°	1043.7	1062.9	1091.5	1122.8	1159.8	1202.5	1245.2	1285.0	1342.0	1413.9	1499.4
27.5°	983.5	998.9	1019.5	1055.1	1097.2	1138.4	1180.8	1231.0	1285.7	1361.6	1450.4
30°	944.8	959.0	979.6	1012.4	1051.6	1095.7	1139.9	1188.2	1245.2	1320.7	1411.1
32.5°	914.0	924.8	943.2	972.5	1008.3	1054.7	1098.2	1148.3	1208.2	1282.5	1370.6
35°	868.6	877.8	884.9	912.8	944.8	987.5	1031.6	1085.0	1142.7	1213.2	1301.5
37.5°	824.0	827.2	837.6	855.8	886.8	926.1	967.1	1019.7	1078.8	1150.4	1229.9
40°	796.7	798.1	804.5	821.6	848.6	885.6	925.5	977.5	1033.8	1101.4	1180.4
42.5°	769.9	769.0	774.9	786.8	812.2	845.8	885.1	932.6	988.7	1051.2	1125.7
45°	727.6	727.6	726.2	736.2	756.8	789.5	822.3	867.9	914.9	976.1	1038.8
47.5°	683.5	679.5	680.7	685.9	703.3	730.2	763.2	800.5	842.0	893.8	948.8
50°	655.0	649.3	647.2	652.8	668.5	692.1	723.4	756.1	795.2	840.8	887.8
52.5°	623.7	618.0	614.1	618.1	632.7	654.4	682.9	711.7	746.8	783.9	824.6
55°	575.2	568.8	566.7	568.1	578.8	595.9	620.1	646.5	672.8	703.4	731.9
57.5°	527.5	517.0	515.1	514.3	521.7	537.3	557.6	580.4	599.6	618.1	648.5
60°	496.2	483.4	479.1	478.4	484.1	497.0	515.4	538.2	551.8	564.5	590.9
62.5°	462.6	450.4	441.0	442.0	447.1	459.3	475.5	492.1	501.1	515.1	532.8
65°	410.8	395.1	388.0	385.8	388.7	398.7	411.5	422.2	432.1	437.8	455.0
67.5°	359.0	345.9	335.4	332.8	331.4	338.3	348.8	355.3	362.4	367.4	377.5
70°	322.5	311.1	298.3	294.0	293.3	299.0	309.0	309.7	319.7	321.8	332.5
72.5°	286.6	272.4	263.6	259.3	256.3	261.4	268.0	269.8	275.3	279.1	284.6
75°	230.7	220.0	211.4	205.0	202.9	205.7	205.7	209.3	212.9	215.0	221.4
77.5°	181.6	169.3	159.2	155.5	152.9	151.1	152.7	154.8	153.1	156.8	158.2
80°	147.4	134.6	126.7	125.3	121.0	117.4	116.7	118.9	116.0	117.4	121.7
82.5°	113.8	105.5	97.1	95.7	90.2	88.5	87.7	86.4	86.4	86.1	87.0
85°	67.6	62.7	57.0	53.4	51.3	47.7	47.7	46.3	44.9	43.4	44.1
87.5°	30.4	29.4	26.2	24.2	23.0	19.6	19.6	17.7	17.0	15.9	15.0
90°	15.2	16.1	14.3	12.5	12.5	7.1	7.1	6.2	5.4	2.7	0.9
92.5°	235.2	282.4	247.1	179.9	110.8	65.5	47.0	34.0	23.2	14.8	10.2
95°	746.0	725.5	547.5	334.7	188.7	111.3	73.9	52.5	40.9	32.0	29.3
97.5°	937.2	764.1	512.4	300.9	180.4	120.7	89.3	71.1	60.4	52.7	52.7
100°	943.6	715.7	464.7	283.1	182.5	130.0	101.5	84.5	73.9	67.7	67.7
102.5°	890.2	655.2	432.7	278.1	189.6	142.0	115.0	98.8	88.8	83.3	81.9
105°	793.2	584.0	405.0	280.4	206.5	163.8	137.9	122.0	111.3	106.8	104.2
107.5°	714.8	544.1	400.0	293.6	226.3	187.1	161.7	146.3	134.9	130.5	128.8
110°	675.6	530.6	401.4	303.5	241.2	202.1	178.1	162.0	151.3	146.9	145.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	653.6	524.1	405.7	314.2	255.5	217.8	193.7	177.7	167.7	162.6	160.8
115°	632.9	520.8	413.9	331.2	277.8	242.1	218.1	201.2	192.3	186.0	183.4
117.5°	623.7	519.9	422.7	348.4	299.3	265.5	240.5	224.7	214.9	209.4	206.9
120°	618.7	519.9	429.1	360.5	314.2	280.4	255.5	240.3	230.6	224.4	222.6
122.5°	613.0	519.2	435.5	371.9	328.5	294.6	270.5	253.9	244.8	238.5	236.8
125°	603.6	518.1	445.1	389.1	348.0	316.0	291.1	274.2	264.4	259.0	255.5
127.5°	590.9	516.1	452.7	403.8	366.2	335.3	310.1	292.5	281.3	274.9	272.1
130°	583.1	515.4	458.4	413.0	378.4	348.0	322.3	305.3	291.9	284.9	281.3
132.5°	576.0	514.7	463.4	422.3	388.3	358.0	333.7	315.3	302.6	293.4	290.5
135°	565.3	513.6	470.9	434.4	402.3	373.0	349.8	331.2	316.0	307.1	303.5
137.5°	556.0	513.4	475.4	443.0	413.0	385.7	363.6	344.1	329.8	319.9	316.6
140°	551.1	512.7	478.9	448.6	420.2	393.5	372.1	353.4	338.3	328.5	325.8
142.5°	546.8	512.7	481.8	452.9	426.6	400.6	380.0	361.9	347.5	338.5	335.8
145°	539.5	511.0	483.4	457.5	433.5	410.4	390.8	373.9	361.4	352.5	349.8
147.5°	532.9	507.7	484.3	461.6	440.7	418.9	401.3	387.3	374.4	366.6	365.7
150°	527.9	505.6	484.3	463.8	444.3	424.6	407.7	394.4	383.7	376.6	375.7
152.5°	522.2	502.0	482.9	465.2	447.1	429.6	414.1	402.2	392.3	385.1	385.0
155°	513.6	496.8	480.7	466.5	451.3	436.2	422.8	413.0	404.1	398.8	397.9
157.5°	504.9	491.2	478.4	466.5	454.3	441.6	431.1	422.5	415.5	410.5	410.5
160°	498.6	487.0	476.3	466.5	455.8	445.1	435.3	428.2	422.0	418.4	418.4
162.5°	492.8	482.7	474.1	466.5	457.2	447.3	439.6	433.2	427.7	424.8	425.5
165°	483.4	476.3	470.0	464.7	457.5	449.5	444.3	439.8	435.3	433.5	433.5
167.5°	474.8	469.8	465.7	462.5	457.4	451.5	447.5	445.0	441.6	440.7	441.6
170°	469.1	465.6	462.9	461.1	456.6	452.2	449.5	447.8	445.1	444.3	445.1
172.5°	464.1	461.3	460.0	459.7	455.9	452.9	450.9	449.9	447.9	447.8	448.6
175°	458.4	456.6	456.6	457.5	454.9	453.1	453.1	452.2	451.3	451.3	452.2
177.5°	454.5	453.8	453.8	455.2	453.8	453.1	453.1	453.1	452.4	453.1	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1730.0	1735.7	1743.1	1755.7	1760.2	1765.9	1773.9	1773.3	1775.6	1784.1	1802.4
5°	1736.4	1758.5	1779.9	1805.5	1832.6	1850.4	1874.6	1889.5	1904.5	1923.7	1956.4
7.5°	1739.0	1774.1	1813.2	1858.2	1898.2	1944.4	1980.4	2014.3	2044.9	2085.4	2124.5
10°	1735.0	1782.0	1832.6	1889.5	1950.0	2001.3	2047.5	2100.2	2145.1	2194.2	2238.4
12.5°	1727.6	1784.3	1851.9	1915.8	1986.5	2062.3	2120.0	2173.2	2232.8	2289.4	2357.4
15°	1710.8	1788.4	1867.4	1951.4	2046.1	2133.7	2217.1	2286.1	2350.2	2434.9	2523.9
17.5°	1689.4	1773.2	1872.9	1974.5	2073.5	2173.6	2276.7	2380.5	2461.4	2566.6	2636.3
20°	1669.6	1766.4	1868.8	1989.9	2088.8	2213.5	2316.0	2416.4	2527.5	2632.1	2715.3
22.5°	1641.6	1747.6	1856.4	1976.8	2107.1	2231.7	2350.2	2459.1	2570.2	2684.0	2784.9
25°	1606.1	1702.3	1831.1	1967.8	2097.4	2232.7	2368.7	2505.4	2624.9	2745.3	2839.3
27.5°	1545.8	1667.1	1787.2	1928.2	2072.2	2225.3	2370.7	2513.7	2639.1	2738.0	2796.2
30°	1515.0	1620.4	1750.7	1892.4	2048.3	2212.8	2364.4	2504.6	2621.5	2700.5	2723.9
32.5°	1469.5	1578.2	1705.7	1852.5	2017.5	2186.6	2344.5	2476.7	2574.1	2615.6	2587.2
35°	1401.9	1500.1	1629.0	1779.1	1950.7	2130.8	2286.8	2398.5	2448.4	2409.2	2311.7
37.5°	1320.7	1418.1	1547.5	1695.1	1872.6	2055.7	2196.6	2277.1	2260.6	2163.2	2017.9
40°	1263.7	1354.9	1478.0	1637.4	1810.5	1994.2	2118.1	2161.5	2115.9	1976.4	1821.9
42.5°	1200.5	1289.3	1413.1	1566.8	1750.2	1919.6	2027.5	2031.0	1954.7	1787.9	1632.8
45°	1104.2	1188.9	1305.7	1465.9	1635.4	1794.8	1866.0	1831.1	1690.1	1529.3	1373.3
47.5°	1009.2	1082.7	1197.7	1349.9	1510.7	1645.0	1680.3	1617.6	1467.3	1311.2	1166.6
50°	939.8	1013.8	1122.0	1267.3	1422.5	1538.6	1555.6	1472.3	1324.9	1167.6	1054.4
52.5°	873.2	946.6	1050.9	1185.3	1327.4	1432.0	1432.6	1336.2	1189.4	1049.1	943.9
55°	775.3	841.5	935.5	1055.8	1182.6	1264.4	1244.5	1144.8	1017.4	895.6	803.8
57.5°	681.1	738.7	825.3	925.7	1037.3	1104.8	1071.7	975.8	862.0	758.8	689.2
60°	620.1	674.9	748.9	843.6	937.6	990.3	959.0	872.2	767.5	684.2	623.7
62.5°	560.9	607.2	678.3	760.5	847.7	886.6	858.7	773.0	682.6	607.3	558.2
65°	477.0	514.8	571.7	642.2	705.5	739.0	715.5	635.8	566.7	512.6	473.4
67.5°	398.7	428.2	471.3	527.8	581.7	599.8	578.4	522.9	464.3	421.1	393.4
70°	344.6	372.4	408.7	452.1	499.1	518.3	497.0	452.8	405.1	365.2	338.1
72.5°	297.3	318.8	349.5	386.6	423.3	442.6	428.0	385.6	345.3	315.7	292.6
75°	226.4	245.0	266.3	292.6	321.1	333.9	321.1	291.9	264.1	242.1	225.7
77.5°	164.6	174.6	191.1	210.7	228.5	238.4	227.3	207.5	190.6	175.4	167.3
80°	125.3	132.4	143.8	159.4	171.6	180.8	173.7	157.3	143.8	133.8	130.3
82.5°	91.1	95.9	103.3	115.0	123.1	127.9	124.8	112.9	107.4	98.5	95.0
85°	44.9	47.7	52.7	56.3	63.4	64.1	64.8	59.8	54.8	52.7	49.8
87.5°	15.9	17.0	18.9	20.8	23.1	24.7	24.2	24.5	22.6	21.8	19.7
90°	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2	16.1
92.5°	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2	174.9
95°	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0	659.6
97.5°	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2	974.6
100°	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6	1073.6
102.5°	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2	1068.6
105°	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2	997.0
107.5°	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8	895.4
110°	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6	834.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6	789.3
115°	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9	744.2
117.5°	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7	722.1
120°	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7	712.1
122.5°	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0	703.6
125°	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6	689.0
127.5°	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9	671.2
130°	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1	657.0
132.5°	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0	642.0
135°	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3	621.3
137.5°	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0	602.7
140°	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1	592.0
142.5°	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8	582.0
145°	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5	567.9
147.5°	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9	556.3
150°	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9	549.3
152.5°	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2	541.4
155°	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6	529.7
157.5°	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9	517.0
160°	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6	509.2
162.5°	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8	501.3
165°	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4	490.5
167.5°	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8	480.0
170°	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1	473.6
172.5°	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1	467.9
175°	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4	460.2
177.5°	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5	455.2
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
2.5°	1811.5	1812.7	1817.8	1821.8	1822.9	1828.5	1829.2
5°	1970.7	1982.8	2006.3	2008.4	2012.0	2030.5	2016.2
7.5°	2157.2	2188.0	2208.5	2226.6	2233.1	2241.2	2239.5
10°	2276.8	2322.4	2345.2	2381.5	2382.9	2392.2	2386.5
12.5°	2397.0	2450.0	2491.5	2498.2	2528.7	2533.4	2541.4
15°	2567.3	2623.5	2681.2	2701.9	2743.9	2753.9	2769.5
17.5°	2727.4	2784.9	2825.3	2878.7	2895.9	2919.0	2903.3
20°	2815.0	2877.7	2929.0	2971.0	2988.7	3001.6	3000.2
22.5°	2868.0	2931.2	2972.8	3004.6	3021.2	3026.6	3026.4
25°	2901.2	2937.5	2950.3	2962.4	2943.9	2937.5	2940.3
27.5°	2809.0	2799.5	2766.1	2722.2	2676.6	2640.4	2620.8
30°	2681.9	2626.4	2575.9	2487.5	2442.0	2414.9	2390.8
32.5°	2502.0	2414.0	2316.7	2235.8	2184.0	2143.9	2137.9
35°	2193.5	2061.1	1942.2	1843.3	1792.0	1748.6	1738.6
37.5°	1864.9	1727.3	1620.2	1533.1	1478.0	1447.4	1418.8
40°	1646.7	1528.6	1423.2	1349.2	1307.2	1285.0	1267.3
42.5°	1478.7	1370.8	1266.0	1209.6	1171.6	1158.1	1147.6
45°	1246.6	1146.2	1073.6	1030.9	1008.8	986.1	975.4
47.5°	1060.8	979.1	931.2	894.9	871.3	857.7	851.0
50°	955.5	888.5	845.8	818.1	796.7	786.0	780.3
52.5°	862.0	807.1	771.2	749.1	734.6	726.7	724.5
55°	742.5	700.5	677.8	658.5	647.9	640.8	637.9
57.5°	645.4	613.1	594.6	578.8	574.7	568.7	566.7
60°	581.7	556.8	541.1	530.4	526.8	519.7	521.1
62.5°	525.3	504.9	491.5	485.4	480.7	474.7	476.7
65°	444.3	429.3	422.2	416.5	410.8	407.2	410.1
67.5°	372.7	362.6	352.8	349.6	346.7	346.2	343.1
70°	326.1	317.5	309.0	306.8	306.8	304.0	303.3
72.5°	281.1	274.8	269.1	267.5	265.3	266.4	263.4
75°	217.1	212.1	210.0	207.9	207.1	207.1	205.0
77.5°	160.5	156.8	153.4	153.4	150.8	149.8	149.5
80°	121.7	120.3	117.4	117.4	116.0	116.7	115.3
82.5°	91.6	89.5	89.0	87.8	85.9	86.0	84.6
85°	49.1	47.0	46.3	44.1	42.7	44.1	42.7
87.5°	20.5	20.1	19.5	18.5	18.2	18.0	16.2
90°	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8



TEST NUMBER: P332699-940

CATALOG NUMBER: SA4XXDIP-C1195D1035U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)